

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011815

Luminaire Tested: S123DIP-B560D585UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011815
REPORT IS A COMBINATION OF REPORTS P990106 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4289.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011815

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011815

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	98	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	59	52	47	51	46	41	44	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	24
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1011815

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.9
10°-20°	234.1	5.5
20°-30°	345.8	8.1
30°-40°	403.8	9.4
40°-50°	406.0	9.5
50°-60°	356.6	8.3
60°-70°	265.6	6.2
70°-80°	151.1	3.5
80°-90°	44.5	1.0
90°-100°	46.4	1.1
100°-110°	140.5	3.3
110°-120°	239.2	5.6
120°-130°	314.7	7.3
130°-140°	353.8	8.2
140°-150°	347.8	8.1
150°-160°	292.8	6.8
160°-170°	194.9	4.5
170°-180°	68.3	1.6
0°-30°	662.8	15.5
0°-40°	1066.7	24.9
0°-60°	1829.3	42.7
0°-90°	2290.5	53.4
90°-120°	426.2	9.9
90°-150°	1442.5	33.6
90°-180°	1998.0	46.6
0°-180°	4289.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	1	6	14	16	17	5
95°	33	37	42	44	44	37
105°	128	129	134	134	135	136
115°	241	242	241	242	241	238
125°	352	354	353	351	348	314
135°	457	461	460	458	457	352
145°	555	556	558	557	555	346
155°	635	635	636	638	634	292
165°	692	690	690	694	690	195
175°	720	717	717	721	717	68
180°	721	721	721	721	721	

TEST NUMBER: P1011815

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	0.6	6.2	13.6	15.9	17.0
92.5°	17.0	20.4	23.8	25.5	24.4
95°	33.4	37.4	41.9	44.2	44.2
97.5°	55.0	57.8	61.2	64.0	63.5
100°	77.1	80.5	83.3	85.0	86.1
102.5°	102.6	104.3	108.2	109.9	109.4
105°	127.5	128.6	133.7	133.7	134.8
107.5°	156.9	157.5	159.8	161.5	160.9
110°	184.1	185.3	186.4	188.7	187.5



TEST NUMBER: P1011815

CATALOG NUMBER: S123DIP-B560D585UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	213.0	213.0	215.9	215.9
115°	240.8	242.5	241.4	241.9	241.4
117.5°	269.7	270.3	269.1	269.1	267.4
120°	296.3	299.7	296.9	296.3	295.2
122.5°	324.1	326.4	325.2	323.5	321.8
125°	352.4	354.1	353.0	350.7	348.4
127.5°	378.5	381.9	380.7	377.3	375.1
130°	404.5	409.1	407.4	405.1	401.1
132.5°	430.6	435.1	434.0	431.2	428.3
135°	457.2	460.6	460.1	457.8	456.7
137.5°	481.6	484.4	486.1	483.3	481.6
140°	507.1	509.9	510.5	509.9	506.0
142.5°	530.3	533.2	534.3	533.7	530.9
145°	554.7	555.8	557.5	556.9	554.7
147.5°	575.6	577.9	579.6	579.6	576.2
150°	597.7	598.9	600.0	600.0	596.6
152.5°	615.9	617.6	618.1	619.3	616.4
155°	635.1	635.1	635.7	638.0	634.0
157.5°	651.6	651.0	651.6	653.8	650.4
160°	666.9	665.7	665.7	668.6	666.3
162.5°	680.5	678.8	679.3	682.2	678.2
165°	691.8	690.1	690.1	693.5	689.5
167.5°	701.4	699.2	699.7	703.1	699.7
170°	709.4	707.1	707.1	711.1	707.1
172.5°	715.6	713.3	713.3	716.7	712.8
175°	719.6	717.3	717.3	720.7	716.7
177.5°	721.8	719.6	719.6	723.0	719.0
180°	721.3	721.3	721.3	721.3	721.3

(END OF REPORT)