

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011546

Luminaire Tested: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011546
REPORT IS A COMBINATION OF REPORTS P989738 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB50-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5481.6 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011546

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011546

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	68	63	59	53	49	47	38	36	34	25	24	23
3	76	67	60	55	68	60	54	49	46	42	39	34	31	29	22	21	19
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4617 cd/sqm

TEST NUMBER: P1011546

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	0.9
10°-20°	135.0	2.5
20°-30°	199.4	3.6
30°-40°	232.9	4.2
40°-50°	234.1	4.3
50°-60°	205.7	3.8
60°-70°	153.2	2.8
70°-80°	87.2	1.6
80°-90°	27.9	0.5
90°-100°	313.4	5.7
100°-110°	876.1	16.0
110°-120°	854.3	15.6
120°-130°	680.2	12.4
130°-140°	536.9	9.8
140°-150°	400.6	7.3
150°-160°	279.5	5.1
160°-170°	164.2	3.0
170°-180°	53.4	1.0
0°-30°	382.2	7.0
0°-40°	615.1	11.2
0°-60°	1054.9	19.2
0°-90°	1323.1	24.1
90°-120°	2043.8	37.3
90°-150°	3661.5	66.8
90°-180°	4159.0	75.9
0°-180°	5481.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	2	13	28	31	32	4
95°	38	123	662	193	130	40
105°	130	192	898	1570	1420	138
115°	229	285	687	1506	1727	227
125°	318	376	641	1161	1362	283
135°	373	445	632	956	1104	288
145°	425	487	624	784	863	267
155°	484	521	604	687	716	222
165°	528	543	578	614	624	149
175°	550	551	555	563	562	52
180°	552	552	552	552	552	

TEST NUMBER: P1011546

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	2.2	13.4	27.9	31.2	32.4
92.5°	16.7	67.0	207.7	70.9	59.2
95°	38.0	123.4	662.1	193.2	129.5
97.5°	60.3	141.2	1018.3	485.6	265.7
100°	82.6	155.8	1057.4	1016.0	700.1
102.5°	106.1	172.5	984.8	1360.5	1108.7
105°	129.5	191.5	897.7	1569.8	1420.2
107.5°	154.1	213.8	820.7	1662.0	1623.4
110°	180.9	236.7	757.0	1664.8	1739.6

TEST NUMBER: P1011546

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	205.4	260.7	714.6	1601.6	1763.0
115°	228.9	285.2	686.7	1505.6	1727.3
117.5°	252.3	308.8	667.7	1402.9	1649.1
120°	276.9	332.2	655.4	1305.8	1546.4
122.5°	298.1	354.5	647.6	1229.3	1450.4
125°	318.2	375.7	640.9	1161.2	1362.2
127.5°	333.8	395.8	637.5	1105.4	1286.2
130°	348.4	413.6	634.2	1054.0	1223.7
132.5°	359.5	429.9	633.1	1006.0	1162.3
135°	372.9	445.0	632.0	956.3	1104.3
137.5°	385.2	457.2	629.7	909.4	1042.8
140°	397.5	468.4	628.6	863.6	978.1
142.5°	410.9	478.4	626.4	821.8	917.8
145°	425.4	487.4	624.1	784.4	863.1
147.5°	439.9	496.8	620.8	755.4	816.2
150°	454.4	504.6	616.3	729.6	776.0
152.5°	468.9	513.0	610.7	707.3	742.5
155°	483.5	521.4	604.0	686.7	715.7
157.5°	494.6	528.6	598.5	666.6	690.0
160°	508.0	534.8	591.8	648.2	665.5
162.5°	518.1	539.3	585.1	630.8	643.1
165°	528.1	543.2	578.4	613.5	624.1
167.5°	535.9	546.6	571.7	598.4	605.2
170°	542.6	548.2	565.0	585.0	588.4
172.5°	547.1	549.9	559.4	573.3	572.8
175°	550.5	551.0	554.9	562.7	561.6
177.5°	552.7	551.6	551.6	556.0	553.8
180°	551.6	551.6	551.6	551.6	551.6

(END OF REPORT)