

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011824

Luminaire Tested: S123DIP-B560D585UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011824
REPORT IS A COMBINATION OF REPORTS P990130 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4327.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011824

CATALOG NUMBER: S123DIP-B560D585UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011824

CATALOG NUMBER: S123DIP-B560D585UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	98	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	59	52	47	51	46	41	44	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	24
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8078 cd/sqm

TEST NUMBER: P1011824

CATALOG NUMBER: S123DIP-B560D585UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.9
10°-20°	236.2	5.5
20°-30°	348.8	8.1
30°-40°	407.4	9.4
40°-50°	409.5	9.5
50°-60°	359.8	8.3
60°-70°	267.9	6.2
70°-80°	152.5	3.5
80°-90°	44.9	1.0
90°-100°	46.8	1.1
100°-110°	141.8	3.3
110°-120°	241.4	5.6
120°-130°	317.6	7.3
130°-140°	356.9	8.2
140°-150°	350.9	8.1
150°-160°	295.4	6.8
160°-170°	196.7	4.5
170°-180°	68.9	1.6
0°-30°	668.6	15.5
0°-40°	1076.0	24.9
0°-60°	1845.2	42.6
0°-90°	2310.5	53.4
90°-120°	430.0	9.9
90°-150°	1455.5	33.6
90°-180°	2016.0	46.6
0°-180°	4327.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	1	6	14	16	17	5
95°	34	38	42	45	45	37
105°	129	130	135	135	136	138
115°	243	245	244	244	244	240
125°	356	357	356	354	352	317
135°	461	465	464	462	461	355
145°	560	561	562	562	560	350
155°	641	641	641	644	640	295
165°	698	696	696	700	696	197
175°	726	724	724	727	723	69
180°	728	728	728	728	728	

TEST NUMBER: P1011824

CATALOG NUMBER: S123DIP-B560D585UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	0.6	6.3	13.7	16.0	17.2
92.5°	17.2	20.6	24.0	25.7	24.6
95°	33.7	37.7	42.3	44.6	44.6
97.5°	55.5	58.3	61.7	64.6	64.0
100°	77.7	81.2	84.0	85.8	86.9
102.5°	103.5	105.2	109.2	110.9	110.3
105°	128.6	129.8	134.9	134.9	136.1
107.5°	158.4	158.9	161.2	162.9	162.4
110°	185.8	186.9	188.1	190.4	189.2



TEST NUMBER: P1011824

CATALOG NUMBER: S123DIP-B560D585UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.4	215.0	215.0	217.8	217.8
115°	243.0	244.7	243.5	244.1	243.5
117.5°	272.1	272.7	271.5	271.5	269.8
120°	299.0	302.4	299.6	299.0	297.8
122.5°	327.0	329.3	328.1	326.4	324.7
125°	355.6	357.3	356.2	353.9	351.6
127.5°	381.9	385.3	384.2	380.7	378.5
130°	408.2	412.8	411.0	408.8	404.7
132.5°	434.5	439.1	437.9	435.0	432.2
135°	461.3	464.8	464.2	461.9	460.8
137.5°	485.9	488.8	490.5	487.6	485.9
140°	511.7	514.5	515.1	514.5	510.5
142.5°	535.1	538.0	539.1	538.5	535.7
145°	559.7	560.8	562.5	562.0	559.7
147.5°	580.8	583.1	584.8	584.8	581.4
150°	603.1	604.3	605.4	605.4	602.0
152.5°	621.4	623.1	623.7	624.8	622.0
155°	640.9	640.9	641.4	643.7	639.7
157.5°	657.4	656.9	657.4	659.7	656.3
160°	672.9	671.7	671.7	674.6	672.3
162.5°	686.6	684.9	685.4	688.3	684.3
165°	698.0	696.3	696.3	699.7	695.7
167.5°	707.7	705.5	706.0	709.5	706.0
170°	715.7	713.5	713.5	717.5	713.5
172.5°	722.0	719.7	719.7	723.2	719.2
175°	726.0	723.7	723.7	727.2	723.2
177.5°	728.3	726.0	726.0	729.5	725.5
180°	727.7	727.7	727.7	727.7	727.7

(END OF REPORT)