

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011834

Luminaire Tested: S123DIP-B560D585UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011834
REPORT IS A COMBINATION OF REPORTS P990140 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D585UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4458.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011834

CATALOG NUMBER: S123DIP-B560D585UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011834

CATALOG NUMBER: S123DIP-B560D585UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58
1	98	94	90	86	91	87	84	80	74	72	69	62	60	59	51	50	49
2	89	82	76	70	82	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8113 cd/sqm

TEST NUMBER: P1011834

CATALOG NUMBER: S123DIP-B560D585UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.9
10°-20°	237.2	5.3
20°-30°	350.3	7.9
30°-40°	409.1	9.2
40°-50°	411.3	9.2
50°-60°	361.3	8.1
60°-70°	269.1	6.0
70°-80°	153.1	3.4
80°-90°	45.1	1.0
90°-100°	161.1	3.6
100°-110°	450.3	10.1
110°-120°	439.1	9.8
120°-130°	349.6	7.8
130°-140°	276.0	6.2
140°-150°	205.9	4.6
150°-160°	143.6	3.2
160°-170°	84.4	1.9
170°-180°	27.4	0.6
0°-30°	671.5	15.1
0°-40°	1080.6	24.2
0°-60°	1853.3	41.6
0°-90°	2320.6	52.1
90°-120°	1050.4	23.6
90°-150°	1881.9	42.2
90°-180°	2137.0	47.9
0°-180°	4458.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	1	7	14	16	17	4
95°	20	63	340	99	67	21
105°	67	98	461	807	730	71
115°	118	147	353	774	888	116
125°	164	193	329	597	700	145
135°	192	229	325	492	568	148
145°	219	250	321	403	444	137
155°	248	268	310	353	368	114
165°	271	279	297	315	321	77
175°	283	283	285	289	289	27
180°	284	284	284	284	284	

TEST NUMBER: P1011834

CATALOG NUMBER: S123DIP-B560D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	1.1	6.9	14.3	16.0	16.6
92.5°	8.6	34.4	106.7	36.4	30.4
95°	19.5	63.4	340.3	99.2	66.6
97.5°	31.0	72.6	523.4	249.6	136.6
100°	42.5	80.1	543.4	522.2	359.8
102.5°	54.5	88.6	506.1	699.2	569.8
105°	66.6	98.4	461.4	806.8	730.0
107.5°	79.2	109.9	421.8	854.2	834.4
110°	93.0	121.6	389.1	855.6	894.1

TEST NUMBER: P1011834

CATALOG NUMBER: S123DIP-B560D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.6	134.0	367.3	823.2	906.1
115°	117.6	146.6	352.9	773.8	887.8
117.5°	129.7	158.6	343.2	721.0	847.6
120°	142.3	170.8	336.9	671.2	794.8
122.5°	153.2	182.2	332.8	631.8	745.4
125°	163.6	193.2	329.4	596.8	700.1
127.5°	171.6	203.4	327.7	568.2	661.1
130°	179.0	212.6	326.0	541.7	629.0
132.5°	184.8	221.0	325.4	517.0	597.4
135°	191.7	228.6	324.8	491.6	567.6
137.5°	198.0	235.0	323.7	467.4	536.0
140°	204.3	240.8	323.1	443.8	502.7
142.5°	211.2	245.9	321.9	422.4	471.7
145°	218.6	250.5	320.8	403.2	443.6
147.5°	226.1	255.4	319.1	388.2	419.5
150°	233.6	259.4	316.8	375.0	398.8
152.5°	241.0	263.7	313.9	363.5	381.6
155°	248.5	268.0	310.5	353.0	367.8
157.5°	254.2	271.8	307.6	342.6	354.6
160°	261.1	274.9	304.1	333.1	342.0
162.5°	266.3	277.2	300.7	324.2	330.5
165°	271.4	279.2	297.3	315.4	320.8
167.5°	275.5	280.9	293.8	307.5	311.0
170°	278.9	281.8	290.4	300.7	302.4
172.5°	281.2	282.6	287.5	294.7	294.4
175°	282.9	283.2	285.2	289.2	288.7
177.5°	284.1	283.5	283.5	285.8	284.6
180°	283.5	283.5	283.5	283.5	283.5

(END OF REPORT)