

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011563

Luminaire Tested: S123DIP-B340D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011563
REPORT IS A COMBINATION OF REPORTS P989770 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2628.0 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011563

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011563

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1011563

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	1.9
10°-20°	140.4	5.3
20°-30°	207.4	7.9
30°-40°	242.2	9.2
40°-50°	243.5	9.3
50°-60°	213.9	8.1
60°-70°	159.3	6.1
70°-80°	90.7	3.4
80°-90°	26.7	1.0
90°-100°	29.1	1.1
100°-110°	88.2	3.4
110°-120°	150.1	5.7
120°-130°	197.5	7.5
130°-140°	222.0	8.4
140°-150°	218.2	8.3
150°-160°	183.7	7.0
160°-170°	122.3	4.7
170°-180°	42.8	1.6
0°-30°	397.6	15.1
0°-40°	639.8	24.3
0°-60°	1097.2	41.8
0°-90°	1374.0	52.3
90°-120°	267.5	10.2
90°-150°	905.2	34.4
90°-180°	1254.0	47.7
0°-180°	2628.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	0	4	8	10	11	3
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	151	152	152	152	152	150
125°	221	222	222	220	219	197
135°	287	289	289	287	287	221
145°	348	349	350	350	348	217
155°	398	398	399	400	398	183
165°	434	433	433	435	433	122
175°	452	450	450	452	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1011563

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	0.4	3.9	8.5	10.0	10.7
92.5°	10.7	12.8	14.9	16.0	15.3
95°	21.0	23.5	26.3	27.7	27.7
97.5°	34.5	36.3	38.4	40.2	39.8
100°	48.4	50.5	52.3	53.3	54.0
102.5°	64.4	65.4	67.9	69.0	68.6
105°	80.0	80.7	83.9	83.9	84.6
107.5°	98.5	98.8	100.3	101.3	101.0
110°	115.5	116.3	117.0	118.4	117.7



TEST NUMBER: P1011563

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.3	133.7	133.7	135.5	135.5
115°	151.1	152.2	151.5	151.8	151.5
117.5°	169.2	169.6	168.9	168.9	167.8
120°	185.9	188.1	186.3	185.9	185.2
122.5°	203.4	204.8	204.1	203.0	201.9
125°	221.1	222.2	221.5	220.1	218.7
127.5°	237.5	239.6	238.9	236.8	235.4
130°	253.8	256.7	255.6	254.2	251.7
132.5°	270.2	273.0	272.3	270.6	268.8
135°	286.9	289.0	288.7	287.3	286.6
137.5°	302.2	304.0	305.0	303.3	302.2
140°	318.2	320.0	320.3	320.0	317.5
142.5°	332.8	334.6	335.3	334.9	333.1
145°	348.1	348.8	349.8	349.5	348.1
147.5°	361.2	362.6	363.7	363.7	361.6
150°	375.1	375.8	376.5	376.5	374.4
152.5°	386.5	387.5	387.9	388.6	386.8
155°	398.5	398.5	398.9	400.3	397.8
157.5°	408.9	408.5	408.9	410.3	408.1
160°	418.5	417.7	417.7	419.5	418.1
162.5°	427.0	425.9	426.3	428.1	425.6
165°	434.1	433.0	433.0	435.2	432.7
167.5°	440.1	438.7	439.1	441.2	439.1
170°	445.1	443.7	443.7	446.2	443.7
172.5°	449.0	447.6	447.6	449.7	447.3
175°	451.5	450.1	450.1	452.2	449.7
177.5°	452.9	451.5	451.5	453.7	451.2
180°	452.6	452.6	452.6	452.6	452.6

(END OF REPORT)