

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011564

Luminaire Tested: S123DIP-B340D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011564
REPORT IS A COMBINATION OF REPORTS P989771 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2698.1 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011564

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011564

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	30
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1011564

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	1.8
10°-20°	140.4	5.2
20°-30°	207.4	7.7
30°-40°	242.2	9.0
40°-50°	243.5	9.0
50°-60°	213.9	7.9
60°-70°	159.3	5.9
70°-80°	90.7	3.4
80°-90°	26.8	1.0
90°-100°	99.8	3.7
100°-110°	278.9	10.3
110°-120°	272.0	10.1
120°-130°	216.6	8.0
130°-140°	171.0	6.3
140°-150°	127.6	4.7
150°-160°	89.0	3.3
160°-170°	52.3	1.9
170°-180°	17.0	0.6
0°-30°	397.6	14.7
0°-40°	639.8	23.7
0°-60°	1097.2	40.7
0°-90°	1374.0	50.9
90°-120°	650.7	24.1
90°-150°	1165.8	43.2
90°-180°	1324.0	49.1
0°-180°	2698.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	1	4	9	10	10	3
95°	12	39	211	62	41	13
105°	41	61	286	500	452	44
115°	73	91	219	479	550	72
125°	101	120	204	370	434	90
135°	119	142	201	304	352	92
145°	135	155	199	250	275	85
155°	154	166	192	219	228	71
165°	168	173	184	195	199	47
175°	175	175	177	179	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1011564

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	0.7	4.2	8.9	10.0	10.3
92.5°	5.3	21.3	66.1	22.6	18.8
95°	12.1	39.3	210.8	61.5	41.2
97.5°	19.2	45.0	324.2	154.6	84.6
100°	26.3	49.6	336.7	323.6	222.9
102.5°	33.8	54.9	313.6	433.2	353.0
105°	41.2	61.0	285.8	499.8	452.2
107.5°	49.1	68.0	261.3	529.2	516.9
110°	57.6	75.4	241.0	530.0	553.9

TEST NUMBER: P1011564

CATALOG NUMBER: S123DIP-B340D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.0	227.5	510.0	561.3
115°	72.9	90.8	218.6	479.4	550.0
117.5°	80.3	98.3	212.6	446.7	525.1
120°	88.2	105.8	208.7	415.8	492.4
122.5°	94.9	112.9	206.2	391.5	461.8
125°	101.3	119.6	204.1	369.7	433.7
127.5°	106.3	126.0	203.0	352.0	409.5
130°	110.9	131.7	201.9	335.6	389.6
132.5°	114.5	136.8	201.6	320.3	370.1
135°	118.7	141.7	201.2	304.5	351.6
137.5°	122.6	145.6	200.5	289.6	332.0
140°	126.6	149.1	200.1	275.0	311.4
142.5°	130.8	152.3	199.4	261.7	292.2
145°	135.4	155.2	198.7	249.8	274.8
147.5°	140.1	158.2	197.7	240.5	259.9
150°	144.7	160.7	196.2	232.3	247.1
152.5°	149.3	163.4	194.5	225.2	236.4
155°	153.9	166.0	192.3	218.6	227.9
157.5°	157.5	168.4	190.6	212.2	219.7
160°	161.8	170.3	188.4	206.4	211.9
162.5°	165.0	171.7	186.3	200.9	204.8
165°	168.2	173.0	184.2	195.4	198.7
167.5°	170.6	174.0	182.0	190.6	192.7
170°	172.8	174.6	179.9	186.2	187.4
172.5°	174.2	175.1	178.1	182.6	182.4
175°	175.3	175.4	176.7	179.2	178.8
177.5°	176.0	175.6	175.6	177.0	176.3
180°	175.6	175.6	175.6	175.6	175.6

(END OF REPORT)