

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011565

Luminaire Tested: S123DIP-B340D365UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011565
REPORT IS A COMBINATION OF REPORTS P989772 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D365UB35-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2885.0 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	34	29	50	39	32	28	34	28	25	29	25	21	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	20	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	1.6
10°-20°	148.5	5.1
20°-30°	249.9	8.7
30°-40°	282.4	9.8
40°-50°	252.9	8.8
50°-60°	204.2	7.1
60°-70°	142.3	4.9
70°-80°	74.7	2.6
80°-90°	18.9	0.7
90°-100°	16.9	0.6
100°-110°	81.9	2.8
110°-120°	200.8	7.0
120°-130°	254.9	8.8
130°-140°	272.3	9.4
140°-150°	254.6	8.8
150°-160°	205.4	7.1
160°-170°	132.5	4.6
170°-180°	45.7	1.6
0°-30°	444.6	15.4
0°-40°	727.0	25.2
0°-60°	1184.1	41.0
0°-90°	1420.0	49.2
90°-120°	299.6	10.4
90°-150°	1081.4	37.5
90°-180°	1465.0	50.8
0°-180°	2885.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	0	11	0	11	0	2
95°	22	14	22	14	22	26
105°	106	16	106	16	106	113
115°	200	210	200	210	200	197
125°	281	287	281	287	281	251
135°	350	354	350	354	350	270
145°	404	408	404	408	404	253
155°	445	444	445	444	445	205
165°	470	468	470	468	470	133
175°	481	479	481	479	481	46
180°	481	481	481	481	481	

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	0.4	1.2	2.0	2.7	3.5	3.9	4.4	5.5	6.5	7.6	8.6
92.5°	8.2	7.7	7.3	6.8	6.3	6.1	6.5	7.2	7.9	8.6	9.3
95°	21.8	18.5	15.3	12.0	8.7	7.1	7.5	8.4	9.3	10.2	11.1
97.5°	39.6	37.4	35.2	32.9	30.7	29.6	27.6	23.5	19.5	15.4	11.4
100°	60.3	61.9	63.5	65.1	66.7	67.5	61.3	48.9	36.6	24.2	11.8
102.5°	83.9	84.9	85.9	87.0	88.0	88.5	81.6	67.8	54.0	40.2	26.4
105°	106.4	107.3	108.1	109.0	109.9	110.3	106.7	99.6	92.5	85.3	78.2
107.5°	130.3	131.0	131.7	132.4	133.1	133.5	134.1	135.3	136.5	137.7	138.9
110°	154.2	154.8	155.5	156.1	156.8	157.1	157.5	158.4	159.3	160.1	161.0

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	177.1	177.7	178.2	178.8	179.3	179.6	180.0	180.9	181.8	182.6	183.5
115°	199.6	200.1	200.5	201.0	201.5	201.7	202.1	202.8	203.5	204.2	204.9
117.5°	221.7	222.3	222.8	223.4	223.9	224.2	224.4	224.8	225.2	225.6	226.0
120°	242.1	242.8	243.5	244.2	244.9	245.3	245.4	245.7	245.9	246.2	246.4
122.5°	262.8	263.4	263.9	264.5	265.0	265.3	265.5	265.8	266.1	266.4	266.7
125°	281.3	281.9	282.6	283.2	283.9	284.2	284.4	284.7	285.0	285.3	285.6
127.5°	299.9	300.5	301.2	301.8	302.5	302.8	303.0	303.4	303.7	304.1	304.5
130°	317.0	317.6	318.3	318.9	319.6	319.9	320.1	320.4	320.7	321.0	321.3
132.5°	333.5	334.1	334.7	335.4	336.0	336.3	336.4	336.7	336.9	337.2	337.4
135°	350.2	350.7	351.2	351.7	352.2	352.4	352.6	352.9	353.2	353.5	353.8
137.5°	364.5	365.1	365.8	366.4	367.1	367.4	367.5	367.6	367.8	367.9	368.1
140°	378.8	379.3	379.8	380.3	380.8	381.0	381.1	381.3	381.6	381.8	382.0
142.5°	392.0	392.5	393.0	393.5	394.0	394.2	394.3	394.5	394.8	395.0	395.2
145°	404.2	404.8	405.3	405.9	406.4	406.7	406.8	406.9	407.1	407.2	407.4
147.5°	415.9	416.3	416.7	417.1	417.5	417.7	417.8	417.9	418.1	418.2	418.4
150°	426.7	426.9	427.1	427.4	427.6	427.7	427.8	427.9	428.1	428.2	428.4
152.5°	436.3	436.4	436.4	436.5	436.6	436.6	436.6	436.7	436.8	436.9	437.0
155°	445.2	445.0	444.9	444.7	444.6	444.5	444.5	444.6	444.7	444.8	444.9
157.5°	452.4	452.4	452.4	452.4	452.4	452.4	452.4	452.3	452.2	452.1	452.0
160°	458.8	458.7	458.6	458.5	458.4	458.4	458.4	458.3	458.2	458.2	458.1
162.5°	464.9	464.7	464.4	464.2	463.9	463.8	463.8	463.7	463.6	463.5	463.4
165°	469.5	469.3	469.0	468.8	468.5	468.4	468.4	468.3	468.2	468.2	468.1
167.5°	473.4	473.1	472.8	472.5	472.2	472.0	472.0	472.0	472.0	472.0	472.0
170°	476.6	476.3	476.0	475.7	475.4	475.2	475.2	475.2	475.2	475.2	475.2
172.5°	478.8	478.4	478.0	477.6	477.2	477.0	477.0	477.1	477.2	477.3	477.4
175°	480.6	480.2	479.8	479.4	479.0	478.8	478.8	478.9	479.0	479.0	479.1
177.5°	481.3	480.9	480.5	480.1	479.7	479.5	479.5	479.6	479.7	479.7	479.8
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	8.9	9.2	9.5	9.8	10.0	10.1	10.2	10.4	10.5	10.7	10.5
92.5°	9.9	10.4	11.0	11.5	11.8	11.8	11.9	12.0	12.0	12.1	12.0
95°	11.7	12.2	12.8	13.3	13.6	13.6	13.6	13.6	13.6	13.6	13.6
97.5°	12.0	12.7	13.3	14.0	14.3	14.3	14.4	14.5	14.5	14.6	14.5
100°	12.4	13.0	13.7	14.3	14.6	14.6	14.7	14.8	14.9	15.0	14.9
102.5°	23.8	21.2	18.5	15.9	14.6	14.7	14.9	15.0	15.2	15.4	15.2
105°	64.2	50.1	36.1	22.0	15.0	15.1	15.2	15.4	15.5	15.7	15.5
107.5°	126.7	114.5	102.2	90.0	83.9	78.7	68.3	57.9	47.5	37.1	47.5
110°	158.4	155.8	153.1	150.5	149.2	143.5	132.2	120.9	109.5	98.2	109.5

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	184.2	184.9	185.6	186.3	186.7	186.6	186.5	186.3	186.2	186.0	186.2
115°	205.7	206.5	207.3	208.1	208.5	208.7	209.0	209.3	209.6	209.9	209.6
117.5°	226.6	227.3	227.9	228.6	228.9	228.9	229.0	229.1	229.1	229.2	229.1
120°	247.0	247.6	248.3	248.9	249.2	249.2	249.2	249.2	249.2	249.2	249.2
122.5°	267.1	267.5	267.9	268.3	268.5	268.5	268.6	268.7	268.7	268.8	268.7
125°	285.8	285.9	286.1	286.2	286.3	286.4	286.6	286.7	286.9	287.1	286.9
127.5°	304.7	305.0	305.2	305.5	305.6	305.5	305.4	305.2	305.1	304.9	305.1
130°	321.6	322.0	322.3	322.6	322.8	322.7	322.5	322.4	322.2	322.0	322.2
132.5°	337.7	338.0	338.3	338.6	338.8	338.7	338.5	338.2	338.0	337.8	338.0
135°	354.0	354.3	354.5	354.8	354.9	354.8	354.5	354.3	354.0	353.8	354.0
137.5°	368.5	368.9	369.3	369.7	369.9	369.8	369.7	369.5	369.4	369.2	369.4
140°	382.3	382.7	383.0	383.3	383.5	383.4	383.2	383.1	382.9	382.7	382.9
142.5°	395.4	395.7	395.9	396.2	396.3	396.2	395.9	395.7	395.4	395.2	395.4
145°	407.6	407.7	407.9	408.0	408.1	408.1	408.1	408.1	408.1	408.1	408.1
147.5°	418.6	418.8	418.9	419.1	419.2	419.0	418.6	418.2	417.8	417.4	417.8
150°	428.6	428.8	428.9	429.1	429.2	429.1	428.8	428.6	428.3	428.1	428.3
152.5°	437.3	437.6	437.9	438.2	438.4	438.2	437.8	437.4	437.0	436.6	437.0
155°	445.3	445.7	446.0	446.4	446.6	446.4	445.9	445.4	445.0	444.5	445.0
157.5°	452.5	452.9	453.4	453.9	454.1	453.8	453.2	452.5	451.9	451.3	451.9
160°	458.6	459.0	459.5	460.0	460.2	459.9	459.4	458.8	458.3	457.7	458.3
162.5°	464.0	464.5	465.1	465.6	465.9	465.7	465.2	464.7	464.3	463.8	464.3
165°	468.7	469.3	470.0	470.6	470.9	470.6	470.1	469.5	469.0	468.4	469.0
167.5°	472.6	473.3	473.9	474.6	474.9	474.6	473.9	473.3	472.6	472.0	472.6
170°	475.8	476.5	477.1	477.8	478.1	477.8	477.1	476.5	475.8	475.2	475.8
172.5°	478.0	478.6	479.3	479.9	480.2	479.8	479.1	478.4	477.7	477.0	477.7
175°	479.7	480.2	480.8	481.3	481.6	481.3	480.7	480.0	479.4	478.8	479.4
177.5°	480.4	481.1	481.7	482.4	482.7	482.3	481.5	480.7	479.9	479.1	479.9
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	10.4	10.2	10.1	10.0	9.8	9.5	9.2	8.9	8.6	7.6	6.5
92.5°	12.0	11.9	11.8	11.8	11.5	11.0	10.4	9.9	9.3	8.6	7.9
95°	13.6	13.6	13.6	13.6	13.3	12.8	12.2	11.7	11.1	10.2	9.3
97.5°	14.5	14.4	14.3	14.3	14.0	13.3	12.7	12.0	11.4	15.4	19.5
100°	14.8	14.7	14.6	14.6	14.3	13.7	13.0	12.4	11.8	24.2	36.6
102.5°	15.0	14.9	14.7	14.6	15.9	18.5	21.2	23.8	26.4	40.2	54.0
105°	15.4	15.2	15.1	15.0	22.0	36.1	50.1	64.2	78.2	85.3	92.5
107.5°	57.9	68.3	78.7	83.9	90.0	102.2	114.5	126.7	138.9	137.7	136.5
110°	120.9	132.2	143.5	149.2	150.5	153.1	155.8	158.4	161.0	160.1	159.3

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	186.3	186.5	186.6	186.7	186.3	185.6	184.9	184.2	183.5	182.6	181.8
115°	209.3	209.0	208.7	208.5	208.1	207.3	206.5	205.7	204.9	204.2	203.5
117.5°	229.1	229.0	228.9	228.9	228.6	227.9	227.3	226.6	226.0	225.6	225.2
120°	249.2	249.2	249.2	249.2	248.9	248.3	247.6	247.0	246.4	246.2	245.9
122.5°	268.7	268.6	268.5	268.5	268.3	267.9	267.5	267.1	266.7	266.4	266.1
125°	286.7	286.6	286.4	286.3	286.2	286.1	285.9	285.8	285.6	285.3	285.0
127.5°	305.2	305.4	305.5	305.6	305.5	305.2	305.0	304.7	304.5	304.1	303.7
130°	322.4	322.5	322.7	322.8	322.6	322.3	322.0	321.6	321.3	321.0	320.7
132.5°	338.2	338.5	338.7	338.8	338.6	338.3	338.0	337.7	337.4	337.2	336.9
135°	354.3	354.5	354.8	354.9	354.8	354.5	354.3	354.0	353.8	353.5	353.2
137.5°	369.5	369.7	369.8	369.9	369.7	369.3	368.9	368.5	368.1	367.9	367.8
140°	383.1	383.2	383.4	383.5	383.3	383.0	382.7	382.3	382.0	381.8	381.6
142.5°	395.7	395.9	396.2	396.3	396.2	395.9	395.7	395.4	395.2	395.0	394.8
145°	408.1	408.1	408.1	408.1	408.0	407.9	407.7	407.6	407.4	407.2	407.1
147.5°	418.2	418.6	419.0	419.2	419.1	418.9	418.8	418.6	418.4	418.2	418.1
150°	428.6	428.8	429.1	429.2	429.1	428.9	428.8	428.6	428.4	428.2	428.1
152.5°	437.4	437.8	438.2	438.4	438.2	437.9	437.6	437.3	437.0	436.9	436.8
155°	445.4	445.9	446.4	446.6	446.4	446.0	445.7	445.3	444.9	444.8	444.7
157.5°	452.5	453.2	453.8	454.1	453.9	453.4	452.9	452.5	452.0	452.1	452.2
160°	458.8	459.4	459.9	460.2	460.0	459.5	459.0	458.6	458.1	458.2	458.2
162.5°	464.7	465.2	465.7	465.9	465.6	465.1	464.5	464.0	463.4	463.5	463.6
165°	469.5	470.1	470.6	470.9	470.6	470.0	469.3	468.7	468.1	468.2	468.2
167.5°	473.3	473.9	474.6	474.9	474.6	473.9	473.3	472.6	472.0	472.0	472.0
170°	476.5	477.1	477.8	478.1	477.8	477.1	476.5	475.8	475.2	475.2	475.2
172.5°	478.4	479.1	479.8	480.2	479.9	479.3	478.6	478.0	477.4	477.3	477.2
175°	480.0	480.7	481.3	481.6	481.3	480.8	480.2	479.7	479.1	479.0	479.0
177.5°	480.7	481.5	482.3	482.7	482.4	481.7	481.1	480.4	479.8	479.7	479.7
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	5.5	4.4	3.9	3.5	2.7	2.0	1.2	0.4	1.2	2.0	2.7
92.5°	7.2	6.5	6.1	6.3	6.8	7.3	7.7	8.2	7.7	7.3	6.8
95°	8.4	7.5	7.1	8.7	12.0	15.3	18.5	21.8	18.5	15.3	12.0
97.5°	23.5	27.6	29.6	30.7	32.9	35.2	37.4	39.6	37.4	35.2	32.9
100°	48.9	61.3	67.5	66.7	65.1	63.5	61.9	60.3	61.9	63.5	65.1
102.5°	67.8	81.6	88.5	88.0	87.0	85.9	84.9	83.9	84.9	85.9	87.0
105°	99.6	106.7	110.3	109.9	109.0	108.1	107.3	106.4	107.3	108.1	109.0
107.5°	135.3	134.1	133.5	133.1	132.4	131.7	131.0	130.3	131.0	131.7	132.4
110°	158.4	157.5	157.1	156.8	156.1	155.5	154.8	154.2	154.8	155.5	156.1

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	180.9	180.0	179.6	179.3	178.8	178.2	177.7	177.1	177.7	178.2	178.8
115°	202.8	202.1	201.7	201.5	201.0	200.5	200.1	199.6	200.1	200.5	201.0
117.5°	224.8	224.4	224.2	223.9	223.4	222.8	222.3	221.7	222.3	222.8	223.4
120°	245.7	245.4	245.3	244.9	244.2	243.5	242.8	242.1	242.8	243.5	244.2
122.5°	265.8	265.5	265.3	265.0	264.5	263.9	263.4	262.8	263.4	263.9	264.5
125°	284.7	284.4	284.2	283.9	283.2	282.6	281.9	281.3	281.9	282.6	283.2
127.5°	303.4	303.0	302.8	302.5	301.8	301.2	300.5	299.9	300.5	301.2	301.8
130°	320.4	320.1	319.9	319.6	318.9	318.3	317.6	317.0	317.6	318.3	318.9
132.5°	336.7	336.4	336.3	336.0	335.4	334.7	334.1	333.5	334.1	334.7	335.4
135°	352.9	352.6	352.4	352.2	351.7	351.2	350.7	350.2	350.7	351.2	351.7
137.5°	367.6	367.5	367.4	367.1	366.4	365.8	365.1	364.5	365.1	365.8	366.4
140°	381.3	381.1	381.0	380.8	380.3	379.8	379.3	378.8	379.3	379.8	380.3
142.5°	394.5	394.3	394.2	394.0	393.5	393.0	392.5	392.0	392.5	393.0	393.5
145°	406.9	406.8	406.7	406.4	405.9	405.3	404.8	404.2	404.8	405.3	405.9
147.5°	417.9	417.8	417.7	417.5	417.1	416.7	416.3	415.9	416.3	416.7	417.1
150°	427.9	427.8	427.7	427.6	427.4	427.1	426.9	426.7	426.9	427.1	427.4
152.5°	436.7	436.6	436.6	436.6	436.5	436.4	436.4	436.3	436.4	436.4	436.5
155°	444.6	444.5	444.5	444.6	444.7	444.9	445.0	445.2	445.0	444.9	444.7
157.5°	452.3	452.4	452.4	452.4	452.4	452.4	452.4	452.4	452.4	452.4	452.4
160°	458.3	458.4	458.4	458.4	458.5	458.6	458.7	458.8	458.7	458.6	458.5
162.5°	463.7	463.8	463.8	463.9	464.2	464.4	464.7	464.9	464.7	464.4	464.2
165°	468.3	468.4	468.4	468.5	468.8	469.0	469.3	469.5	469.3	469.0	468.8
167.5°	472.0	472.0	472.0	472.2	472.5	472.8	473.1	473.4	473.1	472.8	472.5
170°	475.2	475.2	475.2	475.4	475.7	476.0	476.3	476.6	476.3	476.0	475.7
172.5°	477.1	477.0	477.0	477.2	477.6	478.0	478.4	478.8	478.4	478.0	477.6
175°	478.9	478.8	478.8	479.0	479.4	479.8	480.2	480.6	480.2	479.8	479.4
177.5°	479.6	479.5	479.5	479.7	480.1	480.5	480.9	481.3	480.9	480.5	480.1
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	3.5	3.9	4.4	5.5	6.5	7.6	8.6	8.9	9.2	9.5	9.8
92.5°	6.3	6.1	6.5	7.2	7.9	8.6	9.3	9.9	10.4	11.0	11.5
95°	8.7	7.1	7.5	8.4	9.3	10.2	11.1	11.7	12.2	12.8	13.3
97.5°	30.7	29.6	27.6	23.5	19.5	15.4	11.4	12.0	12.7	13.3	14.0
100°	66.7	67.5	61.3	48.9	36.6	24.2	11.8	12.4	13.0	13.7	14.3
102.5°	88.0	88.5	81.6	67.8	54.0	40.2	26.4	23.8	21.2	18.5	15.9
105°	109.9	110.3	106.7	99.6	92.5	85.3	78.2	64.2	50.1	36.1	22.0
107.5°	133.1	133.5	134.1	135.3	136.5	137.7	138.9	126.7	114.5	102.2	90.0
110°	156.8	157.1	157.5	158.4	159.3	160.1	161.0	158.4	155.8	153.1	150.5

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	179.3	179.6	180.0	180.9	181.8	182.6	183.5	184.2	184.9	185.6	186.3
115°	201.5	201.7	202.1	202.8	203.5	204.2	204.9	205.7	206.5	207.3	208.1
117.5°	223.9	224.2	224.4	224.8	225.2	225.6	226.0	226.6	227.3	227.9	228.6
120°	244.9	245.3	245.4	245.7	245.9	246.2	246.4	247.0	247.6	248.3	248.9
122.5°	265.0	265.3	265.5	265.8	266.1	266.4	266.7	267.1	267.5	267.9	268.3
125°	283.9	284.2	284.4	284.7	285.0	285.3	285.6	285.8	285.9	286.1	286.2
127.5°	302.5	302.8	303.0	303.4	303.7	304.1	304.5	304.7	305.0	305.2	305.5
130°	319.6	319.9	320.1	320.4	320.7	321.0	321.3	321.6	322.0	322.3	322.6
132.5°	336.0	336.3	336.4	336.7	336.9	337.2	337.4	337.7	338.0	338.3	338.6
135°	352.2	352.4	352.6	352.9	353.2	353.5	353.8	354.0	354.3	354.5	354.8
137.5°	367.1	367.4	367.5	367.6	367.8	367.9	368.1	368.5	368.9	369.3	369.7
140°	380.8	381.0	381.1	381.3	381.6	381.8	382.0	382.3	382.7	383.0	383.3
142.5°	394.0	394.2	394.3	394.5	394.8	395.0	395.2	395.4	395.7	395.9	396.2
145°	406.4	406.7	406.8	406.9	407.1	407.2	407.4	407.6	407.7	407.9	408.0
147.5°	417.5	417.7	417.8	417.9	418.1	418.2	418.4	418.6	418.8	418.9	419.1
150°	427.6	427.7	427.8	427.9	428.1	428.2	428.4	428.6	428.8	428.9	429.1
152.5°	436.6	436.6	436.6	436.7	436.8	436.9	437.0	437.3	437.6	437.9	438.2
155°	444.6	444.5	444.5	444.6	444.7	444.8	444.9	445.3	445.7	446.0	446.4
157.5°	452.4	452.4	452.4	452.3	452.2	452.1	452.0	452.5	452.9	453.4	453.9
160°	458.4	458.4	458.4	458.3	458.2	458.2	458.1	458.6	459.0	459.5	460.0
162.5°	463.9	463.8	463.8	463.7	463.6	463.5	463.4	464.0	464.5	465.1	465.6
165°	468.5	468.4	468.4	468.3	468.2	468.2	468.1	468.7	469.3	470.0	470.6
167.5°	472.2	472.0	472.0	472.0	472.0	472.0	472.0	472.6	473.3	473.9	474.6
170°	475.4	475.2	475.2	475.2	475.2	475.2	475.2	475.8	476.5	477.1	477.8
172.5°	477.2	477.0	477.0	477.1	477.2	477.3	477.4	478.0	478.6	479.3	479.9
175°	479.0	478.8	478.8	478.9	479.0	479.0	479.1	479.7	480.2	480.8	481.3
177.5°	479.7	479.5	479.5	479.6	479.7	479.7	479.8	480.4	481.1	481.7	482.4
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	10.0	10.1	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	10.0
92.5°	11.8	11.8	11.9	12.0	12.0	12.1	12.0	12.0	11.9	11.8	11.8
95°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6
97.5°	14.3	14.3	14.4	14.5	14.5	14.6	14.5	14.5	14.4	14.3	14.3
100°	14.6	14.6	14.7	14.8	14.9	15.0	14.9	14.8	14.7	14.6	14.6
102.5°	14.6	14.7	14.9	15.0	15.2	15.4	15.2	15.0	14.9	14.7	14.6
105°	15.0	15.1	15.2	15.4	15.5	15.7	15.5	15.4	15.2	15.1	15.0
107.5°	83.9	78.7	68.3	57.9	47.5	37.1	47.5	57.9	68.3	78.7	83.9
110°	149.2	143.5	132.2	120.9	109.5	98.2	109.5	120.9	132.2	143.5	149.2

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	186.7	186.6	186.5	186.3	186.2	186.0	186.2	186.3	186.5	186.6	186.7
115°	208.5	208.7	209.0	209.3	209.6	209.9	209.6	209.3	209.0	208.7	208.5
117.5°	228.9	228.9	229.0	229.1	229.1	229.2	229.1	229.1	229.0	228.9	228.9
120°	249.2	249.2	249.2	249.2	249.2	249.2	249.2	249.2	249.2	249.2	249.2
122.5°	268.5	268.5	268.6	268.7	268.7	268.8	268.7	268.7	268.6	268.5	268.5
125°	286.3	286.4	286.6	286.7	286.9	287.1	286.9	286.7	286.6	286.4	286.3
127.5°	305.6	305.5	305.4	305.2	305.1	304.9	305.1	305.2	305.4	305.5	305.6
130°	322.8	322.7	322.5	322.4	322.2	322.0	322.2	322.4	322.5	322.7	322.8
132.5°	338.8	338.7	338.5	338.2	338.0	337.8	338.0	338.2	338.5	338.7	338.8
135°	354.9	354.8	354.5	354.3	354.0	353.8	354.0	354.3	354.5	354.8	354.9
137.5°	369.9	369.8	369.7	369.5	369.4	369.2	369.4	369.5	369.7	369.8	369.9
140°	383.5	383.4	383.2	383.1	382.9	382.7	382.9	383.1	383.2	383.4	383.5
142.5°	396.3	396.2	395.9	395.7	395.4	395.2	395.4	395.7	395.9	396.2	396.3
145°	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1
147.5°	419.2	419.0	418.6	418.2	417.8	417.4	417.8	418.2	418.6	419.0	419.2
150°	429.2	429.1	428.8	428.6	428.3	428.1	428.3	428.6	428.8	429.1	429.2
152.5°	438.4	438.2	437.8	437.4	437.0	436.6	437.0	437.4	437.8	438.2	438.4
155°	446.6	446.4	445.9	445.4	445.0	444.5	445.0	445.4	445.9	446.4	446.6
157.5°	454.1	453.8	453.2	452.5	451.9	451.3	451.9	452.5	453.2	453.8	454.1
160°	460.2	459.9	459.4	458.8	458.3	457.7	458.3	458.8	459.4	459.9	460.2
162.5°	465.9	465.7	465.2	464.7	464.3	463.8	464.3	464.7	465.2	465.7	465.9
165°	470.9	470.6	470.1	469.5	469.0	468.4	469.0	469.5	470.1	470.6	470.9
167.5°	474.9	474.6	473.9	473.3	472.6	472.0	472.6	473.3	473.9	474.6	474.9
170°	478.1	477.8	477.1	476.5	475.8	475.2	475.8	476.5	477.1	477.8	478.1
172.5°	480.2	479.8	479.1	478.4	477.7	477.0	477.7	478.4	479.1	479.8	480.2
175°	481.6	481.3	480.7	480.0	479.4	478.8	479.4	480.0	480.7	481.3	481.6
177.5°	482.7	482.3	481.5	480.7	479.9	479.1	479.9	480.7	481.5	482.3	482.7
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	9.8	9.5	9.2	8.9	8.6	7.6	6.5	5.5	4.4	3.9	3.5
92.5°	11.5	11.0	10.4	9.9	9.3	8.6	7.9	7.2	6.5	6.1	6.3
95°	13.3	12.8	12.2	11.7	11.1	10.2	9.3	8.4	7.5	7.1	8.7
97.5°	14.0	13.3	12.7	12.0	11.4	15.4	19.5	23.5	27.6	29.6	30.7
100°	14.3	13.7	13.0	12.4	11.8	24.2	36.6	48.9	61.3	67.5	66.7
102.5°	15.9	18.5	21.2	23.8	26.4	40.2	54.0	67.8	81.6	88.5	88.0
105°	22.0	36.1	50.1	64.2	78.2	85.3	92.5	99.6	106.7	110.3	109.9
107.5°	90.0	102.2	114.5	126.7	138.9	137.7	136.5	135.3	134.1	133.5	133.1
110°	150.5	153.1	155.8	158.4	161.0	160.1	159.3	158.4	157.5	157.1	156.8

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	186.3	185.6	184.9	184.2	183.5	182.6	181.8	180.9	180.0	179.6	179.3
115°	208.1	207.3	206.5	205.7	204.9	204.2	203.5	202.8	202.1	201.7	201.5
117.5°	228.6	227.9	227.3	226.6	226.0	225.6	225.2	224.8	224.4	224.2	223.9
120°	248.9	248.3	247.6	247.0	246.4	246.2	245.9	245.7	245.4	245.3	244.9
122.5°	268.3	267.9	267.5	267.1	266.7	266.4	266.1	265.8	265.5	265.3	265.0
125°	286.2	286.1	285.9	285.8	285.6	285.3	285.0	284.7	284.4	284.2	283.9
127.5°	305.5	305.2	305.0	304.7	304.5	304.1	303.7	303.4	303.0	302.8	302.5
130°	322.6	322.3	322.0	321.6	321.3	321.0	320.7	320.4	320.1	319.9	319.6
132.5°	338.6	338.3	338.0	337.7	337.4	337.2	336.9	336.7	336.4	336.3	336.0
135°	354.8	354.5	354.3	354.0	353.8	353.5	353.2	352.9	352.6	352.4	352.2
137.5°	369.7	369.3	368.9	368.5	368.1	367.9	367.8	367.6	367.5	367.4	367.1
140°	383.3	383.0	382.7	382.3	382.0	381.8	381.6	381.3	381.1	381.0	380.8
142.5°	396.2	395.9	395.7	395.4	395.2	395.0	394.8	394.5	394.3	394.2	394.0
145°	408.0	407.9	407.7	407.6	407.4	407.2	407.1	406.9	406.8	406.7	406.4
147.5°	419.1	418.9	418.8	418.6	418.4	418.2	418.1	417.9	417.8	417.7	417.5
150°	429.1	428.9	428.8	428.6	428.4	428.2	428.1	427.9	427.8	427.7	427.6
152.5°	438.2	437.9	437.6	437.3	437.0	436.9	436.8	436.7	436.6	436.6	436.6
155°	446.4	446.0	445.7	445.3	444.9	444.8	444.7	444.6	444.5	444.5	444.6
157.5°	453.9	453.4	452.9	452.5	452.0	452.1	452.2	452.3	452.4	452.4	452.4
160°	460.0	459.5	459.0	458.6	458.1	458.2	458.2	458.3	458.4	458.4	458.4
162.5°	465.6	465.1	464.5	464.0	463.4	463.5	463.6	463.7	463.8	463.8	463.9
165°	470.6	470.0	469.3	468.7	468.1	468.2	468.2	468.3	468.4	468.4	468.5
167.5°	474.6	473.9	473.3	472.6	472.0	472.0	472.0	472.0	472.0	472.0	472.2
170°	477.8	477.1	476.5	475.8	475.2	475.2	475.2	475.2	475.2	475.2	475.4
172.5°	479.9	479.3	478.6	478.0	477.4	477.3	477.2	477.1	477.0	477.0	477.2
175°	481.3	480.8	480.2	479.7	479.1	479.0	479.0	478.9	478.8	478.8	479.0
177.5°	482.4	481.7	481.1	480.4	479.8	479.7	479.7	479.6	479.5	479.5	479.7
180°	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6	480.6

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	2.7	2.0	1.2	0.4
92.5°	6.8	7.3	7.7	8.2
95°	12.0	15.3	18.5	21.8
97.5°	32.9	35.2	37.4	39.6
100°	65.1	63.5	61.9	60.3
102.5°	87.0	85.9	84.9	83.9
105°	109.0	108.1	107.3	106.4
107.5°	132.4	131.7	131.0	130.3
110°	156.1	155.5	154.8	154.2

TEST NUMBER: P1011565

CATALOG NUMBER: S123DIP-B340D365UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	178.8	178.2	177.7	177.1
115°	201.0	200.5	200.1	199.6
117.5°	223.4	222.8	222.3	221.7
120°	244.2	243.5	242.8	242.1
122.5°	264.5	263.9	263.4	262.8
125°	283.2	282.6	281.9	281.3
127.5°	301.8	301.2	300.5	299.9
130°	318.9	318.3	317.6	317.0
132.5°	335.4	334.7	334.1	333.5
135°	351.7	351.2	350.7	350.2
137.5°	366.4	365.8	365.1	364.5
140°	380.3	379.8	379.3	378.8
142.5°	393.5	393.0	392.5	392.0
145°	405.9	405.3	404.8	404.2
147.5°	417.1	416.7	416.3	415.9
150°	427.4	427.1	426.9	426.7
152.5°	436.5	436.4	436.4	436.3
155°	444.7	444.9	445.0	445.2
157.5°	452.4	452.4	452.4	452.4
160°	458.5	458.6	458.7	458.8
162.5°	464.2	464.4	464.7	464.9
165°	468.8	469.0	469.3	469.5
167.5°	472.5	472.8	473.1	473.4
170°	475.7	476.0	476.3	476.6
172.5°	477.6	478.0	478.4	478.8
175°	479.4	479.8	480.2	480.6
177.5°	480.1	480.5	480.9	481.3
180°	480.6	480.6	480.6	480.6

(END OF REPORT)