

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011861

Luminaire Tested: S123DIP-B560D805UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011861
REPORT IS A COMBINATION OF REPORTS P990167 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB27-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5110.6 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011861

CATALOG NUMBER: S123DIP-B560D805UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011861

CATALOG NUMBER: S123DIP-B560D805UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1011861

CATALOG NUMBER: S123DIP-B560D805UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.6
10°-20°	234.1	4.6
20°-30°	345.8	6.8
30°-40°	403.8	7.9
40°-50°	406.0	7.9
50°-60°	356.6	7.0
60°-70°	265.6	5.2
70°-80°	151.1	3.0
80°-90°	45.1	0.9
90°-100°	212.5	4.2
100°-110°	594.0	11.6
110°-120°	579.2	11.3
120°-130°	461.2	9.0
130°-140°	364.0	7.1
140°-150°	271.6	5.3
150°-160°	189.5	3.7
160°-170°	111.3	2.2
170°-180°	36.2	0.7
0°-30°	662.8	13.0
0°-40°	1066.7	20.9
0°-60°	1829.3	35.8
0°-90°	2291.1	44.8
90°-120°	1385.7	27.1
90°-150°	2482.5	48.6
90°-180°	2819.0	55.2
0°-180°	5110.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	2	9	19	21	22	5
95°	26	84	449	131	88	27
105°	88	130	609	1064	963	93
115°	155	193	466	1021	1171	154
125°	216	255	434	787	924	192
135°	253	302	428	648	749	195
145°	288	330	423	532	585	181
155°	328	354	410	466	485	151
165°	358	368	392	416	423	101
175°	373	374	376	382	381	35
180°	374	374	374	374	374	

TEST NUMBER: P1011861

CATALOG NUMBER: S123DIP-B560D805UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	1.5	9.0	18.9	21.2	22.0
92.5°	11.4	45.4	140.8	48.0	40.1
95°	25.7	83.6	448.9	131.0	87.8
97.5°	40.9	95.8	690.4	329.2	180.2
100°	56.0	105.6	716.9	688.8	474.6
102.5°	71.9	117.0	667.7	922.4	751.7
105°	87.8	129.8	608.6	1064.4	962.9
107.5°	104.5	145.0	556.4	1126.8	1100.7
110°	122.6	160.5	513.2	1128.7	1179.4

TEST NUMBER: P1011861

CATALOG NUMBER: S123DIP-B560D805UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.3	176.8	484.5	1086.0	1195.3
115°	155.2	193.4	465.6	1020.8	1171.1
117.5°	171.1	209.3	452.7	951.2	1118.1
120°	187.7	225.2	444.4	885.3	1048.4
122.5°	202.1	240.4	439.1	833.4	983.3
125°	215.7	254.7	434.5	787.3	923.5
127.5°	226.3	268.4	432.2	749.4	872.1
130°	236.2	280.4	430.0	714.6	829.7
132.5°	243.8	291.5	429.2	682.0	788.0
135°	252.8	301.6	428.5	648.3	748.7
137.5°	261.2	310.0	426.9	616.6	707.0
140°	269.5	317.6	426.2	585.6	663.1
142.5°	278.6	324.4	424.7	557.2	622.2
145°	288.4	330.4	423.2	531.8	585.2
147.5°	298.3	336.8	420.9	512.2	553.4
150°	308.1	342.2	417.9	494.7	526.1
152.5°	317.9	347.8	414.1	479.6	503.4
155°	327.8	353.5	409.5	465.6	485.2
157.5°	335.3	358.5	405.7	451.9	467.8
160°	344.4	362.6	401.2	439.4	451.2
162.5°	351.2	365.6	396.7	427.7	436.0
165°	358.1	368.2	392.1	416.0	423.2
167.5°	363.4	370.5	387.6	405.8	410.3
170°	367.9	371.6	383.0	396.6	398.9
172.5°	370.9	372.8	379.3	388.7	388.3
175°	373.2	373.6	376.2	381.5	380.8
177.5°	374.7	374.0	374.0	377.0	375.5
180°	374.0	374.0	374.0	374.0	374.0

(END OF REPORT)