

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011592

Luminaire Tested: S123DIP-B340D585UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011592
REPORT IS A COMBINATION OF REPORTS P989800 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB27-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3401.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	80	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4997	4997	4997	4997
5°	4999	5757	5014	4297
10°	4968	6966	4973	3752
15°	4899	8262	4939	3377
20°	4840	9512	4850	3108
25°	4752	9752	4763	2967
30°	4690	8057	4690	2875
35°	4612	5388	4583	2793
40°	4520	3889	4463	2669
45°	4402	3081	4276	2514
50°	4117	2616	3971	2362
55°	3807	2299	3651	2192
60°	3489	2002	3304	2013
65°	3143	1714	2990	1775
70°	2783	1423	2597	1498
75°	2377	1073	2225	1156
80°	1878	717	1732	759
85°	1297	328	1037	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8059 cd/sqm

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	1.3
10°-20°	146.6	4.3
20°-30°	246.7	7.3
30°-40°	278.8	8.2
40°-50°	249.7	7.3
50°-60°	201.6	5.9
60°-70°	140.5	4.1
70°-80°	73.7	2.2
80°-90°	19.2	0.6
90°-100°	46.4	1.4
100°-110°	140.5	4.1
110°-120°	239.2	7.0
120°-130°	314.7	9.3
130°-140°	353.8	10.4
140°-150°	347.8	10.2
150°-160°	292.8	8.6
160°-170°	194.9	5.7
170°-180°	68.3	2.0
0°-30°	439.0	12.9
0°-40°	717.8	21.1
0°-60°	1169.1	34.4
0°-90°	1402.5	41.2
90°-120°	426.2	12.5
90°-150°	1442.5	42.4
90°-180°	1998.0	58.7
0°-180°	3401.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	464	464	464	464	464	
5°	464	552	465	412	464	44
15°	443	821	446	336	443	125
25°	405	974	406	296	405	187
35°	357	525	355	272	357	224
45°	296	283	288	231	296	227
55°	210	192	202	184	210	188
65°	130	125	124	130	130	129
75°	62	64	58	69	62	67
85°	14	15	11	14	14	16
90°	1	17	1	17	1	3
95°	33	44	33	44	33	37
105°	128	135	128	135	128	136
115°	241	241	241	241	241	238
125°	352	348	352	348	352	314
135°	457	457	457	457	457	352
145°	555	555	555	555	555	346
155°	635	634	635	634	635	292
165°	692	690	692	690	692	195
175°	720	717	720	717	720	68
180°	721	721	721	721	721	

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	465.5	469.1	470.9	473.6	476.3	480.4	481.7	484.0	483.1	484.9	485.8
5°	463.7	470.0	475.4	482.2	488.5	493.0	497.5	504.7	510.1	511.0	515.0
7.5°	460.6	469.6	479.0	488.5	500.6	507.8	515.9	525.8	533.9	547.0	551.9
10°	456.5	469.1	482.6	495.7	512.3	523.6	533.5	550.1	566.7	580.2	592.8
12.5°	450.2	466.0	483.5	502.9	524.5	537.5	551.0	573.0	598.2	618.9	632.4
15°	442.6	462.4	484.9	505.6	529.4	553.7	568.1	592.8	628.8	648.2	682.8
17.5°	436.3	456.5	479.0	511.4	543.8	568.1	578.4	623.9	648.6	681.0	720.1
20°	426.4	452.0	480.8	513.2	555.0	569.9	591.0	636.9	667.5	709.8	757.9
22.5°	416.1	443.5	478.1	511.9	558.6	574.4	603.2	639.6	688.2	730.0	783.1
25°	404.8	434.5	469.6	509.6	555.5	578.4	605.4	650.4	703.0	755.7	804.7
27.5°	393.6	426.0	462.4	502.4	547.0	573.9	600.9	647.7	715.2	772.3	834.8
30°	382.8	415.2	451.6	492.5	539.3	565.4	591.0	649.5	724.6	788.9	851.9
32.5°	371.1	404.4	442.6	476.8	524.0	551.9	580.7	649.5	730.5	798.8	856.4
35°	357.1	391.3	424.2	458.3	505.1	536.2	568.5	645.0	735.9	802.0	837.5
37.5°	343.6	373.8	402.1	435.4	484.4	517.7	555.0	639.6	733.2	788.5	798.4
40°	328.4	358.5	381.4	412.5	464.2	502.9	540.7	632.4	721.5	756.6	727.8
42.5°	313.5	337.3	357.1	387.3	443.5	481.3	522.2	619.4	698.5	705.7	641.0
45°	296.4	313.5	331.1	365.2	421.0	459.7	505.1	600.5	661.7	641.0	559.1
47.5°	274.4	289.7	309.0	340.5	397.2	437.2	480.4	576.2	608.1	564.9	475.4
50°	253.2	266.3	284.3	314.9	372.0	411.1	457.0	538.0	553.7	485.8	409.8
52.5°	232.1	242.0	259.5	290.1	347.2	385.0	426.9	498.8	489.8	417.0	349.5
55°	210.1	218.6	235.2	265.4	318.5	354.4	394.5	450.7	427.3	358.0	304.1
57.5°	188.5	197.5	214.6	239.7	289.7	324.8	356.7	400.8	365.7	310.4	262.7
60°	169.1	176.8	189.8	214.6	260.0	288.3	317.6	347.7	318.5	264.9	228.5
62.5°	148.9	156.1	168.2	190.7	229.8	255.0	278.4	303.2	270.8	231.6	199.3
65°	130.0	135.8	147.1	167.8	199.7	220.4	239.3	256.4	230.3	194.3	170.0
67.5°	112.9	117.8	127.3	145.7	172.7	187.6	202.9	217.3	195.2	166.4	145.7
70°	94.5	98.5	107.1	120.5	142.1	157.4	168.7	179.5	159.7	136.7	122.8
72.5°	78.3	82.3	87.7	101.7	116.5	125.9	138.1	143.9	132.7	113.8	99.9
75°	62.5	65.7	70.6	79.6	93.6	99.9	107.5	112.0	101.7	89.1	80.5
77.5°	49.0	50.4	54.0	60.3	69.7	76.9	82.8	85.5	78.3	70.2	63.0
80°	34.6	36.4	39.1	44.5	51.7	54.0	57.6	60.7	56.2	49.0	44.5
82.5°	22.9	25.2	26.5	28.8	33.3	36.0	36.9	39.6	35.5	32.8	31.0
85°	13.5	14.4	14.8	16.2	18.4	19.8	21.1	21.6	20.7	20.2	18.4
87.5°	6.7	6.7	6.7	7.6	8.1	9.0	9.4	9.4	9.4	9.0	8.5
90°	0.6	1.8	3.1	4.3	5.6	6.2	7.0	8.7	10.3	12.0	13.6
92.5°	17.0	17.8	18.5	19.3	20.0	20.4	20.8	21.5	22.3	23.0	23.8
95°	33.4	34.3	35.2	36.1	37.0	37.4	37.9	38.9	39.9	40.9	41.9
97.5°	55.0	55.6	56.2	56.9	57.5	57.8	58.2	58.9	59.7	60.4	61.2
100°	77.1	77.9	78.6	79.4	80.1	80.5	80.8	81.4	82.1	82.7	83.3
102.5°	102.6	103.0	103.4	103.7	104.1	104.3	104.7	105.6	106.5	107.3	108.2
105°	127.5	127.7	128.0	128.2	128.5	128.6	129.2	130.3	131.4	132.6	133.7
107.5°	156.9	157.0	157.2	157.3	157.4	157.5	157.8	158.3	158.8	159.3	159.8
110°	184.1	184.4	184.6	184.9	185.2	185.3	185.4	185.7	185.9	186.2	186.4

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	212.5	212.6	212.7	212.8	212.9	213.0	213.0	213.0	213.0	213.0	213.0
115°	240.8	241.2	241.6	241.9	242.3	242.5	242.4	242.1	241.9	241.6	241.4
117.5°	269.7	269.8	270.0	270.1	270.2	270.3	270.2	269.9	269.6	269.4	269.1
120°	296.3	297.1	297.8	298.6	299.3	299.7	299.4	298.8	298.1	297.5	296.9
122.5°	324.1	324.6	325.1	325.6	326.1	326.4	326.3	326.0	325.7	325.5	325.2
125°	352.4	352.8	353.2	353.5	353.9	354.1	354.0	353.7	353.5	353.2	353.0
127.5°	378.5	379.3	380.0	380.8	381.5	381.9	381.8	381.5	381.2	381.0	380.7
130°	404.5	405.5	406.5	407.6	408.6	409.1	408.9	408.5	408.2	407.8	407.4
132.5°	430.6	431.6	432.6	433.6	434.6	435.1	435.0	434.7	434.5	434.2	434.0
135°	457.2	458.0	458.7	459.5	460.2	460.6	460.5	460.4	460.3	460.2	460.1
137.5°	481.6	482.2	482.8	483.5	484.1	484.4	484.6	485.0	485.3	485.7	486.1
140°	507.1	507.7	508.3	509.0	509.6	509.9	510.0	510.1	510.2	510.4	510.5
142.5°	530.3	530.9	531.6	532.2	532.9	533.2	533.3	533.6	533.8	534.1	534.3
145°	554.7	554.9	555.2	555.4	555.7	555.8	556.0	556.4	556.7	557.1	557.5
147.5°	575.6	576.1	576.6	577.1	577.6	577.9	578.1	578.5	578.8	579.2	579.6
150°	597.7	598.0	598.2	598.5	598.8	598.9	599.0	599.3	599.5	599.8	600.0
152.5°	615.9	616.3	616.7	617.0	617.4	617.6	617.7	617.8	617.9	618.0	618.1
155°	635.1	635.1	635.1	635.1	635.1	635.1	635.2	635.3	635.4	635.6	635.7
157.5°	651.6	651.5	651.3	651.2	651.1	651.0	651.1	651.2	651.3	651.5	651.6
160°	666.9	666.6	666.4	666.1	665.8	665.7	665.7	665.7	665.7	665.7	665.7
162.5°	680.5	680.1	679.7	679.4	679.0	678.8	678.9	679.0	679.1	679.2	679.3
165°	691.8	691.4	691.0	690.7	690.3	690.1	690.1	690.1	690.1	690.1	690.1
167.5°	701.4	700.9	700.4	699.9	699.4	699.2	699.3	699.4	699.5	699.6	699.7
170°	709.4	708.9	708.4	707.9	707.4	707.1	707.1	707.1	707.1	707.1	707.1
172.5°	715.6	715.1	714.6	714.1	713.6	713.3	713.3	713.3	713.3	713.3	713.3
175°	719.6	719.1	718.6	718.1	717.6	717.3	717.3	717.3	717.3	717.3	717.3
177.5°	721.8	721.3	720.8	720.3	719.8	719.6	719.6	719.6	719.6	719.6	719.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	488.9	489.8	493.0	495.2	499.7	499.3	499.3	498.8	497.5	499.7	501.1
5°	523.1	530.8	531.7	541.6	542.0	546.1	548.8	546.5	551.9	551.5	547.4
7.5°	565.4	575.7	580.7	590.1	600.9	598.2	608.6	610.4	609.5	614.0	617.1
10°	611.7	629.7	642.3	659.9	664.3	667.0	673.8	679.6	691.3	682.3	688.2
12.5°	664.8	677.8	694.5	722.4	736.3	745.3	748.5	752.5	760.6	755.7	756.1
15°	709.3	726.9	755.2	789.8	793.9	805.1	802.4	826.7	838.4	820.9	830.8
17.5°	755.7	779.0	812.8	842.9	860.0	867.7	874.9	898.2	897.3	894.6	896.9
20°	785.3	823.6	865.4	905.4	910.4	916.2	935.6	945.5	943.7	951.3	956.3
22.5°	827.2	867.7	912.2	938.7	950.0	956.7	972.0	978.3	981.0	982.8	979.7
25°	862.3	905.4	938.3	961.7	968.4	972.0	977.0	978.8	977.4	974.3	977.0
27.5°	886.1	920.7	943.2	954.0	950.4	944.6	935.1	928.8	914.9	908.1	916.2
30°	896.0	911.3	918.0	900.0	882.1	867.7	849.7	816.4	790.3	797.9	787.6
32.5°	880.3	870.4	838.0	791.6	777.7	754.3	703.5	664.3	665.7	645.0	653.6
35°	833.9	788.9	727.8	657.6	639.2	626.6	570.8	562.2	544.3	524.9	530.3
37.5°	752.1	686.4	612.2	560.4	533.0	505.6	474.1	455.2	444.4	436.3	442.6
40°	652.2	572.1	511.0	464.6	441.3	423.7	402.1	383.2	371.1	369.7	372.0
42.5°	554.1	486.7	430.5	386.4	378.7	358.0	344.1	329.3	325.7	319.8	323.0
45°	469.1	414.3	367.9	331.9	323.0	317.6	300.5	291.0	287.0	283.4	288.8
47.5°	407.5	349.9	316.2	294.6	285.6	276.6	267.2	260.9	257.7	258.2	257.7
50°	348.1	305.9	276.2	259.5	254.1	247.8	240.2	236.1	234.8	230.7	233.9
52.5°	299.6	269.0	248.3	232.5	228.5	224.0	217.7	215.5	212.3	211.4	211.4
55°	260.4	236.6	220.0	209.6	204.7	201.1	197.5	194.8	192.5	192.5	192.5
57.5°	229.8	209.2	197.0	188.0	186.2	182.6	178.6	178.6	175.4	175.0	176.3
60°	203.8	185.3	175.9	168.2	165.5	164.6	160.6	160.6	159.7	157.4	159.2
62.5°	177.2	163.7	155.6	149.8	147.1	147.1	143.9	141.7	141.7	142.1	141.2
65°	152.9	143.0	135.8	131.3	130.0	128.2	127.7	125.9	124.6	125.0	124.6
67.5°	131.3	123.7	118.7	115.1	112.9	112.0	110.6	110.6	109.8	110.2	108.0
70°	112.0	104.4	100.3	96.7	95.8	95.8	94.0	94.5	93.6	94.9	94.0
72.5°	92.2	86.4	83.2	81.9	81.0	80.5	79.6	78.7	78.3	79.2	78.7
75°	74.7	69.7	67.5	66.6	65.7	65.7	65.2	64.8	64.3	64.3	64.3
77.5°	58.0	54.9	52.2	53.1	51.7	52.2	50.8	50.8	51.3	50.8	50.8
80°	42.7	40.5	40.5	39.6	37.8	38.7	38.7	37.3	36.9	37.8	36.4
82.5°	28.3	27.9	27.0	26.5	25.6	26.1	25.6	25.2	24.7	25.6	24.7
85°	16.6	16.6	16.2	15.3	16.2	15.7	15.3	15.3	14.8	14.8	14.8
87.5°	8.5	7.6	7.6	7.2	7.6	6.7	7.2	6.7	6.3	6.7	6.3
90°	14.1	14.6	15.1	15.6	15.9	16.0	16.3	16.5	16.8	17.0	16.8
92.5°	24.2	24.6	24.9	25.3	25.5	25.4	25.1	24.9	24.6	24.4	24.6
95°	42.4	42.9	43.4	43.9	44.2	44.2	44.2	44.2	44.2	44.2	44.2
97.5°	61.8	62.4	63.1	63.7	64.0	63.9	63.8	63.7	63.6	63.5	63.6
100°	83.7	84.1	84.4	84.8	85.0	85.1	85.4	85.6	85.9	86.1	85.9
102.5°	108.6	109.0	109.3	109.7	109.9	109.8	109.7	109.6	109.5	109.4	109.5
105°	133.7	133.7	133.7	133.7	133.7	133.8	134.1	134.3	134.6	134.8	134.6
107.5°	160.2	160.6	160.9	161.3	161.5	161.4	161.3	161.2	161.0	160.9	161.0
110°	186.9	187.4	187.9	188.4	188.7	188.6	188.3	188.0	187.8	187.5	187.8

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	213.6	214.3	214.9	215.6	215.9	215.9	215.9	215.9	215.9	215.9	215.9
115°	241.5	241.6	241.7	241.8	241.9	241.8	241.7	241.6	241.5	241.4	241.5
117.5°	269.1	269.1	269.1	269.1	269.1	268.9	268.5	268.2	267.8	267.4	267.8
120°	296.8	296.6	296.5	296.4	296.3	296.2	295.9	295.7	295.4	295.2	295.4
122.5°	324.8	324.4	324.1	323.7	323.5	323.3	322.9	322.6	322.2	321.8	322.2
125°	352.5	352.0	351.5	351.0	350.7	350.4	349.9	349.4	348.9	348.4	348.9
127.5°	379.9	379.2	378.4	377.7	377.3	377.1	376.6	376.1	375.6	375.1	375.6
130°	406.9	406.4	405.9	405.4	405.1	404.7	403.8	402.9	402.0	401.1	402.0
132.5°	433.4	432.8	432.1	431.5	431.2	430.9	430.2	429.6	428.9	428.3	428.9
135°	459.6	459.1	458.6	458.1	457.8	457.7	457.4	457.2	456.9	456.7	456.9
137.5°	485.5	484.9	484.2	483.6	483.3	483.1	482.7	482.4	482.0	481.6	482.0
140°	510.4	510.2	510.1	510.0	509.9	509.5	508.6	507.7	506.9	506.0	506.9
142.5°	534.2	534.0	533.9	533.8	533.7	533.4	532.8	532.1	531.5	530.9	531.5
145°	557.4	557.2	557.1	557.0	556.9	556.7	556.2	555.7	555.2	554.7	555.2
147.5°	579.6	579.6	579.6	579.6	579.6	579.2	578.5	577.7	577.0	576.2	577.0
150°	600.0	600.0	600.0	600.0	600.0	599.6	598.9	598.1	597.4	596.6	597.4
152.5°	618.4	618.6	618.9	619.2	619.3	619.0	618.3	617.7	617.0	616.4	617.0
155°	636.2	636.7	637.2	637.7	638.0	637.6	636.7	635.8	634.9	634.0	634.9
157.5°	652.1	652.6	653.1	653.6	653.8	653.4	652.7	651.9	651.2	650.4	651.2
160°	666.3	667.0	667.6	668.3	668.6	668.3	667.8	667.3	666.8	666.3	666.8
162.5°	679.9	680.6	681.2	681.9	682.2	681.8	680.9	680.0	679.1	678.2	679.1
165°	690.9	691.6	692.4	693.1	693.5	693.1	692.2	691.3	690.4	689.5	690.4
167.5°	700.5	701.2	702.0	702.7	703.1	702.7	702.0	701.2	700.5	699.7	700.5
170°	708.0	708.9	709.8	710.7	711.1	710.7	709.8	708.9	708.0	707.1	708.0
172.5°	714.1	714.8	715.6	716.3	716.7	716.3	715.4	714.5	713.7	712.8	713.7
175°	718.1	718.8	719.6	720.3	720.7	720.3	719.4	718.5	717.6	716.7	717.6
177.5°	720.4	721.1	721.9	722.6	723.0	722.6	721.7	720.8	719.9	719.0	719.9
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	497.5	498.8	495.2	494.3	494.3	496.1	494.8	482.6	484.9	482.2	481.3
5°	552.4	549.7	546.1	544.3	542.0	535.7	535.3	521.3	518.6	509.6	505.6
7.5°	612.6	610.4	599.6	598.2	597.3	591.5	576.6	561.8	551.0	540.7	530.8
10°	681.4	674.7	669.7	659.9	654.9	646.8	627.5	613.5	595.1	579.3	558.6
12.5°	764.2	756.6	739.9	732.7	726.4	703.9	684.6	668.8	632.9	622.1	596.4
15°	824.9	808.7	806.9	791.2	790.3	765.6	728.7	711.6	683.7	644.1	617.6
17.5°	890.6	876.2	865.0	846.1	843.4	820.0	793.0	751.2	720.6	682.8	649.1
20°	938.7	931.1	911.7	904.1	888.3	868.6	840.7	788.9	751.6	713.8	672.4
22.5°	977.0	969.3	954.0	943.7	934.7	909.0	875.8	831.7	780.4	730.9	688.2
25°	976.5	974.3	968.0	963.0	956.3	937.4	909.5	867.2	810.1	755.7	696.3
27.5°	921.2	927.5	938.3	943.7	942.3	939.6	923.9	888.3	837.1	772.3	705.7
30°	806.0	829.0	849.2	876.2	884.3	904.1	913.1	892.8	851.9	791.6	717.9
32.5°	668.4	701.7	745.8	760.6	786.2	824.5	867.2	874.9	849.2	802.9	725.5
35°	548.3	575.7	609.9	633.3	656.3	718.3	772.3	819.1	827.6	797.0	723.7
37.5°	453.8	473.2	503.3	523.1	544.3	597.3	672.9	733.6	776.3	777.2	718.8
40°	385.5	394.0	420.1	434.5	454.7	500.6	568.1	647.3	709.8	738.6	705.7
42.5°	326.6	337.8	359.4	370.2	383.2	423.3	467.8	542.9	620.3	681.9	681.4
45°	291.5	299.6	309.5	318.5	333.3	357.1	408.0	464.2	538.4	608.1	635.6
47.5°	260.4	268.1	278.0	280.7	290.6	313.1	344.1	393.1	462.4	531.7	583.4
50°	234.3	240.6	247.4	252.3	256.8	275.3	298.7	340.0	395.4	462.4	526.7
52.5°	214.1	218.6	224.4	227.1	231.2	244.7	262.7	293.3	338.7	399.9	462.4
55°	195.2	198.4	202.0	206.5	208.3	218.2	232.1	258.2	291.9	346.8	406.2
57.5°	177.7	179.0	181.3	184.0	186.2	194.8	206.9	224.4	254.1	296.4	352.6
60°	157.9	161.5	162.8	165.5	166.9	173.6	183.1	197.9	220.9	257.3	299.6
62.5°	141.2	143.5	145.7	147.1	150.2	152.5	160.1	173.6	192.5	219.5	257.7
65°	126.4	127.3	128.6	130.0	130.9	133.6	140.8	149.8	164.2	188.0	217.7
67.5°	109.3	110.2	112.0	112.4	113.3	116.9	121.0	128.6	140.8	158.8	183.1
70°	92.7	94.0	94.9	95.8	97.2	98.5	103.0	109.3	118.7	131.3	150.2
72.5°	78.3	79.6	79.6	80.5	80.1	81.9	86.4	90.9	97.2	107.5	124.1
75°	63.9	63.9	64.8	65.2	65.7	67.5	69.3	72.9	77.8	85.9	96.3
77.5°	50.4	49.9	50.8	50.8	50.8	52.2	54.0	55.8	58.9	64.8	72.9
80°	36.9	36.9	37.8	38.2	37.3	37.8	38.7	40.5	42.7	46.8	51.3
82.5°	24.3	26.1	25.6	26.1	25.6	26.5	27.0	27.4	28.3	30.1	33.3
85°	14.8	14.8	14.8	15.3	14.8	15.3	15.3	15.3	15.7	16.6	18.0
87.5°	6.3	6.3	6.3	6.7	6.3	6.3	6.7	6.3	6.7	6.7	7.2
90°	16.5	16.3	16.0	15.9	15.6	15.1	14.6	14.1	13.6	12.0	10.3
92.5°	24.9	25.1	25.4	25.5	25.3	24.9	24.6	24.2	23.8	23.0	22.3
95°	44.2	44.2	44.2	44.2	43.9	43.4	42.9	42.4	41.9	40.9	39.9
97.5°	63.7	63.8	63.9	64.0	63.7	63.1	62.4	61.8	61.2	60.4	59.7
100°	85.6	85.4	85.1	85.0	84.8	84.4	84.1	83.7	83.3	82.7	82.1
102.5°	109.6	109.7	109.8	109.9	109.7	109.3	109.0	108.6	108.2	107.3	106.5
105°	134.3	134.1	133.8	133.7	133.7	133.7	133.7	133.7	133.7	132.6	131.4
107.5°	161.2	161.3	161.4	161.5	161.3	160.9	160.6	160.2	159.8	159.3	158.8
110°	188.0	188.3	188.6	188.7	188.4	187.9	187.4	186.9	186.4	186.2	185.9

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	215.9	215.9	215.9	215.9	215.6	214.9	214.3	213.6	213.0	213.0	213.0
115°	241.6	241.7	241.8	241.9	241.8	241.7	241.6	241.5	241.4	241.6	241.9
117.5°	268.2	268.5	268.9	269.1	269.1	269.1	269.1	269.1	269.1	269.4	269.6
120°	295.7	295.9	296.2	296.3	296.4	296.5	296.6	296.8	296.9	297.5	298.1
122.5°	322.6	322.9	323.3	323.5	323.7	324.1	324.4	324.8	325.2	325.5	325.7
125°	349.4	349.9	350.4	350.7	351.0	351.5	352.0	352.5	353.0	353.2	353.5
127.5°	376.1	376.6	377.1	377.3	377.7	378.4	379.2	379.9	380.7	381.0	381.2
130°	402.9	403.8	404.7	405.1	405.4	405.9	406.4	406.9	407.4	407.8	408.2
132.5°	429.6	430.2	430.9	431.2	431.5	432.1	432.8	433.4	434.0	434.2	434.5
135°	457.2	457.4	457.7	457.8	458.1	458.6	459.1	459.6	460.1	460.2	460.3
137.5°	482.4	482.7	483.1	483.3	483.6	484.2	484.9	485.5	486.1	485.7	485.3
140°	507.7	508.6	509.5	509.9	510.0	510.1	510.2	510.4	510.5	510.4	510.2
142.5°	532.1	532.8	533.4	533.7	533.8	533.9	534.0	534.2	534.3	534.1	533.8
145°	555.7	556.2	556.7	556.9	557.0	557.1	557.2	557.4	557.5	557.1	556.7
147.5°	577.7	578.5	579.2	579.6	579.6	579.6	579.6	579.6	579.6	579.2	578.8
150°	598.1	598.9	599.6	600.0	600.0	600.0	600.0	600.0	600.0	599.8	599.5
152.5°	617.7	618.3	619.0	619.3	619.2	618.9	618.6	618.4	618.1	618.0	617.9
155°	635.8	636.7	637.6	638.0	637.7	637.2	636.7	636.2	635.7	635.6	635.4
157.5°	651.9	652.7	653.4	653.8	653.6	653.1	652.6	652.1	651.6	651.5	651.3
160°	667.3	667.8	668.3	668.6	668.3	667.6	667.0	666.3	665.7	665.7	665.7
162.5°	680.0	680.9	681.8	682.2	681.9	681.2	680.6	679.9	679.3	679.2	679.1
165°	691.3	692.2	693.1	693.5	693.1	692.4	691.6	690.9	690.1	690.1	690.1
167.5°	701.2	702.0	702.7	703.1	702.7	702.0	701.2	700.5	699.7	699.6	699.5
170°	708.9	709.8	710.7	711.1	710.7	709.8	708.9	708.0	707.1	707.1	707.1
172.5°	714.5	715.4	716.3	716.7	716.3	715.6	714.8	714.1	713.3	713.3	713.3
175°	718.5	719.4	720.3	720.7	720.3	719.6	718.8	718.1	717.3	717.3	717.3
177.5°	720.8	721.7	722.6	723.0	722.6	721.9	721.1	720.4	719.6	719.6	719.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	476.8	475.4	475.4	474.5	471.8	466.9	466.4	467.3	464.6	461.9	457.9
5°	500.2	491.6	488.9	486.2	480.8	471.8	468.2	465.1	460.1	454.3	448.0
7.5°	520.0	507.8	504.2	499.3	488.5	475.9	467.8	461.0	454.3	446.2	438.6
10°	544.7	527.2	518.6	511.4	496.6	479.0	466.9	457.0	446.2	436.3	426.4
12.5°	572.6	544.3	541.6	524.0	506.9	480.8	466.0	451.6	437.2	425.1	414.7
15°	596.0	564.9	553.7	542.0	509.2	476.8	462.4	446.2	429.6	416.5	401.2
17.5°	610.8	585.2	561.3	545.6	511.4	482.6	454.7	436.3	418.8	400.8	388.2
20°	628.8	591.5	570.8	549.7	515.9	478.1	450.2	427.3	405.7	389.5	374.2
22.5°	646.8	596.4	579.3	556.4	516.8	473.6	442.1	419.2	394.5	378.3	361.6
25°	645.0	603.6	575.3	555.9	507.8	469.6	432.7	405.7	382.8	362.1	345.4
27.5°	646.4	595.5	566.7	544.3	501.5	463.7	422.8	394.5	370.6	349.0	331.5
30°	646.8	583.4	558.2	531.2	489.8	449.8	411.6	382.8	357.6	334.2	318.5
32.5°	645.5	573.5	542.0	517.7	471.4	436.3	398.5	367.9	342.3	320.7	305.9
35°	642.3	561.8	525.4	494.8	452.5	417.0	386.4	354.9	327.5	307.7	290.6
37.5°	633.8	549.2	507.8	477.7	430.5	394.5	367.5	341.4	314.9	291.5	277.1
40°	627.5	532.1	490.3	457.4	406.6	371.5	349.0	324.3	298.2	277.1	263.1
42.5°	613.1	515.9	472.3	433.2	383.2	347.2	326.1	306.3	283.8	263.1	250.5
45°	589.7	498.4	450.2	410.7	357.6	323.4	304.1	287.9	268.1	248.3	235.7
47.5°	556.8	473.2	426.9	387.3	332.4	297.8	278.4	266.3	250.5	233.9	223.1
50°	521.3	445.7	403.0	363.9	308.1	274.4	255.5	244.2	233.9	218.6	208.3
52.5°	475.0	416.5	375.6	338.2	282.0	249.6	233.0	224.9	214.1	203.3	194.3
55°	430.0	378.7	345.0	309.5	256.4	226.2	210.1	201.5	195.2	186.2	179.0
57.5°	377.8	343.6	312.6	280.2	232.5	205.1	189.8	179.5	175.4	171.4	164.6
60°	329.7	303.6	278.4	251.4	207.8	183.1	168.2	160.1	156.1	153.4	148.9
62.5°	285.6	265.4	243.8	222.2	182.6	160.1	148.9	140.8	137.2	136.7	132.7
65°	243.3	228.9	211.4	190.3	159.2	139.4	128.6	123.7	119.6	119.6	116.5
67.5°	201.1	191.2	177.2	162.4	138.1	119.6	109.8	105.3	103.0	103.0	100.8
70°	167.3	160.6	148.0	134.9	113.8	99.9	92.2	88.2	86.8	87.3	85.5
72.5°	135.8	128.6	118.3	108.9	93.1	82.8	77.4	72.9	70.6	71.1	70.6
75°	105.3	101.7	92.7	85.5	72.9	65.7	60.7	58.5	56.7	57.1	56.2
77.5°	79.2	73.8	68.8	63.9	56.2	50.4	46.3	44.1	42.7	42.7	42.7
80°	54.0	53.1	49.0	46.3	40.0	35.5	32.4	31.9	30.6	30.6	30.6
82.5°	35.1	32.8	30.6	28.8	25.2	22.5	21.1	20.2	19.8	19.3	20.2
85°	19.3	18.0	17.1	15.3	13.9	12.6	11.2	10.8	10.3	10.8	10.3
87.5°	7.6	6.3	6.3	5.8	5.4	4.9	4.9	4.0	4.0	3.6	3.6
90°	8.7	7.0	6.2	5.6	4.3	3.1	1.8	0.6	1.8	3.1	4.3
92.5°	21.5	20.8	20.4	20.0	19.3	18.5	17.8	17.0	17.8	18.5	19.3
95°	38.9	37.9	37.4	37.0	36.1	35.2	34.3	33.4	34.3	35.2	36.1
97.5°	58.9	58.2	57.8	57.5	56.9	56.2	55.6	55.0	55.6	56.2	56.9
100°	81.4	80.8	80.5	80.1	79.4	78.6	77.9	77.1	77.9	78.6	79.4
102.5°	105.6	104.7	104.3	104.1	103.7	103.4	103.0	102.6	103.0	103.4	103.7
105°	130.3	129.2	128.6	128.5	128.2	128.0	127.7	127.5	127.7	128.0	128.2
107.5°	158.3	157.8	157.5	157.4	157.3	157.2	157.0	156.9	157.0	157.2	157.3
110°	185.7	185.4	185.3	185.2	184.9	184.6	184.4	184.1	184.4	184.6	184.9

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	213.0	213.0	213.0	212.9	212.8	212.7	212.6	212.5	212.6	212.7	212.8
115°	242.1	242.4	242.5	242.3	241.9	241.6	241.2	240.8	241.2	241.6	241.9
117.5°	269.9	270.2	270.3	270.2	270.1	270.0	269.8	269.7	269.8	270.0	270.1
120°	298.8	299.4	299.7	299.3	298.6	297.8	297.1	296.3	297.1	297.8	298.6
122.5°	326.0	326.3	326.4	326.1	325.6	325.1	324.6	324.1	324.6	325.1	325.6
125°	353.7	354.0	354.1	353.9	353.5	353.2	352.8	352.4	352.8	353.2	353.5
127.5°	381.5	381.8	381.9	381.5	380.8	380.0	379.3	378.5	379.3	380.0	380.8
130°	408.5	408.9	409.1	408.6	407.6	406.5	405.5	404.5	405.5	406.5	407.6
132.5°	434.7	435.0	435.1	434.6	433.6	432.6	431.6	430.6	431.6	432.6	433.6
135°	460.4	460.5	460.6	460.2	459.5	458.7	458.0	457.2	458.0	458.7	459.5
137.5°	485.0	484.6	484.4	484.1	483.5	482.8	482.2	481.6	482.2	482.8	483.5
140°	510.1	510.0	509.9	509.6	509.0	508.3	507.7	507.1	507.7	508.3	509.0
142.5°	533.6	533.3	533.2	532.9	532.2	531.6	530.9	530.3	530.9	531.6	532.2
145°	556.4	556.0	555.8	555.7	555.4	555.2	554.9	554.7	554.9	555.2	555.4
147.5°	578.5	578.1	577.9	577.6	577.1	576.6	576.1	575.6	576.1	576.6	577.1
150°	599.3	599.0	598.9	598.8	598.5	598.2	598.0	597.7	598.0	598.2	598.5
152.5°	617.8	617.7	617.6	617.4	617.0	616.7	616.3	615.9	616.3	616.7	617.0
155°	635.3	635.2	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1
157.5°	651.2	651.1	651.0	651.1	651.2	651.3	651.5	651.6	651.5	651.3	651.2
160°	665.7	665.7	665.7	665.8	666.1	666.4	666.6	666.9	666.6	666.4	666.1
162.5°	679.0	678.9	678.8	679.0	679.4	679.7	680.1	680.5	680.1	679.7	679.4
165°	690.1	690.1	690.1	690.3	690.7	691.0	691.4	691.8	691.4	691.0	690.7
167.5°	699.4	699.3	699.2	699.4	699.9	700.4	700.9	701.4	700.9	700.4	699.9
170°	707.1	707.1	707.1	707.4	707.9	708.4	708.9	709.4	708.9	708.4	707.9
172.5°	713.3	713.3	713.3	713.6	714.1	714.6	715.1	715.6	715.1	714.6	714.1
175°	717.3	717.3	717.3	717.6	718.1	718.6	719.1	719.6	719.1	718.6	718.1
177.5°	719.6	719.6	719.6	719.8	720.3	720.8	721.3	721.8	721.3	720.8	720.3
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	457.0	456.5	457.4	454.7	450.2	448.0	441.7	440.4	439.9	440.4	440.8
5°	444.4	443.9	442.6	438.1	432.7	428.7	421.0	420.6	417.9	415.2	416.5
7.5°	432.3	430.5	427.8	421.9	414.7	410.2	403.9	399.4	395.8	393.6	391.8
10°	420.1	417.4	414.7	407.1	398.1	391.3	383.7	380.1	376.0	374.2	372.4
12.5°	404.4	401.7	396.7	387.7	382.3	373.8	366.1	362.5	360.3	356.7	354.4
15°	391.8	386.4	383.7	374.2	363.0	362.1	348.1	347.2	342.7	342.7	339.1
17.5°	377.4	373.3	368.4	358.9	350.8	342.7	335.5	332.8	328.8	327.9	326.1
20°	363.4	358.0	356.2	346.8	338.2	328.4	320.7	318.0	316.2	314.4	315.8
22.5°	349.0	344.5	340.0	331.5	325.2	315.3	310.8	308.1	305.4	304.5	305.0
25°	335.1	331.1	326.6	318.0	311.3	303.2	299.1	297.8	296.4	296.4	296.0
27.5°	321.6	317.6	313.5	305.9	299.1	293.3	290.1	288.8	287.4	288.3	289.2
30°	307.7	304.1	300.5	293.7	288.3	282.9	281.1	280.2	279.8	282.0	282.0
32.5°	295.1	291.9	289.2	282.9	277.5	273.0	271.7	272.1	272.6	273.9	274.8
35°	282.0	279.8	277.1	271.7	267.2	263.1	263.6	263.6	264.5	266.7	268.5
37.5°	270.3	267.2	264.9	260.4	256.8	253.2	254.6	255.9	256.8	259.5	260.4
40°	256.4	255.0	253.2	248.7	245.6	245.1	245.6	246.5	248.3	249.6	251.0
42.5°	245.1	243.3	241.1	237.5	234.8	235.2	235.7	236.6	237.5	239.7	241.1
45°	232.5	231.2	229.4	226.2	224.0	224.4	224.9	224.9	225.8	228.5	229.4
47.5°	218.6	219.1	216.8	213.7	212.3	212.3	212.3	213.2	215.5	216.4	216.8
50°	205.1	204.2	203.8	200.6	199.7	199.3	199.7	200.2	203.3	202.9	204.2
52.5°	190.7	190.7	190.3	188.5	187.1	187.1	186.2	188.5	189.4	190.3	191.6
55°	176.8	175.4	175.0	174.1	172.3	171.8	172.7	175.4	176.3	177.2	178.6
57.5°	161.5	161.5	160.6	159.2	159.2	159.2	159.2	161.0	162.4	163.3	166.0
60°	147.5	145.7	144.4	144.4	144.4	143.9	146.6	146.6	149.3	149.8	150.7
62.5°	130.9	130.0	129.1	129.5	129.1	130.0	130.9	132.7	133.1	134.5	135.8
65°	115.1	115.1	114.2	116.9	115.1	115.1	117.4	117.4	118.3	119.6	121.4
67.5°	99.9	100.3	99.4	99.4	100.3	100.8	101.2	103.0	103.5	105.3	107.5
70°	84.1	85.0	85.5	84.6	85.5	86.4	87.3	87.7	89.5	90.4	91.8
72.5°	70.2	71.1	69.7	70.2	70.6	71.5	72.0	72.9	73.8	76.5	77.4
75°	56.2	55.8	55.3	57.1	56.2	58.0	58.5	58.5	59.4	61.6	62.5
77.5°	43.2	43.2	43.6	42.7	44.1	43.6	44.1	45.4	46.8	46.8	50.4
80°	30.1	31.0	31.0	31.0	31.5	31.9	31.0	33.3	33.7	33.7	35.1
82.5°	19.3	19.8	19.3	20.2	20.2	21.1	20.7	21.1	22.0	22.9	23.4
85°	10.3	10.3	11.2	11.2	10.8	11.2	10.8	11.2	12.1	12.1	12.6
87.5°	3.6	3.6	3.6	3.6	4.0	3.6	4.0	4.0	3.6	3.6	4.9
90°	5.6	6.2	7.0	8.7	10.3	12.0	13.6	14.1	14.6	15.1	15.6
92.5°	20.0	20.4	20.8	21.5	22.3	23.0	23.8	24.2	24.6	24.9	25.3
95°	37.0	37.4	37.9	38.9	39.9	40.9	41.9	42.4	42.9	43.4	43.9
97.5°	57.5	57.8	58.2	58.9	59.7	60.4	61.2	61.8	62.4	63.1	63.7
100°	80.1	80.5	80.8	81.4	82.1	82.7	83.3	83.7	84.1	84.4	84.8
102.5°	104.1	104.3	104.7	105.6	106.5	107.3	108.2	108.6	109.0	109.3	109.7
105°	128.5	128.6	129.2	130.3	131.4	132.6	133.7	133.7	133.7	133.7	133.7
107.5°	157.4	157.5	157.8	158.3	158.8	159.3	159.8	160.2	160.6	160.9	161.3
110°	185.2	185.3	185.4	185.7	185.9	186.2	186.4	186.9	187.4	187.9	188.4

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	212.9	213.0	213.0	213.0	213.0	213.0	213.0	213.6	214.3	214.9	215.6
115°	242.3	242.5	242.4	242.1	241.9	241.6	241.4	241.5	241.6	241.7	241.8
117.5°	270.2	270.3	270.2	269.9	269.6	269.4	269.1	269.1	269.1	269.1	269.1
120°	299.3	299.7	299.4	298.8	298.1	297.5	296.9	296.8	296.6	296.5	296.4
122.5°	326.1	326.4	326.3	326.0	325.7	325.5	325.2	324.8	324.4	324.1	323.7
125°	353.9	354.1	354.0	353.7	353.5	353.2	353.0	352.5	352.0	351.5	351.0
127.5°	381.5	381.9	381.8	381.5	381.2	381.0	380.7	379.9	379.2	378.4	377.7
130°	408.6	409.1	408.9	408.5	408.2	407.8	407.4	406.9	406.4	405.9	405.4
132.5°	434.6	435.1	435.0	434.7	434.5	434.2	434.0	433.4	432.8	432.1	431.5
135°	460.2	460.6	460.5	460.4	460.3	460.2	460.1	459.6	459.1	458.6	458.1
137.5°	484.1	484.4	484.6	485.0	485.3	485.7	486.1	485.5	484.9	484.2	483.6
140°	509.6	509.9	510.0	510.1	510.2	510.4	510.5	510.4	510.2	510.1	510.0
142.5°	532.9	533.2	533.3	533.6	533.8	534.1	534.3	534.2	534.0	533.9	533.8
145°	555.7	555.8	556.0	556.4	556.7	557.1	557.5	557.4	557.2	557.1	557.0
147.5°	577.6	577.9	578.1	578.5	578.8	579.2	579.6	579.6	579.6	579.6	579.6
150°	598.8	598.9	599.0	599.3	599.5	599.8	600.0	600.0	600.0	600.0	600.0
152.5°	617.4	617.6	617.7	617.8	617.9	618.0	618.1	618.4	618.6	618.9	619.2
155°	635.1	635.1	635.2	635.3	635.4	635.6	635.7	636.2	636.7	637.2	637.7
157.5°	651.1	651.0	651.1	651.2	651.3	651.5	651.6	652.1	652.6	653.1	653.6
160°	665.8	665.7	665.7	665.7	665.7	665.7	665.7	666.3	667.0	667.6	668.3
162.5°	679.0	678.8	678.9	679.0	679.1	679.2	679.3	679.9	680.6	681.2	681.9
165°	690.3	690.1	690.1	690.1	690.1	690.1	690.1	690.9	691.6	692.4	693.1
167.5°	699.4	699.2	699.3	699.4	699.5	699.6	699.7	700.5	701.2	702.0	702.7
170°	707.4	707.1	707.1	707.1	707.1	707.1	707.1	708.0	708.9	709.8	710.7
172.5°	713.6	713.3	713.3	713.3	713.3	713.3	713.3	714.1	714.8	715.6	716.3
175°	717.6	717.3	717.3	717.3	717.3	717.3	717.3	718.1	718.8	719.6	720.3
177.5°	719.8	719.6	719.6	719.6	719.6	719.6	719.6	720.4	721.1	721.9	722.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	440.4	440.8	439.0	437.7	441.3	439.0	439.0	439.5	438.6	439.9	439.5
5°	415.6	416.1	412.9	413.8	412.0	411.6	411.1	413.8	413.4	412.9	413.8
7.5°	391.3	391.3	390.0	389.1	389.1	387.7	389.5	389.1	390.0	390.0	391.3
10°	371.1	372.0	369.7	367.5	367.0	367.5	367.5	367.9	368.4	371.5	371.1
12.5°	354.4	353.1	352.6	351.3	349.0	348.1	347.2	352.2	350.8	350.8	350.8
15°	336.0	339.1	338.7	334.6	333.7	335.5	334.6	334.6	339.1	338.7	338.2
17.5°	326.1	325.2	324.3	322.1	322.5	322.1	322.5	322.5	325.2	325.2	325.2
20°	314.9	313.1	313.1	312.2	312.2	310.8	312.6	313.1	314.9	314.9	315.3
22.5°	305.0	303.6	303.6	303.2	304.1	302.3	304.1	304.5	304.5	305.9	305.9
25°	296.4	295.5	295.5	296.4	296.4	296.4	296.4	298.2	296.9	297.3	296.9
27.5°	288.8	289.2	289.7	290.1	289.7	290.1	290.6	291.5	291.9	291.5	290.6
30°	281.6	282.9	283.4	283.4	284.3	284.7	285.2	285.2	285.6	284.3	285.2
32.5°	276.2	276.2	277.1	277.5	278.4	278.9	278.9	279.8	279.3	278.0	278.4
35°	268.5	268.5	270.3	271.2	272.6	272.1	272.6	272.6	273.0	272.1	270.8
37.5°	260.9	261.8	261.8	263.6	264.0	264.5	264.0	264.9	264.5	263.6	263.1
40°	251.9	251.4	251.9	253.2	253.7	253.7	253.7	254.6	254.6	254.6	254.1
42.5°	240.6	242.0	241.5	242.9	242.4	242.4	243.3	244.2	244.7	243.3	243.8
45°	229.8	229.8	230.7	230.7	231.2	231.2	233.0	232.1	233.0	232.1	232.5
47.5°	218.2	218.6	218.6	219.1	220.0	220.9	220.0	220.4	220.4	220.9	220.0
50°	205.1	205.1	206.0	207.4	209.2	208.3	207.8	209.6	208.3	208.3	207.4
52.5°	191.6	193.0	193.4	194.8	196.1	196.6	197.0	196.1	196.6	195.2	195.7
55°	178.6	179.0	180.8	182.2	183.5	183.5	183.1	183.5	184.0	182.2	182.2
57.5°	165.5	166.9	168.7	168.7	170.5	170.5	170.0	170.0	170.5	169.1	168.7
60°	151.6	152.9	155.2	155.2	157.9	158.3	157.4	156.5	156.5	155.2	155.6
62.5°	136.7	138.1	139.4	141.7	143.5	142.6	144.4	142.6	143.0	140.3	140.3
65°	123.7	124.1	126.4	128.6	128.6	129.5	128.6	129.1	127.7	127.7	125.9
67.5°	108.4	108.4	110.6	112.9	115.1	115.1	115.1	113.8	113.8	112.4	112.4
70°	94.9	94.5	96.7	98.1	99.4	99.9	99.0	98.5	97.6	96.3	95.8
72.5°	78.3	79.2	81.4	82.3	84.6	84.1	86.4	83.7	83.7	81.4	81.0
75°	63.4	64.3	66.6	67.9	69.3	69.3	70.6	69.3	67.5	66.6	66.1
77.5°	50.4	49.9	51.7	54.0	54.4	54.0	54.9	54.4	52.6	52.6	51.7
80°	36.0	37.3	39.1	38.7	40.5	40.0	40.0	39.1	39.1	37.8	38.7
82.5°	23.8	25.2	25.6	25.2	25.6	26.5	27.0	26.5	26.5	25.6	26.1
85°	12.6	12.6	13.5	13.9	13.5	13.5	13.9	15.3	14.4	13.5	14.4
87.5°	4.0	3.6	3.6	4.0	3.6	3.6	4.0	4.0	4.5	4.5	4.5
90°	15.9	16.0	16.3	16.5	16.8	17.0	16.8	16.5	16.3	16.0	15.9
92.5°	25.5	25.4	25.1	24.9	24.6	24.4	24.6	24.9	25.1	25.4	25.5
95°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
97.5°	64.0	63.9	63.8	63.7	63.6	63.5	63.6	63.7	63.8	63.9	64.0
100°	85.0	85.1	85.4	85.6	85.9	86.1	85.9	85.6	85.4	85.1	85.0
102.5°	109.9	109.8	109.7	109.6	109.5	109.4	109.5	109.6	109.7	109.8	109.9
105°	133.7	133.8	134.1	134.3	134.6	134.8	134.6	134.3	134.1	133.8	133.7
107.5°	161.5	161.4	161.3	161.2	161.0	160.9	161.0	161.2	161.3	161.4	161.5
110°	188.7	188.6	188.3	188.0	187.8	187.5	187.8	188.0	188.3	188.6	188.7

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9
115°	241.9	241.8	241.7	241.6	241.5	241.4	241.5	241.6	241.7	241.8	241.9
117.5°	269.1	268.9	268.5	268.2	267.8	267.4	267.8	268.2	268.5	268.9	269.1
120°	296.3	296.2	295.9	295.7	295.4	295.2	295.4	295.7	295.9	296.2	296.3
122.5°	323.5	323.3	322.9	322.6	322.2	321.8	322.2	322.6	322.9	323.3	323.5
125°	350.7	350.4	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.7
127.5°	377.3	377.1	376.6	376.1	375.6	375.1	375.6	376.1	376.6	377.1	377.3
130°	405.1	404.7	403.8	402.9	402.0	401.1	402.0	402.9	403.8	404.7	405.1
132.5°	431.2	430.9	430.2	429.6	428.9	428.3	428.9	429.6	430.2	430.9	431.2
135°	457.8	457.7	457.4	457.2	456.9	456.7	456.9	457.2	457.4	457.7	457.8
137.5°	483.3	483.1	482.7	482.4	482.0	481.6	482.0	482.4	482.7	483.1	483.3
140°	509.9	509.5	508.6	507.7	506.9	506.0	506.9	507.7	508.6	509.5	509.9
142.5°	533.7	533.4	532.8	532.1	531.5	530.9	531.5	532.1	532.8	533.4	533.7
145°	556.9	556.7	556.2	555.7	555.2	554.7	555.2	555.7	556.2	556.7	556.9
147.5°	579.6	579.2	578.5	577.7	577.0	576.2	577.0	577.7	578.5	579.2	579.6
150°	600.0	599.6	598.9	598.1	597.4	596.6	597.4	598.1	598.9	599.6	600.0
152.5°	619.3	619.0	618.3	617.7	617.0	616.4	617.0	617.7	618.3	619.0	619.3
155°	638.0	637.6	636.7	635.8	634.9	634.0	634.9	635.8	636.7	637.6	638.0
157.5°	653.8	653.4	652.7	651.9	651.2	650.4	651.2	651.9	652.7	653.4	653.8
160°	668.6	668.3	667.8	667.3	666.8	666.3	666.8	667.3	667.8	668.3	668.6
162.5°	682.2	681.8	680.9	680.0	679.1	678.2	679.1	680.0	680.9	681.8	682.2
165°	693.5	693.1	692.2	691.3	690.4	689.5	690.4	691.3	692.2	693.1	693.5
167.5°	703.1	702.7	702.0	701.2	700.5	699.7	700.5	701.2	702.0	702.7	703.1
170°	711.1	710.7	709.8	708.9	708.0	707.1	708.0	708.9	709.8	710.7	711.1
172.5°	716.7	716.3	715.4	714.5	713.7	712.8	713.7	714.5	715.4	716.3	716.7
175°	720.7	720.3	719.4	718.5	717.6	716.7	717.6	718.5	719.4	720.3	720.7
177.5°	723.0	722.6	721.7	720.8	719.9	719.0	719.9	720.8	721.7	722.6	723.0
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2	464.2
2.5°	440.8	441.7	442.1	440.4	439.0	441.3	444.4	446.6	448.4	450.7	452.0
5°	414.7	417.9	417.9	418.8	420.1	422.4	428.2	432.3	435.9	438.6	440.8
7.5°	392.7	394.9	396.3	398.5	400.8	403.9	410.7	416.5	421.9	425.1	428.7
10°	372.9	374.7	376.9	378.3	382.3	386.8	395.4	400.3	406.6	411.6	416.1
12.5°	354.0	360.3	361.6	361.2	364.8	369.7	378.3	385.9	392.7	397.6	402.6
15°	340.5	342.7	345.4	345.0	352.6	354.0	361.2	370.2	379.2	382.3	386.8
17.5°	325.7	329.3	331.9	333.3	335.5	340.5	347.2	354.0	365.7	366.1	377.8
20°	314.0	317.6	319.4	321.2	322.5	328.4	334.2	341.8	351.3	356.2	362.5
22.5°	306.3	308.1	309.5	310.8	312.6	315.8	323.0	331.5	337.8	343.2	347.2
25°	297.3	299.1	300.9	301.8	303.2	305.0	310.4	317.1	326.1	329.7	333.7
27.5°	291.0	291.0	291.9	291.9	293.7	295.5	299.6	305.9	313.1	317.6	323.0
30°	284.3	283.8	284.3	283.8	283.4	286.1	289.7	295.1	300.0	305.4	309.0
32.5°	277.5	277.1	277.1	277.5	275.7	277.1	278.9	283.8	289.2	291.9	296.0
35°	270.3	269.4	269.4	269.4	268.5	267.6	269.4	273.9	277.5	281.1	284.3
37.5°	263.1	261.8	261.8	260.9	260.0	258.6	258.6	262.2	267.2	268.5	272.6
40°	253.2	253.2	252.3	251.9	251.0	250.1	248.7	251.9	256.4	257.7	260.9
42.5°	243.3	242.0	241.5	241.5	241.5	240.2	239.3	241.5	244.2	246.5	248.3
45°	232.1	231.2	231.6	231.2	230.3	229.8	229.4	230.3	233.4	234.3	236.6
47.5°	220.0	219.5	219.5	219.1	218.6	219.1	217.3	219.5	220.4	221.3	223.1
50°	207.4	206.9	206.5	206.0	206.0	206.5	206.0	206.0	207.8	208.7	210.5
52.5°	194.8	193.4	193.4	193.0	193.0	192.1	193.0	193.4	194.3	195.2	196.1
55°	181.3	181.3	179.9	179.9	179.0	179.0	179.5	179.0	180.8	181.7	181.7
57.5°	168.2	166.4	166.9	166.0	165.1	164.6	164.6	165.5	166.4	166.4	167.3
60°	154.3	152.5	152.0	150.2	151.1	149.8	150.2	150.2	152.0	151.1	152.0
62.5°	140.3	138.1	136.7	135.8	135.8	136.3	135.4	134.9	135.8	136.7	138.5
65°	125.5	124.1	122.8	121.4	121.4	121.0	121.9	120.5	120.1	120.5	121.4
67.5°	110.2	108.9	107.5	106.2	106.6	105.3	104.4	105.7	104.8	105.3	106.2
70°	95.4	94.5	91.8	90.9	90.4	90.9	90.4	89.5	90.9	90.4	90.9
72.5°	80.5	79.6	78.3	76.0	76.0	75.6	75.1	75.1	74.7	74.7	74.7
75°	66.1	64.3	63.0	62.5	61.6	61.2	60.7	59.8	60.3	60.7	59.8
77.5°	51.3	49.0	48.6	48.6	47.2	47.2	47.7	47.2	46.8	46.8	46.8
80°	37.8	36.0	36.0	35.1	34.2	34.2	34.2	34.2	33.7	33.3	33.7
82.5°	24.3	23.8	23.4	23.4	24.3	22.5	23.4	22.9	22.5	22.5	22.0
85°	13.5	13.9	13.5	13.9	13.0	13.5	13.5	13.5	13.0	13.5	12.6
87.5°	4.9	4.9	4.9	5.4	5.4	5.4	5.4	5.4	5.8	5.4	5.4
90°	15.6	15.1	14.6	14.1	13.6	12.0	10.3	8.7	7.0	6.2	5.6
92.5°	25.3	24.9	24.6	24.2	23.8	23.0	22.3	21.5	20.8	20.4	20.0
95°	43.9	43.4	42.9	42.4	41.9	40.9	39.9	38.9	37.9	37.4	37.0
97.5°	63.7	63.1	62.4	61.8	61.2	60.4	59.7	58.9	58.2	57.8	57.5
100°	84.8	84.4	84.1	83.7	83.3	82.7	82.1	81.4	80.8	80.5	80.1
102.5°	109.7	109.3	109.0	108.6	108.2	107.3	106.5	105.6	104.7	104.3	104.1
105°	133.7	133.7	133.7	133.7	133.7	132.6	131.4	130.3	129.2	128.6	128.5
107.5°	161.3	160.9	160.6	160.2	159.8	159.3	158.8	158.3	157.8	157.5	157.4
110°	188.4	187.9	187.4	186.9	186.4	186.2	185.9	185.7	185.4	185.3	185.2

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	215.6	214.9	214.3	213.6	213.0	213.0	213.0	213.0	213.0	213.0	212.9
115°	241.8	241.7	241.6	241.5	241.4	241.6	241.9	242.1	242.4	242.5	242.3
117.5°	269.1	269.1	269.1	269.1	269.1	269.4	269.6	269.9	270.2	270.3	270.2
120°	296.4	296.5	296.6	296.8	296.9	297.5	298.1	298.8	299.4	299.7	299.3
122.5°	323.7	324.1	324.4	324.8	325.2	325.5	325.7	326.0	326.3	326.4	326.1
125°	351.0	351.5	352.0	352.5	353.0	353.2	353.5	353.7	354.0	354.1	353.9
127.5°	377.7	378.4	379.2	379.9	380.7	381.0	381.2	381.5	381.8	381.9	381.5
130°	405.4	405.9	406.4	406.9	407.4	407.8	408.2	408.5	408.9	409.1	408.6
132.5°	431.5	432.1	432.8	433.4	434.0	434.2	434.5	434.7	435.0	435.1	434.6
135°	458.1	458.6	459.1	459.6	460.1	460.2	460.3	460.4	460.5	460.6	460.2
137.5°	483.6	484.2	484.9	485.5	486.1	485.7	485.3	485.0	484.6	484.4	484.1
140°	510.0	510.1	510.2	510.4	510.5	510.4	510.2	510.1	510.0	509.9	509.6
142.5°	533.8	533.9	534.0	534.2	534.3	534.1	533.8	533.6	533.3	533.2	532.9
145°	557.0	557.1	557.2	557.4	557.5	557.1	556.7	556.4	556.0	555.8	555.7
147.5°	579.6	579.6	579.6	579.6	579.6	579.2	578.8	578.5	578.1	577.9	577.6
150°	600.0	600.0	600.0	600.0	600.0	599.8	599.5	599.3	599.0	598.9	598.8
152.5°	619.2	618.9	618.6	618.4	618.1	618.0	617.9	617.8	617.7	617.6	617.4
155°	637.7	637.2	636.7	636.2	635.7	635.6	635.4	635.3	635.2	635.1	635.1
157.5°	653.6	653.1	652.6	652.1	651.6	651.5	651.3	651.2	651.1	651.0	651.1
160°	668.3	667.6	667.0	666.3	665.7	665.7	665.7	665.7	665.7	665.7	665.8
162.5°	681.9	681.2	680.6	679.9	679.3	679.2	679.1	679.0	678.9	678.8	679.0
165°	693.1	692.4	691.6	690.9	690.1	690.1	690.1	690.1	690.1	690.1	690.3
167.5°	702.7	702.0	701.2	700.5	699.7	699.6	699.5	699.4	699.3	699.2	699.4
170°	710.7	709.8	708.9	708.0	707.1	707.1	707.1	707.1	707.1	707.1	707.4
172.5°	716.3	715.6	714.8	714.1	713.3	713.3	713.3	713.3	713.3	713.3	713.6
175°	720.3	719.6	718.8	718.1	717.3	717.3	717.3	717.3	717.3	717.3	717.6
177.5°	722.6	721.9	721.1	720.4	719.6	719.6	719.6	719.6	719.6	719.6	719.8
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	464.2	464.2	464.2	464.2
2.5°	454.3	455.6	460.1	465.5
5°	445.3	448.9	455.2	463.7
7.5°	435.4	440.8	449.8	460.6
10°	424.2	431.8	443.0	456.5
12.5°	412.0	421.9	436.3	450.2
15°	404.4	414.3	427.3	442.6
17.5°	389.5	401.2	414.7	436.3
20°	374.2	387.3	404.8	426.4
22.5°	362.5	376.5	393.1	416.1
25°	348.6	363.0	381.0	404.8
27.5°	333.7	348.1	368.4	393.6
30°	322.5	336.4	355.8	382.8
32.5°	309.0	322.5	342.7	371.1
35°	293.7	309.0	328.4	357.1
37.5°	282.0	296.0	316.2	343.6
40°	269.4	281.6	301.4	328.4
42.5°	255.9	269.4	286.5	313.5
45°	243.3	253.2	270.8	296.4
47.5°	229.8	241.1	254.6	274.4
50°	215.5	224.9	239.7	253.2
52.5°	201.5	209.2	221.7	232.1
55°	186.7	194.3	203.8	210.1
57.5°	172.7	178.1	184.4	188.5
60°	155.6	161.0	165.1	169.1
62.5°	140.3	144.4	146.6	148.9
65°	124.6	126.8	128.2	130.0
67.5°	107.5	109.8	110.2	112.9
70°	91.8	92.2	93.1	94.5
72.5°	76.9	77.8	77.4	78.3
75°	61.6	62.5	61.6	62.5
77.5°	46.8	47.7	47.7	49.0
80°	33.7	34.2	34.6	34.6
82.5°	22.0	23.4	22.5	22.9
85°	12.6	13.0	13.0	13.5
87.5°	5.8	6.3	5.8	6.7
90°	4.3	3.1	1.8	0.6
92.5°	19.3	18.5	17.8	17.0
95°	36.1	35.2	34.3	33.4
97.5°	56.9	56.2	55.6	55.0
100°	79.4	78.6	77.9	77.1
102.5°	103.7	103.4	103.0	102.6
105°	128.2	128.0	127.7	127.5
107.5°	157.3	157.2	157.0	156.9
110°	184.9	184.6	184.4	184.1

TEST NUMBER: P1011592

CATALOG NUMBER: S123DIP-B340D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	212.8	212.7	212.6	212.5
115°	241.9	241.6	241.2	240.8
117.5°	270.1	270.0	269.8	269.7
120°	298.6	297.8	297.1	296.3
122.5°	325.6	325.1	324.6	324.1
125°	353.5	353.2	352.8	352.4
127.5°	380.8	380.0	379.3	378.5
130°	407.6	406.5	405.5	404.5
132.5°	433.6	432.6	431.6	430.6
135°	459.5	458.7	458.0	457.2
137.5°	483.5	482.8	482.2	481.6
140°	509.0	508.3	507.7	507.1
142.5°	532.2	531.6	530.9	530.3
145°	555.4	555.2	554.9	554.7
147.5°	577.1	576.6	576.1	575.6
150°	598.5	598.2	598.0	597.7
152.5°	617.0	616.7	616.3	615.9
155°	635.1	635.1	635.1	635.1
157.5°	651.2	651.3	651.5	651.6
160°	666.1	666.4	666.6	666.9
162.5°	679.4	679.7	680.1	680.5
165°	690.7	691.0	691.4	691.8
167.5°	699.9	700.4	700.9	701.4
170°	707.9	708.4	708.9	709.4
172.5°	714.1	714.6	715.1	715.6
175°	718.1	718.6	719.1	719.6
177.5°	720.3	720.8	721.3	721.8
180°	721.3	721.3	721.3	721.3

(END OF REPORT)