

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011868

Luminaire Tested: S123DIP-B560D805UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011868
REPORT IS A COMBINATION OF REPORTS P990189 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB30-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5444.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011868

CATALOG NUMBER: S123DIP-B560D805UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011868

CATALOG NUMBER: S123DIP-B560D805UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8078 cd/sqm

TEST NUMBER: P1011868

CATALOG NUMBER: S123DIP-B560D805UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.5
10°-20°	236.2	4.3
20°-30°	348.8	6.4
30°-40°	407.4	7.5
40°-50°	409.5	7.5
50°-60°	359.8	6.6
60°-70°	267.9	4.9
70°-80°	152.5	2.8
80°-90°	45.4	0.8
90°-100°	36.2	0.7
100°-110°	175.2	3.2
110°-120°	429.3	7.9
120°-130°	545.1	10.0
130°-140°	582.3	10.7
140°-150°	544.5	10.0
150°-160°	439.2	8.1
160°-170°	283.4	5.2
170°-180°	97.7	1.8
0°-30°	668.6	12.3
0°-40°	1076.0	19.8
0°-60°	1845.2	33.9
0°-90°	2311.0	42.5
90°-120°	640.8	11.8
90°-150°	2312.6	42.5
90°-180°	3133.0	57.5
0°-180°	5444.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	1	8	18	21	23	5
95°	47	15	24	29	29	56
105°	228	236	167	32	34	241
115°	427	431	438	446	449	422
125°	602	608	611	612	614	538
135°	749	754	757	759	757	577
145°	864	870	871	873	873	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1011868

CATALOG NUMBER: S123DIP-B560D805UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	0.8	8.4	18.3	21.4	22.9
92.5°	17.6	13.0	19.9	25.2	26.0
95°	46.6	15.3	23.7	29.0	29.0
97.5°	84.7	63.4	24.4	30.5	31.3
100°	129.0	144.3	25.2	31.3	32.1
102.5°	179.4	189.3	56.5	31.3	32.8
105°	227.5	235.9	167.2	32.1	33.6
107.5°	278.7	285.5	297.0	179.4	79.4
110°	329.8	335.9	344.3	319.1	210.0

TEST NUMBER: P1011868

CATALOG NUMBER: S123DIP-B560D805UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	384.0	392.4	399.3	397.8
115°	426.8	431.4	438.2	445.9	448.9
117.5°	474.1	479.5	483.3	489.4	490.2
120°	517.7	524.5	526.8	532.9	532.9
122.5°	561.9	567.3	570.3	574.2	574.9
125°	601.6	607.7	610.8	612.3	613.9
127.5°	641.3	647.4	651.3	653.6	652.0
130°	678.0	684.1	687.2	690.2	688.7
132.5°	713.1	719.2	721.5	724.6	722.3
135°	749.0	753.6	756.6	758.9	756.6
137.5°	779.5	785.6	787.2	791.0	789.5
140°	810.1	814.7	816.9	820.0	818.5
142.5°	838.3	842.9	845.2	847.5	845.2
145°	864.3	869.6	871.2	872.7	872.7
147.5°	889.5	893.3	894.8	896.4	892.5
150°	912.4	914.7	916.2	917.7	915.4
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)