

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011606

Luminaire Tested: S123DIP-B340D585UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011606
REPORT IS A COMBINATION OF REPORTS P989831 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3502.9 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011606

CATALOG NUMBER: S123DIP-B340D585UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011606

CATALOG NUMBER: S123DIP-B340D585UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1011606

CATALOG NUMBER: S123DIP-B340D585UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	1.4
10°-20°	140.4	4.0
20°-30°	207.4	5.9
30°-40°	242.2	6.9
40°-50°	243.5	7.0
50°-60°	213.9	6.1
60°-70°	159.3	4.5
70°-80°	90.7	2.6
80°-90°	27.3	0.8
90°-100°	160.4	4.6
100°-110°	448.4	12.8
110°-120°	437.2	12.5
120°-130°	348.1	9.9
130°-140°	274.8	7.8
140°-150°	205.0	5.9
150°-160°	143.0	4.1
160°-170°	84.0	2.4
170°-180°	27.3	0.8
0°-30°	397.6	11.3
0°-40°	639.8	18.3
0°-60°	1097.2	31.3
0°-90°	1374.6	39.2
90°-120°	1046.0	29.9
90°-150°	1874.0	53.5
90°-180°	2128.0	60.7
0°-180°	3502.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	1	7	14	16	17	3
95°	19	63	339	99	66	21
105°	66	98	459	803	727	70
115°	117	146	351	771	884	116
125°	163	192	328	594	697	145
135°	191	228	323	489	565	147
145°	218	249	319	401	442	136
155°	247	267	309	351	366	114
165°	270	278	296	314	319	76
175°	282	282	284	288	287	27
180°	282	282	282	282	282	

TEST NUMBER: P1011606

CATALOG NUMBER: S123DIP-B340D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	1.1	6.8	14.3	16.0	16.6
92.5°	8.6	34.2	106.3	36.3	30.3
95°	19.4	63.2	338.9	98.8	66.3
97.5°	30.9	72.3	521.2	248.6	136.0
100°	42.3	79.8	541.2	520.0	358.3
102.5°	54.3	88.3	504.0	696.3	567.4
105°	66.3	98.0	459.4	803.4	726.9
107.5°	78.9	109.4	420.0	850.6	830.9
110°	92.6	121.1	387.4	852.0	890.3

TEST NUMBER: P1011606

CATALOG NUMBER: S123DIP-B340D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.1	133.4	365.7	819.8	902.3
115°	117.1	146.0	351.4	770.6	884.0
117.5°	129.1	158.0	341.7	718.0	844.0
120°	141.7	170.0	335.4	668.3	791.4
122.5°	152.6	181.4	331.4	629.2	742.3
125°	162.9	192.3	328.0	594.3	697.2
127.5°	170.9	202.6	326.3	565.8	658.3
130°	178.3	211.7	324.6	539.4	626.3
132.5°	184.0	220.0	324.0	514.9	594.9
135°	190.9	227.7	323.4	489.4	565.2
137.5°	197.1	234.0	322.3	465.4	533.7
140°	203.4	239.8	321.7	442.0	500.6
142.5°	210.3	244.8	320.6	420.6	469.7
145°	217.7	249.4	319.4	401.4	441.7
147.5°	225.1	254.3	317.7	386.6	417.7
150°	232.6	258.2	315.4	373.4	397.2
152.5°	240.0	262.5	312.6	362.0	380.0
155°	247.4	266.9	309.2	351.4	366.3
157.5°	253.1	270.5	306.3	341.2	353.2
160°	260.0	273.8	302.9	331.7	340.6
162.5°	265.1	276.0	299.4	322.9	329.2
165°	270.3	278.0	296.0	314.0	319.4
167.5°	274.3	279.8	292.6	306.3	309.7
170°	277.7	280.6	289.2	299.4	301.2
172.5°	280.0	281.4	286.3	293.4	293.2
175°	281.7	282.0	284.0	288.0	287.4
177.5°	282.9	282.3	282.3	284.6	283.4
180°	282.3	282.3	282.3	282.3	282.3

(END OF REPORT)