

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011884

Luminaire Tested: S123DIP-B560D805UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011884
REPORT IS A COMBINATION OF REPORTS P990208 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4976.0 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011884

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011884

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	46	45	44
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	30	27
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1011884

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.7
10°-20°	234.8	4.7
20°-30°	346.8	7.0
30°-40°	405.1	8.1
40°-50°	407.2	8.2
50°-60°	357.7	7.2
60°-70°	266.4	5.4
70°-80°	151.6	3.0
80°-90°	45.1	0.9
90°-100°	62.2	1.3
100°-110°	188.3	3.8
110°-120°	320.6	6.4
120°-130°	421.7	8.5
130°-140°	474.0	9.5
140°-150°	466.0	9.4
150°-160°	392.4	7.9
160°-170°	261.2	5.2
170°-180°	91.5	1.8
0°-30°	664.8	13.4
0°-40°	1069.9	21.5
0°-60°	1834.9	36.9
0°-90°	2298.0	46.2
90°-120°	571.1	11.5
90°-150°	1932.9	38.8
90°-180°	2678.0	53.8
0°-180°	4976.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	1	8	18	21	23	6
95°	45	50	56	59	59	49
105°	171	172	179	179	181	183
115°	323	325	323	324	323	319
125°	472	474	473	470	467	421
135°	613	617	616	613	612	472
145°	743	745	747	746	743	464
155°	851	851	852	855	850	392
165°	927	925	925	929	924	261
175°	964	961	961	966	960	92
180°	966	966	966	966	966	

TEST NUMBER: P1011884

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	0.8	8.4	18.2	21.3	22.8
92.5°	22.8	27.3	31.9	34.2	32.6
95°	44.8	50.1	56.2	59.2	59.2
97.5°	73.6	77.4	82.0	85.8	85.0
100°	103.3	107.8	111.6	113.9	115.4
102.5°	137.4	139.7	145.0	147.3	146.5
105°	170.8	172.3	179.2	179.2	180.7
107.5°	210.3	211.1	214.1	216.4	215.6
110°	246.7	248.3	249.8	252.8	251.3

TEST NUMBER: P1011884

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	285.5	285.5	289.3	289.3
115°	322.7	324.9	323.4	324.2	323.4
117.5°	361.4	362.1	360.6	360.6	358.4
120°	397.1	401.6	397.8	397.1	395.6
122.5°	434.3	437.3	435.8	433.5	431.2
125°	472.2	474.5	473.0	470.0	466.9
127.5°	507.2	511.7	510.2	505.6	502.6
130°	542.1	548.2	545.9	542.8	537.5
132.5°	577.0	583.1	581.6	577.8	574.0
135°	612.7	617.2	616.5	613.4	611.9
137.5°	645.3	649.1	651.4	647.6	645.3
140°	679.5	683.3	684.1	683.3	678.0
142.5°	710.6	714.4	715.9	715.2	711.4
145°	743.3	744.8	747.1	746.3	743.3
147.5°	771.4	774.4	776.7	776.7	772.1
150°	801.0	802.5	804.0	804.0	799.5
152.5°	825.3	827.5	828.3	829.8	826.0
155°	851.1	851.1	851.8	854.9	849.6
157.5°	873.1	872.3	873.1	876.1	871.6
160°	893.6	892.1	892.1	895.9	892.8
162.5°	911.8	909.5	910.3	914.1	908.8
165°	927.0	924.7	924.7	929.3	924.0
167.5°	939.9	936.9	937.6	942.2	937.6
170°	950.5	947.5	947.5	952.8	947.5
172.5°	958.9	955.9	955.9	960.4	955.1
175°	964.2	961.2	961.2	965.7	960.4
177.5°	967.2	964.2	964.2	968.8	963.4
180°	966.5	966.5	966.5	966.5	966.5

(END OF REPORT)