

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011615

Luminaire Tested: S123DIP-B340D585UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011615
REPORT IS A COMBINATION OF REPORTS P989840 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3517.9 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011615

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011615

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011615

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.4
10°-20°	141.0	4.0
20°-30°	208.3	5.9
30°-40°	243.3	6.9
40°-50°	244.6	7.0
50°-60°	214.8	6.1
60°-70°	160.0	4.5
70°-80°	91.1	2.6
80°-90°	27.5	0.8
90°-100°	161.1	4.6
100°-110°	450.3	12.8
110°-120°	439.1	12.5
120°-130°	349.6	9.9
130°-140°	276.0	7.8
140°-150°	205.9	5.9
150°-160°	143.6	4.1
160°-170°	84.4	2.4
170°-180°	27.4	0.8
0°-30°	399.3	11.4
0°-40°	642.6	18.3
0°-60°	1102.0	31.3
0°-90°	1380.6	39.2
90°-120°	1050.4	29.9
90°-150°	1881.9	53.5
90°-180°	2137.0	60.7
0°-180°	3517.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	7	14	16	17	3
95°	20	63	340	99	67	21
105°	67	98	461	807	730	71
115°	118	147	353	774	888	116
125°	164	193	329	597	700	145
135°	192	229	325	492	568	148
145°	219	250	321	403	444	137
155°	248	268	310	353	368	114
165°	271	279	297	315	321	77
175°	283	283	285	289	289	27
180°	284	284	284	284	284	

TEST NUMBER: P1011615

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.1	6.9	14.3	16.0	16.6
92.5°	8.6	34.4	106.7	36.4	30.4
95°	19.5	63.4	340.3	99.2	66.6
97.5°	31.0	72.6	523.4	249.6	136.6
100°	42.5	80.1	543.4	522.2	359.8
102.5°	54.5	88.6	506.1	699.2	569.8
105°	66.6	98.4	461.4	806.8	730.0
107.5°	79.2	109.9	421.8	854.2	834.4
110°	93.0	121.6	389.1	855.6	894.1



TEST NUMBER: P1011615

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.6	134.0	367.3	823.2	906.1
115°	117.6	146.6	352.9	773.8	887.8
117.5°	129.7	158.6	343.2	721.0	847.6
120°	142.3	170.8	336.9	671.2	794.8
122.5°	153.2	182.2	332.8	631.8	745.4
125°	163.6	193.2	329.4	596.8	700.1
127.5°	171.6	203.4	327.7	568.2	661.1
130°	179.0	212.6	326.0	541.7	629.0
132.5°	184.8	221.0	325.4	517.0	597.4
135°	191.7	228.6	324.8	491.6	567.6
137.5°	198.0	235.0	323.7	467.4	536.0
140°	204.3	240.8	323.1	443.8	502.7
142.5°	211.2	245.9	321.9	422.4	471.7
145°	218.6	250.5	320.8	403.2	443.6
147.5°	226.1	255.4	319.1	388.2	419.5
150°	233.6	259.4	316.8	375.0	398.8
152.5°	241.0	263.7	313.9	363.5	381.6
155°	248.5	268.0	310.5	353.0	367.8
157.5°	254.2	271.8	307.6	342.6	354.6
160°	261.1	274.9	304.1	333.1	342.0
162.5°	266.3	277.2	300.7	324.2	330.5
165°	271.4	279.2	297.3	315.4	320.8
167.5°	275.5	280.9	293.8	307.5	311.0
170°	278.9	281.8	290.4	300.7	302.4
172.5°	281.2	282.6	287.5	294.7	294.4
175°	282.9	283.2	285.2	289.2	288.7
177.5°	284.1	283.5	283.5	285.8	284.6
180°	283.5	283.5	283.5	283.5	283.5

(END OF REPORT)