

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011625

Luminaire Tested: S123DIP-B340D585UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011625
REPORT IS A COMBINATION OF REPORTS P989850 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB50-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3614.0 lumens
Efficiency: N/A
Efficacy: 127.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	21	19
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	18	16
8	52	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4843	4843	4843	4843
5°	4846	5580	4860	4164
10°	4815	6753	4821	3637
15°	4749	8009	4788	3273
20°	4692	9220	4702	3013
25°	4607	9453	4617	2876
30°	4546	7809	4546	2787
35°	4471	5223	4443	2708
40°	4381	3770	4326	2587
45°	4267	2987	4143	2437
50°	3992	2537	3849	2290
55°	3689	2229	3539	2125
60°	3382	1941	3202	1952
65°	3046	1662	2898	1722
70°	2698	1379	2518	1451
75°	2305	1039	2157	1119
80°	1824	694	1683	736
85°	1258	319	1009	290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	1.2
10°-20°	142.1	3.9
20°-30°	239.1	6.6
30°-40°	270.3	7.5
40°-50°	242.1	6.7
50°-60°	195.4	5.4
60°-70°	136.2	3.8
70°-80°	71.5	2.0
80°-90°	18.6	0.5
90°-100°	26.1	0.7
100°-110°	126.1	3.5
110°-120°	309.0	8.5
120°-130°	392.2	10.9
130°-140°	419.0	11.6
140°-150°	391.8	10.8
150°-160°	316.0	8.7
160°-170°	204.0	5.6
170°-180°	70.3	1.9
0°-30°	425.5	11.8
0°-40°	695.8	19.3
0°-60°	1133.2	31.4
0°-90°	1359.5	37.6
90°-120°	461.2	12.8
90°-150°	1664.2	46.0
90°-180°	2255.0	62.4
0°-180°	3614.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	450	450	450	450	450	
5°	450	534	451	399	450	43
15°	429	796	432	325	429	121
25°	392	944	393	287	392	181
35°	346	509	344	264	346	217
45°	287	275	279	224	287	220
55°	204	187	195	178	204	182
65°	126	121	120	126	126	125
75°	61	62	57	67	61	65
85°	13	14	10	13	13	15
90°	0	16	0	16	0	3
95°	34	21	34	21	34	40
105°	164	24	164	24	164	174
115°	307	323	307	323	307	303
125°	433	442	433	442	433	387
135°	539	544	539	544	539	415
145°	622	628	622	628	622	389
155°	685	684	685	684	685	316
165°	722	721	722	721	722	204
175°	740	737	740	737	740	70
180°	740	740	740	740	740	

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	451.3	454.7	456.5	459.1	461.7	465.6	466.9	469.1	468.3	470.0	470.9
5°	449.5	455.6	460.8	467.4	473.5	477.8	482.2	489.2	494.4	495.3	499.2
7.5°	446.5	455.2	464.3	473.5	485.3	492.2	500.1	509.7	517.5	530.2	535.0
10°	442.5	454.7	467.8	480.5	496.6	507.5	517.1	533.2	549.3	562.4	574.6
12.5°	436.4	451.7	468.7	487.4	508.4	521.0	534.1	555.5	579.9	599.9	613.0
15°	429.0	448.2	470.0	490.1	513.2	536.7	550.7	574.6	609.5	628.3	661.8
17.5°	422.9	442.5	464.3	495.7	527.1	550.7	560.7	604.7	628.7	660.1	698.0
20°	413.3	438.2	466.1	497.5	538.0	552.4	572.9	617.4	647.0	688.0	734.6
22.5°	403.3	429.9	463.5	496.2	541.5	556.8	584.7	620.0	667.1	707.6	759.1
25°	392.4	421.2	455.2	494.0	538.4	560.7	586.8	630.4	681.5	732.5	780.0
27.5°	381.5	412.9	448.2	487.0	530.2	556.3	582.5	627.8	693.2	748.6	809.2
30°	371.0	402.4	437.7	477.4	522.8	548.0	572.9	629.6	702.4	764.7	825.8
32.5°	359.7	392.0	429.0	462.2	507.9	535.0	562.9	629.6	708.0	774.3	830.1
35°	346.2	379.3	411.1	444.3	489.6	519.7	551.1	625.2	713.3	777.4	811.8
37.5°	333.1	362.3	389.8	422.0	469.6	501.8	538.0	620.0	710.7	764.3	773.9
40°	318.3	347.5	369.7	399.8	449.9	487.4	524.1	613.0	699.3	733.3	705.4
42.5°	303.9	327.0	346.2	375.4	429.9	466.5	506.2	600.4	677.1	684.1	621.3
45°	287.3	303.9	320.9	354.0	408.1	445.6	489.6	582.0	641.3	621.3	541.9
47.5°	266.0	280.8	299.5	330.0	385.0	423.8	465.6	558.5	589.5	547.6	460.8
50°	245.5	258.1	275.5	305.2	360.6	398.5	443.0	521.4	536.7	470.9	397.2
52.5°	225.0	234.6	251.6	281.2	336.6	373.2	413.8	483.5	474.8	404.2	338.8
55°	203.6	211.9	228.0	257.2	308.7	343.6	382.4	436.9	414.2	347.0	294.7
57.5°	182.7	191.4	208.0	232.4	280.8	314.8	345.7	388.5	354.5	300.8	254.6
60°	163.9	171.3	184.0	208.0	252.0	279.5	307.8	337.0	308.7	256.8	221.5
62.5°	144.3	151.3	163.1	184.9	222.8	247.2	269.9	293.9	262.5	224.5	193.1
65°	126.0	131.7	142.6	162.6	193.6	213.6	231.9	248.5	223.2	188.3	164.8
67.5°	109.4	114.2	123.4	141.3	167.4	181.8	196.6	210.6	189.2	161.3	141.3
70°	91.6	95.5	103.8	116.8	137.8	152.6	163.5	174.0	154.8	132.5	119.0
72.5°	75.9	79.8	85.0	98.5	112.9	122.1	133.8	139.5	128.6	110.3	96.8
75°	60.6	63.7	68.5	77.2	90.7	96.8	104.2	108.6	98.5	86.3	78.0
77.5°	47.5	48.8	52.3	58.4	67.6	74.6	80.2	82.8	75.9	68.0	61.0
80°	33.6	35.3	37.9	43.2	50.1	52.3	55.8	58.9	54.5	47.5	43.2
82.5°	22.2	24.4	25.7	27.9	32.3	34.9	35.8	38.4	34.4	31.8	30.1
85°	13.1	14.0	14.4	15.7	17.9	19.2	20.5	20.9	20.1	19.6	17.9
87.5°	6.5	6.5	6.5	7.4	7.8	8.7	9.2	9.2	9.2	8.7	8.3
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.8	8.4	10.0	11.6	13.2
92.5°	12.6	11.9	11.1	10.4	9.7	9.3	9.9	11.0	12.1	13.2	14.3
95°	33.5	28.5	23.5	18.5	13.5	11.0	11.7	13.0	14.3	15.7	17.0
97.5°	61.0	57.6	54.2	50.7	47.3	45.6	42.5	36.3	30.0	23.8	17.6
100°	92.9	95.3	97.7	100.2	102.6	103.8	94.3	75.2	56.2	37.1	18.1
102.5°	129.1	130.7	132.3	133.9	135.5	136.3	125.7	104.4	83.2	61.9	40.7
105°	163.7	165.1	166.4	167.8	169.1	169.8	164.3	153.3	142.3	131.3	120.3
107.5°	200.5	201.6	202.7	203.8	204.9	205.5	206.4	208.2	210.1	211.9	213.7
110°	237.4	238.4	239.3	240.3	241.2	241.7	242.4	243.7	245.1	246.4	247.8

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	272.5	273.4	274.2	275.1	276.0	276.4	277.1	278.4	279.7	281.1	282.4
115°	307.1	307.8	308.6	309.3	310.0	310.4	311.0	312.1	313.2	314.3	315.4
117.5°	341.2	342.0	342.9	343.7	344.6	345.0	345.3	345.9	346.6	347.2	347.8
120°	372.5	373.6	374.7	375.8	376.9	377.5	377.7	378.0	378.4	378.7	379.1
122.5°	404.4	405.2	406.1	406.9	407.8	408.2	408.4	408.9	409.4	409.9	410.4
125°	432.9	433.9	434.9	435.8	436.8	437.3	437.5	438.0	438.5	439.0	439.5
127.5°	461.5	462.5	463.5	464.4	465.4	465.9	466.2	466.8	467.5	468.1	468.7
130°	487.9	488.9	489.9	490.8	491.8	492.3	492.5	493.0	493.5	494.0	494.5
132.5°	513.2	514.2	515.2	516.1	517.1	517.6	517.8	518.1	518.5	518.8	519.2
135°	539.0	539.7	540.5	541.2	541.9	542.3	542.5	543.0	543.5	544.0	544.5
137.5°	561.0	562.0	563.0	563.9	564.9	565.4	565.5	565.8	566.0	566.3	566.5
140°	582.9	583.6	584.4	585.1	585.8	586.2	586.4	586.8	587.1	587.5	587.9
142.5°	603.3	604.0	604.8	605.5	606.2	606.6	606.8	607.1	607.5	607.8	608.2
145°	622.0	622.8	623.7	624.5	625.4	625.8	625.9	626.2	626.4	626.7	626.9
147.5°	640.1	640.7	641.3	641.9	642.5	642.8	642.9	643.2	643.4	643.7	643.9
150°	656.6	657.0	657.3	657.7	658.0	658.2	658.3	658.6	658.8	659.1	659.3
152.5°	671.4	671.5	671.7	671.8	671.9	672.0	672.1	672.2	672.3	672.4	672.5
155°	685.1	684.9	684.6	684.4	684.1	684.0	684.1	684.2	684.3	684.5	684.6
157.5°	696.1	696.1	696.1	696.1	696.1	696.1	696.0	695.9	695.8	695.7	695.6
160°	706.0	705.9	705.8	705.7	705.6	705.5	705.4	705.3	705.2	705.0	704.9
162.5°	715.4	715.0	714.6	714.3	713.9	713.7	713.6	713.5	713.4	713.3	713.2
165°	722.5	722.1	721.8	721.4	721.1	720.9	720.8	720.7	720.6	720.4	720.3
167.5°	728.5	728.0	727.5	727.0	726.5	726.3	726.3	726.3	726.3	726.3	726.3
170°	733.5	733.0	732.5	732.0	731.5	731.3	731.3	731.3	731.3	731.3	731.3
172.5°	736.8	736.2	735.6	734.9	734.3	734.0	734.1	734.2	734.3	734.5	734.6
175°	739.5	738.9	738.3	737.7	737.1	736.8	736.9	737.0	737.1	737.2	737.3
177.5°	740.6	740.0	739.4	738.8	738.2	737.9	738.0	738.1	738.2	738.3	738.4
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	473.9	474.8	477.8	480.0	484.4	484.0	484.0	483.5	482.2	484.4	485.7
5°	507.1	514.5	515.3	524.9	525.4	529.3	531.9	529.7	535.0	534.5	530.6
7.5°	548.0	558.1	562.9	572.0	582.5	579.9	589.9	591.6	590.8	595.1	598.2
10°	592.9	610.4	622.6	639.6	644.0	646.6	653.1	658.8	670.1	661.4	667.1
12.5°	644.4	657.0	673.2	700.2	713.7	722.4	725.5	729.4	737.3	732.5	732.9
15°	687.6	704.6	732.0	765.6	769.5	780.4	777.8	801.4	812.7	795.7	805.3
17.5°	732.5	755.1	787.8	817.0	833.6	841.0	848.0	870.7	869.8	867.2	869.4
20°	761.2	798.3	838.8	877.7	882.4	888.1	906.9	916.5	914.7	922.1	926.9
22.5°	801.8	841.0	884.2	909.9	920.8	927.4	942.2	948.3	950.9	952.6	949.6
25°	835.8	877.7	909.5	932.1	938.7	942.2	947.0	948.7	947.4	944.4	947.0
27.5°	858.9	892.5	914.3	924.7	921.2	915.6	906.4	900.3	886.8	880.3	888.1
30°	868.5	883.3	889.9	872.4	855.0	841.0	823.6	791.3	766.0	773.4	763.4
32.5°	853.2	843.6	812.3	767.3	753.8	731.2	681.9	644.0	645.3	625.2	633.5
35°	808.3	764.7	705.4	637.4	619.5	607.3	553.3	545.0	527.5	508.8	514.0
37.5°	729.0	665.3	593.4	543.2	516.6	490.1	459.5	441.2	430.8	422.9	429.0
40°	632.2	554.6	495.3	450.4	427.7	410.7	389.8	371.5	359.7	358.4	360.6
42.5°	537.1	471.7	417.2	374.5	367.1	347.0	333.5	319.1	315.7	310.0	313.0
45°	454.7	401.5	356.6	321.8	313.0	307.8	291.2	282.1	278.2	274.7	279.9
47.5°	395.0	339.2	306.5	285.6	276.9	268.1	259.0	252.9	249.8	250.3	249.8
50°	337.5	296.5	267.7	251.6	246.3	240.2	232.8	228.9	227.6	223.7	226.7
52.5°	290.4	260.7	240.7	225.4	221.5	217.1	211.0	208.8	205.8	204.9	204.9
55°	252.4	229.3	213.2	203.2	198.4	194.9	191.4	188.8	186.6	186.6	186.6
57.5°	222.8	202.7	191.0	182.2	180.5	177.0	173.1	173.1	170.0	169.6	170.9
60°	197.5	179.6	170.5	163.1	160.4	159.6	155.6	155.6	154.8	152.6	154.3
62.5°	171.8	158.7	150.9	145.2	142.6	142.6	139.5	137.3	137.3	137.8	136.9
65°	148.2	138.6	131.7	127.3	126.0	124.3	123.8	122.1	120.8	121.2	120.8
67.5°	127.3	119.9	115.1	111.6	109.4	108.6	107.3	107.3	106.4	106.8	104.6
70°	108.6	101.1	97.2	93.7	92.9	92.9	91.1	91.6	90.7	92.0	91.1
72.5°	89.4	83.7	80.7	79.4	78.5	78.0	77.2	76.3	75.9	76.7	76.3
75°	72.4	67.6	65.4	64.5	63.7	63.7	63.2	62.8	62.3	62.3	62.3
77.5°	56.2	53.2	50.6	51.4	50.1	50.6	49.3	49.3	49.7	49.3	49.3
80°	41.4	39.2	39.2	38.4	36.6	37.5	37.5	36.2	35.8	36.6	35.3
82.5°	27.5	27.0	26.2	25.7	24.9	25.3	24.9	24.4	24.0	24.9	24.0
85°	16.1	16.1	15.7	14.8	15.7	15.3	14.8	14.8	14.4	14.4	14.4
87.5°	8.3	7.4	7.4	7.0	7.4	6.5	7.0	6.5	6.1	6.5	6.1
90°	13.7	14.2	14.7	15.2	15.4	15.5	15.8	16.0	16.3	16.5	16.3
92.5°	15.1	16.0	16.8	17.7	18.1	18.2	18.3	18.4	18.6	18.7	18.6
95°	17.9	18.7	19.6	20.5	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	18.6	19.6	20.5	21.5	22.0	22.1	22.2	22.3	22.4	22.5	22.4
100°	19.1	20.1	21.0	22.0	22.5	22.6	22.7	22.8	23.0	23.1	23.0
102.5°	36.7	32.6	28.6	24.5	22.5	22.6	22.9	23.1	23.4	23.6	23.4
105°	98.7	77.1	55.5	33.9	23.1	23.2	23.5	23.7	24.0	24.2	24.0
107.5°	194.9	176.1	157.3	138.5	129.1	121.1	105.1	89.1	73.1	57.1	73.1
110°	243.8	239.8	235.7	231.7	229.7	221.0	203.5	186.0	168.6	151.1	168.6

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	283.5	284.6	285.7	286.8	287.4	287.3	287.0	286.8	286.5	286.3	286.5
115°	316.6	317.8	319.1	320.3	320.9	321.1	321.6	322.1	322.6	323.1	322.6
117.5°	348.8	349.8	350.7	351.7	352.2	352.3	352.4	352.5	352.6	352.7	352.6
120°	380.1	381.1	382.0	383.0	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	411.0	411.6	412.3	412.9	413.2	413.3	413.4	413.5	413.6	413.7	413.6
125°	439.7	440.0	440.2	440.5	440.6	440.7	441.0	441.2	441.5	441.7	441.5
127.5°	469.1	469.4	469.8	470.1	470.3	470.2	469.9	469.7	469.4	469.2	469.4
130°	495.0	495.5	496.0	496.5	496.7	496.6	496.3	496.1	495.8	495.6	495.8
132.5°	519.7	520.2	520.7	521.2	521.4	521.2	520.9	520.5	520.2	519.8	520.2
135°	544.9	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.9
137.5°	567.1	567.7	568.3	568.9	569.2	569.1	568.8	568.6	568.3	568.1	568.3
140°	588.4	588.9	589.4	589.9	590.1	590.0	589.7	589.5	589.2	589.0	589.2
142.5°	608.6	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	608.6
145°	627.1	627.4	627.6	627.9	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	644.1	644.4	644.6	644.9	645.0	644.7	644.1	643.5	642.9	642.3	642.9
150°	659.5	659.8	660.0	660.3	660.4	660.2	659.9	659.5	659.2	658.8	659.2
152.5°	673.0	673.5	674.0	674.5	674.7	674.4	673.8	673.2	672.6	672.0	672.6
155°	685.2	685.8	686.4	687.0	687.3	686.9	686.2	685.5	684.7	684.0	684.7
157.5°	696.3	697.1	697.8	698.5	698.9	698.4	697.4	696.5	695.5	694.5	695.5
160°	705.6	706.4	707.1	707.8	708.2	707.8	706.9	706.1	705.2	704.4	705.2
162.5°	714.0	714.9	715.7	716.6	717.0	716.6	715.9	715.2	714.4	713.7	714.4
165°	721.3	722.3	723.2	724.2	724.7	724.3	723.4	722.6	721.7	720.9	721.7
167.5°	727.3	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	727.3
170°	732.3	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	732.3
172.5°	735.6	736.6	737.5	738.5	739.0	738.4	737.3	736.2	735.1	734.0	735.1
175°	738.2	739.0	739.9	740.8	741.2	740.7	739.7	738.8	737.8	736.8	737.8
177.5°	739.4	740.4	741.3	742.3	742.8	742.2	741.0	739.7	738.5	737.3	738.5
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	482.2	483.5	480.0	479.2	479.2	480.9	479.6	467.8	470.0	467.4	466.5
5°	535.4	532.8	529.3	527.5	525.4	519.3	518.8	505.3	502.7	494.0	490.1
7.5°	593.8	591.6	581.2	579.9	579.0	573.3	558.9	544.6	534.1	524.1	514.5
10°	660.5	654.0	649.2	639.6	634.8	627.0	608.2	594.7	576.8	561.6	541.5
12.5°	740.7	733.3	717.2	710.2	704.1	682.3	663.6	648.3	613.4	603.0	578.1
15°	799.6	783.9	782.2	766.9	766.0	742.1	706.3	689.7	662.7	624.3	598.6
17.5°	863.3	849.3	838.4	820.1	817.5	794.8	768.7	728.1	698.5	661.8	629.1
20°	909.9	902.5	883.8	876.3	861.1	841.9	814.9	764.7	728.5	691.9	651.8
22.5°	947.0	939.6	924.7	914.7	906.0	881.1	848.9	806.1	756.4	708.5	667.1
25°	946.5	944.4	938.3	933.5	926.9	908.6	881.6	840.6	785.2	732.5	674.9
27.5°	892.9	899.0	909.5	914.7	913.4	910.8	895.5	861.1	811.4	748.6	684.1
30°	781.3	803.5	823.2	849.3	857.2	876.3	885.1	865.4	825.8	767.3	695.8
32.5°	647.9	680.1	722.9	737.3	762.1	799.2	840.6	848.0	823.2	778.2	703.3
35°	531.5	558.1	591.2	613.9	636.1	696.3	748.6	793.9	802.2	772.6	701.5
37.5°	439.9	458.7	487.9	507.1	527.5	579.0	652.2	711.1	752.5	753.4	696.7
40°	373.6	381.9	407.2	421.2	440.8	485.3	550.7	627.4	688.0	715.9	684.1
42.5°	316.5	327.4	348.4	358.8	371.5	410.3	453.4	526.2	601.2	661.0	660.5
45°	282.5	290.4	300.0	308.7	323.1	346.2	395.4	449.9	521.9	589.5	616.1
47.5°	252.4	259.9	269.4	272.1	281.7	303.4	333.5	381.1	448.2	515.3	565.5
50°	227.2	233.3	239.8	244.6	249.0	266.8	289.5	329.6	383.2	448.2	510.5
52.5°	207.5	211.9	217.6	220.2	224.1	237.2	254.6	284.3	328.3	387.6	448.2
55°	189.2	192.3	195.8	200.1	201.9	211.5	225.0	250.3	283.0	336.1	393.7
57.5°	172.2	173.5	175.7	178.3	180.5	188.8	200.6	217.6	246.3	287.3	341.8
60°	153.0	156.5	157.8	160.4	161.8	168.3	177.4	191.8	214.1	249.4	290.4
62.5°	136.9	139.1	141.3	142.6	145.6	147.8	155.2	168.3	186.6	212.8	249.8
65°	122.5	123.4	124.7	126.0	126.9	129.5	136.5	145.2	159.1	182.2	211.0
67.5°	105.9	106.8	108.6	109.0	109.9	113.4	117.3	124.7	136.5	153.9	177.4
70°	89.8	91.1	92.0	92.9	94.2	95.5	99.8	105.9	115.1	127.3	145.6
72.5°	75.9	77.2	77.2	78.0	77.6	79.4	83.7	88.1	94.2	104.2	120.3
75°	61.9	61.9	62.8	63.2	63.7	65.4	67.1	70.6	75.4	83.3	93.3
77.5°	48.8	48.4	49.3	49.3	49.3	50.6	52.3	54.1	57.1	62.8	70.6
80°	35.8	35.8	36.6	37.1	36.2	36.6	37.5	39.2	41.4	45.3	49.7
82.5°	23.5	25.3	24.9	25.3	24.9	25.7	26.2	26.6	27.5	29.2	32.3
85°	14.4	14.4	14.4	14.8	14.4	14.8	14.8	14.8	15.3	16.1	17.4
87.5°	6.1	6.1	6.1	6.5	6.1	6.1	6.5	6.1	6.5	6.5	7.0
90°	16.0	15.8	15.5	15.4	15.2	14.7	14.2	13.7	13.2	11.6	10.0
92.5°	18.4	18.3	18.2	18.1	17.7	16.8	16.0	15.1	14.3	13.2	12.1
95°	20.9	20.9	20.9	20.9	20.5	19.6	18.7	17.9	17.0	15.7	14.3
97.5°	22.3	22.2	22.1	22.0	21.5	20.5	19.6	18.6	17.6	23.8	30.0
100°	22.8	22.7	22.6	22.5	22.0	21.0	20.1	19.1	18.1	37.1	56.2
102.5°	23.1	22.9	22.6	22.5	24.5	28.6	32.6	36.7	40.7	61.9	83.2
105°	23.7	23.5	23.2	23.1	33.9	55.5	77.1	98.7	120.3	131.3	142.3
107.5°	89.1	105.1	121.1	129.1	138.5	157.3	176.1	194.9	213.7	211.9	210.1
110°	186.0	203.5	221.0	229.7	231.7	235.7	239.8	243.8	247.8	246.4	245.1

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	286.8	287.0	287.3	287.4	286.8	285.7	284.6	283.5	282.4	281.1	279.7
115°	322.1	321.6	321.1	320.9	320.3	319.1	317.8	316.6	315.4	314.3	313.2
117.5°	352.5	352.4	352.3	352.2	351.7	350.7	349.8	348.8	347.8	347.2	346.6
120°	383.5	383.5	383.5	383.5	383.0	382.0	381.1	380.1	379.1	378.7	378.4
122.5°	413.5	413.4	413.3	413.2	412.9	412.3	411.6	411.0	410.4	409.9	409.4
125°	441.2	441.0	440.7	440.6	440.5	440.2	440.0	439.7	439.5	439.0	438.5
127.5°	469.7	469.9	470.2	470.3	470.1	469.8	469.4	469.1	468.7	468.1	467.5
130°	496.1	496.3	496.6	496.7	496.5	496.0	495.5	495.0	494.5	494.0	493.5
132.5°	520.5	520.9	521.2	521.4	521.2	520.7	520.2	519.7	519.2	518.8	518.5
135°	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.0	543.5
137.5°	568.6	568.8	569.1	569.2	568.9	568.3	567.7	567.1	566.5	566.3	566.0
140°	589.5	589.7	590.0	590.1	589.9	589.4	588.9	588.4	587.9	587.5	587.1
142.5°	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	607.8	607.5
145°	628.0	628.0	628.0	628.0	627.9	627.6	627.4	627.1	626.9	626.7	626.4
147.5°	643.5	644.1	644.7	645.0	644.9	644.6	644.4	644.1	643.9	643.7	643.4
150°	659.5	659.9	660.2	660.4	660.3	660.0	659.8	659.5	659.3	659.1	658.8
152.5°	673.2	673.8	674.4	674.7	674.5	674.0	673.5	673.0	672.5	672.4	672.3
155°	685.5	686.2	686.9	687.3	687.0	686.4	685.8	685.2	684.6	684.5	684.3
157.5°	696.5	697.4	698.4	698.9	698.5	697.8	697.1	696.3	695.6	695.7	695.8
160°	706.1	706.9	707.8	708.2	707.8	707.1	706.4	705.6	704.9	705.0	705.2
162.5°	715.2	715.9	716.6	717.0	716.6	715.7	714.9	714.0	713.2	713.3	713.4
165°	722.6	723.4	724.3	724.7	724.2	723.2	722.3	721.3	720.3	720.4	720.6
167.5°	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	726.3	726.3
170°	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	731.3	731.3
172.5°	736.2	737.3	738.4	739.0	738.5	737.5	736.6	735.6	734.6	734.5	734.3
175°	738.8	739.7	740.7	741.2	740.8	739.9	739.0	738.2	737.3	737.2	737.1
177.5°	739.7	741.0	742.2	742.8	742.3	741.3	740.4	739.4	738.4	738.3	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	462.2	460.8	460.8	460.0	457.4	452.6	452.1	453.0	450.4	447.8	443.8
5°	484.8	476.5	473.9	471.3	466.1	457.4	453.9	450.8	446.0	440.4	434.2
7.5°	504.0	492.2	488.7	484.0	473.5	461.3	453.4	446.9	440.4	432.5	425.1
10°	528.0	511.0	502.7	495.7	481.3	464.3	452.6	443.0	432.5	422.9	413.3
12.5°	555.0	527.5	524.9	507.9	491.4	466.1	451.7	437.7	423.8	412.0	402.0
15°	577.7	547.6	536.7	525.4	493.5	462.2	448.2	432.5	416.4	403.7	388.9
17.5°	592.1	567.2	544.1	528.9	495.7	467.8	440.8	422.9	405.9	388.5	376.3
20°	609.5	573.3	553.3	532.8	500.1	463.5	436.4	414.2	393.3	377.6	362.7
22.5°	627.0	578.1	561.6	539.3	501.0	459.1	428.6	406.3	382.4	366.7	350.5
25°	625.2	585.1	557.6	538.9	492.2	455.2	419.4	393.3	371.0	351.0	334.8
27.5°	626.5	577.3	549.3	527.5	486.1	449.5	409.8	382.4	359.3	338.3	321.3
30°	627.0	565.5	541.1	514.9	474.8	436.0	398.9	371.0	346.6	323.9	308.7
32.5°	625.6	555.9	525.4	501.8	456.9	422.9	386.3	356.6	331.8	310.9	296.5
35°	622.6	544.6	509.2	479.6	438.6	404.2	374.5	344.0	317.4	298.2	281.7
37.5°	614.3	532.3	492.2	463.0	417.2	382.4	356.2	330.9	305.2	282.5	268.6
40°	608.2	515.8	475.2	443.4	394.1	360.1	338.3	314.3	289.1	268.6	255.1
42.5°	594.3	500.1	457.8	419.9	371.5	336.6	316.1	296.9	275.1	255.1	242.8
45°	571.6	483.1	436.4	398.1	346.6	313.5	294.7	279.0	259.9	240.7	228.5
47.5°	539.8	458.7	413.8	375.4	322.2	288.6	269.9	258.1	242.8	226.7	216.3
50°	505.3	432.1	390.6	352.7	298.7	266.0	247.6	236.7	226.7	211.9	201.9
52.5°	460.4	403.7	364.1	327.9	273.4	242.0	225.8	218.0	207.5	197.1	188.3
55°	416.8	367.1	334.4	300.0	248.5	219.3	203.6	195.3	189.2	180.5	173.5
57.5°	366.2	333.1	303.0	271.6	225.4	198.8	184.0	174.0	170.0	166.1	159.6
60°	319.6	294.3	269.9	243.7	201.4	177.4	163.1	155.2	151.3	148.7	144.3
62.5°	276.9	257.2	236.3	215.4	177.0	155.2	144.3	136.5	133.0	132.5	128.6
65°	235.9	221.9	204.9	184.4	154.3	135.2	124.7	119.9	116.0	116.0	112.9
67.5°	194.9	185.3	171.8	157.4	133.8	116.0	106.4	102.0	99.8	99.8	97.7
70°	162.2	155.6	143.4	130.8	110.3	96.8	89.4	85.5	84.1	84.6	82.8
72.5°	131.7	124.7	114.7	105.5	90.3	80.2	75.0	70.6	68.5	68.9	68.5
75°	102.0	98.5	89.8	82.8	70.6	63.7	58.9	56.7	54.9	55.4	54.5
77.5°	76.7	71.5	66.7	61.9	54.5	48.8	44.9	42.7	41.4	41.4	41.4
80°	52.3	51.4	47.5	44.9	38.8	34.4	31.4	31.0	29.6	29.6	29.6
82.5°	34.0	31.8	29.6	27.9	24.4	21.8	20.5	19.6	19.2	18.7	19.6
85°	18.7	17.4	16.6	14.8	13.5	12.2	10.9	10.5	10.0	10.5	10.0
87.5°	7.4	6.1	6.1	5.7	5.2	4.8	4.8	3.9	3.9	3.5	3.5
90°	8.4	6.8	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.0	9.9	9.3	9.7	10.4	11.1	11.9	12.6	11.9	11.1	10.4
95°	13.0	11.7	11.0	13.5	18.5	23.5	28.5	33.5	28.5	23.5	18.5
97.5°	36.3	42.5	45.6	47.3	50.7	54.2	57.6	61.0	57.6	54.2	50.7
100°	75.2	94.3	103.8	102.6	100.2	97.7	95.3	92.9	95.3	97.7	100.2
102.5°	104.4	125.7	136.3	135.5	133.9	132.3	130.7	129.1	130.7	132.3	133.9
105°	153.3	164.3	169.8	169.1	167.8	166.4	165.1	163.7	165.1	166.4	167.8
107.5°	208.2	206.4	205.5	204.9	203.8	202.7	201.6	200.5	201.6	202.7	203.8
110°	243.7	242.4	241.7	241.2	240.3	239.3	238.4	237.4	238.4	239.3	240.3

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.4	277.1	276.4	276.0	275.1	274.2	273.4	272.5	273.4	274.2	275.1
115°	312.1	311.0	310.4	310.0	309.3	308.6	307.8	307.1	307.8	308.6	309.3
117.5°	345.9	345.3	345.0	344.6	343.7	342.9	342.0	341.2	342.0	342.9	343.7
120°	378.0	377.7	377.5	376.9	375.8	374.7	373.6	372.5	373.6	374.7	375.8
122.5°	408.9	408.4	408.2	407.8	406.9	406.1	405.2	404.4	405.2	406.1	406.9
125°	438.0	437.5	437.3	436.8	435.8	434.9	433.9	432.9	433.9	434.9	435.8
127.5°	466.8	466.2	465.9	465.4	464.4	463.5	462.5	461.5	462.5	463.5	464.4
130°	493.0	492.5	492.3	491.8	490.8	489.9	488.9	487.9	488.9	489.9	490.8
132.5°	518.1	517.8	517.6	517.1	516.1	515.2	514.2	513.2	514.2	515.2	516.1
135°	543.0	542.5	542.3	541.9	541.2	540.5	539.7	539.0	539.7	540.5	541.2
137.5°	565.8	565.5	565.4	564.9	563.9	563.0	562.0	561.0	562.0	563.0	563.9
140°	586.8	586.4	586.2	585.8	585.1	584.4	583.6	582.9	583.6	584.4	585.1
142.5°	607.1	606.8	606.6	606.2	605.5	604.8	604.0	603.3	604.0	604.8	605.5
145°	626.2	625.9	625.8	625.4	624.5	623.7	622.8	622.0	622.8	623.7	624.5
147.5°	643.2	642.9	642.8	642.5	641.9	641.3	640.7	640.1	640.7	641.3	641.9
150°	658.6	658.3	658.2	658.0	657.7	657.3	657.0	656.6	657.0	657.3	657.7
152.5°	672.2	672.1	672.0	671.9	671.8	671.7	671.5	671.4	671.5	671.7	671.8
155°	684.2	684.1	684.0	684.1	684.4	684.6	684.9	685.1	684.9	684.6	684.4
157.5°	695.9	696.0	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1
160°	705.3	705.4	705.5	705.6	705.7	705.8	705.9	706.0	705.9	705.8	705.7
162.5°	713.5	713.6	713.7	713.9	714.3	714.6	715.0	715.4	715.0	714.6	714.3
165°	720.7	720.8	720.9	721.1	721.4	721.8	722.1	722.5	722.1	721.8	721.4
167.5°	726.3	726.3	726.3	726.5	727.0	727.5	728.0	728.5	728.0	727.5	727.0
170°	731.3	731.3	731.3	731.5	732.0	732.5	733.0	733.5	733.0	732.5	732.0
172.5°	734.2	734.1	734.0	734.3	734.9	735.6	736.2	736.8	736.2	735.6	734.9
175°	737.0	736.9	736.8	737.1	737.7	738.3	738.9	739.5	738.9	738.3	737.7
177.5°	738.1	738.0	737.9	738.2	738.8	739.4	740.0	740.6	740.0	739.4	738.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	443.0	442.5	443.4	440.8	436.4	434.2	428.1	426.8	426.4	426.8	427.3
5°	430.8	430.3	429.0	424.7	419.4	415.5	408.1	407.7	405.0	402.4	403.7
7.5°	419.0	417.2	414.6	409.0	402.0	397.6	391.5	387.2	383.7	381.5	379.7
10°	407.2	404.6	402.0	394.6	385.9	379.3	371.9	368.4	364.5	362.7	361.0
12.5°	392.0	389.3	384.5	375.8	370.6	362.3	354.9	351.4	349.2	345.7	343.6
15°	379.7	374.5	371.9	362.7	351.8	351.0	337.5	336.6	332.2	332.2	328.7
17.5°	365.8	361.9	357.1	347.9	340.1	332.2	325.2	322.6	318.7	317.8	316.1
20°	352.3	347.0	345.3	336.1	327.9	318.3	310.9	308.2	306.5	304.8	306.1
22.5°	338.3	334.0	329.6	321.3	315.2	305.6	301.3	298.7	296.0	295.2	295.6
25°	324.8	320.9	316.5	308.2	301.7	293.9	289.9	288.6	287.3	287.3	286.9
27.5°	311.7	307.8	303.9	296.5	289.9	284.3	281.2	279.9	278.6	279.5	280.3
30°	298.2	294.7	291.2	284.7	279.5	274.2	272.5	271.6	271.2	273.4	273.4
32.5°	286.0	283.0	280.3	274.2	269.0	264.6	263.3	263.8	264.2	265.5	266.4
35°	273.4	271.2	268.6	263.3	259.0	255.1	255.5	255.5	256.4	258.5	260.3
37.5°	262.0	259.0	256.8	252.4	249.0	245.5	246.8	248.1	249.0	251.6	252.4
40°	248.5	247.2	245.5	241.1	238.1	237.6	238.1	238.9	240.7	242.0	243.3
42.5°	237.6	235.9	233.7	230.2	227.6	228.0	228.5	229.3	230.2	232.4	233.7
45°	225.4	224.1	222.4	219.3	217.1	217.6	218.0	218.0	218.9	221.5	222.4
47.5°	211.9	212.3	210.1	207.1	205.8	205.8	205.8	206.7	208.8	209.7	210.1
50°	198.8	197.9	197.5	194.5	193.6	193.1	193.6	194.0	197.1	196.6	197.9
52.5°	184.9	184.9	184.4	182.7	181.4	181.4	180.5	182.7	183.6	184.4	185.7
55°	171.3	170.0	169.6	168.7	167.0	166.5	167.4	170.0	170.9	171.8	173.1
57.5°	156.5	156.5	155.6	154.3	154.3	154.3	154.3	156.1	157.4	158.3	160.9
60°	143.0	141.3	140.0	140.0	140.0	139.5	142.1	142.1	144.7	145.2	146.1
62.5°	126.9	126.0	125.1	125.6	125.1	126.0	126.9	128.6	129.1	130.4	131.7
65°	111.6	111.6	110.7	113.4	111.6	111.6	113.8	113.8	114.7	116.0	117.7
67.5°	96.8	97.2	96.4	96.4	97.2	97.7	98.1	99.8	100.3	102.0	104.2
70°	81.5	82.4	82.8	82.0	82.8	83.7	84.6	85.0	86.8	87.6	88.9
72.5°	68.0	68.9	67.6	68.0	68.5	69.3	69.8	70.6	71.5	74.1	75.0
75°	54.5	54.1	53.6	55.4	54.5	56.2	56.7	56.7	57.6	59.7	60.6
77.5°	41.9	41.9	42.3	41.4	42.7	42.3	42.7	44.0	45.3	45.3	48.8
80°	29.2	30.1	30.1	30.1	30.5	31.0	30.1	32.3	32.7	32.7	34.0
82.5°	18.7	19.2	18.7	19.6	19.6	20.5	20.1	20.5	21.4	22.2	22.7
85°	10.0	10.0	10.9	10.9	10.5	10.9	10.5	10.9	11.8	11.8	12.2
87.5°	3.5	3.5	3.5	3.5	3.9	3.5	3.9	3.9	3.5	3.5	4.8
90°	5.4	6.0	6.8	8.4	10.0	11.6	13.2	13.7	14.2	14.7	15.2
92.5°	9.7	9.3	9.9	11.0	12.1	13.2	14.3	15.1	16.0	16.8	17.7
95°	13.5	11.0	11.7	13.0	14.3	15.7	17.0	17.9	18.7	19.6	20.5
97.5°	47.3	45.6	42.5	36.3	30.0	23.8	17.6	18.6	19.6	20.5	21.5
100°	102.6	103.8	94.3	75.2	56.2	37.1	18.1	19.1	20.1	21.0	22.0
102.5°	135.5	136.3	125.7	104.4	83.2	61.9	40.7	36.7	32.6	28.6	24.5
105°	169.1	169.8	164.3	153.3	142.3	131.3	120.3	98.7	77.1	55.5	33.9
107.5°	204.9	205.5	206.4	208.2	210.1	211.9	213.7	194.9	176.1	157.3	138.5
110°	241.2	241.7	242.4	243.7	245.1	246.4	247.8	243.8	239.8	235.7	231.7

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	276.0	276.4	277.1	278.4	279.7	281.1	282.4	283.5	284.6	285.7	286.8
115°	310.0	310.4	311.0	312.1	313.2	314.3	315.4	316.6	317.8	319.1	320.3
117.5°	344.6	345.0	345.3	345.9	346.6	347.2	347.8	348.8	349.8	350.7	351.7
120°	376.9	377.5	377.7	378.0	378.4	378.7	379.1	380.1	381.1	382.0	383.0
122.5°	407.8	408.2	408.4	408.9	409.4	409.9	410.4	411.0	411.6	412.3	412.9
125°	436.8	437.3	437.5	438.0	438.5	439.0	439.5	439.7	440.0	440.2	440.5
127.5°	465.4	465.9	466.2	466.8	467.5	468.1	468.7	469.1	469.4	469.8	470.1
130°	491.8	492.3	492.5	493.0	493.5	494.0	494.5	495.0	495.5	496.0	496.5
132.5°	517.1	517.6	517.8	518.1	518.5	518.8	519.2	519.7	520.2	520.7	521.2
135°	541.9	542.3	542.5	543.0	543.5	544.0	544.5	544.9	545.2	545.6	545.9
137.5°	564.9	565.4	565.5	565.8	566.0	566.3	566.5	567.1	567.7	568.3	568.9
140°	585.8	586.2	586.4	586.8	587.1	587.5	587.9	588.4	588.9	589.4	589.9
142.5°	606.2	606.6	606.8	607.1	607.5	607.8	608.2	608.6	609.0	609.3	609.7
145°	625.4	625.8	625.9	626.2	626.4	626.7	626.9	627.1	627.4	627.6	627.9
147.5°	642.5	642.8	642.9	643.2	643.4	643.7	643.9	644.1	644.4	644.6	644.9
150°	658.0	658.2	658.3	658.6	658.8	659.1	659.3	659.5	659.8	660.0	660.3
152.5°	671.9	672.0	672.1	672.2	672.3	672.4	672.5	673.0	673.5	674.0	674.5
155°	684.1	684.0	684.1	684.2	684.3	684.5	684.6	685.2	685.8	686.4	687.0
157.5°	696.1	696.1	696.0	695.9	695.8	695.7	695.6	696.3	697.1	697.8	698.5
160°	705.6	705.5	705.4	705.3	705.2	705.0	704.9	705.6	706.4	707.1	707.8
162.5°	713.9	713.7	713.6	713.5	713.4	713.3	713.2	714.0	714.9	715.7	716.6
165°	721.1	720.9	720.8	720.7	720.6	720.4	720.3	721.3	722.3	723.2	724.2
167.5°	726.5	726.3	726.3	726.3	726.3	726.3	726.3	727.3	728.3	729.2	730.2
170°	731.5	731.3	731.3	731.3	731.3	731.3	731.3	732.3	733.3	734.2	735.2
172.5°	734.3	734.0	734.1	734.2	734.3	734.5	734.6	735.6	736.6	737.5	738.5
175°	737.1	736.8	736.9	737.0	737.1	737.2	737.3	738.2	739.0	739.9	740.8
177.5°	738.2	737.9	738.0	738.1	738.2	738.3	738.4	739.4	740.4	741.3	742.3
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	426.8	427.3	425.5	424.2	427.7	425.5	425.5	426.0	425.1	426.4	426.0
5°	402.9	403.3	400.2	401.1	399.4	398.9	398.5	401.1	400.7	400.2	401.1
7.5°	379.3	379.3	378.0	377.1	377.1	375.8	377.6	377.1	378.0	378.0	379.3
10°	359.7	360.6	358.4	356.2	355.8	356.2	356.2	356.6	357.1	360.1	359.7
12.5°	343.6	342.3	341.8	340.5	338.3	337.5	336.6	341.4	340.1	340.1	340.1
15°	325.7	328.7	328.3	324.4	323.5	325.2	324.4	324.4	328.7	328.3	327.9
17.5°	316.1	315.2	314.3	312.2	312.6	312.2	312.6	312.6	315.2	315.2	315.2
20°	305.2	303.4	303.4	302.6	302.6	301.3	303.0	303.4	305.2	305.2	305.6
22.5°	295.6	294.3	294.3	293.9	294.7	293.0	294.7	295.2	295.2	296.5	296.5
25°	287.3	286.4	286.4	287.3	287.3	287.3	287.3	289.1	287.8	288.2	287.8
27.5°	279.9	280.3	280.8	281.2	280.8	281.2	281.7	282.5	283.0	282.5	281.7
30°	272.9	274.2	274.7	274.7	275.5	276.0	276.4	276.4	276.9	275.5	276.4
32.5°	267.7	267.7	268.6	269.0	269.9	270.3	270.3	271.2	270.8	269.4	269.9
35°	260.3	260.3	262.0	262.9	264.2	263.8	264.2	264.2	264.6	263.8	262.5
37.5°	252.9	253.7	253.7	255.5	255.9	256.4	255.9	256.8	256.4	255.5	255.1
40°	244.2	243.7	244.2	245.5	245.9	245.9	245.9	246.8	246.8	246.8	246.3
42.5°	233.3	234.6	234.1	235.4	235.0	235.0	235.9	236.7	237.2	235.9	236.3
45°	222.8	222.8	223.7	223.7	224.1	224.1	225.8	225.0	225.8	225.0	225.4
47.5°	211.5	211.9	211.9	212.3	213.2	214.1	213.2	213.6	213.6	214.1	213.2
50°	198.8	198.8	199.7	201.0	202.7	201.9	201.4	203.2	201.9	201.9	201.0
52.5°	185.7	187.0	187.5	188.8	190.1	190.5	191.0	190.1	190.5	189.2	189.7
55°	173.1	173.5	175.3	176.6	177.9	177.9	177.4	177.9	178.3	176.6	176.6
57.5°	160.4	161.8	163.5	163.5	165.2	165.2	164.8	164.8	165.2	163.9	163.5
60°	146.9	148.2	150.4	150.4	153.0	153.5	152.6	151.7	151.7	150.4	150.9
62.5°	132.5	133.8	135.2	137.3	139.1	138.2	140.0	138.2	138.6	136.0	136.0
65°	119.9	120.3	122.5	124.7	124.7	125.6	124.7	125.1	123.8	123.8	122.1
67.5°	105.1	105.1	107.3	109.4	111.6	111.6	111.6	110.3	110.3	109.0	109.0
70°	92.0	91.6	93.7	95.0	96.4	96.8	95.9	95.5	94.6	93.3	92.9
72.5°	75.9	76.7	78.9	79.8	82.0	81.5	83.7	81.1	81.1	78.9	78.5
75°	61.5	62.3	64.5	65.8	67.1	67.1	68.5	67.1	65.4	64.5	64.1
77.5°	48.8	48.4	50.1	52.3	52.8	52.3	53.2	52.8	51.0	51.0	50.1
80°	34.9	36.2	37.9	37.5	39.2	38.8	38.8	37.9	37.9	36.6	37.5
82.5°	23.1	24.4	24.9	24.4	24.9	25.7	26.2	25.7	25.7	24.9	25.3
85°	12.2	12.2	13.1	13.5	13.1	13.1	13.5	14.8	14.0	13.1	14.0
87.5°	3.9	3.5	3.5	3.9	3.5	3.5	3.9	3.9	4.4	4.4	4.4
90°	15.4	15.5	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.5	15.4
92.5°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
95°	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	22.0	22.1	22.2	22.3	22.4	22.5	22.4	22.3	22.2	22.1	22.0
100°	22.5	22.6	22.7	22.8	23.0	23.1	23.0	22.8	22.7	22.6	22.5
102.5°	22.5	22.6	22.9	23.1	23.4	23.6	23.4	23.1	22.9	22.6	22.5
105°	23.1	23.2	23.5	23.7	24.0	24.2	24.0	23.7	23.5	23.2	23.1
107.5°	129.1	121.1	105.1	89.1	73.1	57.1	73.1	89.1	105.1	121.1	129.1
110°	229.7	221.0	203.5	186.0	168.6	151.1	168.6	186.0	203.5	221.0	229.7

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	287.4	287.3	287.0	286.8	286.5	286.3	286.5	286.8	287.0	287.3	287.4
115°	320.9	321.1	321.6	322.1	322.6	323.1	322.6	322.1	321.6	321.1	320.9
117.5°	352.2	352.3	352.4	352.5	352.6	352.7	352.6	352.5	352.4	352.3	352.2
120°	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	413.2	413.3	413.4	413.5	413.6	413.7	413.6	413.5	413.4	413.3	413.2
125°	440.6	440.7	441.0	441.2	441.5	441.7	441.5	441.2	441.0	440.7	440.6
127.5°	470.3	470.2	469.9	469.7	469.4	469.2	469.4	469.7	469.9	470.2	470.3
130°	496.7	496.6	496.3	496.1	495.8	495.6	495.8	496.1	496.3	496.6	496.7
132.5°	521.4	521.2	520.9	520.5	520.2	519.8	520.2	520.5	520.9	521.2	521.4
135°	546.1	545.9	545.6	545.2	544.9	544.5	544.9	545.2	545.6	545.9	546.1
137.5°	569.2	569.1	568.8	568.6	568.3	568.1	568.3	568.6	568.8	569.1	569.2
140°	590.1	590.0	589.7	589.5	589.2	589.0	589.2	589.5	589.7	590.0	590.1
142.5°	609.9	609.7	609.3	609.0	608.6	608.2	608.6	609.0	609.3	609.7	609.9
145°	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	645.0	644.7	644.1	643.5	642.9	642.3	642.9	643.5	644.1	644.7	645.0
150°	660.4	660.2	659.9	659.5	659.2	658.8	659.2	659.5	659.9	660.2	660.4
152.5°	674.7	674.4	673.8	673.2	672.6	672.0	672.6	673.2	673.8	674.4	674.7
155°	687.3	686.9	686.2	685.5	684.7	684.0	684.7	685.5	686.2	686.9	687.3
157.5°	698.9	698.4	697.4	696.5	695.5	694.5	695.5	696.5	697.4	698.4	698.9
160°	708.2	707.8	706.9	706.1	705.2	704.4	705.2	706.1	706.9	707.8	708.2
162.5°	717.0	716.6	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	717.0
165°	724.7	724.3	723.4	722.6	721.7	720.9	721.7	722.6	723.4	724.3	724.7
167.5°	730.7	730.2	729.2	728.3	727.3	726.3	727.3	728.3	729.2	730.2	730.7
170°	735.7	735.2	734.2	733.3	732.3	731.3	732.3	733.3	734.2	735.2	735.7
172.5°	739.0	738.4	737.3	736.2	735.1	734.0	735.1	736.2	737.3	738.4	739.0
175°	741.2	740.7	739.7	738.8	737.8	736.8	737.8	738.8	739.7	740.7	741.2
177.5°	742.8	742.2	741.0	739.7	738.5	737.3	738.5	739.7	741.0	742.2	742.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	427.3	428.1	428.6	426.8	425.5	427.7	430.8	432.9	434.7	436.9	438.2
5°	402.0	405.0	405.0	405.9	407.2	409.4	415.1	419.0	422.5	425.1	427.3
7.5°	380.6	382.8	384.1	386.3	388.5	391.5	398.1	403.7	409.0	412.0	415.5
10°	361.4	363.2	365.4	366.7	370.6	375.0	383.2	388.0	394.1	398.9	403.3
12.5°	343.1	349.2	350.5	350.1	353.6	358.4	366.7	374.1	380.6	385.4	390.2
15°	330.0	332.2	334.8	334.4	341.8	343.1	350.1	358.8	367.5	370.6	375.0
17.5°	315.7	319.1	321.8	323.1	325.2	330.0	336.6	343.1	354.5	354.9	366.2
20°	304.3	307.8	309.6	311.3	312.6	318.3	323.9	331.4	340.5	345.3	351.4
22.5°	296.9	298.7	300.0	301.3	303.0	306.1	313.0	321.3	327.4	332.7	336.6
25°	288.2	289.9	291.7	292.6	293.9	295.6	300.8	307.4	316.1	319.6	323.5
27.5°	282.1	282.1	283.0	283.0	284.7	286.4	290.4	296.5	303.4	307.8	313.0
30°	275.5	275.1	275.5	275.1	274.7	277.3	280.8	286.0	290.8	296.0	299.5
32.5°	269.0	268.6	268.6	269.0	267.3	268.6	270.3	275.1	280.3	283.0	286.9
35°	262.0	261.2	261.2	261.2	260.3	259.4	261.2	265.5	269.0	272.5	275.5
37.5°	255.1	253.7	253.7	252.9	252.0	250.7	250.7	254.2	259.0	260.3	264.2
40°	245.5	245.5	244.6	244.2	243.3	242.4	241.1	244.2	248.5	249.8	252.9
42.5°	235.9	234.6	234.1	234.1	234.1	232.8	231.9	234.1	236.7	238.9	240.7
45°	225.0	224.1	224.5	224.1	223.2	222.8	222.4	223.2	226.3	227.2	229.3
47.5°	213.2	212.8	212.8	212.3	211.9	212.3	210.6	212.8	213.6	214.5	216.3
50°	201.0	200.6	200.1	199.7	199.7	200.1	199.7	199.7	201.4	202.3	204.0
52.5°	188.8	187.5	187.5	187.0	187.0	186.2	187.0	187.5	188.3	189.2	190.1
55°	175.7	175.7	174.4	174.4	173.5	173.5	174.0	173.5	175.3	176.1	176.1
57.5°	163.1	161.3	161.8	160.9	160.0	159.6	159.6	160.4	161.3	161.3	162.2
60°	149.5	147.8	147.4	145.6	146.5	145.2	145.6	145.6	147.4	146.5	147.4
62.5°	136.0	133.8	132.5	131.7	131.7	132.1	131.2	130.8	131.7	132.5	134.3
65°	121.6	120.3	119.0	117.7	117.7	117.3	118.2	116.8	116.4	116.8	117.7
67.5°	106.8	105.5	104.2	102.9	103.3	102.0	101.1	102.5	101.6	102.0	102.9
70°	92.4	91.6	88.9	88.1	87.6	88.1	87.6	86.8	88.1	87.6	88.1
72.5°	78.0	77.2	75.9	73.7	73.7	73.2	72.8	72.8	72.4	72.4	72.4
75°	64.1	62.3	61.0	60.6	59.7	59.3	58.9	58.0	58.4	58.9	58.0
77.5°	49.7	47.5	47.1	47.1	45.8	45.8	46.2	45.8	45.3	45.3	45.3
80°	36.6	34.9	34.9	34.0	33.1	33.1	33.1	33.1	32.7	32.3	32.7
82.5°	23.5	23.1	22.7	22.7	23.5	21.8	22.7	22.2	21.8	21.8	21.4
85°	13.1	13.5	13.1	13.5	12.6	13.1	13.1	13.1	12.6	13.1	12.2
87.5°	4.8	4.8	4.8	5.2	5.2	5.2	5.2	5.2	5.7	5.2	5.2
90°	15.2	14.7	14.2	13.7	13.2	11.6	10.0	8.4	6.8	6.0	5.4
92.5°	17.7	16.8	16.0	15.1	14.3	13.2	12.1	11.0	9.9	9.3	9.7
95°	20.5	19.6	18.7	17.9	17.0	15.7	14.3	13.0	11.7	11.0	13.5
97.5°	21.5	20.5	19.6	18.6	17.6	23.8	30.0	36.3	42.5	45.6	47.3
100°	22.0	21.0	20.1	19.1	18.1	37.1	56.2	75.2	94.3	103.8	102.6
102.5°	24.5	28.6	32.6	36.7	40.7	61.9	83.2	104.4	125.7	136.3	135.5
105°	33.9	55.5	77.1	98.7	120.3	131.3	142.3	153.3	164.3	169.8	169.1
107.5°	138.5	157.3	176.1	194.9	213.7	211.9	210.1	208.2	206.4	205.5	204.9
110°	231.7	235.7	239.8	243.8	247.8	246.4	245.1	243.7	242.4	241.7	241.2

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	286.8	285.7	284.6	283.5	282.4	281.1	279.7	278.4	277.1	276.4	276.0
115°	320.3	319.1	317.8	316.6	315.4	314.3	313.2	312.1	311.0	310.4	310.0
117.5°	351.7	350.7	349.8	348.8	347.8	347.2	346.6	345.9	345.3	345.0	344.6
120°	383.0	382.0	381.1	380.1	379.1	378.7	378.4	378.0	377.7	377.5	376.9
122.5°	412.9	412.3	411.6	411.0	410.4	409.9	409.4	408.9	408.4	408.2	407.8
125°	440.5	440.2	440.0	439.7	439.5	439.0	438.5	438.0	437.5	437.3	436.8
127.5°	470.1	469.8	469.4	469.1	468.7	468.1	467.5	466.8	466.2	465.9	465.4
130°	496.5	496.0	495.5	495.0	494.5	494.0	493.5	493.0	492.5	492.3	491.8
132.5°	521.2	520.7	520.2	519.7	519.2	518.8	518.5	518.1	517.8	517.6	517.1
135°	545.9	545.6	545.2	544.9	544.5	544.0	543.5	543.0	542.5	542.3	541.9
137.5°	568.9	568.3	567.7	567.1	566.5	566.3	566.0	565.8	565.5	565.4	564.9
140°	589.9	589.4	588.9	588.4	587.9	587.5	587.1	586.8	586.4	586.2	585.8
142.5°	609.7	609.3	609.0	608.6	608.2	607.8	607.5	607.1	606.8	606.6	606.2
145°	627.9	627.6	627.4	627.1	626.9	626.7	626.4	626.2	625.9	625.8	625.4
147.5°	644.9	644.6	644.4	644.1	643.9	643.7	643.4	643.2	642.9	642.8	642.5
150°	660.3	660.0	659.8	659.5	659.3	659.1	658.8	658.6	658.3	658.2	658.0
152.5°	674.5	674.0	673.5	673.0	672.5	672.4	672.3	672.2	672.1	672.0	671.9
155°	687.0	686.4	685.8	685.2	684.6	684.5	684.3	684.2	684.1	684.0	684.1
157.5°	698.5	697.8	697.1	696.3	695.6	695.7	695.8	695.9	696.0	696.1	696.1
160°	707.8	707.1	706.4	705.6	704.9	705.0	705.2	705.3	705.4	705.5	705.6
162.5°	716.6	715.7	714.9	714.0	713.2	713.3	713.4	713.5	713.6	713.7	713.9
165°	724.2	723.2	722.3	721.3	720.3	720.4	720.6	720.7	720.8	720.9	721.1
167.5°	730.2	729.2	728.3	727.3	726.3	726.3	726.3	726.3	726.3	726.3	726.5
170°	735.2	734.2	733.3	732.3	731.3	731.3	731.3	731.3	731.3	731.3	731.5
172.5°	738.5	737.5	736.6	735.6	734.6	734.5	734.3	734.2	734.1	734.0	734.3
175°	740.8	739.9	739.0	738.2	737.3	737.2	737.1	737.0	736.9	736.8	737.1
177.5°	742.3	741.3	740.4	739.4	738.4	738.3	738.2	738.1	738.0	737.9	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	449.9	449.9	449.9	449.9
2.5°	440.4	441.7	446.0	451.3
5°	431.6	435.1	441.2	449.5
7.5°	422.0	427.3	436.0	446.5
10°	411.1	418.6	429.5	442.5
12.5°	399.4	409.0	422.9	436.4
15°	392.0	401.5	414.2	429.0
17.5°	377.6	388.9	402.0	422.9
20°	362.7	375.4	392.4	413.3
22.5°	351.4	364.9	381.1	403.3
25°	337.9	351.8	369.3	392.4
27.5°	323.5	337.5	357.1	381.5
30°	312.6	326.1	344.9	371.0
32.5°	299.5	312.6	332.2	359.7
35°	284.7	299.5	318.3	346.2
37.5°	273.4	286.9	306.5	333.1
40°	261.2	272.9	292.1	318.3
42.5°	248.1	261.2	277.7	303.9
45°	235.9	245.5	262.5	287.3
47.5°	222.8	233.7	246.8	266.0
50°	208.8	218.0	232.4	245.5
52.5°	195.3	202.7	214.9	225.0
55°	180.9	188.3	197.5	203.6
57.5°	167.4	172.7	178.8	182.7
60°	150.9	156.1	160.0	163.9
62.5°	136.0	140.0	142.1	144.3
65°	120.8	122.9	124.3	126.0
67.5°	104.2	106.4	106.8	109.4
70°	88.9	89.4	90.3	91.6
72.5°	74.6	75.4	75.0	75.9
75°	59.7	60.6	59.7	60.6
77.5°	45.3	46.2	46.2	47.5
80°	32.7	33.1	33.6	33.6
82.5°	21.4	22.7	21.8	22.2
85°	12.2	12.6	12.6	13.1
87.5°	5.7	6.1	5.7	6.5
90°	4.2	2.9	1.7	0.5
92.5°	10.4	11.1	11.9	12.6
95°	18.5	23.5	28.5	33.5
97.5°	50.7	54.2	57.6	61.0
100°	100.2	97.7	95.3	92.9
102.5°	133.9	132.3	130.7	129.1
105°	167.8	166.4	165.1	163.7
107.5°	203.8	202.7	201.6	200.5
110°	240.3	239.3	238.4	237.4



TEST NUMBER: P1011625

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	275.1	274.2	273.4	272.5
115°	309.3	308.6	307.8	307.1
117.5°	343.7	342.9	342.0	341.2
120°	375.8	374.7	373.6	372.5
122.5°	406.9	406.1	405.2	404.4
125°	435.8	434.9	433.9	432.9
127.5°	464.4	463.5	462.5	461.5
130°	490.8	489.9	488.9	487.9
132.5°	516.1	515.2	514.2	513.2
135°	541.2	540.5	539.7	539.0
137.5°	563.9	563.0	562.0	561.0
140°	585.1	584.4	583.6	582.9
142.5°	605.5	604.8	604.0	603.3
145°	624.5	623.7	622.8	622.0
147.5°	641.9	641.3	640.7	640.1
150°	657.7	657.3	657.0	656.6
152.5°	671.8	671.7	671.5	671.4
155°	684.4	684.6	684.9	685.1
157.5°	696.1	696.1	696.1	696.1
160°	705.7	705.8	705.9	706.0
162.5°	714.3	714.6	715.0	715.4
165°	721.4	721.8	722.1	722.5
167.5°	727.0	727.5	728.0	728.5
170°	732.0	732.5	733.0	733.5
172.5°	734.9	735.6	736.2	736.8
175°	737.7	738.3	738.9	739.5
177.5°	738.8	739.4	740.0	740.6
180°	739.5	739.5	739.5	739.5

(END OF REPORT)