

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011904

Luminaire Tested: S123DIP-B775D1025UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011904
REPORT IS A COMBINATION OF REPORTS P990243 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB30-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7336.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	46	45	44			38
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	41	39	37			32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32			28
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28			24
5	68	56	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24			21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21			18
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	24	21	19			16
8	54	42	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17			15
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	21	18	15			13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11694	11694	11694	11694
5°	11702	13475	11736	10057
10°	11627	16305	11639	8781
15°	11467	19337	11560	7904
20°	11329	22263	11353	7273
25°	11123	22824	11148	6945
30°	10977	18858	10977	6729
35°	10795	12611	10727	6538
40°	10577	9103	10446	6246
45°	10304	7211	10007	5883
50°	9638	6125	9295	5527
55°	8907	5382	8545	5130
60°	8167	4686	7734	4713
65°	7354	4013	6998	4157
70°	6511	3330	6075	3504
75°	5565	2511	5208	2704
80°	4403	1676	4055	1777
85°	3035	769	2430	700

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18860 cd/sqm

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.8	1.5
10°-20°	343.2	4.7
20°-30°	577.4	7.9
30°-40°	652.6	8.9
40°-50°	584.5	8.0
50°-60°	471.8	6.4
60°-70°	328.8	4.5
70°-80°	172.6	2.4
80°-90°	44.0	0.6
90°-100°	46.9	0.6
100°-110°	226.7	3.1
110°-120°	555.6	7.6
120°-130°	705.4	9.6
130°-140°	753.5	10.3
140°-150°	704.6	9.6
150°-160°	568.4	7.7
160°-170°	366.8	5.0
170°-180°	126.4	1.7
0°-30°	1027.5	14.0
0°-40°	1680.0	22.9
0°-60°	2736.3	37.3
0°-90°	3281.7	44.7
90°-120°	829.3	11.3
90°-150°	2992.8	40.8
90°-180°	4054.0	55.3
0°-180°	7336.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1086	1086	1086	1086	1086	
5°	1085	1291	1088	963	1085	103
15°	1036	1921	1044	785	1036	293
25°	948	2280	950	694	948	437
35°	836	1228	831	637	836	523
45°	694	663	674	541	694	531
55°	492	451	472	430	492	440
65°	304	293	290	303	304	303
75°	146	150	137	162	146	157
85°	32	35	25	32	32	36
90°	1	30	1	30	1	6
95°	60	38	60	38	60	72
105°	294	44	294	44	294	312
115°	552	581	552	581	552	545
125°	779	794	779	794	779	696
135°	969	979	969	979	969	746
145°	1118	1129	1118	1129	1118	700
155°	1232	1230	1232	1230	1232	568
165°	1299	1296	1299	1296	1299	367
175°	1330	1325	1330	1325	1330	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1089.6	1098.0	1102.2	1108.5	1114.8	1124.3	1127.5	1132.7	1130.6	1134.8	1137.0
5°	1085.4	1100.1	1112.7	1128.5	1143.3	1153.8	1164.3	1181.2	1193.8	1195.9	1205.4
7.5°	1078.0	1099.1	1121.2	1143.3	1171.7	1188.5	1207.5	1230.6	1249.6	1280.1	1291.7
10°	1068.5	1098.0	1129.6	1160.1	1199.1	1225.4	1248.5	1287.5	1326.4	1358.0	1387.5
12.5°	1053.8	1090.6	1131.7	1177.0	1227.5	1258.0	1289.6	1341.2	1400.1	1448.6	1480.1
15°	1035.9	1082.2	1134.8	1183.3	1239.1	1295.9	1329.6	1387.5	1471.7	1517.0	1598.1
17.5°	1021.2	1068.5	1121.2	1197.0	1272.8	1329.6	1353.8	1460.1	1518.0	1593.8	1685.4
20°	998.0	1058.0	1125.4	1201.2	1299.1	1333.8	1383.3	1490.7	1562.3	1661.2	1773.9
22.5°	973.8	1038.0	1119.1	1198.0	1307.5	1344.3	1411.7	1497.0	1610.7	1708.6	1832.8
25°	947.5	1016.9	1099.1	1192.7	1300.1	1353.8	1417.0	1522.3	1645.4	1768.6	1883.3
27.5°	921.1	996.9	1082.2	1175.9	1280.1	1343.3	1406.5	1515.9	1673.8	1807.5	1953.9
30°	895.9	971.7	1056.9	1152.7	1262.2	1323.3	1383.3	1520.2	1696.0	1846.5	1993.9
32.5°	868.5	946.4	1035.9	1115.9	1226.4	1291.7	1359.1	1520.2	1709.6	1869.7	2004.4
35°	835.9	915.9	992.7	1072.7	1182.2	1254.9	1330.7	1509.6	1722.3	1877.0	1960.2
37.5°	804.3	874.8	941.1	1019.0	1133.8	1211.7	1299.1	1497.0	1716.0	1845.4	1868.6
40°	768.5	839.0	892.7	965.4	1086.4	1177.0	1265.4	1480.1	1688.6	1770.7	1703.3
42.5°	733.8	789.6	835.9	906.4	1038.0	1126.4	1222.2	1449.6	1634.9	1651.7	1500.1
45°	693.8	733.8	774.8	854.8	985.4	1075.9	1182.2	1405.4	1548.6	1500.1	1308.6
47.5°	642.2	678.0	723.2	796.9	929.6	1023.3	1124.3	1348.6	1423.3	1322.2	1112.7
50°	592.7	623.2	665.3	736.9	870.6	962.2	1069.6	1259.1	1295.9	1137.0	959.0
52.5°	543.2	566.4	607.4	679.0	812.7	901.1	999.0	1167.5	1146.4	975.9	818.0
55°	491.6	511.6	550.6	621.1	745.3	829.6	923.2	1054.8	1000.1	838.0	711.6
57.5°	441.1	462.2	502.2	561.1	678.0	760.1	834.8	938.0	855.9	726.4	614.8
60°	395.8	413.7	444.3	502.2	608.5	674.8	743.2	813.8	745.3	620.1	534.8
62.5°	348.5	365.3	393.7	446.4	537.9	596.9	651.6	709.5	633.7	542.2	466.4
65°	304.2	317.9	344.2	392.7	467.4	515.8	560.1	600.1	539.0	454.8	397.9
67.5°	264.2	275.8	297.9	341.1	404.3	439.0	474.8	508.5	456.9	389.5	341.1
70°	221.1	230.5	250.6	282.1	332.7	368.5	394.8	420.0	373.7	320.0	287.4
72.5°	183.2	192.7	205.3	237.9	272.7	294.8	323.2	336.9	310.6	266.3	233.7
75°	146.3	153.7	165.3	186.3	219.0	233.7	251.6	262.1	237.9	208.4	188.4
77.5°	114.7	117.9	126.3	141.1	163.2	180.0	193.7	200.0	183.2	164.2	147.4
80°	81.1	85.3	91.6	104.2	121.1	126.3	134.8	142.1	131.6	114.7	104.2
82.5°	53.7	59.0	62.1	67.4	77.9	84.2	86.3	92.6	83.2	76.8	72.6
85°	31.6	33.7	34.7	37.9	43.2	46.3	49.5	50.5	48.4	47.4	43.2
87.5°	15.8	15.8	15.8	17.9	18.9	21.1	22.1	22.1	22.1	21.1	20.0
90°	1.0	3.2	5.4	7.6	9.8	10.9	12.3	15.2	18.0	20.9	23.7
92.5°	22.7	21.4	20.1	18.8	17.5	16.8	17.8	19.8	21.7	23.7	25.7
95°	60.3	51.3	42.3	33.3	24.3	19.8	21.0	23.4	25.8	28.2	30.6
97.5°	109.7	103.5	97.4	91.2	85.1	82.0	76.4	65.2	54.0	42.8	31.6
100°	167.0	171.4	175.8	180.1	184.5	186.7	169.6	135.3	101.1	66.8	32.6
102.5°	232.2	235.0	237.9	240.7	243.6	245.0	225.9	187.7	149.5	111.3	73.1
105°	294.4	296.8	299.2	301.7	304.1	305.3	295.4	275.7	255.9	236.2	216.4
107.5°	360.6	362.6	364.6	366.5	368.5	369.5	371.1	374.4	377.7	381.0	384.3
110°	426.8	428.6	430.3	432.1	433.8	434.7	435.9	438.3	440.8	443.2	445.6

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	490.1	491.6	493.2	494.7	496.2	497.0	498.2	500.6	503.1	505.5	507.9
115°	552.3	553.6	554.9	556.2	557.5	558.2	559.2	561.2	563.1	565.1	567.1
117.5°	613.6	615.1	616.7	618.2	619.7	620.5	621.0	622.1	623.2	624.3	625.4
120°	669.9	671.9	673.9	675.8	677.8	678.8	679.1	679.8	680.5	681.1	681.8
122.5°	727.2	728.7	730.3	731.8	733.3	734.1	734.5	735.4	736.3	737.2	738.1
125°	778.6	780.4	782.1	783.9	785.6	786.5	786.9	787.8	788.7	789.5	790.4
127.5°	830.0	831.8	833.5	835.3	837.0	837.9	838.4	839.5	840.6	841.7	842.8
130°	877.4	879.2	880.9	882.7	884.4	885.3	885.7	886.6	887.5	888.3	889.2
132.5°	922.8	924.6	926.3	928.1	929.8	930.7	931.0	931.7	932.4	933.0	933.7
135°	969.3	970.6	971.9	973.2	974.5	975.2	975.6	976.5	977.4	978.3	979.2
137.5°	1008.8	1010.6	1012.3	1014.1	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7
140°	1048.3	1049.6	1050.9	1052.2	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2
142.5°	1084.9	1086.2	1087.5	1088.8	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8
145°	1118.5	1120.0	1121.6	1123.1	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4
147.5°	1151.1	1152.2	1153.3	1154.4	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0
150°	1180.7	1181.4	1182.0	1182.7	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7
152.5°	1207.4	1207.6	1207.8	1208.1	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4
155°	1232.1	1231.7	1231.2	1230.8	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1
157.5°	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9
160°	1269.6	1269.4	1269.2	1269.0	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7
162.5°	1286.4	1285.8	1285.1	1284.5	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5
165°	1299.3	1298.6	1298.0	1297.3	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3
167.5°	1310.1	1309.2	1308.4	1307.5	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2
170°	1319.0	1318.1	1317.3	1316.4	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1
172.5°	1325.0	1323.9	1322.8	1321.7	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0
175°	1329.9	1328.8	1327.7	1326.6	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0
177.5°	1331.9	1330.8	1329.7	1328.6	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1144.3	1146.4	1153.8	1159.1	1169.6	1168.5	1168.5	1167.5	1164.3	1169.6	1172.7
5°	1224.3	1242.2	1244.3	1267.5	1268.5	1278.0	1284.3	1279.1	1291.7	1290.7	1281.2
7.5°	1323.3	1347.5	1359.1	1381.2	1406.5	1400.1	1424.4	1428.6	1426.5	1437.0	1444.4
10°	1431.7	1473.8	1503.3	1544.4	1554.9	1561.2	1577.0	1590.7	1618.1	1597.0	1610.7
12.5°	1555.9	1586.5	1625.4	1690.7	1723.3	1744.4	1751.8	1761.2	1780.2	1768.6	1769.6
15°	1660.2	1701.2	1767.5	1848.6	1858.1	1884.4	1878.1	1934.9	1962.3	1921.2	1944.4
17.5°	1768.6	1823.3	1902.3	1972.8	2012.8	2030.7	2047.6	2102.3	2100.2	2093.9	2099.2
20°	1838.1	1927.6	2025.5	2119.2	2130.7	2144.4	2189.7	2212.9	2208.6	2226.5	2238.1
22.5°	1936.0	2030.7	2134.9	2197.1	2223.4	2239.2	2275.0	2289.7	2296.0	2300.2	2292.9
25°	2018.1	2119.2	2196.0	2250.7	2266.5	2275.0	2286.5	2290.8	2287.6	2280.2	2286.5
27.5°	2073.9	2155.0	2207.6	2232.9	2224.4	2210.7	2188.6	2173.9	2141.3	2125.5	2144.4
30°	2097.0	2132.8	2148.6	2106.5	2064.4	2030.7	1988.6	1910.7	1849.7	1867.6	1843.3
32.5°	2060.2	2037.0	1961.2	1852.8	1820.2	1765.4	1646.5	1554.9	1558.0	1509.6	1529.6
35°	1951.8	1846.5	1703.3	1539.1	1495.9	1466.5	1335.9	1315.9	1273.8	1228.5	1241.2
37.5°	1760.2	1606.5	1432.8	1311.7	1247.5	1183.3	1109.6	1065.4	1040.1	1021.2	1035.9
40°	1526.5	1339.1	1195.9	1087.5	1032.7	991.7	941.1	896.9	868.5	865.3	870.6
42.5°	1297.0	1139.1	1007.5	904.3	886.4	838.0	805.3	770.6	762.2	748.5	755.9
45°	1098.0	969.6	861.1	776.9	755.9	743.2	703.2	681.1	671.6	663.2	675.9
47.5°	953.8	819.0	740.1	689.5	668.5	647.4	625.3	610.6	603.2	604.3	603.2
50°	814.8	715.9	646.4	607.4	594.8	580.1	562.2	552.7	549.5	540.1	547.4
52.5°	701.1	629.5	581.1	544.3	534.8	524.3	509.5	504.3	496.9	494.8	494.8
55°	609.5	553.7	514.8	490.6	479.0	470.6	462.2	455.8	450.6	450.6	450.6
57.5°	537.9	489.5	461.1	440.0	435.8	427.4	417.9	417.9	410.6	409.5	412.7
60°	476.9	433.7	411.6	393.7	387.4	385.3	375.8	375.8	373.7	368.5	372.7
62.5°	414.8	383.2	364.2	350.6	344.2	344.2	336.9	331.6	331.6	332.7	330.6
65°	357.9	334.8	317.9	307.4	304.2	300.0	299.0	294.8	291.6	292.7	291.6
67.5°	307.4	289.5	277.9	269.5	264.2	262.1	259.0	259.0	256.9	257.9	252.7
70°	262.1	244.2	234.8	226.3	224.2	224.2	220.0	221.1	219.0	222.1	220.0
72.5°	215.8	202.1	194.8	191.6	189.5	188.4	186.3	184.2	183.2	185.3	184.2
75°	174.8	163.2	157.9	155.8	153.7	153.7	152.6	151.6	150.5	150.5	150.5
77.5°	135.8	128.4	122.1	124.2	121.1	122.1	119.0	119.0	120.0	119.0	119.0
80°	100.0	94.7	94.7	92.6	88.4	90.5	90.5	87.4	86.3	88.4	85.3
82.5°	66.3	65.3	63.2	62.1	60.0	61.1	60.0	59.0	57.9	60.0	57.9
85°	39.0	39.0	37.9	35.8	37.9	36.8	35.8	35.8	34.7	34.7	34.7
87.5°	20.0	17.9	17.9	16.8	17.9	15.8	16.8	15.8	14.7	15.8	14.7
90°	24.6	25.5	26.4	27.3	27.7	27.9	28.3	28.8	29.2	29.6	29.2
92.5°	27.2	28.8	30.3	31.8	32.6	32.7	32.9	33.2	33.4	33.6	33.4
95°	32.1	33.7	35.2	36.7	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	33.4	35.1	36.9	38.6	39.5	39.6	39.8	40.1	40.3	40.5	40.3
100°	34.4	36.1	37.9	39.6	40.5	40.6	40.8	41.1	41.3	41.5	41.3
102.5°	65.9	58.6	51.4	44.1	40.5	40.7	41.2	41.6	42.1	42.5	42.1
105°	177.5	138.7	99.8	60.9	41.5	41.7	42.2	42.6	43.1	43.5	43.1
107.5°	350.5	316.7	282.9	249.1	232.2	217.8	189.1	160.3	131.6	102.8	131.6
110°	438.4	431.1	423.9	416.6	413.0	397.3	365.9	334.5	303.1	271.7	303.1

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	509.9	511.8	513.8	515.7	516.7	516.5	516.1	515.6	515.2	514.8	515.2
115°	569.3	571.5	573.7	575.9	577.0	577.4	578.3	579.2	580.1	581.0	580.1
117.5°	627.2	628.9	630.7	632.4	633.3	633.4	633.6	633.9	634.1	634.3	634.1
120°	683.6	685.3	687.1	688.8	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	739.2	740.3	741.4	742.5	743.0	743.1	743.3	743.6	743.8	744.0	743.8
125°	790.8	791.3	791.7	792.2	792.4	792.6	793.1	793.5	794.0	794.4	794.0
127.5°	843.5	844.1	844.8	845.5	845.8	845.6	845.1	844.7	844.2	843.8	844.2
130°	890.1	891.0	891.9	892.8	893.2	893.0	892.5	892.1	891.6	891.2	891.6
132.5°	934.6	935.5	936.4	937.3	937.7	937.4	936.7	936.0	935.4	934.7	935.4
135°	979.8	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	979.8
137.5°	1019.8	1020.9	1022.0	1023.1	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0
140°	1058.1	1059.0	1059.9	1060.8	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6
142.5°	1094.4	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4
145°	1127.8	1128.2	1128.7	1129.1	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1158.4	1158.9	1159.3	1159.8	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1
150°	1186.1	1186.5	1187.0	1187.4	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3
152.5°	1210.3	1211.1	1212.0	1212.9	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5
155°	1232.2	1233.3	1234.4	1235.5	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4
157.5°	1252.2	1253.5	1254.8	1256.1	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7
160°	1269.0	1270.3	1271.6	1272.9	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2
162.5°	1284.0	1285.6	1287.1	1288.6	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8
165°	1297.1	1298.8	1300.6	1302.3	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8
167.5°	1308.0	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0
170°	1316.9	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9
172.5°	1322.8	1324.5	1326.3	1328.0	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0
175°	1327.5	1329.1	1330.6	1332.1	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8
177.5°	1329.7	1331.4	1333.2	1334.9	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1164.3	1167.5	1159.1	1157.0	1157.0	1161.2	1158.0	1129.6	1134.8	1128.5	1126.4
5°	1292.8	1286.4	1278.0	1273.8	1268.5	1253.8	1252.8	1220.1	1213.8	1192.7	1183.3
7.5°	1433.8	1428.6	1403.3	1400.1	1398.0	1384.3	1349.6	1314.9	1289.6	1265.4	1242.2
10°	1594.9	1579.1	1567.5	1544.4	1532.8	1513.8	1468.6	1435.9	1392.8	1355.9	1307.5
12.5°	1788.6	1770.7	1731.8	1714.9	1700.2	1647.5	1602.3	1565.4	1481.2	1455.9	1395.9
15°	1930.7	1892.8	1888.6	1851.8	1849.7	1791.8	1705.4	1665.4	1600.2	1507.5	1445.4
17.5°	2084.4	2050.7	2024.4	1980.2	1973.9	1919.1	1856.0	1758.1	1686.5	1598.1	1519.1
20°	2197.1	2179.2	2133.9	2116.0	2079.2	2032.8	1967.6	1846.5	1759.1	1670.7	1573.8
22.5°	2286.5	2268.6	2232.9	2208.6	2187.6	2127.6	2049.7	1946.5	1826.5	1710.7	1610.7
25°	2285.5	2280.2	2265.5	2253.9	2238.1	2193.9	2128.6	2029.7	1896.0	1768.6	1629.6
27.5°	2156.0	2170.7	2196.0	2208.6	2205.5	2199.2	2162.3	2079.2	1959.1	1807.5	1651.7
30°	1886.5	1940.2	1987.6	2050.7	2069.7	2116.0	2137.1	2089.7	1993.9	1852.8	1680.2
32.5°	1564.4	1642.3	1745.4	1780.2	1840.2	1929.7	2029.7	2047.6	1987.6	1879.1	1698.1
35°	1283.3	1347.5	1427.5	1482.3	1535.9	1681.2	1807.5	1917.0	1937.0	1865.4	1693.9
37.5°	1062.2	1107.5	1178.0	1224.3	1273.8	1398.0	1574.9	1717.0	1817.0	1819.1	1682.3
40°	902.2	922.2	983.3	1016.9	1064.3	1171.7	1329.6	1514.9	1661.2	1728.6	1651.7
42.5°	764.3	790.6	841.1	866.4	896.9	990.6	1094.8	1270.7	1451.7	1595.9	1594.9
45°	682.2	701.1	724.3	745.3	780.1	835.9	954.8	1086.4	1260.1	1423.3	1487.5
47.5°	609.5	627.4	650.6	656.9	680.1	732.7	805.3	920.1	1082.2	1244.3	1365.4
50°	548.5	563.2	579.0	590.6	601.1	644.3	699.0	795.9	925.4	1082.2	1232.8
52.5°	501.1	511.6	525.3	531.6	541.1	572.7	614.8	686.4	792.7	935.9	1082.2
55°	456.9	464.3	472.7	483.2	487.4	510.6	543.2	604.3	683.2	811.7	950.6
57.5°	415.8	419.0	424.3	430.6	435.8	455.8	484.3	525.3	594.8	693.8	825.3
60°	369.5	377.9	381.1	387.4	390.6	406.4	428.5	463.2	516.9	602.2	701.1
62.5°	330.6	335.8	341.1	344.2	351.6	356.9	374.8	406.4	450.6	513.7	603.2
65°	295.8	297.9	301.1	304.2	306.3	312.7	329.5	350.6	384.2	440.0	509.5
67.5°	255.8	257.9	262.1	263.2	265.3	273.7	283.2	301.1	329.5	371.6	428.5
70°	216.9	220.0	222.1	224.2	227.4	230.5	241.1	255.8	277.9	307.4	351.6
72.5°	183.2	186.3	186.3	188.4	187.4	191.6	202.1	212.7	227.4	251.6	290.6
75°	149.5	149.5	151.6	152.6	153.7	157.9	162.1	170.5	182.1	201.1	225.3
77.5°	117.9	116.9	119.0	119.0	119.0	122.1	126.3	130.5	137.9	151.6	170.5
80°	86.3	86.3	88.4	89.5	87.4	88.4	90.5	94.7	100.0	109.5	120.0
82.5°	56.8	61.1	60.0	61.1	60.0	62.1	63.2	64.2	66.3	70.5	77.9
85°	34.7	34.7	34.7	35.8	34.7	35.8	35.8	35.8	36.8	39.0	42.1
87.5°	14.7	14.7	14.7	15.8	14.7	14.7	15.8	14.7	15.8	15.8	16.8
90°	28.8	28.3	27.9	27.7	27.3	26.4	25.5	24.6	23.7	20.9	18.0
92.5°	33.2	32.9	32.7	32.6	31.8	30.3	28.8	27.2	25.7	23.7	21.7
95°	37.5	37.5	37.5	37.5	36.7	35.2	33.7	32.1	30.6	28.2	25.8
97.5°	40.1	39.8	39.6	39.5	38.6	36.9	35.1	33.4	31.6	42.8	54.0
100°	41.1	40.8	40.6	40.5	39.6	37.9	36.1	34.4	32.6	66.8	101.1
102.5°	41.6	41.2	40.7	40.5	44.1	51.4	58.6	65.9	73.1	111.3	149.5
105°	42.6	42.2	41.7	41.5	60.9	99.8	138.7	177.5	216.4	236.2	255.9
107.5°	160.3	189.1	217.8	232.2	249.1	282.9	316.7	350.5	384.3	381.0	377.7
110°	334.5	365.9	397.3	413.0	416.6	423.9	431.1	438.4	445.6	443.2	440.8

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	515.6	516.1	516.5	516.7	515.7	513.8	511.8	509.9	507.9	505.5	503.1
115°	579.2	578.3	577.4	577.0	575.9	573.7	571.5	569.3	567.1	565.1	563.1
117.5°	633.9	633.6	633.4	633.3	632.4	630.7	628.9	627.2	625.4	624.3	623.2
120°	689.7	689.7	689.7	689.7	688.8	687.1	685.3	683.6	681.8	681.1	680.5
122.5°	743.6	743.3	743.1	743.0	742.5	741.4	740.3	739.2	738.1	737.2	736.3
125°	793.5	793.1	792.6	792.4	792.2	791.7	791.3	790.8	790.4	789.5	788.7
127.5°	844.7	845.1	845.6	845.8	845.5	844.8	844.1	843.5	842.8	841.7	840.6
130°	892.1	892.5	893.0	893.2	892.8	891.9	891.0	890.1	889.2	888.3	887.5
132.5°	936.0	936.7	937.4	937.7	937.3	936.4	935.5	934.6	933.7	933.0	932.4
135°	980.5	981.1	981.8	982.1	981.8	981.1	980.5	979.8	979.2	978.3	977.4
137.5°	1022.5	1022.9	1023.4	1023.6	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8
140°	1060.1	1060.5	1061.0	1061.2	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9
142.5°	1095.1	1095.7	1096.4	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5
145°	1129.3	1129.3	1129.3	1129.3	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5
147.5°	1157.2	1158.3	1159.4	1160.0	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1
150°	1186.0	1186.6	1187.3	1187.6	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8
152.5°	1210.6	1211.7	1212.8	1213.3	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0
155°	1232.7	1234.0	1235.3	1236.0	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7
157.5°	1252.4	1254.2	1255.9	1256.8	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3
160°	1269.8	1271.3	1272.8	1273.6	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1
162.5°	1286.1	1287.4	1288.7	1289.4	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9
165°	1299.4	1300.9	1302.4	1303.2	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7
167.5°	1309.7	1311.5	1313.2	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2
170°	1318.6	1320.4	1322.1	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1
172.5°	1324.0	1325.9	1327.9	1328.9	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6
175°	1328.5	1330.3	1332.0	1332.9	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6
177.5°	1330.4	1332.5	1334.7	1335.8	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1115.9	1112.7	1112.7	1110.6	1104.3	1092.7	1091.7	1093.8	1087.5	1081.2	1071.7
5°	1170.6	1150.6	1144.3	1138.0	1125.4	1104.3	1095.9	1088.5	1076.9	1063.3	1048.5
7.5°	1217.0	1188.5	1180.1	1168.5	1143.3	1113.8	1094.8	1079.1	1063.3	1044.3	1026.4
10°	1274.9	1233.8	1213.8	1197.0	1162.2	1121.2	1092.7	1069.6	1044.3	1021.2	998.0
12.5°	1340.1	1273.8	1267.5	1226.4	1186.4	1125.4	1090.6	1056.9	1023.3	994.8	970.6
15°	1394.9	1322.2	1295.9	1268.5	1191.7	1115.9	1082.2	1044.3	1005.4	974.8	939.0
17.5°	1429.6	1369.6	1313.8	1277.0	1197.0	1129.6	1064.3	1021.2	980.1	938.0	908.5
20°	1471.7	1384.3	1335.9	1286.4	1207.5	1119.1	1053.8	1000.1	949.6	911.7	875.9
22.5°	1513.8	1395.9	1355.9	1302.2	1209.6	1108.5	1034.8	981.1	923.2	885.4	846.4
25°	1509.6	1412.8	1346.4	1301.2	1188.5	1099.1	1012.7	949.6	895.9	847.5	808.5
27.5°	1512.8	1393.8	1326.4	1273.8	1173.8	1085.4	989.6	923.2	867.5	816.9	775.9
30°	1513.8	1365.4	1306.4	1243.3	1146.4	1052.7	963.3	895.9	836.9	782.2	745.3
32.5°	1510.7	1342.2	1268.5	1211.7	1103.3	1021.2	932.7	861.1	801.1	750.6	715.9
35°	1503.3	1314.9	1229.6	1158.0	1059.1	975.9	904.3	830.6	766.4	720.1	680.1
37.5°	1483.3	1285.4	1188.5	1118.0	1007.5	923.2	860.1	799.0	736.9	682.2	648.5
40°	1468.6	1245.4	1147.5	1070.6	951.7	869.6	816.9	759.0	698.0	648.5	615.9
42.5°	1434.9	1207.5	1105.4	1013.8	896.9	812.7	763.2	716.9	664.3	615.9	586.4
45°	1380.1	1166.4	1053.8	961.1	836.9	756.9	711.6	673.8	627.4	581.1	551.6
47.5°	1303.3	1107.5	999.0	906.4	778.0	696.9	651.6	623.2	586.4	547.4	522.2
50°	1220.1	1043.3	943.3	851.7	721.1	642.2	598.0	571.6	547.4	511.6	487.4
52.5°	1111.7	974.8	879.0	791.7	660.1	584.3	545.3	526.4	501.1	475.8	454.8
55°	1006.4	886.4	807.4	724.3	600.1	529.5	491.6	471.6	456.9	435.8	419.0
57.5°	884.3	804.3	731.7	655.9	544.3	480.0	444.3	420.0	410.6	401.1	385.3
60°	771.7	710.6	651.6	588.5	486.4	428.5	393.7	374.8	365.3	359.0	348.5
62.5°	668.5	621.1	570.6	520.1	427.4	374.8	348.5	329.5	321.1	320.0	310.6
65°	569.5	535.8	494.8	445.3	372.7	326.3	301.1	289.5	280.0	280.0	272.7
67.5°	470.6	447.4	414.8	380.0	323.2	280.0	256.9	246.3	241.1	241.1	235.8
70°	391.6	375.8	346.4	315.8	266.3	233.7	215.8	206.3	203.2	204.2	200.0
72.5°	317.9	301.1	276.9	254.8	217.9	193.7	181.1	170.5	165.3	166.3	165.3
75°	246.3	237.9	216.9	200.0	170.5	153.7	142.1	136.9	132.6	133.7	131.6
77.5°	185.3	172.6	161.1	149.5	131.6	117.9	108.4	103.2	100.0	100.0	100.0
80°	126.3	124.2	114.7	108.4	93.7	83.2	75.8	74.7	71.6	71.6	71.6
82.5°	82.1	76.8	71.6	67.4	59.0	52.6	49.5	47.4	46.3	45.3	47.4
85°	45.3	42.1	40.0	35.8	32.6	29.5	26.3	25.3	24.2	25.3	24.2
87.5°	17.9	14.7	14.7	13.7	12.6	11.6	11.6	9.5	9.5	8.4	8.4
90°	15.2	12.3	10.9	9.8	7.6	5.4	3.2	1.0	3.2	5.4	7.6
92.5°	19.8	17.8	16.8	17.5	18.8	20.1	21.4	22.7	21.4	20.1	18.8
95°	23.4	21.0	19.8	24.3	33.3	42.3	51.3	60.3	51.3	42.3	33.3
97.5°	65.2	76.4	82.0	85.1	91.2	97.4	103.5	109.7	103.5	97.4	91.2
100°	135.3	169.6	186.7	184.5	180.1	175.8	171.4	167.0	171.4	175.8	180.1
102.5°	187.7	225.9	245.0	243.6	240.7	237.9	235.0	232.2	235.0	237.9	240.7
105°	275.7	295.4	305.3	304.1	301.7	299.2	296.8	294.4	296.8	299.2	301.7
107.5°	374.4	371.1	369.5	368.5	366.5	364.6	362.6	360.6	362.6	364.6	366.5
110°	438.3	435.9	434.7	433.8	432.1	430.3	428.6	426.8	428.6	430.3	432.1

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	500.6	498.2	497.0	496.2	494.7	493.2	491.6	490.1	491.6	493.2	494.7
115°	561.2	559.2	558.2	557.5	556.2	554.9	553.6	552.3	553.6	554.9	556.2
117.5°	622.1	621.0	620.5	619.7	618.2	616.7	615.1	613.6	615.1	616.7	618.2
120°	679.8	679.1	678.8	677.8	675.8	673.9	671.9	669.9	671.9	673.9	675.8
122.5°	735.4	734.5	734.1	733.3	731.8	730.3	728.7	727.2	728.7	730.3	731.8
125°	787.8	786.9	786.5	785.6	783.9	782.1	780.4	778.6	780.4	782.1	783.9
127.5°	839.5	838.4	837.9	837.0	835.3	833.5	831.8	830.0	831.8	833.5	835.3
130°	886.6	885.7	885.3	884.4	882.7	880.9	879.2	877.4	879.2	880.9	882.7
132.5°	931.7	931.0	930.7	929.8	928.1	926.3	924.6	922.8	924.6	926.3	928.1
135°	976.5	975.6	975.2	974.5	973.2	971.9	970.6	969.3	970.6	971.9	973.2
137.5°	1017.4	1016.9	1016.7	1015.8	1014.1	1012.3	1010.6	1008.8	1010.6	1012.3	1014.1
140°	1055.2	1054.5	1054.2	1053.5	1052.2	1050.9	1049.6	1048.3	1049.6	1050.9	1052.2
142.5°	1091.8	1091.1	1090.8	1090.1	1088.8	1087.5	1086.2	1084.9	1086.2	1087.5	1088.8
145°	1126.1	1125.6	1125.4	1124.6	1123.1	1121.6	1120.0	1118.5	1120.0	1121.6	1123.1
147.5°	1156.7	1156.2	1156.0	1155.5	1154.4	1153.3	1152.2	1151.1	1152.2	1153.3	1154.4
150°	1184.4	1183.9	1183.7	1183.4	1182.7	1182.0	1181.4	1180.7	1181.4	1182.0	1182.7
152.5°	1208.7	1208.5	1208.4	1208.3	1208.1	1207.8	1207.6	1207.4	1207.6	1207.8	1208.1
155°	1230.4	1230.2	1230.1	1230.3	1230.8	1231.2	1231.7	1232.1	1231.7	1231.2	1230.8
157.5°	1251.6	1251.8	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9	1251.9
160°	1268.4	1268.6	1268.7	1268.8	1269.0	1269.2	1269.4	1269.6	1269.4	1269.2	1269.0
162.5°	1283.2	1283.4	1283.5	1283.8	1284.5	1285.1	1285.8	1286.4	1285.8	1285.1	1284.5
165°	1296.0	1296.2	1296.3	1296.6	1297.3	1298.0	1298.6	1299.3	1298.6	1298.0	1297.3
167.5°	1306.2	1306.2	1306.2	1306.6	1307.5	1308.4	1309.2	1310.1	1309.2	1308.4	1307.5
170°	1315.1	1315.1	1315.1	1315.5	1316.4	1317.3	1318.1	1319.0	1318.1	1317.3	1316.4
172.5°	1320.3	1320.1	1320.0	1320.6	1321.7	1322.8	1323.9	1325.0	1323.9	1322.8	1321.7
175°	1325.3	1325.1	1325.0	1325.5	1326.6	1327.7	1328.8	1329.9	1328.8	1327.7	1326.6
177.5°	1327.2	1327.0	1326.9	1327.5	1328.6	1329.7	1330.8	1331.9	1330.8	1329.7	1328.6
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1069.6	1068.5	1070.6	1064.3	1053.8	1048.5	1033.8	1030.6	1029.6	1030.6	1031.7
5°	1040.1	1039.1	1035.9	1025.4	1012.7	1003.3	985.4	984.3	978.0	971.7	974.8
7.5°	1011.7	1007.5	1001.2	987.5	970.6	960.1	945.4	934.8	926.4	921.1	916.9
10°	983.3	976.9	970.6	952.7	931.7	915.9	898.0	889.6	880.1	875.9	871.7
12.5°	946.4	940.1	928.5	907.5	894.8	874.8	856.9	848.5	843.2	834.8	829.6
15°	916.9	904.3	898.0	875.9	849.6	847.5	814.8	812.7	802.2	802.2	793.8
17.5°	883.2	873.8	862.2	840.1	821.1	802.2	785.3	779.0	769.5	767.4	763.2
20°	850.6	838.0	833.8	811.7	791.7	768.5	750.6	744.3	740.1	735.9	739.0
22.5°	816.9	806.4	795.9	775.9	761.1	738.0	727.4	721.1	714.8	712.7	713.8
25°	784.3	774.8	764.3	744.3	728.5	709.5	700.1	696.9	693.8	693.8	692.7
27.5°	752.7	743.2	733.8	715.9	700.1	686.4	679.0	675.9	672.7	674.8	676.9
30°	720.1	711.6	703.2	687.4	674.8	662.2	658.0	655.9	654.8	660.1	660.1
32.5°	690.6	683.2	676.9	662.2	649.5	639.0	635.9	636.9	638.0	641.1	643.2
35°	660.1	654.8	648.5	635.9	625.3	615.9	616.9	616.9	619.0	624.3	628.5
37.5°	632.7	625.3	620.1	609.5	601.1	592.7	595.8	599.0	601.1	607.4	609.5
40°	600.1	596.9	592.7	582.2	574.8	573.7	574.8	576.9	581.1	584.3	587.4
42.5°	573.7	569.5	564.3	555.8	549.5	550.6	551.6	553.7	555.8	561.1	564.3
45°	544.3	541.1	536.9	529.5	524.3	525.3	526.4	526.4	528.5	534.8	536.9
47.5°	511.6	512.7	507.4	500.0	496.9	496.9	496.9	499.0	504.3	506.4	507.4
50°	480.0	477.9	476.9	469.5	467.4	466.4	467.4	468.5	475.8	474.8	477.9
52.5°	446.4	446.4	445.3	441.1	437.9	437.9	435.8	441.1	443.2	445.3	448.5
55°	413.7	410.6	409.5	407.4	403.2	402.1	404.3	410.6	412.7	414.8	417.9
57.5°	377.9	377.9	375.8	372.7	372.7	372.7	372.7	376.9	380.0	382.1	388.5
60°	345.3	341.1	337.9	337.9	337.9	336.9	343.2	343.2	349.5	350.6	352.7
62.5°	306.3	304.2	302.1	303.2	302.1	304.2	306.3	310.6	311.6	314.8	317.9
65°	269.5	269.5	267.4	273.7	269.5	269.5	274.8	274.8	276.9	280.0	284.2
67.5°	233.7	234.8	232.7	232.7	234.8	235.8	236.9	241.1	242.1	246.3	251.6
70°	196.9	199.0	200.0	197.9	200.0	202.1	204.2	205.3	209.5	211.6	214.8
72.5°	164.2	166.3	163.2	164.2	165.3	167.4	168.4	170.5	172.6	179.0	181.1
75°	131.6	130.5	129.5	133.7	131.6	135.8	136.9	136.9	139.0	144.2	146.3
77.5°	101.1	101.1	102.1	100.0	103.2	102.1	103.2	106.3	109.5	109.5	117.9
80°	70.5	72.6	72.6	72.6	73.7	74.7	72.6	77.9	79.0	79.0	82.1
82.5°	45.3	46.3	45.3	47.4	47.4	49.5	48.4	49.5	51.6	53.7	54.7
85°	24.2	24.2	26.3	26.3	25.3	26.3	25.3	26.3	28.4	28.4	29.5
87.5°	8.4	8.4	8.4	8.4	9.5	8.4	9.5	9.5	8.4	8.4	11.6
90°	9.8	10.9	12.3	15.2	18.0	20.9	23.7	24.6	25.5	26.4	27.3
92.5°	17.5	16.8	17.8	19.8	21.7	23.7	25.7	27.2	28.8	30.3	31.8
95°	24.3	19.8	21.0	23.4	25.8	28.2	30.6	32.1	33.7	35.2	36.7
97.5°	85.1	82.0	76.4	65.2	54.0	42.8	31.6	33.4	35.1	36.9	38.6
100°	184.5	186.7	169.6	135.3	101.1	66.8	32.6	34.4	36.1	37.9	39.6
102.5°	243.6	245.0	225.9	187.7	149.5	111.3	73.1	65.9	58.6	51.4	44.1
105°	304.1	305.3	295.4	275.7	255.9	236.2	216.4	177.5	138.7	99.8	60.9
107.5°	368.5	369.5	371.1	374.4	377.7	381.0	384.3	350.5	316.7	282.9	249.1
110°	433.8	434.7	435.9	438.3	440.8	443.2	445.6	438.4	431.1	423.9	416.6

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	496.2	497.0	498.2	500.6	503.1	505.5	507.9	509.9	511.8	513.8	515.7
115°	557.5	558.2	559.2	561.2	563.1	565.1	567.1	569.3	571.5	573.7	575.9
117.5°	619.7	620.5	621.0	622.1	623.2	624.3	625.4	627.2	628.9	630.7	632.4
120°	677.8	678.8	679.1	679.8	680.5	681.1	681.8	683.6	685.3	687.1	688.8
122.5°	733.3	734.1	734.5	735.4	736.3	737.2	738.1	739.2	740.3	741.4	742.5
125°	785.6	786.5	786.9	787.8	788.7	789.5	790.4	790.8	791.3	791.7	792.2
127.5°	837.0	837.9	838.4	839.5	840.6	841.7	842.8	843.5	844.1	844.8	845.5
130°	884.4	885.3	885.7	886.6	887.5	888.3	889.2	890.1	891.0	891.9	892.8
132.5°	929.8	930.7	931.0	931.7	932.4	933.0	933.7	934.6	935.5	936.4	937.3
135°	974.5	975.2	975.6	976.5	977.4	978.3	979.2	979.8	980.5	981.1	981.8
137.5°	1015.8	1016.7	1016.9	1017.4	1017.8	1018.3	1018.7	1019.8	1020.9	1022.0	1023.1
140°	1053.5	1054.2	1054.5	1055.2	1055.9	1056.5	1057.2	1058.1	1059.0	1059.9	1060.8
142.5°	1090.1	1090.8	1091.1	1091.8	1092.5	1093.1	1093.8	1094.4	1095.1	1095.7	1096.4
145°	1124.6	1125.4	1125.6	1126.1	1126.5	1127.0	1127.4	1127.8	1128.2	1128.7	1129.1
147.5°	1155.5	1156.0	1156.2	1156.7	1157.1	1157.6	1158.0	1158.4	1158.9	1159.3	1159.8
150°	1183.4	1183.7	1183.9	1184.4	1184.8	1185.3	1185.7	1186.1	1186.5	1187.0	1187.4
152.5°	1208.3	1208.4	1208.5	1208.7	1209.0	1209.2	1209.4	1210.3	1211.1	1212.0	1212.9
155°	1230.3	1230.1	1230.2	1230.4	1230.7	1230.9	1231.1	1232.2	1233.3	1234.4	1235.5
157.5°	1251.9	1251.9	1251.8	1251.6	1251.3	1251.1	1250.9	1252.2	1253.5	1254.8	1256.1
160°	1268.8	1268.7	1268.6	1268.4	1268.1	1267.9	1267.7	1269.0	1270.3	1271.6	1272.9
162.5°	1283.8	1283.5	1283.4	1283.2	1282.9	1282.7	1282.5	1284.0	1285.6	1287.1	1288.6
165°	1296.6	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3	1297.1	1298.8	1300.6	1302.3
167.5°	1306.6	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1308.0	1309.7	1311.5	1313.2
170°	1315.5	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1316.9	1318.6	1320.4	1322.1
172.5°	1320.6	1320.0	1320.1	1320.3	1320.6	1320.8	1321.0	1322.8	1324.5	1326.3	1328.0
175°	1325.5	1325.0	1325.1	1325.3	1325.6	1325.8	1326.0	1327.5	1329.1	1330.6	1332.1
177.5°	1327.5	1326.9	1327.0	1327.2	1327.5	1327.7	1327.9	1329.7	1331.4	1333.2	1334.9
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1030.6	1031.7	1027.5	1024.3	1032.7	1027.5	1027.5	1028.5	1026.4	1029.6	1028.5
5°	972.7	973.8	966.4	968.5	964.3	963.3	962.2	968.5	967.5	966.4	968.5
7.5°	915.9	915.9	912.7	910.6	910.6	907.5	911.7	910.6	912.7	912.7	915.9
10°	868.5	870.6	865.3	860.1	859.0	860.1	860.1	861.1	862.2	869.6	868.5
12.5°	829.6	826.4	825.3	822.2	816.9	814.8	812.7	824.3	821.1	821.1	821.1
15°	786.4	793.8	792.7	783.2	781.1	785.3	783.2	783.2	793.8	792.7	791.7
17.5°	763.2	761.1	759.0	753.8	754.8	753.8	754.8	754.8	761.1	761.1	761.1
20°	736.9	732.7	732.7	730.6	730.6	727.4	731.7	732.7	736.9	736.9	738.0
22.5°	713.8	710.6	710.6	709.5	711.6	707.4	711.6	712.7	712.7	715.9	715.9
25°	693.8	691.6	691.6	693.8	693.8	693.8	693.8	698.0	694.8	695.9	694.8
27.5°	675.9	676.9	678.0	679.0	678.0	679.0	680.1	682.2	683.2	682.2	680.1
30°	659.0	662.2	663.2	663.2	665.3	666.4	667.4	667.4	668.5	665.3	667.4
32.5°	646.4	646.4	648.5	649.5	651.6	652.7	652.7	654.8	653.7	650.6	651.6
35°	628.5	628.5	632.7	634.8	638.0	636.9	638.0	638.0	639.0	636.9	633.7
37.5°	610.6	612.7	612.7	616.9	618.0	619.0	618.0	620.1	619.0	616.9	615.9
40°	589.5	588.5	589.5	592.7	593.7	593.7	593.7	595.8	595.8	595.8	594.8
42.5°	563.2	566.4	565.3	568.5	567.4	567.4	569.5	571.6	572.7	569.5	570.6
45°	537.9	537.9	540.1	540.1	541.1	541.1	545.3	543.2	545.3	543.2	544.3
47.5°	510.6	511.6	511.6	512.7	514.8	516.9	514.8	515.8	515.8	516.9	514.8
50°	480.0	480.0	482.2	485.3	489.5	487.4	486.4	490.6	487.4	487.4	485.3
52.5°	448.5	451.6	452.7	455.8	459.0	460.0	461.1	459.0	460.0	456.9	457.9
55°	417.9	419.0	423.2	426.4	429.5	429.5	428.5	429.5	430.6	426.4	426.4
57.5°	387.4	390.6	394.8	394.8	399.0	399.0	397.9	397.9	399.0	395.8	394.8
60°	354.8	357.9	363.2	363.2	369.5	370.6	368.5	366.4	366.4	363.2	364.2
62.5°	320.0	323.2	326.3	331.6	335.8	333.7	337.9	333.7	334.8	328.5	328.5
65°	289.5	290.6	295.8	301.1	301.1	303.2	301.1	302.1	299.0	299.0	294.8
67.5°	253.7	253.7	259.0	264.2	269.5	269.5	269.5	266.3	266.3	263.2	263.2
70°	222.1	221.1	226.3	229.5	232.7	233.7	231.6	230.5	228.4	225.3	224.2
72.5°	183.2	185.3	190.5	192.7	197.9	196.9	202.1	195.8	195.8	190.5	189.5
75°	148.4	150.5	155.8	159.0	162.1	162.1	165.3	162.1	157.9	155.8	154.8
77.5°	117.9	116.9	121.1	126.3	127.4	126.3	128.4	127.4	123.2	123.2	121.1
80°	84.2	87.4	91.6	90.5	94.7	93.7	93.7	91.6	91.6	88.4	90.5
82.5°	55.8	59.0	60.0	59.0	60.0	62.1	63.2	62.1	62.1	60.0	61.1
85°	29.5	29.5	31.6	32.6	31.6	31.6	32.6	35.8	33.7	31.6	33.7
87.5°	9.5	8.4	8.4	9.5	8.4	8.4	9.5	9.5	10.5	10.5	10.5
90°	27.7	27.9	28.3	28.8	29.2	29.6	29.2	28.8	28.3	27.9	27.7
92.5°	32.6	32.7	32.9	33.2	33.4	33.6	33.4	33.2	32.9	32.7	32.6
95°	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5	37.5
97.5°	39.5	39.6	39.8	40.1	40.3	40.5	40.3	40.1	39.8	39.6	39.5
100°	40.5	40.6	40.8	41.1	41.3	41.5	41.3	41.1	40.8	40.6	40.5
102.5°	40.5	40.7	41.2	41.6	42.1	42.5	42.1	41.6	41.2	40.7	40.5
105°	41.5	41.7	42.2	42.6	43.1	43.5	43.1	42.6	42.2	41.7	41.5
107.5°	232.2	217.8	189.1	160.3	131.6	102.8	131.6	160.3	189.1	217.8	232.2
110°	413.0	397.3	365.9	334.5	303.1	271.7	303.1	334.5	365.9	397.3	413.0

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	516.7	516.5	516.1	515.6	515.2	514.8	515.2	515.6	516.1	516.5	516.7
115°	577.0	577.4	578.3	579.2	580.1	581.0	580.1	579.2	578.3	577.4	577.0
117.5°	633.3	633.4	633.6	633.9	634.1	634.3	634.1	633.9	633.6	633.4	633.3
120°	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7	689.7
122.5°	743.0	743.1	743.3	743.6	743.8	744.0	743.8	743.6	743.3	743.1	743.0
125°	792.4	792.6	793.1	793.5	794.0	794.4	794.0	793.5	793.1	792.6	792.4
127.5°	845.8	845.6	845.1	844.7	844.2	843.8	844.2	844.7	845.1	845.6	845.8
130°	893.2	893.0	892.5	892.1	891.6	891.2	891.6	892.1	892.5	893.0	893.2
132.5°	937.7	937.4	936.7	936.0	935.4	934.7	935.4	936.0	936.7	937.4	937.7
135°	982.1	981.8	981.1	980.5	979.8	979.2	979.8	980.5	981.1	981.8	982.1
137.5°	1023.6	1023.4	1022.9	1022.5	1022.0	1021.6	1022.0	1022.5	1022.9	1023.4	1023.6
140°	1061.2	1061.0	1060.5	1060.1	1059.6	1059.2	1059.6	1060.1	1060.5	1061.0	1061.2
142.5°	1096.7	1096.4	1095.7	1095.1	1094.4	1093.8	1094.4	1095.1	1095.7	1096.4	1096.7
145°	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3	1129.3
147.5°	1160.0	1159.4	1158.3	1157.2	1156.1	1155.0	1156.1	1157.2	1158.3	1159.4	1160.0
150°	1187.6	1187.3	1186.6	1186.0	1185.3	1184.7	1185.3	1186.0	1186.6	1187.3	1187.6
152.5°	1213.3	1212.8	1211.7	1210.6	1209.5	1208.4	1209.5	1210.6	1211.7	1212.8	1213.3
155°	1236.0	1235.3	1234.0	1232.7	1231.4	1230.1	1231.4	1232.7	1234.0	1235.3	1236.0
157.5°	1256.8	1255.9	1254.2	1252.4	1250.7	1248.9	1250.7	1252.4	1254.2	1255.9	1256.8
160°	1273.6	1272.8	1271.3	1269.8	1268.2	1266.7	1268.2	1269.8	1271.3	1272.8	1273.6
162.5°	1289.4	1288.7	1287.4	1286.1	1284.8	1283.5	1284.8	1286.1	1287.4	1288.7	1289.4
165°	1303.2	1302.4	1300.9	1299.4	1297.8	1296.3	1297.8	1299.4	1300.9	1302.4	1303.2
167.5°	1314.1	1313.2	1311.5	1309.7	1308.0	1306.2	1308.0	1309.7	1311.5	1313.2	1314.1
170°	1323.0	1322.1	1320.4	1318.6	1316.9	1315.1	1316.9	1318.6	1320.4	1322.1	1323.0
172.5°	1328.9	1327.9	1325.9	1324.0	1322.0	1320.0	1322.0	1324.0	1325.9	1327.9	1328.9
175°	1332.9	1332.0	1330.3	1328.5	1326.8	1325.0	1326.8	1328.5	1330.3	1332.0	1332.9
177.5°	1335.8	1334.7	1332.5	1330.4	1328.2	1326.0	1328.2	1330.4	1332.5	1334.7	1335.8
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4	1086.4
2.5°	1031.7	1033.8	1034.8	1030.6	1027.5	1032.7	1040.1	1045.4	1049.6	1054.8	1058.0
5°	970.6	978.0	978.0	980.1	983.3	988.5	1002.2	1011.7	1020.1	1026.4	1031.7
7.5°	919.0	924.3	927.5	932.7	938.0	945.4	961.1	974.8	987.5	994.8	1003.3
10°	872.7	876.9	882.2	885.4	894.8	905.4	925.4	936.9	951.7	963.3	973.8
12.5°	828.5	843.2	846.4	845.3	853.8	865.3	885.4	903.2	919.0	930.6	942.2
15°	796.9	802.2	808.5	807.4	825.3	828.5	845.3	866.4	887.5	894.8	905.4
17.5°	762.2	770.6	776.9	780.1	785.3	796.9	812.7	828.5	855.9	856.9	884.3
20°	734.8	743.2	747.4	751.7	754.8	768.5	782.2	800.1	822.2	833.8	848.5
22.5°	716.9	721.1	724.3	727.4	731.7	739.0	755.9	775.9	790.6	803.2	812.7
25°	695.9	700.1	704.3	706.4	709.5	713.8	726.4	742.2	763.2	771.7	781.1
27.5°	681.1	681.1	683.2	683.2	687.4	691.6	701.1	715.9	732.7	743.2	755.9
30°	665.3	664.3	665.3	664.3	663.2	669.5	678.0	690.6	702.2	714.8	723.2
32.5°	649.5	648.5	648.5	649.5	645.3	648.5	652.7	664.3	676.9	683.2	692.7
35°	632.7	630.6	630.6	630.6	628.5	626.4	630.6	641.1	649.5	658.0	665.3
37.5°	615.9	612.7	612.7	610.6	608.5	605.3	605.3	613.7	625.3	628.5	638.0
40°	592.7	592.7	590.6	589.5	587.4	585.3	582.2	589.5	600.1	603.2	610.6
42.5°	569.5	566.4	565.3	565.3	565.3	562.2	560.1	565.3	571.6	576.9	581.1
45°	543.2	541.1	542.2	541.1	539.0	537.9	536.9	539.0	546.4	548.5	553.7
47.5°	514.8	513.7	513.7	512.7	511.6	512.7	508.5	513.7	515.8	517.9	522.2
50°	485.3	484.3	483.2	482.2	482.2	483.2	482.2	482.2	486.4	488.5	492.7
52.5°	455.8	452.7	452.7	451.6	451.6	449.5	451.6	452.7	454.8	456.9	459.0
55°	424.3	424.3	421.1	421.1	419.0	419.0	420.0	419.0	423.2	425.3	425.3
57.5°	393.7	389.5	390.6	388.5	386.4	385.3	385.3	387.4	389.5	389.5	391.6
60°	361.1	356.9	355.8	351.6	353.7	350.6	351.6	351.6	355.8	353.7	355.8
62.5°	328.5	323.2	320.0	317.9	317.9	319.0	316.9	315.8	317.9	320.0	324.2
65°	293.7	290.6	287.4	284.2	284.2	283.2	285.3	282.1	281.1	282.1	284.2
67.5°	257.9	254.8	251.6	248.4	249.5	246.3	244.2	247.4	245.3	246.3	248.4
70°	223.2	221.1	214.8	212.7	211.6	212.7	211.6	209.5	212.7	211.6	212.7
72.5°	188.4	186.3	183.2	177.9	177.9	176.9	175.8	175.8	174.8	174.8	174.8
75°	154.8	150.5	147.4	146.3	144.2	143.2	142.1	140.0	141.1	142.1	140.0
77.5°	120.0	114.7	113.7	113.7	110.5	110.5	111.6	110.5	109.5	109.5	109.5
80°	88.4	84.2	84.2	82.1	80.0	80.0	80.0	80.0	79.0	77.9	79.0
82.5°	56.8	55.8	54.7	54.7	56.8	52.6	54.7	53.7	52.6	52.6	51.6
85°	31.6	32.6	31.6	32.6	30.5	31.6	31.6	31.6	30.5	31.6	29.5
87.5°	11.6	11.6	11.6	12.6	12.6	12.6	12.6	12.6	13.7	12.6	12.6
90°	27.3	26.4	25.5	24.6	23.7	20.9	18.0	15.2	12.3	10.9	9.8
92.5°	31.8	30.3	28.8	27.2	25.7	23.7	21.7	19.8	17.8	16.8	17.5
95°	36.7	35.2	33.7	32.1	30.6	28.2	25.8	23.4	21.0	19.8	24.3
97.5°	38.6	36.9	35.1	33.4	31.6	42.8	54.0	65.2	76.4	82.0	85.1
100°	39.6	37.9	36.1	34.4	32.6	66.8	101.1	135.3	169.6	186.7	184.5
102.5°	44.1	51.4	58.6	65.9	73.1	111.3	149.5	187.7	225.9	245.0	243.6
105°	60.9	99.8	138.7	177.5	216.4	236.2	255.9	275.7	295.4	305.3	304.1
107.5°	249.1	282.9	316.7	350.5	384.3	381.0	377.7	374.4	371.1	369.5	368.5
110°	416.6	423.9	431.1	438.4	445.6	443.2	440.8	438.3	435.9	434.7	433.8

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	515.7	513.8	511.8	509.9	507.9	505.5	503.1	500.6	498.2	497.0	496.2
115°	575.9	573.7	571.5	569.3	567.1	565.1	563.1	561.2	559.2	558.2	557.5
117.5°	632.4	630.7	628.9	627.2	625.4	624.3	623.2	622.1	621.0	620.5	619.7
120°	688.8	687.1	685.3	683.6	681.8	681.1	680.5	679.8	679.1	678.8	677.8
122.5°	742.5	741.4	740.3	739.2	738.1	737.2	736.3	735.4	734.5	734.1	733.3
125°	792.2	791.7	791.3	790.8	790.4	789.5	788.7	787.8	786.9	786.5	785.6
127.5°	845.5	844.8	844.1	843.5	842.8	841.7	840.6	839.5	838.4	837.9	837.0
130°	892.8	891.9	891.0	890.1	889.2	888.3	887.5	886.6	885.7	885.3	884.4
132.5°	937.3	936.4	935.5	934.6	933.7	933.0	932.4	931.7	931.0	930.7	929.8
135°	981.8	981.1	980.5	979.8	979.2	978.3	977.4	976.5	975.6	975.2	974.5
137.5°	1023.1	1022.0	1020.9	1019.8	1018.7	1018.3	1017.8	1017.4	1016.9	1016.7	1015.8
140°	1060.8	1059.9	1059.0	1058.1	1057.2	1056.5	1055.9	1055.2	1054.5	1054.2	1053.5
142.5°	1096.4	1095.7	1095.1	1094.4	1093.8	1093.1	1092.5	1091.8	1091.1	1090.8	1090.1
145°	1129.1	1128.7	1128.2	1127.8	1127.4	1127.0	1126.5	1126.1	1125.6	1125.4	1124.6
147.5°	1159.8	1159.3	1158.9	1158.4	1158.0	1157.6	1157.1	1156.7	1156.2	1156.0	1155.5
150°	1187.4	1187.0	1186.5	1186.1	1185.7	1185.3	1184.8	1184.4	1183.9	1183.7	1183.4
152.5°	1212.9	1212.0	1211.1	1210.3	1209.4	1209.2	1209.0	1208.7	1208.5	1208.4	1208.3
155°	1235.5	1234.4	1233.3	1232.2	1231.1	1230.9	1230.7	1230.4	1230.2	1230.1	1230.3
157.5°	1256.1	1254.8	1253.5	1252.2	1250.9	1251.1	1251.3	1251.6	1251.8	1251.9	1251.9
160°	1272.9	1271.6	1270.3	1269.0	1267.7	1267.9	1268.1	1268.4	1268.6	1268.7	1268.8
162.5°	1288.6	1287.1	1285.6	1284.0	1282.5	1282.7	1282.9	1283.2	1283.4	1283.5	1283.8
165°	1302.3	1300.6	1298.8	1297.1	1295.3	1295.5	1295.7	1296.0	1296.2	1296.3	1296.6
167.5°	1313.2	1311.5	1309.7	1308.0	1306.2	1306.2	1306.2	1306.2	1306.2	1306.2	1306.6
170°	1322.1	1320.4	1318.6	1316.9	1315.1	1315.1	1315.1	1315.1	1315.1	1315.1	1315.5
172.5°	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6	1320.3	1320.1	1320.0	1320.6
175°	1332.1	1330.6	1329.1	1327.5	1326.0	1325.8	1325.6	1325.3	1325.1	1325.0	1325.5
177.5°	1334.9	1333.2	1331.4	1329.7	1327.9	1327.7	1327.5	1327.2	1327.0	1326.9	1327.5
180°	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9	1329.9

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1086.4	1086.4	1086.4	1086.4
2.5°	1063.3	1066.4	1076.9	1089.6
5°	1042.2	1050.6	1065.4	1085.4
7.5°	1019.0	1031.7	1052.7	1078.0
10°	992.7	1010.6	1036.9	1068.5
12.5°	964.3	987.5	1021.2	1053.8
15°	946.4	969.6	1000.1	1035.9
17.5°	911.7	939.0	970.6	1021.2
20°	875.9	906.4	947.5	998.0
22.5°	848.5	881.1	920.1	973.8
25°	815.9	849.6	891.7	947.5
27.5°	781.1	814.8	862.2	921.1
30°	754.8	787.4	832.7	895.9
32.5°	723.2	754.8	802.2	868.5
35°	687.4	723.2	768.5	835.9
37.5°	660.1	692.7	740.1	804.3
40°	630.6	659.0	705.3	768.5
42.5°	599.0	630.6	670.6	733.8
45°	569.5	592.7	633.7	693.8
47.5°	537.9	564.3	595.8	642.2
50°	504.3	526.4	561.1	592.7
52.5°	471.6	489.5	519.0	543.2
55°	436.9	454.8	476.9	491.6
57.5°	404.3	416.9	431.6	441.1
60°	364.2	376.9	386.4	395.8
62.5°	328.5	337.9	343.2	348.5
65°	291.6	296.9	300.0	304.2
67.5°	251.6	256.9	257.9	264.2
70°	214.8	215.8	217.9	221.1
72.5°	180.0	182.1	181.1	183.2
75°	144.2	146.3	144.2	146.3
77.5°	109.5	111.6	111.6	114.7
80°	79.0	80.0	81.1	81.1
82.5°	51.6	54.7	52.6	53.7
85°	29.5	30.5	30.5	31.6
87.5°	13.7	14.7	13.7	15.8
90°	7.6	5.4	3.2	1.0
92.5°	18.8	20.1	21.4	22.7
95°	33.3	42.3	51.3	60.3
97.5°	91.2	97.4	103.5	109.7
100°	180.1	175.8	171.4	167.0
102.5°	240.7	237.9	235.0	232.2
105°	301.7	299.2	296.8	294.4
107.5°	366.5	364.6	362.6	360.6
110°	432.1	430.3	428.6	426.8

TEST NUMBER: P1011904

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	494.7	493.2	491.6	490.1
115°	556.2	554.9	553.6	552.3
117.5°	618.2	616.7	615.1	613.6
120°	675.8	673.9	671.9	669.9
122.5°	731.8	730.3	728.7	727.2
125°	783.9	782.1	780.4	778.6
127.5°	835.3	833.5	831.8	830.0
130°	882.7	880.9	879.2	877.4
132.5°	928.1	926.3	924.6	922.8
135°	973.2	971.9	970.6	969.3
137.5°	1014.1	1012.3	1010.6	1008.8
140°	1052.2	1050.9	1049.6	1048.3
142.5°	1088.8	1087.5	1086.2	1084.9
145°	1123.1	1121.6	1120.0	1118.5
147.5°	1154.4	1153.3	1152.2	1151.1
150°	1182.7	1182.0	1181.4	1180.7
152.5°	1208.1	1207.8	1207.6	1207.4
155°	1230.8	1231.2	1231.7	1232.1
157.5°	1251.9	1251.9	1251.9	1251.9
160°	1269.0	1269.2	1269.4	1269.6
162.5°	1284.5	1285.1	1285.8	1286.4
165°	1297.3	1298.0	1298.6	1299.3
167.5°	1307.5	1308.4	1309.2	1310.1
170°	1316.4	1317.3	1318.1	1319.0
172.5°	1321.7	1322.8	1323.9	1325.0
175°	1326.6	1327.7	1328.8	1329.9
177.5°	1328.6	1329.7	1330.8	1331.9
180°	1329.9	1329.9	1329.9	1329.9

(END OF REPORT)