

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011912

Luminaire Tested: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011912
REPORT IS A COMBINATION OF REPORTS P990251 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6869.5 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011912

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011912

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	46	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1011912

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.7
10°-20°	325.9	4.7
20°-30°	481.3	7.0
30°-40°	562.1	8.2
40°-50°	565.1	8.2
50°-60°	496.4	7.2
60°-70°	369.7	5.4
70°-80°	210.4	3.1
80°-90°	62.5	0.9
90°-100°	277.4	4.0
100°-110°	775.4	11.3
110°-120°	756.1	11.0
120°-130°	602.1	8.8
130°-140°	475.2	6.9
140°-150°	354.6	5.2
150°-160°	247.4	3.6
160°-170°	145.3	2.1
170°-180°	47.3	0.7
0°-30°	922.6	13.4
0°-40°	1484.6	21.6
0°-60°	2546.1	37.1
0°-90°	3188.7	46.4
90°-120°	1809.0	26.3
90°-150°	3240.9	47.2
90°-180°	3681.0	53.6
0°-180°	6869.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	2	12	25	28	29	6
95°	34	109	586	171	115	36
105°	115	170	795	1389	1257	122
115°	203	252	608	1333	1529	201
125°	282	332	567	1028	1206	250
135°	330	394	559	846	977	255
145°	376	431	552	694	764	236
155°	428	462	535	608	634	197
165°	467	481	512	543	552	132
175°	487	488	491	498	497	46
180°	488	488	488	488	488	

TEST NUMBER: P1011912

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	2.0	11.9	24.7	27.7	28.7
92.5°	14.8	59.3	183.8	62.8	52.4
95°	33.6	109.2	586.0	171.0	114.6
97.5°	53.4	125.0	901.3	429.9	235.2
100°	73.1	137.8	935.9	899.4	619.6
102.5°	93.9	152.7	871.6	1204.2	981.3
105°	114.6	169.5	794.6	1389.4	1257.1
107.5°	136.4	189.2	726.4	1471.1	1436.9
110°	160.1	209.5	670.0	1473.5	1539.7

TEST NUMBER: P1011912

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	230.8	632.5	1417.6	1560.5
115°	202.6	252.5	607.8	1332.6	1528.8
117.5°	223.3	273.2	591.0	1241.8	1459.7
120°	245.1	294.0	580.1	1155.8	1368.7
122.5°	263.9	313.8	573.2	1088.0	1283.8
125°	281.7	332.5	567.3	1027.8	1205.7
127.5°	295.5	350.4	564.3	978.4	1138.5
130°	308.3	366.2	561.3	932.9	1083.1
132.5°	318.2	380.5	560.3	890.4	1028.8
135°	330.1	393.8	559.4	846.4	977.4
137.5°	341.0	404.6	557.4	804.9	923.0
140°	351.8	414.6	556.4	764.4	865.7
142.5°	363.7	423.4	554.4	727.4	812.4
145°	376.5	431.4	552.4	694.2	763.9
147.5°	389.4	439.8	549.5	668.6	722.4
150°	402.2	446.7	545.5	645.8	686.8
152.5°	415.1	454.1	540.6	626.1	657.2
155°	427.9	461.5	534.6	607.8	633.5
157.5°	437.8	468.0	529.7	590.0	610.7
160°	449.7	473.4	523.8	573.7	589.0
162.5°	458.6	477.4	517.8	558.3	569.2
165°	467.4	480.8	511.9	543.0	552.4
167.5°	474.4	483.8	506.0	529.7	535.6
170°	480.3	485.2	500.1	517.8	520.8
172.5°	484.2	486.7	495.1	507.5	507.0
175°	487.2	487.7	491.2	498.1	497.1
177.5°	489.2	488.2	488.2	492.2	490.2
180°	488.2	488.2	488.2	488.2	488.2

(END OF REPORT)