

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011929

Luminaire Tested: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011929
REPORT IS A COMBINATION OF REPORTS P990268 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6637.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011929

CATALOG NUMBER: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011929

CATALOG NUMBER: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	86	82	79	72	69	67	59	58	56	48	47	46
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13135	12651	12631
10°	13018	12222	12097
15°	12837	11777	11514
20°	12630	11282	10937
25°	12361	10762	10320
30°	12067	10221	9670
35°	11760	9669	9025
40°	11437	9091	8391
45°	11083	8527	7728
50°	10723	7898	7063
55°	10259	7243	6387
60°	9783	6520	5671
65°	9336	5738	4922
70°	8693	4872	4048
75°	7764	3858	3143
80°	6705	2712	2223
85°	5225	1456	1113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11083 cd/sqm

TEST NUMBER: P1011929

CATALOG NUMBER: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	1.7
10°-20°	324.0	4.9
20°-30°	478.6	7.2
30°-40°	558.9	8.4
40°-50°	561.9	8.5
50°-60°	493.6	7.4
60°-70°	367.6	5.5
70°-80°	209.2	3.2
80°-90°	62.1	0.9
90°-100°	80.5	1.2
100°-110°	243.7	3.7
110°-120°	415.0	6.3
120°-130°	545.9	8.2
130°-140°	613.6	9.2
140°-150°	603.2	9.1
150°-160°	507.9	7.7
160°-170°	338.1	5.1
170°-180°	118.4	1.8
0°-30°	917.4	13.8
0°-40°	1476.3	22.2
0°-60°	2531.7	38.1
0°-90°	3170.7	47.8
90°-120°	739.2	11.1
90°-150°	2502.0	37.7
90°-180°	3466.0	52.2
0°-180°	6637.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	58
90°	1	11	24	28	30	8
95°	58	65	73	77	77	64
105°	221	223	232	232	234	237
115°	418	421	419	420	419	413
125°	611	614	612	608	604	545
135°	793	799	798	794	792	611
145°	962	964	967	966	962	601
155°	1102	1102	1103	1107	1100	507
165°	1200	1197	1197	1203	1196	338
175°	1248	1244	1244	1250	1243	119
180°	1251	1251	1251	1251	1251	

TEST NUMBER: P1011929

CATALOG NUMBER: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	1.0	10.8	23.6	27.5	29.5
92.5°	29.5	35.4	41.3	44.2	42.3
95°	58.0	64.9	72.7	76.7	76.7
97.5°	95.3	100.2	106.1	111.0	110.1
100°	133.7	139.5	144.5	147.4	149.4
102.5°	177.9	180.8	187.7	190.7	189.7
105°	221.1	223.1	231.9	231.9	233.9
107.5°	272.2	273.2	277.1	280.1	279.1
110°	319.4	321.4	323.3	327.3	325.3

TEST NUMBER: P1011929

CATALOG NUMBER: S123DIP-B775D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.5	369.5	369.5	374.4	374.4
115°	417.7	420.6	418.6	419.6	418.6
117.5°	467.8	468.8	466.8	466.8	463.9
120°	514.0	519.9	515.0	514.0	512.0
122.5°	562.1	566.1	564.1	561.1	558.2
125°	611.3	614.2	612.2	608.3	604.4
127.5°	656.5	662.4	660.4	654.5	650.6
130°	701.7	709.5	706.6	702.7	695.8
132.5°	746.9	754.7	752.8	747.9	742.9
135°	793.1	799.0	798.0	794.1	792.1
137.5°	835.3	840.2	843.2	838.3	835.3
140°	879.5	884.5	885.4	884.5	877.6
142.5°	919.8	924.8	926.7	925.7	920.8
145°	962.1	964.1	967.0	966.0	962.1
147.5°	998.5	1002.4	1005.3	1005.3	999.4
150°	1036.8	1038.8	1040.7	1040.7	1034.8
152.5°	1068.2	1071.2	1072.2	1074.1	1069.2
155°	1101.6	1101.6	1102.6	1106.6	1099.7
157.5°	1130.1	1129.2	1130.1	1134.1	1128.2
160°	1156.7	1154.7	1154.7	1159.6	1155.7
162.5°	1180.3	1177.3	1178.3	1183.2	1176.3
165°	1199.9	1197.0	1197.0	1202.9	1196.0
167.5°	1216.6	1212.7	1213.7	1219.6	1213.7
170°	1230.4	1226.5	1226.5	1233.3	1226.5
172.5°	1241.2	1237.3	1237.3	1243.2	1236.3
175°	1248.1	1244.1	1244.1	1250.0	1243.2
177.5°	1252.0	1248.1	1248.1	1254.0	1247.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)