

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011651

Luminaire Tested: S123DIP-B340D805UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011651
REPORT IS A COMBINATION OF REPORTS P989891 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4218.6 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011651

CATALOG NUMBER: S123DIP-B340D805UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011651

CATALOG NUMBER: S123DIP-B340D805UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	25	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	28	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1011651

CATALOG NUMBER: S123DIP-B340D805UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	1.2
10°-20°	140.4	3.3
20°-30°	207.4	4.9
30°-40°	242.2	5.7
40°-50°	243.5	5.8
50°-60°	213.9	5.1
60°-70°	159.3	3.8
70°-80°	90.7	2.1
80°-90°	27.9	0.7
90°-100°	214.3	5.1
100°-110°	599.0	14.2
110°-120°	584.1	13.8
120°-130°	465.1	11.0
130°-140°	367.1	8.7
140°-150°	273.9	6.5
150°-160°	191.1	4.5
160°-170°	112.3	2.7
170°-180°	36.5	0.9
0°-30°	397.6	9.4
0°-40°	639.8	15.2
0°-60°	1097.2	26.0
0°-90°	1375.1	32.6
90°-120°	1397.5	33.1
90°-150°	2503.6	59.3
90°-180°	2844.0	67.4
0°-180°	4218.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	2	9	19	21	22	4
95°	26	84	453	132	89	28
105°	89	131	614	1073	971	94
115°	156	195	470	1030	1181	155
125°	218	257	438	794	931	193
135°	255	304	432	654	755	197
145°	291	333	427	536	590	182
155°	331	356	413	470	489	152
165°	361	371	396	420	427	102
175°	376	377	379	385	384	36
180°	377	377	377	377	377	

TEST NUMBER: P1011651

CATALOG NUMBER: S123DIP-B340D805UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	1.5	9.2	19.1	21.4	22.1
92.5°	11.5	45.8	142.0	48.5	40.5
95°	26.0	84.4	452.7	132.0	88.6
97.5°	41.2	96.6	696.3	332.1	181.7
100°	56.5	106.5	723.0	694.7	478.7
102.5°	72.5	118.0	673.4	930.3	758.1
105°	88.6	131.0	613.8	1073.4	971.1
107.5°	105.4	146.2	561.1	1136.4	1110.1
110°	123.7	161.8	517.6	1138.3	1189.5

TEST NUMBER: P1011651

CATALOG NUMBER: S123DIP-B340D805UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.5	178.3	488.6	1095.2	1205.5
115°	156.5	195.1	469.5	1029.5	1181.1
117.5°	172.5	211.1	456.5	959.2	1127.6
120°	189.3	227.2	448.1	892.8	1057.4
122.5°	203.8	242.4	442.8	840.6	991.7
125°	217.6	256.9	438.2	794.0	931.4
127.5°	228.3	270.6	435.9	755.8	879.5
130°	238.2	282.9	433.6	720.7	836.7
132.5°	245.8	294.0	432.9	687.8	794.7
135°	255.0	304.2	432.1	653.9	755.1
137.5°	263.4	312.6	430.6	621.8	713.1
140°	271.8	320.2	429.8	590.5	668.8
142.5°	280.9	327.2	428.3	561.9	627.6
145°	290.9	333.2	426.8	536.3	590.1
147.5°	300.8	339.8	424.5	516.5	558.1
150°	310.7	345.0	421.4	499.0	530.6
152.5°	320.6	350.8	417.6	483.6	507.7
155°	330.6	356.5	413.0	469.5	489.4
157.5°	338.2	361.5	409.2	455.8	471.8
160°	347.4	365.7	404.6	443.2	455.0
162.5°	354.2	368.8	400.0	431.4	439.7
165°	361.1	371.4	395.5	419.5	426.8
167.5°	366.5	373.7	390.9	409.2	413.8
170°	371.0	374.8	386.3	400.0	402.3
172.5°	374.1	376.0	382.5	392.0	391.6
175°	376.4	376.8	379.4	384.8	384.0
177.5°	377.9	377.1	377.1	380.2	378.7
180°	377.1	377.1	377.1	377.1	377.1

(END OF REPORT)