

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011933

Luminaire Tested: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011933
REPORT IS A COMBINATION OF REPORTS P990272 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6685.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40	40	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34	34	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29	29	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25	22	22	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19	19	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17	17	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15	15	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14	14	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.5
10°-20°	329.9	4.9
20°-30°	555.1	8.3
30°-40°	627.3	9.4
40°-50°	561.8	8.4
50°-60°	453.5	6.8
60°-70°	316.0	4.7
70°-80°	165.9	2.5
80°-90°	42.4	0.6
90°-100°	254.7	3.8
100°-110°	745.6	11.2
110°-120°	728.1	10.9
120°-130°	579.9	8.7
130°-140°	457.5	6.8
140°-150°	341.3	5.1
150°-160°	238.0	3.6
160°-170°	139.8	2.1
170°-180°	45.5	0.7
0°-30°	987.7	14.8
0°-40°	1615.0	24.2
0°-60°	2630.3	39.3
0°-90°	3154.6	47.2
90°-120°	1728.5	25.9
90°-150°	3107.2	46.5
90°-180°	3530.0	52.8
0°-180°	6685.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	2	28	2	28	2	5
95°	32	110	32	110	32	34
105°	110	1208	110	1208	110	117
115°	195	1470	195	1470	195	193
125°	271	1159	271	1159	271	241
135°	317	940	317	940	317	245
145°	362	734	362	734	362	227
155°	411	609	411	609	411	189
165°	449	531	449	531	449	127
175°	468	478	468	478	468	44
180°	469	469	469	469	469	

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	1.9	3.8	5.7	8.6	10.5	11.4	12.4	15.2	18.1	20.9	23.8
92.5°	14.3	20.9	30.4	39.0	48.5	57.0	65.6	96.0	146.3	195.7	176.7
95°	32.3	35.2	45.6	61.8	86.5	105.0	123.5	204.3	345.8	501.6	563.4
97.5°	51.3	52.3	60.8	75.1	99.8	120.2	140.6	220.4	384.8	647.0	866.5
100°	70.3	71.3	77.9	91.2	114.0	132.6	151.1	217.6	358.2	608.0	899.7
102.5°	90.3	92.2	97.9	110.2	130.2	146.8	163.4	221.4	335.4	551.0	838.0
105°	110.2	113.1	118.8	130.2	148.2	163.0	177.7	229.0	326.8	506.4	763.9
107.5°	131.1	134.0	139.7	151.1	168.2	182.0	195.7	241.3	324.9	474.1	698.3
110°	153.9	156.8	161.5	172.0	188.1	201.4	214.7	257.5	329.7	457.0	644.2

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.8	177.7	182.4	192.9	209.0	221.8	234.7	273.6	339.2	447.5	608.0
115°	194.8	198.6	204.3	213.8	229.9	242.8	255.6	291.7	349.6	446.5	584.3
117.5°	214.7	219.5	224.2	232.8	250.8	262.7	274.6	310.7	362.9	447.5	568.1
120°	235.6	238.5	243.2	252.7	270.8	282.6	294.5	328.7	378.1	451.3	557.7
122.5°	253.7	256.5	261.3	271.7	288.8	301.6	314.5	347.7	392.4	457.9	551.0
125°	270.8	272.7	278.4	288.8	306.9	319.7	332.5	365.8	407.6	464.6	545.3
127.5°	284.1	286.9	293.6	304.0	324.0	336.8	349.6	381.9	419.9	472.2	542.5
130°	296.4	299.3	307.8	319.2	339.2	352.0	364.8	396.2	432.3	479.8	539.6
132.5°	305.9	309.7	319.2	333.5	353.4	365.8	378.1	408.5	443.7	485.5	538.7
135°	317.3	321.1	331.6	345.8	365.8	378.6	391.4	420.9	453.2	491.2	537.7
137.5°	327.8	331.6	342.0	357.2	377.2	389.0	400.9	429.4	460.8	495.0	535.8
140°	338.2	343.0	352.5	367.7	386.7	398.5	410.4	438.0	466.5	498.8	534.9
142.5°	349.6	353.4	363.9	377.2	396.2	407.1	418.0	444.6	472.2	501.6	533.0
145°	362.0	364.8	373.4	387.6	403.8	414.7	425.6	450.3	476.0	502.6	531.1
147.5°	374.3	376.2	384.8	397.1	413.3	422.8	432.3	455.1	478.8	502.6	528.2
150°	386.7	387.6	395.2	407.6	420.9	429.4	438.0	459.8	479.8	502.6	524.4
152.5°	399.0	399.0	406.6	417.1	428.5	436.6	444.6	462.7	481.7	499.7	519.7
155°	411.4	411.4	417.1	426.6	437.0	443.6	450.3	466.5	481.7	497.8	514.0
157.5°	420.9	421.8	426.6	435.1	444.6	449.8	455.1	468.4	482.6	495.0	509.2
160°	432.3	432.3	436.1	443.7	450.3	455.0	459.8	471.2	482.6	493.1	503.5
162.5°	440.8	440.8	443.7	449.4	455.1	458.9	462.7	472.2	481.7	489.3	497.8
165°	449.4	448.4	450.3	455.1	458.9	462.2	465.5	473.1	479.8	485.5	492.1
167.5°	456.0	455.1	456.0	459.8	462.7	465.0	467.4	473.1	478.8	481.7	486.4
170°	461.7	459.8	460.8	463.6	465.5	466.4	467.4	472.2	476.0	477.9	480.7
172.5°	465.5	464.6	464.6	466.5	467.4	467.9	468.4	472.2	475.0	475.0	476.0
175°	468.4	467.4	466.5	468.4	468.4	468.8	469.3	471.2	473.1	472.2	472.2
177.5°	470.3	469.3	468.4	469.3	469.3	469.3	469.3	470.3	472.2	470.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	22.8	23.8	24.7	25.7	26.6	27.6	26.6	27.6	28.5	27.6	28.5
92.5°	132.1	94.1	73.2	63.7	60.4	57.0	55.1	51.3	52.3	50.4	52.3
95°	457.0	342.0	231.8	181.5	164.4	147.3	129.2	120.7	114.0	110.2	114.0
97.5°	895.9	785.7	592.8	467.4	413.2	359.1	295.5	259.4	236.6	226.1	236.6
100°	1086.9	1120.1	1043.2	932.0	864.6	797.1	701.2	631.8	594.7	595.7	594.7
102.5°	1096.4	1231.3	1247.4	1194.2	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0
105°	1036.5	1235.1	1330.1	1348.2	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2
107.5°	951.0	1178.1	1327.3	1401.4	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9
110°	871.2	1088.8	1263.6	1383.3	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.9	1000.4	1180.0	1317.8	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2
115°	748.7	924.4	1089.7	1229.4	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0
117.5°	713.5	865.5	1011.8	1140.1	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6
120°	686.9	820.9	949.1	1063.1	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2
122.5°	665.1	785.7	898.8	1002.3	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5
125°	647.0	755.3	858.9	950.1	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4
127.5°	629.9	727.8	821.8	905.4	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8
130°	616.6	702.1	787.6	864.6	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7
132.5°	604.2	678.4	755.3	825.6	856.0	886.4	933.0	967.2	984.3	989.0	984.3
135°	593.8	657.5	724.9	786.7	813.8	840.8	887.4	915.9	933.0	939.6	933.0
137.5°	584.3	637.5	694.5	749.6	773.8	798.1	838.0	867.4	881.7	887.4	881.7
140°	575.7	620.4	668.9	714.5	734.9	755.3	791.4	818.0	833.2	832.3	833.2
142.5°	568.1	604.2	644.2	682.2	699.3	716.4	745.8	768.6	781.9	781.0	781.9
145°	561.5	591.9	623.2	653.7	667.4	681.2	705.0	724.9	732.5	734.4	732.5
147.5°	554.8	581.4	607.1	632.8	642.8	652.7	671.7	686.0	693.6	694.5	693.6
150°	548.2	570.0	591.9	611.8	620.8	629.9	644.2	654.6	660.3	660.3	660.3
152.5°	540.6	559.6	577.6	594.7	601.8	609.0	619.4	628.9	631.8	631.8	631.8
155°	533.0	549.1	564.3	578.6	584.3	590.0	598.5	606.1	608.0	609.0	608.0
157.5°	524.4	537.7	551.0	562.4	567.2	571.9	579.5	585.2	587.1	587.1	587.1
160°	515.9	528.2	538.7	548.2	551.5	554.8	561.5	567.2	567.2	566.2	567.2
162.5°	507.3	516.8	525.4	533.9	536.8	539.6	543.4	548.2	548.2	547.2	548.2
165°	499.7	507.3	513.0	519.7	522.0	524.4	528.2	532.0	531.1	531.1	531.1
167.5°	492.1	498.8	503.5	507.3	509.2	511.1	513.0	515.9	514.9	514.9	514.9
170°	485.5	490.2	493.1	496.9	497.8	498.8	499.7	501.6	500.7	500.7	500.7
172.5°	478.8	482.6	484.5	487.4	487.8	488.3	488.3	490.2	488.3	487.4	488.3
175°	474.1	476.0	476.9	478.8	478.8	478.8	478.8	479.8	478.8	477.9	478.8
177.5°	470.3	471.2	472.2	473.1	473.1	473.1	472.2	473.1	471.2	471.2	471.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	27.6	26.6	27.6	26.6	25.7	24.7	23.8	22.8	23.8	20.9	18.1
92.5°	51.3	55.1	57.0	60.4	63.7	73.2	94.1	132.1	176.7	195.7	146.3
95°	120.7	129.2	147.3	164.4	181.5	231.8	342.0	457.0	563.4	501.6	345.8
97.5°	259.4	295.5	359.1	413.2	467.4	592.8	785.7	895.9	866.5	647.0	384.8
100°	631.8	701.2	797.1	864.6	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2
102.5°	1000.4	1051.7	1121.1	1157.6	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4
105°	1243.6	1279.8	1323.5	1335.8	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8
107.5°	1404.2	1421.3	1427.0	1414.2	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9
110°	1484.0	1476.4	1449.8	1416.6	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1489.7	1462.2	1408.0	1362.9	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2
115°	1446.0	1404.2	1333.0	1281.2	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6
117.5°	1368.1	1321.6	1247.4	1193.8	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9
120°	1287.4	1234.1	1159.1	1111.1	1063.1	949.1	820.9	686.9	557.7	451.3	378.1
122.5°	1200.9	1154.3	1089.7	1046.0	1002.3	898.8	785.7	665.1	551.0	457.9	392.4
125°	1128.7	1086.9	1026.1	988.1	950.1	858.9	755.3	647.0	545.3	464.6	407.6
127.5°	1066.9	1030.8	975.7	940.6	905.4	821.8	727.8	629.9	542.5	472.2	419.9
130°	1013.7	979.5	929.2	896.9	864.6	787.6	702.1	616.6	539.6	479.8	432.3
132.5°	967.2	933.0	886.4	856.0	825.6	755.3	678.4	604.2	538.7	485.5	443.7
135°	915.9	887.4	840.8	813.8	786.7	724.9	657.5	593.8	537.7	491.2	453.2
137.5°	867.4	838.0	798.1	773.8	749.6	694.5	637.5	584.3	535.8	495.0	460.8
140°	818.0	791.4	755.3	734.9	714.5	668.9	620.4	575.7	534.9	498.8	466.5
142.5°	768.6	745.8	716.4	699.3	682.2	644.2	604.2	568.1	533.0	501.6	472.2
145°	724.9	705.0	681.2	667.4	653.7	623.2	591.9	561.5	531.1	502.6	476.0
147.5°	686.0	671.7	652.7	642.8	632.8	607.1	581.4	554.8	528.2	502.6	478.8
150°	654.6	644.2	629.9	620.8	611.8	591.9	570.0	548.2	524.4	502.6	479.8
152.5°	628.9	619.4	609.0	601.8	594.7	577.6	559.6	540.6	519.7	499.7	481.7
155°	606.1	598.5	590.0	584.3	578.6	564.3	549.1	533.0	514.0	497.8	481.7
157.5°	585.2	579.5	571.9	567.2	562.4	551.0	537.7	524.4	509.2	495.0	482.6
160°	567.2	561.5	554.8	551.5	548.2	538.7	528.2	515.9	503.5	493.1	482.6
162.5°	548.2	543.4	539.6	536.8	533.9	525.4	516.8	507.3	497.8	489.3	481.7
165°	532.0	528.2	524.4	522.0	519.7	513.0	507.3	499.7	492.1	485.5	479.8
167.5°	515.9	513.0	511.1	509.2	507.3	503.5	498.8	492.1	486.4	481.7	478.8
170°	501.6	499.7	498.8	497.8	496.9	493.1	490.2	485.5	480.7	477.9	476.0
172.5°	490.2	488.3	488.3	487.8	487.4	484.5	482.6	478.8	476.0	475.0	475.0
175°	479.8	478.8	478.8	478.8	478.8	476.9	476.0	474.1	472.2	472.2	473.1
177.5°	473.1	472.2	473.1	473.1	473.1	472.2	471.2	470.3	469.3	470.3	472.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	15.2	12.4	11.4	10.5	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	96.0	65.6	57.0	48.5	39.0	30.4	20.9	14.3	20.9	30.4	39.0
95°	204.3	123.5	105.0	86.5	61.8	45.6	35.2	32.3	35.2	45.6	61.8
97.5°	220.4	140.6	120.2	99.8	75.1	60.8	52.3	51.3	52.3	60.8	75.1
100°	217.6	151.1	132.6	114.0	91.2	77.9	71.3	70.3	71.3	77.9	91.2
102.5°	221.4	163.4	146.8	130.2	110.2	97.9	92.2	90.3	92.2	97.9	110.2
105°	229.0	177.7	163.0	148.2	130.2	118.8	113.1	110.2	113.1	118.8	130.2
107.5°	241.3	195.7	182.0	168.2	151.1	139.7	134.0	131.1	134.0	139.7	151.1
110°	257.5	214.7	201.4	188.1	172.0	161.5	156.8	153.9	156.8	161.5	172.0

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.6	234.7	221.8	209.0	192.9	182.4	177.7	174.8	177.7	182.4	192.9
115°	291.7	255.6	242.8	229.9	213.8	204.3	198.6	194.8	198.6	204.3	213.8
117.5°	310.7	274.6	262.7	250.8	232.8	224.2	219.5	214.7	219.5	224.2	232.8
120°	328.7	294.5	282.6	270.8	252.7	243.2	238.5	235.6	238.5	243.2	252.7
122.5°	347.7	314.5	301.6	288.8	271.7	261.3	256.5	253.7	256.5	261.3	271.7
125°	365.8	332.5	319.7	306.9	288.8	278.4	272.7	270.8	272.7	278.4	288.8
127.5°	381.9	349.6	336.8	324.0	304.0	293.6	286.9	284.1	286.9	293.6	304.0
130°	396.2	364.8	352.0	339.2	319.2	307.8	299.3	296.4	299.3	307.8	319.2
132.5°	408.5	378.1	365.8	353.4	333.5	319.2	309.7	305.9	309.7	319.2	333.5
135°	420.9	391.4	378.6	365.8	345.8	331.6	321.1	317.3	321.1	331.6	345.8
137.5°	429.4	400.9	389.0	377.2	357.2	342.0	331.6	327.8	331.6	342.0	357.2
140°	438.0	410.4	398.5	386.7	367.7	352.5	343.0	338.2	343.0	352.5	367.7
142.5°	444.6	418.0	407.1	396.2	377.2	363.9	353.4	349.6	353.4	363.9	377.2
145°	450.3	425.6	414.7	403.8	387.6	373.4	364.8	362.0	364.8	373.4	387.6
147.5°	455.1	432.3	422.8	413.3	397.1	384.8	376.2	374.3	376.2	384.8	397.1
150°	459.8	438.0	429.4	420.9	407.6	395.2	387.6	386.7	387.6	395.2	407.6
152.5°	462.7	444.6	436.6	428.5	417.1	406.6	399.0	399.0	399.0	406.6	417.1
155°	466.5	450.3	443.6	437.0	426.6	417.1	411.4	411.4	411.4	417.1	426.6
157.5°	468.4	455.1	449.8	444.6	435.1	426.6	421.8	420.9	421.8	426.6	435.1
160°	471.2	459.8	455.0	450.3	443.7	436.1	432.3	432.3	432.3	436.1	443.7
162.5°	472.2	462.7	458.9	455.1	449.4	443.7	440.8	440.8	440.8	443.7	449.4
165°	473.1	465.5	462.2	458.9	455.1	450.3	448.4	449.4	448.4	450.3	455.1
167.5°	473.1	467.4	465.0	462.7	459.8	456.0	455.1	456.0	455.1	456.0	459.8
170°	472.2	467.4	466.4	465.5	463.6	460.8	459.8	461.7	459.8	460.8	463.6
172.5°	472.2	468.4	467.9	467.4	466.5	464.6	464.6	465.5	464.6	464.6	466.5
175°	471.2	469.3	468.8	468.4	468.4	466.5	467.4	468.4	467.4	466.5	468.4
177.5°	470.3	469.3	469.3	469.3	469.3	468.4	469.3	470.3	469.3	468.4	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	10.5	11.4	12.4	15.2	18.1	20.9	23.8	22.8	23.8	24.7	25.7
92.5°	48.5	57.0	65.6	96.0	146.3	195.7	176.7	132.1	94.1	73.2	63.7
95°	86.5	105.0	123.5	204.3	345.8	501.6	563.4	457.0	342.0	231.8	181.5
97.5°	99.8	120.2	140.6	220.4	384.8	647.0	866.5	895.9	785.7	592.8	467.4
100°	114.0	132.6	151.1	217.6	358.2	608.0	899.7	1086.9	1120.1	1043.2	932.0
102.5°	130.2	146.8	163.4	221.4	335.4	551.0	838.0	1096.4	1231.3	1247.4	1194.2
105°	148.2	163.0	177.7	229.0	326.8	506.4	763.9	1036.5	1235.1	1330.1	1348.2
107.5°	168.2	182.0	195.7	241.3	324.9	474.1	698.3	951.0	1178.1	1327.3	1401.4
110°	188.1	201.4	214.7	257.5	329.7	457.0	644.2	871.2	1088.8	1263.6	1383.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	209.0	221.8	234.7	273.6	339.2	447.5	608.0	801.9	1000.4	1180.0	1317.8
115°	229.9	242.8	255.6	291.7	349.6	446.5	584.3	748.7	924.4	1089.7	1229.4
117.5°	250.8	262.7	274.6	310.7	362.9	447.5	568.1	713.5	865.5	1011.8	1140.1
120°	270.8	282.6	294.5	328.7	378.1	451.3	557.7	686.9	820.9	949.1	1063.1
122.5°	288.8	301.6	314.5	347.7	392.4	457.9	551.0	665.1	785.7	898.8	1002.3
125°	306.9	319.7	332.5	365.8	407.6	464.6	545.3	647.0	755.3	858.9	950.1
127.5°	324.0	336.8	349.6	381.9	419.9	472.2	542.5	629.9	727.8	821.8	905.4
130°	339.2	352.0	364.8	396.2	432.3	479.8	539.6	616.6	702.1	787.6	864.6
132.5°	353.4	365.8	378.1	408.5	443.7	485.5	538.7	604.2	678.4	755.3	825.6
135°	365.8	378.6	391.4	420.9	453.2	491.2	537.7	593.8	657.5	724.9	786.7
137.5°	377.2	389.0	400.9	429.4	460.8	495.0	535.8	584.3	637.5	694.5	749.6
140°	386.7	398.5	410.4	438.0	466.5	498.8	534.9	575.7	620.4	668.9	714.5
142.5°	396.2	407.1	418.0	444.6	472.2	501.6	533.0	568.1	604.2	644.2	682.2
145°	403.8	414.7	425.6	450.3	476.0	502.6	531.1	561.5	591.9	623.2	653.7
147.5°	413.3	422.8	432.3	455.1	478.8	502.6	528.2	554.8	581.4	607.1	632.8
150°	420.9	429.4	438.0	459.8	479.8	502.6	524.4	548.2	570.0	591.9	611.8
152.5°	428.5	436.6	444.6	462.7	481.7	499.7	519.7	540.6	559.6	577.6	594.7
155°	437.0	443.6	450.3	466.5	481.7	497.8	514.0	533.0	549.1	564.3	578.6
157.5°	444.6	449.8	455.1	468.4	482.6	495.0	509.2	524.4	537.7	551.0	562.4
160°	450.3	455.0	459.8	471.2	482.6	493.1	503.5	515.9	528.2	538.7	548.2
162.5°	455.1	458.9	462.7	472.2	481.7	489.3	497.8	507.3	516.8	525.4	533.9
165°	458.9	462.2	465.5	473.1	479.8	485.5	492.1	499.7	507.3	513.0	519.7
167.5°	462.7	465.0	467.4	473.1	478.8	481.7	486.4	492.1	498.8	503.5	507.3
170°	465.5	466.4	467.4	472.2	476.0	477.9	480.7	485.5	490.2	493.1	496.9
172.5°	467.4	467.9	468.4	472.2	475.0	475.0	476.0	478.8	482.6	484.5	487.4
175°	468.4	468.8	469.3	471.2	473.1	472.2	472.2	474.1	476.0	476.9	478.8
177.5°	469.3	469.3	469.3	470.3	472.2	470.3	469.3	470.3	471.2	472.2	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	26.6	27.6	26.6	27.6	28.5	27.6	28.5	27.6	26.6	27.6	26.6
92.5°	60.4	57.0	55.1	51.3	52.3	50.4	52.3	51.3	55.1	57.0	60.4
95°	164.4	147.3	129.2	120.7	114.0	110.2	114.0	120.7	129.2	147.3	164.4
97.5°	413.2	359.1	295.5	259.4	236.6	226.1	236.6	259.4	295.5	359.1	413.2
100°	864.6	797.1	701.2	631.8	594.7	595.7	594.7	631.8	701.2	797.1	864.6
102.5°	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0	1000.4	1051.7	1121.1	1157.6
105°	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2	1243.6	1279.8	1323.5	1335.8
107.5°	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9	1404.2	1421.3	1427.0	1414.2
110°	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1	1484.0	1476.4	1449.8	1416.6

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2	1489.7	1462.2	1408.0	1362.9
115°	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0	1446.0	1404.2	1333.0	1281.2
117.5°	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6	1368.1	1321.6	1247.4	1193.8
120°	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2	1287.4	1234.1	1159.1	1111.1
122.5°	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5	1200.9	1154.3	1089.7	1046.0
125°	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4	1128.7	1086.9	1026.1	988.1
127.5°	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8	1066.9	1030.8	975.7	940.6
130°	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7	1013.7	979.5	929.2	896.9
132.5°	856.0	886.4	933.0	967.2	984.3	989.0	984.3	967.2	933.0	886.4	856.0
135°	813.8	840.8	887.4	915.9	933.0	939.6	933.0	915.9	887.4	840.8	813.8
137.5°	773.8	798.1	838.0	867.4	881.7	887.4	881.7	867.4	838.0	798.1	773.8
140°	734.9	755.3	791.4	818.0	833.2	832.3	833.2	818.0	791.4	755.3	734.9
142.5°	699.3	716.4	745.8	768.6	781.9	781.0	781.9	768.6	745.8	716.4	699.3
145°	667.4	681.2	705.0	724.9	732.5	734.4	732.5	724.9	705.0	681.2	667.4
147.5°	642.8	652.7	671.7	686.0	693.6	694.5	693.6	686.0	671.7	652.7	642.8
150°	620.8	629.9	644.2	654.6	660.3	660.3	660.3	654.6	644.2	629.9	620.8
152.5°	601.8	609.0	619.4	628.9	631.8	631.8	631.8	628.9	619.4	609.0	601.8
155°	584.3	590.0	598.5	606.1	608.0	609.0	608.0	606.1	598.5	590.0	584.3
157.5°	567.2	571.9	579.5	585.2	587.1	587.1	587.1	585.2	579.5	571.9	567.2
160°	551.5	554.8	561.5	567.2	567.2	566.2	567.2	567.2	561.5	554.8	551.5
162.5°	536.8	539.6	543.4	548.2	548.2	547.2	548.2	548.2	543.4	539.6	536.8
165°	522.0	524.4	528.2	532.0	531.1	531.1	531.1	532.0	528.2	524.4	522.0
167.5°	509.2	511.1	513.0	515.9	514.9	514.9	514.9	515.9	513.0	511.1	509.2
170°	497.8	498.8	499.7	501.6	500.7	500.7	500.7	501.6	499.7	498.8	497.8
172.5°	487.8	488.3	488.3	490.2	488.3	487.4	488.3	490.2	488.3	488.3	487.8
175°	478.8	478.8	478.8	479.8	478.8	477.9	478.8	479.8	478.8	478.8	478.8
177.5°	473.1	473.1	472.2	473.1	471.2	471.2	471.2	473.1	472.2	473.1	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	25.7	24.7	23.8	22.8	23.8	20.9	18.1	15.2	12.4	11.4	10.5
92.5°	63.7	73.2	94.1	132.1	176.7	195.7	146.3	96.0	65.6	57.0	48.5
95°	181.5	231.8	342.0	457.0	563.4	501.6	345.8	204.3	123.5	105.0	86.5
97.5°	467.4	592.8	785.7	895.9	866.5	647.0	384.8	220.4	140.6	120.2	99.8
100°	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2	217.6	151.1	132.6	114.0
102.5°	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4	221.4	163.4	146.8	130.2
105°	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8	229.0	177.7	163.0	148.2
107.5°	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9	241.3	195.7	182.0	168.2
110°	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7	257.5	214.7	201.4	188.1

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2	273.6	234.7	221.8	209.0
115°	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6	291.7	255.6	242.8	229.9
117.5°	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9	310.7	274.6	262.7	250.8
120°	1063.1	949.1	820.9	686.9	557.7	451.3	378.1	328.7	294.5	282.6	270.8
122.5°	1002.3	898.8	785.7	665.1	551.0	457.9	392.4	347.7	314.5	301.6	288.8
125°	950.1	858.9	755.3	647.0	545.3	464.6	407.6	365.8	332.5	319.7	306.9
127.5°	905.4	821.8	727.8	629.9	542.5	472.2	419.9	381.9	349.6	336.8	324.0
130°	864.6	787.6	702.1	616.6	539.6	479.8	432.3	396.2	364.8	352.0	339.2
132.5°	825.6	755.3	678.4	604.2	538.7	485.5	443.7	408.5	378.1	365.8	353.4
135°	786.7	724.9	657.5	593.8	537.7	491.2	453.2	420.9	391.4	378.6	365.8
137.5°	749.6	694.5	637.5	584.3	535.8	495.0	460.8	429.4	400.9	389.0	377.2
140°	714.5	668.9	620.4	575.7	534.9	498.8	466.5	438.0	410.4	398.5	386.7
142.5°	682.2	644.2	604.2	568.1	533.0	501.6	472.2	444.6	418.0	407.1	396.2
145°	653.7	623.2	591.9	561.5	531.1	502.6	476.0	450.3	425.6	414.7	403.8
147.5°	632.8	607.1	581.4	554.8	528.2	502.6	478.8	455.1	432.3	422.8	413.3
150°	611.8	591.9	570.0	548.2	524.4	502.6	479.8	459.8	438.0	429.4	420.9
152.5°	594.7	577.6	559.6	540.6	519.7	499.7	481.7	462.7	444.6	436.6	428.5
155°	578.6	564.3	549.1	533.0	514.0	497.8	481.7	466.5	450.3	443.6	437.0
157.5°	562.4	551.0	537.7	524.4	509.2	495.0	482.6	468.4	455.1	449.8	444.6
160°	548.2	538.7	528.2	515.9	503.5	493.1	482.6	471.2	459.8	455.0	450.3
162.5°	533.9	525.4	516.8	507.3	497.8	489.3	481.7	472.2	462.7	458.9	455.1
165°	519.7	513.0	507.3	499.7	492.1	485.5	479.8	473.1	465.5	462.2	458.9
167.5°	507.3	503.5	498.8	492.1	486.4	481.7	478.8	473.1	467.4	465.0	462.7
170°	496.9	493.1	490.2	485.5	480.7	477.9	476.0	472.2	467.4	466.4	465.5
172.5°	487.4	484.5	482.6	478.8	476.0	475.0	475.0	472.2	468.4	467.9	467.4
175°	478.8	476.9	476.0	474.1	472.2	472.2	473.1	471.2	469.3	468.8	468.4
177.5°	473.1	472.2	471.2	470.3	469.3	470.3	472.2	470.3	469.3	469.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	8.6	5.7	3.8	1.9
92.5°	39.0	30.4	20.9	14.3
95°	61.8	45.6	35.2	32.3
97.5°	75.1	60.8	52.3	51.3
100°	91.2	77.9	71.3	70.3
102.5°	110.2	97.9	92.2	90.3
105°	130.2	118.8	113.1	110.2
107.5°	151.1	139.7	134.0	131.1
110°	172.0	161.5	156.8	153.9

TEST NUMBER: P1011933

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	192.9	182.4	177.7	174.8
115°	213.8	204.3	198.6	194.8
117.5°	232.8	224.2	219.5	214.7
120°	252.7	243.2	238.5	235.6
122.5°	271.7	261.3	256.5	253.7
125°	288.8	278.4	272.7	270.8
127.5°	304.0	293.6	286.9	284.1
130°	319.2	307.8	299.3	296.4
132.5°	333.5	319.2	309.7	305.9
135°	345.8	331.6	321.1	317.3
137.5°	357.2	342.0	331.6	327.8
140°	367.7	352.5	343.0	338.2
142.5°	377.2	363.9	353.4	349.6
145°	387.6	373.4	364.8	362.0
147.5°	397.1	384.8	376.2	374.3
150°	407.6	395.2	387.6	386.7
152.5°	417.1	406.6	399.0	399.0
155°	426.6	417.1	411.4	411.4
157.5°	435.1	426.6	421.8	420.9
160°	443.7	436.1	432.3	432.3
162.5°	449.4	443.7	440.8	440.8
165°	455.1	450.3	448.4	449.4
167.5°	459.8	456.0	455.1	456.0
170°	463.6	460.8	459.8	461.7
172.5°	466.5	464.6	464.6	465.5
175°	468.4	466.5	467.4	468.4
177.5°	469.3	468.4	469.3	470.3
180°	469.3	469.3	469.3	469.3

(END OF REPORT)