

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011657

Luminaire Tested: S123DIP-B340D805UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011657
REPORT IS A COMBINATION OF REPORTS P989900 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4237.6 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011657

CATALOG NUMBER: S123DIP-B340D805UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011657

CATALOG NUMBER: S123DIP-B340D805UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	25	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	28	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011657

CATALOG NUMBER: S123DIP-B340D805UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.2
10°-20°	141.0	3.3
20°-30°	208.3	4.9
30°-40°	243.3	5.7
40°-50°	244.6	5.8
50°-60°	214.8	5.1
60°-70°	160.0	3.8
70°-80°	91.1	2.1
80°-90°	28.0	0.7
90°-100°	215.3	5.1
100°-110°	601.8	14.2
110°-120°	586.8	13.8
120°-130°	467.2	11.0
130°-140°	368.8	8.7
140°-150°	275.2	6.5
150°-160°	192.0	4.5
160°-170°	112.8	2.7
170°-180°	36.7	0.9
0°-30°	399.3	9.4
0°-40°	642.6	15.2
0°-60°	1102.0	26.0
0°-90°	1381.1	32.6
90°-120°	1403.9	33.1
90°-150°	2515.1	59.4
90°-180°	2857.0	67.4
0°-180°	4237.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	2	9	19	21	22	4
95°	26	85	455	133	89	28
105°	89	132	617	1078	976	94
115°	157	196	472	1034	1186	156
125°	219	258	440	798	936	194
135°	256	306	434	657	758	198
145°	292	335	429	539	593	183
155°	332	358	415	472	492	153
165°	363	373	397	421	429	102
175°	378	378	381	386	386	36
180°	379	379	379	379	379	

TEST NUMBER: P1011657

CATALOG NUMBER: S123DIP-B340D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.5	9.2	19.2	21.4	22.2
92.5°	11.5	46.0	142.7	48.7	40.6
95°	26.1	84.8	454.8	132.7	89.0
97.5°	41.4	97.0	699.5	333.6	182.5
100°	56.8	107.0	726.3	698.0	480.9
102.5°	72.9	118.5	676.4	934.5	761.6
105°	89.0	131.5	616.6	1078.4	975.6
107.5°	105.8	146.8	563.7	1141.6	1115.1
110°	124.2	162.6	520.0	1143.6	1194.9

TEST NUMBER: P1011657

CATALOG NUMBER: S123DIP-B340D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.1	179.0	490.8	1100.2	1211.0
115°	157.2	196.0	471.7	1034.2	1186.5
117.5°	173.3	212.0	458.6	963.6	1132.8
120°	190.2	228.2	450.2	897.0	1062.2
122.5°	204.8	243.6	444.8	844.4	996.3
125°	218.6	258.0	440.2	797.6	935.7
127.5°	229.3	271.8	437.9	759.3	883.5
130°	239.3	284.2	435.6	724.0	840.6
132.5°	247.0	295.2	434.9	691.0	798.4
135°	256.2	305.6	434.1	656.8	758.5
137.5°	264.6	314.1	432.6	624.7	716.3
140°	273.0	321.7	431.8	593.2	671.8
142.5°	282.2	328.6	430.3	564.5	630.4
145°	292.2	334.8	428.7	538.8	592.8
147.5°	302.2	341.3	426.4	518.8	560.6
150°	312.1	346.7	423.4	501.2	533.0
152.5°	322.1	352.4	419.5	485.8	510.0
155°	332.1	358.2	414.9	471.7	491.6
157.5°	339.8	363.2	411.1	457.8	474.0
160°	349.0	367.4	406.5	445.2	457.1
162.5°	355.9	370.4	401.9	433.3	441.8
165°	362.8	373.1	397.3	421.4	428.7
167.5°	368.1	375.4	392.7	411.0	415.7
170°	372.7	376.6	388.1	401.8	404.2
172.5°	375.8	377.7	384.2	393.8	393.4
175°	378.1	378.5	381.2	386.5	385.8
177.5°	379.6	378.9	378.9	381.9	380.4
180°	378.9	378.9	378.9	378.9	378.9

(END OF REPORT)