

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011939

Luminaire Tested: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011939
REPORT IS A COMBINATION OF REPORTS P990278 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB50-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6604.2 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011939

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011939

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	46	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12668	12668	12668
5°	12699	12231	12212
10°	12587	11818	11695
15°	12412	11387	11133
20°	12211	10909	10574
25°	11951	10404	9978
30°	11668	9882	9350
35°	11370	9349	8726
40°	11058	8790	8112
45°	10715	8244	7471
50°	10367	7636	6828
55°	9920	7003	6176
60°	9459	6305	5482
65°	9026	5548	4759
70°	8405	4710	3915
75°	7505	3730	3040
80°	6482	2622	2149
85°	5052	1409	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10715 cd/sqm

TEST NUMBER: P1011939

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.7
10°-20°	313.3	4.7
20°-30°	462.7	7.0
30°-40°	540.4	8.2
40°-50°	543.3	8.2
50°-60°	477.2	7.2
60°-70°	355.4	5.4
70°-80°	202.3	3.1
80°-90°	60.1	0.9
90°-100°	266.7	4.0
100°-110°	745.5	11.3
110°-120°	726.9	11.0
120°-130°	578.8	8.8
130°-140°	456.9	6.9
140°-150°	340.9	5.2
150°-160°	237.8	3.6
160°-170°	139.7	2.1
170°-180°	45.4	0.7
0°-30°	886.9	13.4
0°-40°	1427.3	21.6
0°-60°	2447.8	37.1
0°-90°	3065.6	46.4
90°-120°	1739.1	26.3
90°-150°	3115.7	47.2
90°-180°	3539.0	53.6
0°-180°	6604.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1177	1177	1177	1177	1177	
5°	1178	1173	1162	1172	1170	112
15°	1121	1117	1104	1112	1106	316
25°	1018	1012	999	1000	997	469
35°	880	874	861	855	850	551
45°	722	718	704	692	687	557
55°	548	546	533	522	517	490
65°	373	368	358	350	347	368
75°	197	193	190	185	182	211
85°	53	51	51	49	49	56
90°	2	11	24	27	28	6
95°	32	105	563	164	110	34
105°	110	163	764	1336	1208	117
115°	195	243	584	1281	1470	193
125°	271	320	545	988	1159	241
135°	317	379	538	814	940	245
145°	362	415	531	667	734	227
155°	411	444	514	584	609	189
165°	449	462	492	522	531	127
175°	468	469	472	479	478	44
180°	469	469	469	469	469	

TEST NUMBER: P1011939

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1176.9	1176.9	1176.9	1176.9	1176.9
2.5°	1182.0	1177.9	1166.8	1176.9	1175.9
5°	1177.9	1172.9	1161.7	1171.9	1169.8
7.5°	1168.8	1163.8	1152.6	1161.7	1160.7
10°	1156.7	1151.6	1138.5	1147.6	1145.5
12.5°	1140.5	1136.4	1124.3	1130.4	1129.4
15°	1121.3	1117.2	1104.1	1112.2	1106.1
17.5°	1100.0	1095.0	1081.8	1087.9	1085.8
20°	1075.7	1069.7	1056.5	1060.5	1057.5
22.5°	1048.4	1042.3	1029.2	1032.2	1028.2
25°	1018.0	1012.0	998.8	999.8	996.8
27.5°	986.7	980.6	966.4	967.4	964.4
30°	952.3	947.2	933.0	933.0	926.0
32.5°	917.9	910.8	900.7	893.6	890.5
35°	880.4	874.3	861.2	855.1	850.1
37.5°	843.0	834.9	821.7	814.6	811.6
40°	803.5	797.4	783.3	775.2	771.1
42.5°	764.0	757.0	742.8	734.7	730.6
45°	721.5	717.5	704.3	692.2	687.1
47.5°	680.0	674.0	661.8	649.7	645.6
50°	637.5	632.5	619.3	608.2	602.1
52.5°	593.0	590.0	575.8	566.7	560.6
55°	547.5	546.5	533.3	522.2	517.1
57.5°	505.0	500.9	490.8	480.7	474.6
60°	458.4	457.4	445.3	436.2	431.1
62.5°	416.9	413.9	401.8	392.6	389.6
65°	373.4	368.4	358.2	350.1	347.1
67.5°	326.9	322.8	314.7	307.6	303.6
70°	285.4	279.3	273.2	266.1	261.1
72.5°	241.9	237.8	230.7	224.7	222.6
75°	197.3	193.3	190.3	185.2	182.2
77.5°	157.9	155.8	151.8	147.7	147.7
80°	119.4	116.4	114.4	113.3	113.3
82.5°	82.0	82.0	82.0	79.9	78.9
85°	52.6	50.6	50.6	48.6	48.6
87.5°	26.3	23.3	22.3	21.3	21.3
90°	1.9	11.4	23.8	26.6	27.6
92.5°	14.3	57.0	176.7	60.4	50.4
95°	32.3	105.0	563.4	164.4	110.2
97.5°	51.3	120.2	866.5	413.2	226.1
100°	70.3	132.6	899.7	864.6	595.7
102.5°	90.3	146.8	838.0	1157.6	943.4
105°	110.2	163.0	763.9	1335.8	1208.5
107.5°	131.1	182.0	698.3	1414.2	1381.4
110°	153.9	201.4	644.2	1416.6	1480.2

TEST NUMBER: P1011939

CATALOG NUMBER: S123DIP-B775D1025UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	221.8	608.0	1362.9	1500.2
115°	194.8	242.8	584.3	1281.2	1469.8
117.5°	214.7	262.7	568.1	1193.8	1403.3
120°	235.6	282.6	557.7	1111.1	1315.9
122.5°	253.7	301.6	551.0	1046.0	1234.1
125°	270.8	319.7	545.3	988.1	1159.1
127.5°	284.1	336.8	542.5	940.6	1094.5
130°	296.4	352.0	539.6	896.9	1041.3
132.5°	305.9	365.8	538.7	856.0	989.0
135°	317.3	378.6	537.7	813.8	939.6
137.5°	327.8	389.0	535.8	773.8	887.4
140°	338.2	398.5	534.9	734.9	832.3
142.5°	349.6	407.1	533.0	699.3	781.0
145°	362.0	414.7	531.1	667.4	734.4
147.5°	374.3	422.8	528.2	642.8	694.5
150°	386.7	429.4	524.4	620.8	660.3
152.5°	399.0	436.6	519.7	601.8	631.8
155°	411.4	443.6	514.0	584.3	609.0
157.5°	420.9	449.8	509.2	567.2	587.1
160°	432.3	455.0	503.5	551.5	566.2
162.5°	440.8	458.9	497.8	536.8	547.2
165°	449.4	462.2	492.1	522.0	531.1
167.5°	456.0	465.0	486.4	509.2	514.9
170°	461.7	466.4	480.7	497.8	500.7
172.5°	465.5	467.9	476.0	487.8	487.4
175°	468.4	468.8	472.2	478.8	477.9
177.5°	470.3	469.3	469.3	473.1	471.2
180°	469.3	469.3	469.3	469.3	469.3

(END OF REPORT)