

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011942

Luminaire Tested: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011942
REPORT IS A COMBINATION OF REPORTS P990281 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB27-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7531.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11591	11591	11591	11591
5°	11599	13354	11632	9967
10°	11525	16161	11536	8704
15°	11365	19167	11458	7834
20°	11229	22066	11253	7209
25°	11025	22623	11050	6883
30°	10880	18690	10880	6669
35°	10699	12500	10632	6480
40°	10483	9023	10354	6191
45°	10212	7148	9918	5831
50°	9552	6070	9214	5478
55°	8830	5334	8471	5084
60°	8095	4644	7666	4671
65°	7288	3977	6935	4120
70°	6452	3302	6022	3473
75°	5516	2489	5158	2681
80°	4359	1661	4023	1762
85°	3007	762	2401	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18693 cd/sqm

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	1.4
10°-20°	340.1	4.5
20°-30°	572.3	7.6
30°-40°	646.8	8.6
40°-50°	579.3	7.7
50°-60°	467.6	6.2
60°-70°	325.9	4.3
70°-80°	171.0	2.3
80°-90°	44.1	0.6
90°-100°	308.6	4.1
100°-110°	903.5	12.0
110°-120°	882.3	11.7
120°-130°	702.7	9.3
130°-140°	554.4	7.4
140°-150°	413.6	5.5
150°-160°	288.4	3.8
160°-170°	169.4	2.2
170°-180°	55.1	0.7
0°-30°	1018.4	13.5
0°-40°	1665.2	22.1
0°-60°	2712.1	36.0
0°-90°	3253.1	43.2
90°-120°	2094.4	27.8
90°-150°	3765.0	50.0
90°-180°	4278.0	56.8
0°-180°	7531.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1077	1077	1077	1077	1077	
5°	1076	1279	1079	955	1076	102
15°	1027	1904	1035	778	1027	290
25°	939	2260	941	688	939	433
35°	828	1218	823	631	828	518
45°	688	657	668	536	688	526
55°	487	447	468	426	487	436
65°	302	290	287	300	302	300
75°	145	149	136	161	145	156
85°	31	34	25	31	31	36
90°	2	33	2	33	2	5
95°	39	134	39	134	39	41
105°	134	1464	134	1464	134	142
115°	236	1781	236	1781	236	234
125°	328	1404	328	1404	328	291
135°	384	1139	384	1139	384	297
145°	439	890	439	890	439	275
155°	498	738	498	738	498	229
165°	544	644	544	644	544	153
175°	568	579	568	579	568	54
180°	569	569	569	569	569	

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1079.9	1088.3	1092.5	1098.7	1105.0	1114.4	1117.5	1122.7	1120.6	1124.8	1126.9
5°	1075.8	1090.4	1102.9	1118.6	1133.2	1143.6	1154.0	1170.7	1183.2	1185.3	1194.7
7.5°	1068.5	1089.3	1111.2	1133.2	1161.3	1178.0	1196.8	1219.8	1238.5	1268.8	1280.3
10°	1059.1	1088.3	1119.6	1149.9	1188.5	1214.5	1237.5	1276.1	1314.7	1346.0	1375.2
12.5°	1044.5	1081.0	1121.7	1166.5	1216.6	1246.9	1278.2	1329.3	1387.8	1435.8	1467.1
15°	1026.7	1072.6	1124.8	1172.8	1228.1	1284.5	1317.8	1375.2	1458.7	1503.6	1583.9
17.5°	1012.1	1059.1	1111.2	1186.4	1261.5	1317.8	1341.8	1447.2	1504.6	1579.7	1670.5
20°	989.2	1048.6	1115.4	1190.5	1287.6	1322.0	1371.1	1477.5	1548.4	1646.5	1758.2
22.5°	965.2	1028.8	1109.2	1187.4	1295.9	1332.5	1399.2	1483.8	1596.4	1693.5	1816.6
25°	939.1	1007.9	1089.3	1182.2	1288.6	1341.8	1404.5	1508.8	1630.9	1753.0	1866.7
27.5°	913.0	988.1	1072.6	1165.5	1268.8	1331.4	1394.0	1502.5	1659.0	1791.6	1936.6
30°	888.0	963.1	1047.6	1142.6	1251.1	1311.6	1371.1	1506.7	1681.0	1830.2	1976.2
32.5°	860.8	938.0	1026.7	1106.0	1215.6	1280.3	1347.1	1506.7	1694.5	1853.1	1986.7
35°	828.5	907.8	983.9	1063.3	1171.8	1243.8	1318.9	1496.3	1707.0	1860.4	1942.9
37.5°	797.2	867.1	932.8	1010.0	1123.8	1201.0	1287.6	1483.8	1700.8	1829.1	1852.1
40°	761.7	831.6	884.8	956.8	1076.8	1166.5	1254.2	1467.1	1673.7	1755.0	1688.3
42.5°	727.3	782.6	828.5	898.4	1028.8	1116.5	1211.4	1436.8	1620.4	1637.1	1486.9
45°	687.6	727.3	768.0	847.3	976.6	1066.4	1171.8	1393.0	1534.9	1486.9	1297.0
47.5°	636.5	672.0	716.8	789.9	921.3	1014.2	1114.4	1336.6	1410.7	1310.5	1102.9
50°	587.4	617.7	659.4	730.4	862.9	953.7	1060.1	1247.9	1284.5	1126.9	950.6
52.5°	538.4	561.4	602.1	673.0	805.5	893.2	990.2	1157.2	1136.3	967.3	810.7
55°	487.3	507.1	545.7	615.6	738.7	822.2	915.1	1045.5	991.3	830.6	705.4
57.5°	437.2	458.1	497.7	556.1	672.0	753.4	827.4	929.7	848.3	720.0	609.4
60°	392.3	410.1	440.3	497.7	603.1	668.8	736.7	806.6	738.7	614.6	530.1
62.5°	345.4	362.1	390.2	442.4	533.2	591.6	645.9	703.3	628.1	537.4	462.2
65°	301.5	315.1	341.2	389.2	463.3	511.3	555.1	594.8	534.2	450.8	394.4
67.5°	261.9	273.4	295.3	338.1	400.7	435.1	470.6	504.0	452.8	386.1	338.1
70°	219.1	228.5	248.3	279.6	329.7	365.2	391.3	416.3	370.4	317.2	284.9
72.5°	181.6	190.9	203.5	235.8	270.2	292.2	320.3	333.9	307.8	264.0	231.6
75°	145.0	152.3	163.8	184.7	217.0	231.6	249.4	259.8	235.8	206.6	186.8
77.5°	113.7	116.9	125.2	139.8	161.7	178.4	192.0	198.3	181.6	162.8	146.1
80°	80.3	84.5	90.8	103.3	120.0	125.2	133.6	140.9	130.4	113.7	103.3
82.5°	53.2	58.4	61.6	66.8	77.2	83.5	85.6	91.8	82.4	76.2	72.0
85°	31.3	33.4	34.4	37.6	42.8	45.9	49.0	50.1	48.0	47.0	42.8
87.5°	15.7	15.7	15.7	17.7	18.8	20.9	21.9	21.9	21.9	20.9	19.8
90°	2.3	4.6	6.9	10.4	12.7	13.8	15.0	18.4	21.9	25.3	28.8
92.5°	17.3	25.3	36.8	47.2	58.7	69.1	79.4	116.3	177.3	237.2	214.1
95°	39.1	42.6	55.3	74.8	104.8	127.2	149.7	247.5	419.0	607.8	682.7
97.5°	62.2	63.3	73.7	90.9	120.9	145.6	170.4	267.1	466.2	784.0	1049.9
100°	85.2	86.3	94.4	110.5	138.1	160.6	183.0	263.6	434.0	736.8	1090.2
102.5°	109.4	111.7	118.6	133.5	157.7	177.8	198.0	268.2	406.4	667.7	1015.4
105°	133.5	137.0	143.9	157.7	179.6	197.4	215.3	277.4	396.0	613.6	925.6
107.5°	158.9	162.3	169.2	183.0	203.8	220.5	237.2	292.4	393.7	574.5	846.1
110°	186.5	190.0	195.7	208.4	227.9	244.0	260.2	312.0	399.5	553.7	780.5

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	211.8	215.3	221.0	233.7	253.3	268.8	284.4	331.6	411.0	542.2	736.8
115°	236.0	240.6	247.5	259.0	278.6	294.2	309.7	353.4	423.7	541.1	708.0
117.5°	260.2	265.9	271.7	282.0	303.9	318.3	332.7	376.4	439.8	542.2	688.4
120°	285.5	289.0	294.7	306.2	328.1	342.5	356.9	398.3	458.2	546.8	675.8
122.5°	307.4	310.8	316.6	329.2	350.0	365.6	381.1	421.3	475.5	554.9	667.7
125°	328.1	330.4	337.3	350.0	371.8	387.4	402.9	443.2	493.9	562.9	660.8
127.5°	344.2	347.7	355.7	368.4	392.6	408.2	423.7	462.8	508.8	572.2	657.3
130°	359.2	362.6	373.0	386.8	411.0	426.6	442.1	480.1	523.8	581.4	653.9
132.5°	370.7	375.3	386.8	404.1	428.3	443.2	458.2	495.0	537.6	588.3	652.7
135°	384.5	389.1	401.8	419.0	443.2	458.8	474.3	510.0	549.1	595.2	651.6
137.5°	397.2	401.8	414.4	432.9	457.0	471.4	485.8	520.4	558.3	599.8	649.3
140°	409.8	415.6	427.1	445.5	468.5	482.9	497.3	530.7	565.3	604.4	648.1
142.5°	423.7	428.3	440.9	457.0	480.1	493.3	506.5	538.8	572.2	607.8	645.8
145°	438.6	442.1	452.4	469.7	489.3	502.5	515.7	545.7	576.8	609.0	643.5
147.5°	453.6	455.9	466.2	481.2	500.8	512.3	523.8	551.4	580.2	609.0	640.1
150°	468.5	469.7	478.9	493.9	510.0	520.4	530.7	557.2	581.4	609.0	635.5
152.5°	483.5	483.5	492.7	505.4	519.2	529.0	538.8	560.6	583.7	605.5	629.7
155°	498.5	498.5	505.4	516.9	529.6	537.7	545.7	565.3	583.7	603.2	622.8
157.5°	510.0	511.1	516.9	527.3	538.8	545.1	551.4	567.6	584.8	599.8	617.1
160°	523.8	523.8	528.4	537.6	545.7	551.4	557.2	571.0	584.8	597.5	610.1
162.5°	534.2	534.2	537.6	544.5	551.4	556.0	560.6	572.2	583.7	592.9	603.2
165°	544.5	543.4	545.7	551.4	556.0	560.0	564.1	573.3	581.4	588.3	596.3
167.5°	552.6	551.4	552.6	557.2	560.6	563.5	566.4	573.3	580.2	583.7	589.4
170°	559.5	557.2	558.3	561.8	564.1	565.2	566.4	572.2	576.8	579.1	582.5
172.5°	564.1	562.9	562.9	565.3	566.4	567.0	567.6	572.2	575.6	575.6	576.8
175°	567.6	566.4	565.3	567.6	567.6	568.2	568.7	571.0	573.3	572.2	572.2
177.5°	569.9	568.7	567.6	568.7	568.7	568.7	568.7	569.9	572.2	569.9	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1134.2	1136.3	1143.6	1148.8	1159.2	1158.2	1158.2	1157.2	1154.0	1159.2	1162.4
5°	1213.5	1231.2	1233.3	1256.3	1257.3	1266.7	1273.0	1267.8	1280.3	1279.2	1269.8
7.5°	1311.6	1335.6	1347.1	1369.0	1394.0	1387.8	1411.8	1415.9	1413.8	1424.3	1431.6
10°	1419.1	1460.8	1490.0	1530.7	1541.1	1547.4	1563.1	1576.6	1603.7	1582.9	1596.4
12.5°	1542.2	1572.4	1611.0	1675.7	1708.1	1729.0	1736.3	1745.7	1764.4	1753.0	1754.0
15°	1645.5	1686.2	1751.9	1832.3	1841.6	1867.7	1861.5	1917.8	1944.9	1904.3	1927.2
17.5°	1753.0	1807.2	1885.5	1955.4	1995.0	2012.8	2029.5	2083.7	2081.6	2075.4	2080.6
20°	1821.8	1910.5	2007.6	2100.4	2111.9	2125.5	2170.3	2193.3	2189.1	2206.8	2218.3
22.5°	1918.9	2012.8	2116.1	2177.6	2203.7	2219.4	2254.8	2269.4	2275.7	2279.9	2272.6
25°	2000.2	2100.4	2176.6	2230.8	2246.5	2254.8	2266.3	2270.5	2267.4	2260.1	2266.3
27.5°	2055.5	2135.9	2188.1	2213.1	2204.8	2191.2	2169.3	2154.7	2122.3	2106.7	2125.5
30°	2078.5	2114.0	2129.6	2087.9	2046.2	2012.8	1971.0	1893.8	1833.3	1851.0	1827.0
32.5°	2042.0	2019.0	1943.9	1836.4	1804.1	1749.8	1631.9	1541.1	1544.3	1496.3	1516.1
35°	1934.5	1830.2	1688.3	1525.5	1482.7	1453.5	1324.1	1304.3	1262.5	1217.7	1230.2
37.5°	1744.6	1592.3	1420.1	1300.1	1236.5	1172.8	1099.8	1055.9	1030.9	1012.1	1026.7
40°	1513.0	1327.2	1185.3	1077.9	1023.6	982.9	932.8	889.0	860.8	857.7	862.9
42.5°	1285.5	1129.0	998.6	896.3	878.6	830.6	798.2	763.8	755.4	741.9	749.2
45°	1088.3	961.0	853.5	770.0	749.2	736.7	697.0	675.1	665.7	657.4	669.9
47.5°	945.3	811.8	733.5	683.4	662.6	641.7	619.8	605.2	597.9	598.9	597.9
50°	807.6	709.5	640.7	602.1	589.5	574.9	557.2	547.8	544.7	535.3	542.6
52.5°	694.9	624.0	576.0	539.5	530.1	519.6	505.0	499.8	492.5	490.4	490.4
55°	604.1	548.8	510.2	486.2	474.8	466.4	458.1	451.8	446.6	446.6	446.6
57.5°	533.2	485.2	457.0	436.2	432.0	423.6	414.2	414.2	406.9	405.9	409.0
60°	472.7	429.9	408.0	390.2	384.0	381.9	372.5	372.5	370.4	365.2	369.4
62.5°	411.1	379.8	361.0	347.5	341.2	341.2	333.9	328.7	328.7	329.7	327.6
65°	354.8	331.8	315.1	304.7	301.5	297.4	296.3	292.2	289.0	290.1	289.0
67.5°	304.7	286.9	275.5	267.1	261.9	259.8	256.7	256.7	254.6	255.6	250.4
70°	259.8	242.1	232.7	224.3	222.2	222.2	218.1	219.1	217.0	220.2	218.1
72.5°	213.9	200.3	193.0	189.9	187.8	186.8	184.7	182.6	181.6	183.6	182.6
75°	173.2	161.7	156.5	154.4	152.3	152.3	151.3	150.3	149.2	149.2	149.2
77.5°	134.6	127.3	121.0	123.1	120.0	121.0	117.9	117.9	119.0	117.9	117.9
80°	99.1	93.9	93.9	91.8	87.6	89.7	89.7	86.6	85.6	87.6	84.5
82.5°	65.7	64.7	62.6	61.6	59.5	60.5	59.5	58.4	57.4	59.5	57.4
85°	38.6	38.6	37.6	35.5	37.6	36.5	35.5	35.5	34.4	34.4	34.4
87.5°	19.8	17.7	17.7	16.7	17.7	15.7	16.7	15.7	14.6	15.7	14.6
90°	27.6	28.8	29.9	31.1	32.2	33.4	32.2	33.4	34.5	33.4	34.5
92.5°	160.0	114.0	88.6	77.1	73.1	69.1	66.8	62.2	63.3	61.0	63.3
95°	553.7	414.4	280.9	219.9	199.2	178.4	156.6	146.2	138.1	133.5	138.1
97.5°	1085.6	952.1	718.4	566.4	500.8	435.2	358.0	314.3	286.7	274.0	286.7
100°	1317.0	1357.3	1264.0	1129.3	1047.6	965.9	849.6	765.6	720.7	721.8	720.7
102.5°	1328.5	1492.0	1511.6	1447.1	1402.8	1358.4	1274.4	1212.2	1176.6	1143.2	1176.6
105°	1256.0	1496.6	1611.7	1633.6	1618.6	1603.7	1550.7	1507.0	1470.1	1464.4	1470.1
107.5°	1152.4	1427.5	1608.3	1698.1	1713.6	1729.1	1722.2	1701.5	1686.5	1673.9	1686.5
110°	1055.7	1319.3	1531.1	1676.2	1716.5	1756.8	1789.0	1798.2	1795.9	1793.6	1795.9

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	971.6	1212.2	1429.8	1596.7	1651.4	1706.1	1771.7	1805.1	1816.6	1817.8	1816.6
115°	907.2	1120.1	1320.5	1489.7	1552.4	1615.2	1701.5	1752.2	1775.2	1780.9	1775.2
117.5°	864.6	1048.8	1226.1	1381.5	1446.6	1511.6	1601.4	1657.8	1692.3	1700.4	1692.3
120°	832.3	994.7	1150.1	1288.2	1346.4	1404.5	1495.4	1559.9	1587.5	1594.4	1587.5
122.5°	805.9	952.1	1089.1	1214.5	1267.5	1320.5	1398.7	1455.1	1486.2	1495.4	1486.2
125°	784.0	915.2	1040.7	1151.2	1197.2	1243.3	1317.0	1367.7	1396.4	1404.5	1396.4
127.5°	763.3	881.8	995.8	1097.1	1139.7	1182.3	1249.1	1292.8	1319.3	1326.2	1319.3
130°	747.1	850.8	954.4	1047.6	1086.8	1125.9	1186.9	1228.4	1252.5	1261.7	1252.5
132.5°	732.2	822.0	915.2	1000.4	1037.2	1074.1	1130.5	1171.9	1192.7	1198.4	1192.7
135°	719.5	796.6	878.4	953.2	986.0	1018.8	1075.2	1109.8	1130.5	1138.6	1130.5
137.5°	708.0	772.5	841.5	908.3	937.6	967.0	1015.4	1051.1	1068.3	1075.2	1068.3
140°	697.6	751.7	810.5	865.7	890.4	915.2	959.0	991.2	1009.6	1008.5	1009.6
142.5°	688.4	732.2	780.5	826.6	847.3	868.0	903.7	931.3	947.5	946.3	947.5
145°	680.4	717.2	755.2	792.0	808.7	825.4	854.2	878.4	887.6	889.9	887.6
147.5°	672.3	704.5	735.6	766.7	778.8	790.9	813.9	831.2	840.4	841.5	840.4
150°	664.3	690.7	717.2	741.4	752.3	763.3	780.5	793.2	800.1	800.1	800.1
152.5°	655.0	678.1	699.9	720.7	729.3	737.9	750.6	762.1	765.6	765.6	765.6
155°	645.8	665.4	683.8	701.1	708.0	714.9	725.3	734.5	736.8	737.9	736.8
157.5°	635.5	651.6	667.7	681.5	687.2	693.0	702.2	709.2	711.5	711.5	711.5
160°	625.1	640.1	652.7	664.3	668.3	672.3	680.4	687.3	687.3	686.1	687.3
162.5°	614.8	626.3	636.6	647.0	650.4	653.9	658.5	664.3	664.3	663.1	664.3
165°	605.5	614.8	621.7	629.7	632.6	635.5	640.1	644.7	643.5	643.5	643.5
167.5°	596.3	604.4	610.1	614.8	617.1	619.4	621.7	625.1	624.0	624.0	624.0
170°	588.3	594.0	597.5	602.1	603.2	604.4	605.5	607.8	606.7	606.7	606.7
172.5°	580.2	584.8	587.1	590.6	591.2	591.7	591.7	594.0	591.7	590.6	591.7
175°	574.5	576.8	577.9	580.2	580.2	580.2	580.2	581.4	580.2	579.1	580.2
177.5°	569.9	571.0	572.2	573.3	573.3	573.3	572.2	573.3	571.0	571.0	571.0
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1154.0	1157.2	1148.8	1146.7	1146.7	1150.9	1147.8	1119.6	1124.8	1118.6	1116.5
5°	1281.3	1275.1	1266.7	1262.5	1257.3	1242.7	1241.7	1209.3	1203.1	1182.2	1172.8
7.5°	1421.1	1415.9	1390.9	1387.8	1385.7	1372.1	1337.7	1303.2	1278.2	1254.2	1231.2
10°	1580.8	1565.1	1553.7	1530.7	1519.2	1500.4	1455.6	1423.2	1380.5	1343.9	1295.9
12.5°	1772.8	1755.0	1716.4	1699.7	1685.1	1633.0	1588.1	1551.6	1468.1	1443.1	1383.6
15°	1913.6	1876.1	1871.9	1835.4	1833.3	1775.9	1690.3	1650.7	1586.0	1494.2	1432.6
17.5°	2066.0	2032.6	2006.5	1962.7	1956.4	1902.2	1839.6	1742.5	1671.6	1583.9	1505.7
20°	2177.6	2159.9	2115.0	2097.3	2060.8	2014.9	1950.2	1830.2	1743.6	1655.9	1559.9
22.5°	2266.3	2248.6	2213.1	2189.1	2168.2	2108.8	2031.5	1929.3	1810.3	1695.6	1596.4
25°	2265.3	2260.1	2245.5	2234.0	2218.3	2174.5	2109.8	2011.7	1879.2	1753.0	1615.2
27.5°	2136.9	2151.5	2176.6	2189.1	2186.0	2179.7	2143.2	2060.8	1941.8	1791.6	1637.1
30°	1869.8	1923.0	1970.0	2032.6	2051.4	2097.3	2118.2	2071.2	1976.2	1836.4	1665.3
32.5°	1550.5	1627.7	1730.0	1764.4	1823.9	1912.6	2011.7	2029.5	1970.0	1862.5	1683.0
35°	1271.9	1335.6	1414.9	1469.1	1522.4	1666.4	1791.6	1900.1	1919.9	1848.9	1678.9
37.5°	1052.8	1097.7	1167.6	1213.5	1262.5	1385.7	1561.0	1701.8	1801.0	1803.0	1667.4
40°	894.2	914.0	974.6	1007.9	1054.9	1161.3	1317.8	1501.5	1646.5	1713.3	1637.1
42.5°	757.5	783.6	833.7	858.7	889.0	981.9	1085.2	1259.4	1438.9	1581.8	1580.8
45°	676.1	694.9	717.9	738.7	773.2	828.5	946.4	1076.8	1249.0	1410.7	1474.4
47.5°	604.1	621.9	644.8	651.1	674.1	726.2	798.2	912.0	1072.6	1233.3	1353.3
50°	543.6	558.2	573.9	585.4	595.8	638.6	692.8	788.8	917.2	1072.6	1221.9
52.5°	496.7	507.1	520.7	526.9	536.3	567.6	609.4	680.3	785.7	927.6	1072.6
55°	452.8	460.2	468.5	478.9	483.1	506.1	538.4	598.9	677.2	804.5	942.2
57.5°	412.2	415.3	420.5	426.8	432.0	451.8	480.0	520.7	589.5	687.6	818.0
60°	366.2	374.6	377.7	384.0	387.1	402.8	424.7	459.1	512.3	596.8	694.9
62.5°	327.6	332.9	338.1	341.2	348.5	353.7	371.5	402.8	446.6	509.2	597.9
65°	293.2	295.3	298.4	301.5	303.6	309.9	326.6	347.5	380.9	436.2	505.0
67.5°	253.6	255.6	259.8	260.9	262.9	271.3	280.7	298.4	326.6	368.3	424.7
70°	214.9	218.1	220.2	222.2	225.4	228.5	238.9	253.6	275.5	304.7	348.5
72.5°	181.6	184.7	184.7	186.8	185.7	189.9	200.3	210.8	225.4	249.4	288.0
75°	148.2	148.2	150.3	151.3	152.3	156.5	160.7	169.0	180.5	199.3	223.3
77.5°	116.9	115.8	117.9	117.9	117.9	121.0	125.2	129.4	136.7	150.3	169.0
80°	85.6	85.6	87.6	88.7	86.6	87.6	89.7	93.9	99.1	108.5	119.0
82.5°	56.3	60.5	59.5	60.5	59.5	61.6	62.6	63.6	65.7	69.9	77.2
85°	34.4	34.4	34.4	35.5	34.4	35.5	35.5	35.5	36.5	38.6	41.7
87.5°	14.6	14.6	14.6	15.7	14.6	14.6	15.7	14.6	15.7	15.7	16.7
90°	33.4	32.2	33.4	32.2	31.1	29.9	28.8	27.6	28.8	25.3	21.9
92.5°	62.2	66.8	69.1	73.1	77.1	88.6	114.0	160.0	214.1	237.2	177.3
95°	146.2	156.6	178.4	199.2	219.9	280.9	414.4	553.7	682.7	607.8	419.0
97.5°	314.3	358.0	435.2	500.8	566.4	718.4	952.1	1085.6	1049.9	784.0	466.2
100°	765.6	849.6	965.9	1047.6	1129.3	1264.0	1357.3	1317.0	1090.2	736.8	434.0
102.5°	1212.2	1274.4	1358.4	1402.8	1447.1	1511.6	1492.0	1328.5	1015.4	667.7	406.4
105°	1507.0	1550.7	1603.7	1618.6	1633.6	1611.7	1496.6	1256.0	925.6	613.6	396.0
107.5°	1701.5	1722.2	1729.1	1713.6	1698.1	1608.3	1427.5	1152.4	846.1	574.5	393.7
110°	1798.2	1789.0	1756.8	1716.5	1676.2	1531.1	1319.3	1055.7	780.5	553.7	399.5

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1805.1	1771.7	1706.1	1651.4	1596.7	1429.8	1212.2	971.6	736.8	542.2	411.0
115°	1752.2	1701.5	1615.2	1552.4	1489.7	1320.5	1120.1	907.2	708.0	541.1	423.7
117.5°	1657.8	1601.4	1511.6	1446.6	1381.5	1226.1	1048.8	864.6	688.4	542.2	439.8
120°	1559.9	1495.4	1404.5	1346.4	1288.2	1150.1	994.7	832.3	675.8	546.8	458.2
122.5°	1455.1	1398.7	1320.5	1267.5	1214.5	1089.1	952.1	805.9	667.7	554.9	475.5
125°	1367.7	1317.0	1243.3	1197.2	1151.2	1040.7	915.2	784.0	660.8	562.9	493.9
127.5°	1292.8	1249.1	1182.3	1139.7	1097.1	995.8	881.8	763.3	657.3	572.2	508.8
130°	1228.4	1186.9	1125.9	1086.8	1047.6	954.4	850.8	747.1	653.9	581.4	523.8
132.5°	1171.9	1130.5	1074.1	1037.2	1000.4	915.2	822.0	732.2	652.7	588.3	537.6
135°	1109.8	1075.2	1018.8	986.0	953.2	878.4	796.6	719.5	651.6	595.2	549.1
137.5°	1051.1	1015.4	967.0	937.6	908.3	841.5	772.5	708.0	649.3	599.8	558.3
140°	991.2	959.0	915.2	890.4	865.7	810.5	751.7	697.6	648.1	604.4	565.3
142.5°	931.3	903.7	868.0	847.3	826.6	780.5	732.2	688.4	645.8	607.8	572.2
145°	878.4	854.2	825.4	808.7	792.0	755.2	717.2	680.4	643.5	609.0	576.8
147.5°	831.2	813.9	790.9	778.8	766.7	735.6	704.5	672.3	640.1	609.0	580.2
150°	793.2	780.5	763.3	752.3	741.4	717.2	690.7	664.3	635.5	609.0	581.4
152.5°	762.1	750.6	737.9	729.3	720.7	699.9	678.1	655.0	629.7	605.5	583.7
155°	734.5	725.3	714.9	708.0	701.1	683.8	665.4	645.8	622.8	603.2	583.7
157.5°	709.2	702.2	693.0	687.2	681.5	667.7	651.6	635.5	617.1	599.8	584.8
160°	687.3	680.4	672.3	668.3	664.3	652.7	640.1	625.1	610.1	597.5	584.8
162.5°	664.3	658.5	653.9	650.4	647.0	636.6	626.3	614.8	603.2	592.9	583.7
165°	644.7	640.1	635.5	632.6	629.7	621.7	614.8	605.5	596.3	588.3	581.4
167.5°	625.1	621.7	619.4	617.1	614.8	610.1	604.4	596.3	589.4	583.7	580.2
170°	607.8	605.5	604.4	603.2	602.1	597.5	594.0	588.3	582.5	579.1	576.8
172.5°	594.0	591.7	591.7	591.2	590.6	587.1	584.8	580.2	576.8	575.6	575.6
175°	581.4	580.2	580.2	580.2	580.2	577.9	576.8	574.5	572.2	572.2	573.3
177.5°	573.3	572.2	573.3	573.3	573.3	572.2	571.0	569.9	568.7	569.9	572.2
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1106.0	1102.9	1102.9	1100.8	1094.6	1083.1	1082.0	1084.1	1077.9	1071.6	1062.2
5°	1160.3	1140.5	1134.2	1127.9	1115.4	1094.6	1086.2	1078.9	1067.4	1053.9	1039.3
7.5°	1206.2	1178.0	1169.7	1158.2	1133.2	1103.9	1085.2	1069.5	1053.9	1035.1	1017.3
10°	1263.6	1222.9	1203.1	1186.4	1151.9	1111.2	1083.1	1060.1	1035.1	1012.1	989.2
12.5°	1328.3	1262.5	1256.3	1215.6	1175.9	1115.4	1081.0	1047.6	1014.2	986.0	962.0
15°	1382.5	1310.5	1284.5	1257.3	1181.2	1106.0	1072.6	1035.1	996.5	966.2	930.7
17.5°	1417.0	1357.5	1302.2	1265.7	1186.4	1119.6	1054.9	1012.1	971.4	929.7	900.5
20°	1458.7	1372.1	1324.1	1275.1	1196.8	1109.2	1044.5	991.3	941.2	903.6	868.1
22.5°	1500.4	1383.6	1343.9	1290.7	1198.9	1098.7	1025.7	972.5	915.1	877.5	838.9
25°	1496.3	1400.3	1334.5	1289.7	1178.0	1089.3	1003.8	941.2	888.0	840.0	801.4
27.5°	1499.4	1381.5	1314.7	1262.5	1163.4	1075.8	980.8	915.1	859.8	809.7	769.0
30°	1500.4	1353.3	1294.9	1232.3	1136.3	1043.4	954.7	888.0	829.5	775.3	738.7
32.5°	1497.3	1330.4	1257.3	1201.0	1093.5	1012.1	924.5	853.5	794.0	744.0	709.5
35°	1490.0	1303.2	1218.7	1147.8	1049.7	967.3	896.3	823.3	759.6	713.7	674.1
37.5°	1470.2	1274.0	1178.0	1108.1	998.6	915.1	852.5	792.0	730.4	676.1	642.7
40°	1455.6	1234.4	1137.3	1061.2	943.3	861.9	809.7	752.3	691.8	642.7	610.4
42.5°	1422.2	1196.8	1095.6	1004.8	889.0	805.5	756.5	710.6	658.4	610.4	581.2
45°	1367.9	1156.1	1044.5	952.6	829.5	750.2	705.4	667.8	621.9	576.0	546.8
47.5°	1291.8	1097.7	990.2	898.4	771.1	690.7	645.9	617.7	581.2	542.6	517.5
50°	1209.3	1034.0	934.9	844.1	714.7	636.5	592.7	566.6	542.6	507.1	483.1
52.5°	1101.9	966.2	871.3	784.7	654.2	579.1	540.5	521.7	496.7	471.6	450.8
55°	997.5	878.6	800.3	717.9	594.8	524.8	487.3	467.5	452.8	432.0	415.3
57.5°	876.5	797.2	725.2	650.1	539.5	475.8	440.3	416.3	406.9	397.5	381.9
60°	764.8	704.3	645.9	583.3	482.1	424.7	390.2	371.5	362.1	355.8	345.4
62.5°	662.6	615.6	565.5	515.5	423.6	371.5	345.4	326.6	318.2	317.2	307.8
65°	564.5	531.1	490.4	441.4	369.4	323.5	298.4	286.9	277.6	277.6	270.2
67.5°	466.4	443.5	411.1	376.7	320.3	277.6	254.6	244.2	238.9	238.9	233.7
70°	388.2	372.5	343.3	313.0	264.0	231.6	213.9	204.5	201.4	202.4	198.3
72.5°	315.1	298.4	274.4	252.5	216.0	192.0	179.5	169.0	163.8	164.9	163.8
75°	244.2	235.8	214.9	198.3	169.0	152.3	140.9	135.6	131.5	132.5	130.4
77.5°	183.6	171.1	159.6	148.2	130.4	116.9	107.5	102.3	99.1	99.1	99.1
80°	125.2	123.1	113.7	107.5	92.9	82.4	75.1	74.1	71.0	71.0	71.0
82.5°	81.4	76.2	71.0	66.8	58.4	52.2	49.0	47.0	45.9	44.9	47.0
85°	44.9	41.7	39.7	35.5	32.3	29.2	26.1	25.0	24.0	25.0	24.0
87.5°	17.7	14.6	14.6	13.6	12.5	11.5	11.5	9.4	9.4	8.3	8.3
90°	18.4	15.0	13.8	12.7	10.4	6.9	4.6	2.3	4.6	6.9	10.4
92.5°	116.3	79.4	69.1	58.7	47.2	36.8	25.3	17.3	25.3	36.8	47.2
95°	247.5	149.7	127.2	104.8	74.8	55.3	42.6	39.1	42.6	55.3	74.8
97.5°	267.1	170.4	145.6	120.9	90.9	73.7	63.3	62.2	63.3	73.7	90.9
100°	263.6	183.0	160.6	138.1	110.5	94.4	86.3	85.2	86.3	94.4	110.5
102.5°	268.2	198.0	177.8	157.7	133.5	118.6	111.7	109.4	111.7	118.6	133.5
105°	277.4	215.3	197.4	179.6	157.7	143.9	137.0	133.5	137.0	143.9	157.7
107.5°	292.4	237.2	220.5	203.8	183.0	169.2	162.3	158.9	162.3	169.2	183.0
110°	312.0	260.2	244.0	227.9	208.4	195.7	190.0	186.5	190.0	195.7	208.4

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	331.6	284.4	268.8	253.3	233.7	221.0	215.3	211.8	215.3	221.0	233.7
115°	353.4	309.7	294.2	278.6	259.0	247.5	240.6	236.0	240.6	247.5	259.0
117.5°	376.4	332.7	318.3	303.9	282.0	271.7	265.9	260.2	265.9	271.7	282.0
120°	398.3	356.9	342.5	328.1	306.2	294.7	289.0	285.5	289.0	294.7	306.2
122.5°	421.3	381.1	365.6	350.0	329.2	316.6	310.8	307.4	310.8	316.6	329.2
125°	443.2	402.9	387.4	371.8	350.0	337.3	330.4	328.1	330.4	337.3	350.0
127.5°	462.8	423.7	408.2	392.6	368.4	355.7	347.7	344.2	347.7	355.7	368.4
130°	480.1	442.1	426.6	411.0	386.8	373.0	362.6	359.2	362.6	373.0	386.8
132.5°	495.0	458.2	443.2	428.3	404.1	386.8	375.3	370.7	375.3	386.8	404.1
135°	510.0	474.3	458.8	443.2	419.0	401.8	389.1	384.5	389.1	401.8	419.0
137.5°	520.4	485.8	471.4	457.0	432.9	414.4	401.8	397.2	401.8	414.4	432.9
140°	530.7	497.3	482.9	468.5	445.5	427.1	415.6	409.8	415.6	427.1	445.5
142.5°	538.8	506.5	493.3	480.1	457.0	440.9	428.3	423.7	428.3	440.9	457.0
145°	545.7	515.7	502.5	489.3	469.7	452.4	442.1	438.6	442.1	452.4	469.7
147.5°	551.4	523.8	512.3	500.8	481.2	466.2	455.9	453.6	455.9	466.2	481.2
150°	557.2	530.7	520.4	510.0	493.9	478.9	469.7	468.5	469.7	478.9	493.9
152.5°	560.6	538.8	529.0	519.2	505.4	492.7	483.5	483.5	483.5	492.7	505.4
155°	565.3	545.7	537.7	529.6	516.9	505.4	498.5	498.5	498.5	505.4	516.9
157.5°	567.6	551.4	545.1	538.8	527.3	516.9	511.1	510.0	511.1	516.9	527.3
160°	571.0	557.2	551.4	545.7	537.6	528.4	523.8	523.8	523.8	528.4	537.6
162.5°	572.2	560.6	556.0	551.4	544.5	537.6	534.2	534.2	534.2	537.6	544.5
165°	573.3	564.1	560.0	556.0	551.4	545.7	543.4	544.5	543.4	545.7	551.4
167.5°	573.3	566.4	563.5	560.6	557.2	552.6	551.4	552.6	551.4	552.6	557.2
170°	572.2	566.4	565.2	564.1	561.8	558.3	557.2	559.5	557.2	558.3	561.8
172.5°	572.2	567.6	567.0	566.4	565.3	562.9	562.9	564.1	562.9	562.9	565.3
175°	571.0	568.7	568.2	567.6	567.6	565.3	566.4	567.6	566.4	565.3	567.6
177.5°	569.9	568.7	568.7	568.7	568.7	567.6	568.7	569.9	568.7	567.6	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1060.1	1059.1	1061.2	1054.9	1044.5	1039.3	1024.6	1021.5	1020.5	1021.5	1022.6
5°	1030.9	1029.9	1026.7	1016.3	1003.8	994.4	976.6	975.6	969.3	963.1	966.2
7.5°	1002.7	998.6	992.3	978.7	962.0	951.6	937.0	926.6	918.2	913.0	908.8
10°	974.6	968.3	962.0	944.3	923.4	907.8	890.0	881.7	872.3	868.1	864.0
12.5°	938.0	931.8	920.3	899.4	886.9	867.1	849.3	841.0	835.8	827.4	822.2
15°	908.8	896.3	890.0	868.1	842.0	840.0	807.6	805.5	795.1	795.1	786.7
17.5°	875.4	866.0	854.6	832.7	813.9	795.1	778.4	772.1	762.7	760.7	756.5
20°	843.1	830.6	826.4	804.5	784.7	761.7	744.0	737.7	733.5	729.4	732.5
22.5°	809.7	799.3	788.8	769.0	754.4	731.4	721.0	714.7	708.5	706.4	707.4
25°	777.4	768.0	757.5	737.7	722.1	703.3	693.9	690.7	687.6	687.6	686.6
27.5°	746.0	736.7	727.3	709.5	693.9	680.3	673.0	669.9	666.7	668.8	670.9
30°	713.7	705.4	697.0	681.4	668.8	656.3	652.1	650.1	649.0	654.2	654.2
32.5°	684.5	677.2	670.9	656.3	643.8	633.4	630.2	631.3	632.3	635.4	637.5
35°	654.2	649.0	642.7	630.2	619.8	610.4	611.4	611.4	613.5	618.8	622.9
37.5°	627.1	619.8	614.6	604.1	595.8	587.4	590.6	593.7	595.8	602.1	604.1
40°	594.8	591.6	587.4	577.0	569.7	568.7	569.7	571.8	576.0	579.1	582.2
42.5°	568.7	564.5	559.3	550.9	544.7	545.7	546.8	548.8	550.9	556.1	559.3
45°	539.5	536.3	532.1	524.8	519.6	520.7	521.7	521.7	523.8	530.1	532.1
47.5°	507.1	508.1	502.9	495.6	492.5	492.5	492.5	494.6	499.8	501.9	502.9
50°	475.8	473.7	472.7	465.4	463.3	462.2	463.3	464.3	471.6	470.6	473.7
52.5°	442.4	442.4	441.4	437.2	434.1	434.1	432.0	437.2	439.3	441.4	444.5
55°	410.1	406.9	405.9	403.8	399.6	398.6	400.7	406.9	409.0	411.1	414.2
57.5°	374.6	374.6	372.5	369.4	369.4	369.4	369.4	373.5	376.7	378.8	385.0
60°	342.2	338.1	334.9	334.9	334.9	333.9	340.2	340.2	346.4	347.5	349.5
62.5°	303.6	301.5	299.5	300.5	299.5	301.5	303.6	307.8	308.9	312.0	315.1
65°	267.1	267.1	265.0	271.3	267.1	267.1	272.3	272.3	274.4	277.6	281.7
67.5°	231.6	232.7	230.6	230.6	232.7	233.7	234.8	238.9	240.0	244.2	249.4
70°	195.1	197.2	198.3	196.2	198.3	200.3	202.4	203.5	207.6	209.7	212.9
72.5°	162.8	164.9	161.7	162.8	163.8	165.9	166.9	169.0	171.1	177.4	179.5
75°	130.4	129.4	128.3	132.5	130.4	134.6	135.6	135.6	137.7	142.9	145.0
77.5°	100.2	100.2	101.2	99.1	102.3	101.2	102.3	105.4	108.5	108.5	116.9
80°	69.9	72.0	72.0	72.0	73.0	74.1	72.0	77.2	78.3	78.3	81.4
82.5°	44.9	45.9	44.9	47.0	47.0	49.0	48.0	49.0	51.1	53.2	54.3
85°	24.0	24.0	26.1	26.1	25.0	26.1	25.0	26.1	28.2	28.2	29.2
87.5°	8.3	8.3	8.3	8.3	9.4	8.3	9.4	9.4	8.3	8.3	11.5
90°	12.7	13.8	15.0	18.4	21.9	25.3	28.8	27.6	28.8	29.9	31.1
92.5°	58.7	69.1	79.4	116.3	177.3	237.2	214.1	160.0	114.0	88.6	77.1
95°	104.8	127.2	149.7	247.5	419.0	607.8	682.7	553.7	414.4	280.9	219.9
97.5°	120.9	145.6	170.4	267.1	466.2	784.0	1049.9	1085.6	952.1	718.4	566.4
100°	138.1	160.6	183.0	263.6	434.0	736.8	1090.2	1317.0	1357.3	1264.0	1129.3
102.5°	157.7	177.8	198.0	268.2	406.4	667.7	1015.4	1328.5	1492.0	1511.6	1447.1
105°	179.6	197.4	215.3	277.4	396.0	613.6	925.6	1256.0	1496.6	1611.7	1633.6
107.5°	203.8	220.5	237.2	292.4	393.7	574.5	846.1	1152.4	1427.5	1608.3	1698.1
110°	227.9	244.0	260.2	312.0	399.5	553.7	780.5	1055.7	1319.3	1531.1	1676.2

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	253.3	268.8	284.4	331.6	411.0	542.2	736.8	971.6	1212.2	1429.8	1596.7
115°	278.6	294.2	309.7	353.4	423.7	541.1	708.0	907.2	1120.1	1320.5	1489.7
117.5°	303.9	318.3	332.7	376.4	439.8	542.2	688.4	864.6	1048.8	1226.1	1381.5
120°	328.1	342.5	356.9	398.3	458.2	546.8	675.8	832.3	994.7	1150.1	1288.2
122.5°	350.0	365.6	381.1	421.3	475.5	554.9	667.7	805.9	952.1	1089.1	1214.5
125°	371.8	387.4	402.9	443.2	493.9	562.9	660.8	784.0	915.2	1040.7	1151.2
127.5°	392.6	408.2	423.7	462.8	508.8	572.2	657.3	763.3	881.8	995.8	1097.1
130°	411.0	426.6	442.1	480.1	523.8	581.4	653.9	747.1	850.8	954.4	1047.6
132.5°	428.3	443.2	458.2	495.0	537.6	588.3	652.7	732.2	822.0	915.2	1000.4
135°	443.2	458.8	474.3	510.0	549.1	595.2	651.6	719.5	796.6	878.4	953.2
137.5°	457.0	471.4	485.8	520.4	558.3	599.8	649.3	708.0	772.5	841.5	908.3
140°	468.5	482.9	497.3	530.7	565.3	604.4	648.1	697.6	751.7	810.5	865.7
142.5°	480.1	493.3	506.5	538.8	572.2	607.8	645.8	688.4	732.2	780.5	826.6
145°	489.3	502.5	515.7	545.7	576.8	609.0	643.5	680.4	717.2	755.2	792.0
147.5°	500.8	512.3	523.8	551.4	580.2	609.0	640.1	672.3	704.5	735.6	766.7
150°	510.0	520.4	530.7	557.2	581.4	609.0	635.5	664.3	690.7	717.2	741.4
152.5°	519.2	529.0	538.8	560.6	583.7	605.5	629.7	655.0	678.1	699.9	720.7
155°	529.6	537.7	545.7	565.3	583.7	603.2	622.8	645.8	665.4	683.8	701.1
157.5°	538.8	545.1	551.4	567.6	584.8	599.8	617.1	635.5	651.6	667.7	681.5
160°	545.7	551.4	557.2	571.0	584.8	597.5	610.1	625.1	640.1	652.7	664.3
162.5°	551.4	556.0	560.6	572.2	583.7	592.9	603.2	614.8	626.3	636.6	647.0
165°	556.0	560.0	564.1	573.3	581.4	588.3	596.3	605.5	614.8	621.7	629.7
167.5°	560.6	563.5	566.4	573.3	580.2	583.7	589.4	596.3	604.4	610.1	614.8
170°	564.1	565.2	566.4	572.2	576.8	579.1	582.5	588.3	594.0	597.5	602.1
172.5°	566.4	567.0	567.6	572.2	575.6	575.6	576.8	580.2	584.8	587.1	590.6
175°	567.6	568.2	568.7	571.0	573.3	572.2	572.2	574.5	576.8	577.9	580.2
177.5°	568.7	568.7	568.7	569.9	572.2	569.9	568.7	569.9	571.0	572.2	573.3
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1021.5	1022.6	1018.4	1015.3	1023.6	1018.4	1018.4	1019.4	1017.3	1020.5	1019.4
5°	964.1	965.2	957.9	960.0	955.8	954.7	953.7	960.0	958.9	957.9	960.0
7.5°	907.8	907.8	904.6	902.6	902.6	899.4	903.6	902.6	904.6	904.6	907.8
10°	860.8	862.9	857.7	852.5	851.4	852.5	852.5	853.5	854.6	861.9	860.8
12.5°	822.2	819.1	818.0	814.9	809.7	807.6	805.5	817.0	813.9	813.9	813.9
15°	779.4	786.7	785.7	776.3	774.2	778.4	776.3	776.3	786.7	785.7	784.7
17.5°	756.5	754.4	752.3	747.1	748.1	747.1	748.1	748.1	754.4	754.4	754.4
20°	730.4	726.2	726.2	724.1	724.1	721.0	725.2	726.2	730.4	730.4	731.4
22.5°	707.4	704.3	704.3	703.3	705.4	701.2	705.4	706.4	706.4	709.5	709.5
25°	687.6	685.5	685.5	687.6	687.6	687.6	687.6	691.8	688.7	689.7	688.7
27.5°	669.9	670.9	672.0	673.0	672.0	673.0	674.1	676.1	677.2	676.1	674.1
30°	653.2	656.3	657.4	657.4	659.4	660.5	661.5	661.5	662.6	659.4	661.5
32.5°	640.7	640.7	642.7	643.8	645.9	646.9	646.9	649.0	648.0	644.8	645.9
35°	622.9	622.9	627.1	629.2	632.3	631.3	632.3	632.3	633.4	631.3	628.1
37.5°	605.2	607.3	607.3	611.4	612.5	613.5	612.5	614.6	613.5	611.4	610.4
40°	584.3	583.3	584.3	587.4	588.5	588.5	588.5	590.6	590.6	590.6	589.5
42.5°	558.2	561.4	560.3	563.4	562.4	562.4	564.5	566.6	567.6	564.5	565.5
45°	533.2	533.2	535.3	535.3	536.3	536.3	540.5	538.4	540.5	538.4	539.5
47.5°	506.1	507.1	507.1	508.1	510.2	512.3	510.2	511.3	511.3	512.3	510.2
50°	475.8	475.8	477.9	481.0	485.2	483.1	482.1	486.2	483.1	483.1	481.0
52.5°	444.5	447.6	448.7	451.8	454.9	456.0	457.0	454.9	456.0	452.8	453.9
55°	414.2	415.3	419.5	422.6	425.7	425.7	424.7	425.7	426.8	422.6	422.6
57.5°	384.0	387.1	391.3	391.3	395.5	395.5	394.4	394.4	395.5	392.3	391.3
60°	351.6	354.8	360.0	360.0	366.2	367.3	365.2	363.1	363.1	360.0	361.0
62.5°	317.2	320.3	323.5	328.7	332.9	330.8	334.9	330.8	331.8	325.5	325.5
65°	286.9	288.0	293.2	298.4	298.4	300.5	298.4	299.5	296.3	296.3	292.2
67.5°	251.5	251.5	256.7	261.9	267.1	267.1	267.1	264.0	264.0	260.9	260.9
70°	220.2	219.1	224.3	227.5	230.6	231.6	229.6	228.5	226.4	223.3	222.2
72.5°	181.6	183.6	188.9	190.9	196.2	195.1	200.3	194.1	194.1	188.9	187.8
75°	147.1	149.2	154.4	157.6	160.7	160.7	163.8	160.7	156.5	154.4	153.4
77.5°	116.9	115.8	120.0	125.2	126.3	125.2	127.3	126.3	122.1	122.1	120.0
80°	83.5	86.6	90.8	89.7	93.9	92.9	92.9	90.8	90.8	87.6	89.7
82.5°	55.3	58.4	59.5	58.4	59.5	61.6	62.6	61.6	61.6	59.5	60.5
85°	29.2	29.2	31.3	32.3	31.3	31.3	32.3	35.5	33.4	31.3	33.4
87.5°	9.4	8.3	8.3	9.4	8.3	8.3	9.4	9.4	10.4	10.4	10.4
90°	32.2	33.4	32.2	33.4	34.5	33.4	34.5	33.4	32.2	33.4	32.2
92.5°	73.1	69.1	66.8	62.2	63.3	61.0	63.3	62.2	66.8	69.1	73.1
95°	199.2	178.4	156.6	146.2	138.1	133.5	138.1	146.2	156.6	178.4	199.2
97.5°	500.8	435.2	358.0	314.3	286.7	274.0	286.7	314.3	358.0	435.2	500.8
100°	1047.6	965.9	849.6	765.6	720.7	721.8	720.7	765.6	849.6	965.9	1047.6
102.5°	1402.8	1358.4	1274.4	1212.2	1176.6	1143.2	1176.6	1212.2	1274.4	1358.4	1402.8
105°	1618.6	1603.7	1550.7	1507.0	1470.1	1464.4	1470.1	1507.0	1550.7	1603.7	1618.6
107.5°	1713.6	1729.1	1722.2	1701.5	1686.5	1673.9	1686.5	1701.5	1722.2	1729.1	1713.6
110°	1716.5	1756.8	1789.0	1798.2	1795.9	1793.6	1795.9	1798.2	1789.0	1756.8	1716.5

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1651.4	1706.1	1771.7	1805.1	1816.6	1817.8	1816.6	1805.1	1771.7	1706.1	1651.4
115°	1552.4	1615.2	1701.5	1752.2	1775.2	1780.9	1775.2	1752.2	1701.5	1615.2	1552.4
117.5°	1446.6	1511.6	1601.4	1657.8	1692.3	1700.4	1692.3	1657.8	1601.4	1511.6	1446.6
120°	1346.4	1404.5	1495.4	1559.9	1587.5	1594.4	1587.5	1559.9	1495.4	1404.5	1346.4
122.5°	1267.5	1320.5	1398.7	1455.1	1486.2	1495.4	1486.2	1455.1	1398.7	1320.5	1267.5
125°	1197.2	1243.3	1317.0	1367.7	1396.4	1404.5	1396.4	1367.7	1317.0	1243.3	1197.2
127.5°	1139.7	1182.3	1249.1	1292.8	1319.3	1326.2	1319.3	1292.8	1249.1	1182.3	1139.7
130°	1086.8	1125.9	1186.9	1228.4	1252.5	1261.7	1252.5	1228.4	1186.9	1125.9	1086.8
132.5°	1037.2	1074.1	1130.5	1171.9	1192.7	1198.4	1192.7	1171.9	1130.5	1074.1	1037.2
135°	986.0	1018.8	1075.2	1109.8	1130.5	1138.6	1130.5	1109.8	1075.2	1018.8	986.0
137.5°	937.6	967.0	1015.4	1051.1	1068.3	1075.2	1068.3	1051.1	1015.4	967.0	937.6
140°	890.4	915.2	959.0	991.2	1009.6	1008.5	1009.6	991.2	959.0	915.2	890.4
142.5°	847.3	868.0	903.7	931.3	947.5	946.3	947.5	931.3	903.7	868.0	847.3
145°	808.7	825.4	854.2	878.4	887.6	889.9	887.6	878.4	854.2	825.4	808.7
147.5°	778.8	790.9	813.9	831.2	840.4	841.5	840.4	831.2	813.9	790.9	778.8
150°	752.3	763.3	780.5	793.2	800.1	800.1	800.1	793.2	780.5	763.3	752.3
152.5°	729.3	737.9	750.6	762.1	765.6	765.6	765.6	762.1	750.6	737.9	729.3
155°	708.0	714.9	725.3	734.5	736.8	737.9	736.8	734.5	725.3	714.9	708.0
157.5°	687.2	693.0	702.2	709.2	711.5	711.5	711.5	709.2	702.2	693.0	687.2
160°	668.3	672.3	680.4	687.3	687.3	686.1	687.3	687.3	680.4	672.3	668.3
162.5°	650.4	653.9	658.5	664.3	664.3	663.1	664.3	664.3	658.5	653.9	650.4
165°	632.6	635.5	640.1	644.7	643.5	643.5	643.5	644.7	640.1	635.5	632.6
167.5°	617.1	619.4	621.7	625.1	624.0	624.0	624.0	625.1	621.7	619.4	617.1
170°	603.2	604.4	605.5	607.8	606.7	606.7	606.7	607.8	605.5	604.4	603.2
172.5°	591.2	591.7	591.7	594.0	591.7	590.6	591.7	594.0	591.7	591.7	591.2
175°	580.2	580.2	580.2	581.4	580.2	579.1	580.2	581.4	580.2	580.2	580.2
177.5°	573.3	573.3	572.2	573.3	571.0	571.0	571.0	573.3	572.2	573.3	573.3
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1022.6	1024.6	1025.7	1021.5	1018.4	1023.6	1030.9	1036.1	1040.3	1045.5	1048.6
5°	962.0	969.3	969.3	971.4	974.6	979.8	993.3	1002.7	1011.1	1017.3	1022.6
7.5°	910.9	916.1	919.3	924.5	929.7	937.0	952.6	966.2	978.7	986.0	994.4
10°	865.0	869.2	874.4	877.5	886.9	897.3	917.2	928.6	943.3	954.7	965.2
12.5°	821.2	835.8	838.9	837.9	846.2	857.7	877.5	895.3	910.9	922.4	933.9
15°	789.9	795.1	801.4	800.3	818.0	821.2	837.9	858.7	879.6	886.9	897.3
17.5°	755.4	763.8	770.0	773.2	778.4	789.9	805.5	821.2	848.3	849.3	876.5
20°	728.3	736.7	740.8	745.0	748.1	761.7	775.3	793.0	814.9	826.4	841.0
22.5°	710.6	714.7	717.9	721.0	725.2	732.5	749.2	769.0	783.6	796.1	805.5
25°	689.7	693.9	698.1	700.1	703.3	707.4	720.0	735.6	756.5	764.8	774.2
27.5°	675.1	675.1	677.2	677.2	681.4	685.5	694.9	709.5	726.2	736.7	749.2
30°	659.4	658.4	659.4	658.4	657.4	663.6	672.0	684.5	696.0	708.5	716.8
32.5°	643.8	642.7	642.7	643.8	639.6	642.7	646.9	658.4	670.9	677.2	686.6
35°	627.1	625.0	625.0	625.0	622.9	620.8	625.0	635.4	643.8	652.1	659.4
37.5°	610.4	607.3	607.3	605.2	603.1	600.0	600.0	608.3	619.8	622.9	632.3
40°	587.4	587.4	585.4	584.3	582.2	580.1	577.0	584.3	594.8	597.9	605.2
42.5°	564.5	561.4	560.3	560.3	560.3	557.2	555.1	560.3	566.6	571.8	576.0
45°	538.4	536.3	537.4	536.3	534.2	533.2	532.1	534.2	541.5	543.6	548.8
47.5°	510.2	509.2	509.2	508.1	507.1	508.1	504.0	509.2	511.3	513.4	517.5
50°	481.0	480.0	478.9	477.9	477.9	478.9	477.9	477.9	482.1	484.1	488.3
52.5°	451.8	448.7	448.7	447.6	447.6	445.5	447.6	448.7	450.8	452.8	454.9
55°	420.5	420.5	417.4	417.4	415.3	415.3	416.3	415.3	419.5	421.5	421.5
57.5°	390.2	386.1	387.1	385.0	382.9	381.9	381.9	384.0	386.1	386.1	388.2
60°	357.9	353.7	352.7	348.5	350.6	347.5	348.5	348.5	352.7	350.6	352.7
62.5°	325.5	320.3	317.2	315.1	315.1	316.2	314.1	313.0	315.1	317.2	321.4
65°	291.1	288.0	284.9	281.7	281.7	280.7	282.8	279.6	278.6	279.6	281.7
67.5°	255.6	252.5	249.4	246.2	247.3	244.2	242.1	245.2	243.1	244.2	246.2
70°	221.2	219.1	212.9	210.8	209.7	210.8	209.7	207.6	210.8	209.7	210.8
72.5°	186.8	184.7	181.6	176.3	176.3	175.3	174.3	174.3	173.2	173.2	173.2
75°	153.4	149.2	146.1	145.0	142.9	141.9	140.9	138.8	139.8	140.9	138.8
77.5°	119.0	113.7	112.7	112.7	109.6	109.6	110.6	109.6	108.5	108.5	108.5
80°	87.6	83.5	83.5	81.4	79.3	79.3	79.3	79.3	78.3	77.2	78.3
82.5°	56.3	55.3	54.3	54.3	56.3	52.2	54.3	53.2	52.2	52.2	51.1
85°	31.3	32.3	31.3	32.3	30.3	31.3	31.3	31.3	30.3	31.3	29.2
87.5°	11.5	11.5	11.5	12.5	12.5	12.5	12.5	12.5	13.6	12.5	12.5
90°	31.1	29.9	28.8	27.6	28.8	25.3	21.9	18.4	15.0	13.8	12.7
92.5°	77.1	88.6	114.0	160.0	214.1	237.2	177.3	116.3	79.4	69.1	58.7
95°	219.9	280.9	414.4	553.7	682.7	607.8	419.0	247.5	149.7	127.2	104.8
97.5°	566.4	718.4	952.1	1085.6	1049.9	784.0	466.2	267.1	170.4	145.6	120.9
100°	1129.3	1264.0	1357.3	1317.0	1090.2	736.8	434.0	263.6	183.0	160.6	138.1
102.5°	1447.1	1511.6	1492.0	1328.5	1015.4	667.7	406.4	268.2	198.0	177.8	157.7
105°	1633.6	1611.7	1496.6	1256.0	925.6	613.6	396.0	277.4	215.3	197.4	179.6
107.5°	1698.1	1608.3	1427.5	1152.4	846.1	574.5	393.7	292.4	237.2	220.5	203.8
110°	1676.2	1531.1	1319.3	1055.7	780.5	553.7	399.5	312.0	260.2	244.0	227.9

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1596.7	1429.8	1212.2	971.6	736.8	542.2	411.0	331.6	284.4	268.8	253.3
115°	1489.7	1320.5	1120.1	907.2	708.0	541.1	423.7	353.4	309.7	294.2	278.6
117.5°	1381.5	1226.1	1048.8	864.6	688.4	542.2	439.8	376.4	332.7	318.3	303.9
120°	1288.2	1150.1	994.7	832.3	675.8	546.8	458.2	398.3	356.9	342.5	328.1
122.5°	1214.5	1089.1	952.1	805.9	667.7	554.9	475.5	421.3	381.1	365.6	350.0
125°	1151.2	1040.7	915.2	784.0	660.8	562.9	493.9	443.2	402.9	387.4	371.8
127.5°	1097.1	995.8	881.8	763.3	657.3	572.2	508.8	462.8	423.7	408.2	392.6
130°	1047.6	954.4	850.8	747.1	653.9	581.4	523.8	480.1	442.1	426.6	411.0
132.5°	1000.4	915.2	822.0	732.2	652.7	588.3	537.6	495.0	458.2	443.2	428.3
135°	953.2	878.4	796.6	719.5	651.6	595.2	549.1	510.0	474.3	458.8	443.2
137.5°	908.3	841.5	772.5	708.0	649.3	599.8	558.3	520.4	485.8	471.4	457.0
140°	865.7	810.5	751.7	697.6	648.1	604.4	565.3	530.7	497.3	482.9	468.5
142.5°	826.6	780.5	732.2	688.4	645.8	607.8	572.2	538.8	506.5	493.3	480.1
145°	792.0	755.2	717.2	680.4	643.5	609.0	576.8	545.7	515.7	502.5	489.3
147.5°	766.7	735.6	704.5	672.3	640.1	609.0	580.2	551.4	523.8	512.3	500.8
150°	741.4	717.2	690.7	664.3	635.5	609.0	581.4	557.2	530.7	520.4	510.0
152.5°	720.7	699.9	678.1	655.0	629.7	605.5	583.7	560.6	538.8	529.0	519.2
155°	701.1	683.8	665.4	645.8	622.8	603.2	583.7	565.3	545.7	537.7	529.6
157.5°	681.5	667.7	651.6	635.5	617.1	599.8	584.8	567.6	551.4	545.1	538.8
160°	664.3	652.7	640.1	625.1	610.1	597.5	584.8	571.0	557.2	551.4	545.7
162.5°	647.0	636.6	626.3	614.8	603.2	592.9	583.7	572.2	560.6	556.0	551.4
165°	629.7	621.7	614.8	605.5	596.3	588.3	581.4	573.3	564.1	560.0	556.0
167.5°	614.8	610.1	604.4	596.3	589.4	583.7	580.2	573.3	566.4	563.5	560.6
170°	602.1	597.5	594.0	588.3	582.5	579.1	576.8	572.2	566.4	565.2	564.1
172.5°	590.6	587.1	584.8	580.2	576.8	575.6	575.6	572.2	567.6	567.0	566.4
175°	580.2	577.9	576.8	574.5	572.2	572.2	573.3	571.0	568.7	568.2	567.6
177.5°	573.3	572.2	571.0	569.9	568.7	569.9	572.2	569.9	568.7	568.7	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1076.8	1076.8	1076.8	1076.8
2.5°	1053.9	1057.0	1067.4	1079.9
5°	1033.0	1041.3	1055.9	1075.8
7.5°	1010.0	1022.6	1043.4	1068.5
10°	983.9	1001.7	1027.8	1059.1
12.5°	955.8	978.7	1012.1	1044.5
15°	938.0	961.0	991.3	1026.7
17.5°	903.6	930.7	962.0	1012.1
20°	868.1	898.4	939.1	989.2
22.5°	841.0	873.3	912.0	965.2
25°	808.7	842.0	883.8	939.1
27.5°	774.2	807.6	854.6	913.0
30°	748.1	780.5	825.3	888.0
32.5°	716.8	748.1	795.1	860.8
35°	681.4	716.8	761.7	828.5
37.5°	654.2	686.6	733.5	797.2
40°	625.0	653.2	699.1	761.7
42.5°	593.7	625.0	664.7	727.3
45°	564.5	587.4	628.1	687.6
47.5°	533.2	559.3	590.6	636.5
50°	499.8	521.7	556.1	587.4
52.5°	467.5	485.2	514.4	538.4
55°	433.0	450.8	472.7	487.3
57.5°	400.7	413.2	427.8	437.2
60°	361.0	373.5	382.9	392.3
62.5°	325.5	334.9	340.2	345.4
65°	289.0	294.2	297.4	301.5
67.5°	249.4	254.6	255.6	261.9
70°	212.9	213.9	216.0	219.1
72.5°	178.4	180.5	179.5	181.6
75°	142.9	145.0	142.9	145.0
77.5°	108.5	110.6	110.6	113.7
80°	78.3	79.3	80.3	80.3
82.5°	51.1	54.3	52.2	53.2
85°	29.2	30.3	30.3	31.3
87.5°	13.6	14.6	13.6	15.7
90°	10.4	6.9	4.6	2.3
92.5°	47.2	36.8	25.3	17.3
95°	74.8	55.3	42.6	39.1
97.5°	90.9	73.7	63.3	62.2
100°	110.5	94.4	86.3	85.2
102.5°	133.5	118.6	111.7	109.4
105°	157.7	143.9	137.0	133.5
107.5°	183.0	169.2	162.3	158.9
110°	208.4	195.7	190.0	186.5

TEST NUMBER: P1011942

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	233.7	221.0	215.3	211.8
115°	259.0	247.5	240.6	236.0
117.5°	282.0	271.7	265.9	260.2
120°	306.2	294.7	289.0	285.5
122.5°	329.2	316.6	310.8	307.4
125°	350.0	337.3	330.4	328.1
127.5°	368.4	355.7	347.7	344.2
130°	386.8	373.0	362.6	359.2
132.5°	404.1	386.8	375.3	370.7
135°	419.0	401.8	389.1	384.5
137.5°	432.9	414.4	401.8	397.2
140°	445.5	427.1	415.6	409.8
142.5°	457.0	440.9	428.3	423.7
145°	469.7	452.4	442.1	438.6
147.5°	481.2	466.2	455.9	453.6
150°	493.9	478.9	469.7	468.5
152.5°	505.4	492.7	483.5	483.5
155°	516.9	505.4	498.5	498.5
157.5°	527.3	516.9	511.1	510.0
160°	537.6	528.4	523.8	523.8
162.5°	544.5	537.6	534.2	534.2
165°	551.4	545.7	543.4	544.5
167.5°	557.2	552.6	551.4	552.6
170°	561.8	558.3	557.2	559.5
172.5°	565.3	562.9	562.9	564.1
175°	567.6	565.3	566.4	567.6
177.5°	568.7	567.6	568.7	569.9
180°	568.7	568.7	568.7	568.7

(END OF REPORT)