

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011947

Luminaire Tested: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011947
REPORT IS A COMBINATION OF REPORTS P990286 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7223.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011947

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011947

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		50
1	96	92	88	85	88	84	81	78	70	68	65		57	55	54		44
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35
4	73	62	55	49	67	57	51	45	48	43	39		39	35	32		31
5	67	56	47	42	61	51	44	39	43	37	33		35	31	28		28
6	62	50	42	36	56	46	39	34	39	33	29		32	28	24		25
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		20
10	46	34	27	22	42	32	25	21	27	22	18		22	18	16		18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13065	13065	13065
5°	13097	12615	12595
10°	12981	12187	12063
15°	12801	11744	11481
20°	12593	11250	10906
25°	12326	10730	10290
30°	12033	10192	9643
35°	11726	9642	9000
40°	11405	9065	8367
45°	11051	8502	7706
50°	10692	7875	7042
55°	10230	7222	6369
60°	9756	6501	5654
65°	9309	5723	4908
70°	8667	4858	4038
75°	7741	3846	3135
80°	6688	2702	2217
85°	5216	1454	1110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11051 cd/sqm

TEST NUMBER: P1011947

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	1.6
10°-20°	323.1	4.5
20°-30°	477.2	6.6
30°-40°	557.3	7.7
40°-50°	560.3	7.8
50°-60°	492.2	6.8
60°-70°	366.6	5.1
70°-80°	208.6	2.9
80°-90°	62.4	0.9
90°-100°	94.3	1.3
100°-110°	285.6	4.0
110°-120°	486.1	6.7
120°-130°	639.5	8.9
130°-140°	718.9	10.0
140°-150°	706.7	9.8
150°-160°	595.0	8.2
160°-170°	396.1	5.5
170°-180°	138.7	1.9
0°-30°	914.7	12.7
0°-40°	1472.1	20.4
0°-60°	2524.5	35.0
0°-90°	3162.1	43.8
90°-120°	866.0	12.0
90°-150°	2931.1	40.6
90°-180°	4061.0	56.2
0°-180°	7223.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1214	1214	1214	1214	1214	
5°	1215	1210	1198	1209	1206	115
15°	1156	1152	1139	1147	1141	326
25°	1050	1044	1030	1031	1028	484
35°	908	902	888	882	877	568
45°	744	740	726	714	709	574
55°	565	564	550	538	533	506
65°	385	380	370	361	358	380
75°	204	199	196	191	188	217
85°	54	52	52	50	50	58
90°	1	13	28	32	34	9
95°	68	76	85	90	90	75
105°	259	261	272	272	274	277
115°	489	493	490	492	490	484
125°	716	720	717	713	708	639
135°	929	936	935	930	928	716
145°	1127	1129	1133	1132	1127	704
155°	1291	1291	1292	1296	1288	594
165°	1406	1402	1402	1409	1401	396
175°	1462	1458	1458	1464	1456	139
180°	1466	1466	1466	1466	1466	

TEST NUMBER: P1011947

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1213.8	1213.8	1213.8	1213.8	1213.8
2.5°	1219.0	1214.8	1203.4	1213.8	1212.8
5°	1214.8	1209.6	1198.2	1208.6	1206.5
7.5°	1205.5	1200.2	1188.8	1198.2	1197.1
10°	1192.9	1187.7	1174.1	1183.5	1181.5
12.5°	1176.2	1172.1	1159.5	1165.8	1164.8
15°	1156.4	1152.2	1138.7	1147.0	1140.7
17.5°	1134.5	1129.3	1115.7	1122.0	1119.9
20°	1109.4	1103.2	1089.6	1093.8	1090.7
22.5°	1081.3	1075.0	1061.4	1064.6	1060.4
25°	1049.9	1043.7	1030.1	1031.2	1028.0
27.5°	1017.6	1011.3	996.7	997.8	994.6
30°	982.1	976.9	962.3	962.3	955.0
32.5°	946.6	939.3	928.9	921.6	918.4
35°	908.0	901.7	888.2	881.9	876.7
37.5°	869.4	861.0	847.5	840.2	837.0
40°	828.7	822.4	807.8	799.5	795.3
42.5°	788.0	780.7	766.1	757.7	753.5
45°	744.1	740.0	726.4	713.9	708.7
47.5°	701.4	695.1	682.6	670.0	665.9
50°	657.5	652.3	638.7	627.3	621.0
52.5°	611.6	608.5	593.9	584.5	578.2
55°	564.6	563.6	550.0	538.5	533.3
57.5°	520.8	516.6	506.2	495.8	489.5
60°	472.8	471.7	459.2	449.8	444.6
62.5°	430.0	426.9	414.3	404.9	401.8
65°	385.1	379.9	369.5	361.1	358.0
67.5°	337.1	332.9	324.6	317.3	313.1
70°	294.3	288.1	281.8	274.5	269.3
72.5°	249.4	245.3	238.0	231.7	229.6
75°	203.5	199.3	196.2	191.0	187.9
77.5°	162.8	160.7	156.6	152.4	152.4
80°	123.2	120.0	117.9	116.9	116.9
82.5°	84.5	84.5	84.5	82.5	81.4
85°	54.3	52.2	52.2	50.1	50.1
87.5°	27.1	24.0	23.0	21.9	21.9
90°	1.2	12.7	27.6	32.2	34.5
92.5°	34.5	41.4	48.4	51.8	49.5
95°	67.9	76.0	85.2	89.8	89.8
97.5°	111.7	117.4	124.3	130.1	128.9
100°	156.6	163.5	169.2	172.7	175.0
102.5°	208.4	211.8	219.9	223.4	222.2
105°	259.0	261.3	271.7	271.7	274.0
107.5°	318.9	320.1	324.7	328.1	327.0
110°	374.2	376.5	378.8	383.4	381.1

TEST NUMBER: P1011947

CATALOG NUMBER: S123DIP-B775D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	431.7	432.9	432.9	438.6	438.6
115°	489.3	492.8	490.5	491.6	490.5
117.5°	548.0	549.2	546.9	546.9	543.4
120°	602.1	609.0	603.3	602.1	599.8
122.5°	658.5	663.1	660.8	657.4	653.9
125°	716.1	719.6	717.3	712.7	708.0
127.5°	769.1	776.0	773.7	766.8	762.2
130°	822.0	831.2	827.8	823.2	815.1
132.5°	875.0	884.2	881.9	876.1	870.4
135°	929.1	936.0	934.9	930.2	927.9
137.5°	978.6	984.4	987.8	982.1	978.6
140°	1030.4	1036.2	1037.3	1036.2	1028.1
142.5°	1077.6	1083.4	1085.7	1084.5	1078.8
145°	1127.1	1129.4	1132.9	1131.7	1127.1
147.5°	1169.7	1174.3	1177.8	1177.8	1170.9
150°	1214.6	1216.9	1219.2	1219.2	1212.3
152.5°	1251.5	1254.9	1256.1	1258.4	1252.6
155°	1290.6	1290.6	1291.8	1296.4	1288.3
157.5°	1324.0	1322.8	1324.0	1328.6	1321.7
160°	1355.1	1352.8	1352.8	1358.5	1353.9
162.5°	1382.7	1379.2	1380.4	1386.2	1378.1
165°	1405.7	1402.3	1402.3	1409.2	1401.1
167.5°	1425.3	1420.7	1421.8	1428.8	1421.8
170°	1441.4	1436.8	1436.8	1444.9	1436.8
172.5°	1454.1	1449.5	1449.5	1456.4	1448.3
175°	1462.1	1457.5	1457.5	1464.4	1456.4
177.5°	1466.7	1462.1	1462.1	1469.1	1461.0
180°	1465.6	1465.6	1465.6	1465.6	1465.6

(END OF REPORT)