

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011965

Luminaire Tested: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011965
REPORT IS A COMBINATION OF REPORTS P990319 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7316.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011965

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011965

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1011965

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.6
10°-20°	327.3	4.5
20°-30°	483.4	6.6
30°-40°	564.6	7.7
40°-50°	567.5	7.8
50°-60°	498.6	6.8
60°-70°	371.3	5.1
70°-80°	211.3	2.9
80°-90°	63.2	0.9
90°-100°	95.6	1.3
100°-110°	289.2	4.0
110°-120°	492.4	6.7
120°-130°	647.7	8.9
130°-140°	728.0	10.0
140°-150°	715.8	9.8
150°-160°	602.6	8.2
160°-170°	401.2	5.5
170°-180°	140.5	1.9
0°-30°	926.6	12.7
0°-40°	1491.2	20.4
0°-60°	2557.3	35.0
0°-90°	3203.1	43.8
90°-120°	877.1	12.0
90°-150°	2968.6	40.6
90°-180°	4113.0	56.2
0°-180°	7316.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	1	13	28	33	35	9
95°	69	77	86	91	91	76
105°	262	265	275	275	278	281
115°	496	499	497	498	497	490
125°	725	729	726	722	717	647
135°	941	948	947	942	940	725
145°	1142	1144	1147	1146	1142	713
155°	1307	1307	1308	1313	1305	602
165°	1424	1420	1420	1427	1419	402
175°	1481	1476	1476	1483	1475	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1011965

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	1.2	12.8	28.0	32.6	35.0
92.5°	35.0	42.0	49.0	52.5	50.1
95°	68.8	77.0	86.3	90.9	90.9
97.5°	113.1	118.9	125.9	131.8	130.6
100°	158.6	165.6	171.4	174.9	177.2
102.5°	211.1	214.5	222.7	226.2	225.0
105°	262.4	264.7	275.2	275.2	277.5
107.5°	323.0	324.2	328.8	332.3	331.2
110°	379.0	381.3	383.6	388.3	386.0

TEST NUMBER: P1011965

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.3	438.4	438.4	444.3	444.3
115°	495.6	499.1	496.7	497.9	496.7
117.5°	555.0	556.2	553.9	553.9	550.4
120°	609.8	616.8	611.0	609.8	607.5
122.5°	667.0	671.6	669.3	665.8	662.3
125°	725.3	728.8	726.4	721.8	717.1
127.5°	778.9	785.9	783.6	776.6	771.9
130°	832.5	841.9	838.4	833.7	825.5
132.5°	886.2	895.5	893.2	887.3	881.5
135°	941.0	948.0	946.8	942.1	939.8
137.5°	991.1	997.0	1000.4	994.6	991.1
140°	1043.6	1049.4	1050.6	1049.4	1041.3
142.5°	1091.4	1097.2	1099.6	1098.4	1092.6
145°	1141.5	1143.9	1147.4	1146.2	1141.5
147.5°	1184.7	1189.3	1192.8	1192.8	1185.8
150°	1230.2	1232.5	1234.8	1234.8	1227.8
152.5°	1267.5	1271.0	1272.1	1274.5	1268.6
155°	1307.1	1307.1	1308.3	1312.9	1304.8
157.5°	1340.9	1339.8	1340.9	1345.6	1338.6
160°	1372.4	1370.1	1370.1	1375.9	1371.2
162.5°	1400.4	1396.9	1398.1	1403.9	1395.7
165°	1423.7	1420.2	1420.2	1427.2	1419.1
167.5°	1443.5	1438.9	1440.0	1447.0	1440.0
170°	1459.9	1455.2	1455.2	1463.4	1455.2
172.5°	1472.7	1468.0	1468.0	1475.0	1466.9
175°	1480.9	1476.2	1476.2	1483.2	1475.0
177.5°	1485.5	1480.9	1480.9	1487.8	1479.7
180°	1484.3	1484.3	1484.3	1484.3	1484.3

(END OF REPORT)