

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011693

Luminaire Tested: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011693
REPORT IS A COMBINATION OF REPORTS P989951 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5992.5 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011693

CATALOG NUMBER: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011693

CATALOG NUMBER: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	62	57	71	64	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	48	36	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8078 cd/sqm

TEST NUMBER: P1011693

CATALOG NUMBER: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.4
10°-20°	236.2	3.9
20°-30°	348.8	5.8
30°-40°	407.4	6.8
40°-50°	409.5	6.8
50°-60°	359.8	6.0
60°-70°	267.9	4.5
70°-80°	152.5	2.5
80°-90°	46.1	0.8
90°-100°	277.4	4.6
100°-110°	775.4	12.9
110°-120°	756.1	12.6
120°-130°	602.1	10.0
130°-140°	475.2	7.9
140°-150°	354.6	5.9
150°-160°	247.4	4.1
160°-170°	145.3	2.4
170°-180°	47.3	0.8
0°-30°	668.6	11.2
0°-40°	1076.0	18.0
0°-60°	1845.2	30.8
0°-90°	2311.7	38.6
90°-120°	1809.0	30.2
90°-150°	3240.9	54.1
90°-180°	3681.0	61.4
0°-180°	5992.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	2	12	25	28	29	5
95°	34	109	586	171	115	36
105°	115	170	795	1389	1257	122
115°	203	252	608	1333	1529	201
125°	282	332	567	1028	1206	250
135°	330	394	559	846	977	255
145°	376	431	552	694	764	236
155°	428	462	535	608	634	197
165°	467	481	512	543	552	132
175°	487	488	491	498	497	46
180°	488	488	488	488	488	

TEST NUMBER: P1011693

CATALOG NUMBER: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	2.0	11.9	24.7	27.7	28.7
92.5°	14.8	59.3	183.8	62.8	52.4
95°	33.6	109.2	586.0	171.0	114.6
97.5°	53.4	125.0	901.3	429.9	235.2
100°	73.1	137.8	935.9	899.4	619.6
102.5°	93.9	152.7	871.6	1204.2	981.3
105°	114.6	169.5	794.6	1389.4	1257.1
107.5°	136.4	189.2	726.4	1471.1	1436.9
110°	160.1	209.5	670.0	1473.5	1539.7

TEST NUMBER: P1011693

CATALOG NUMBER: S123DIP-B560D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	230.8	632.5	1417.6	1560.5
115°	202.6	252.5	607.8	1332.6	1528.8
117.5°	223.3	273.2	591.0	1241.8	1459.7
120°	245.1	294.0	580.1	1155.8	1368.7
122.5°	263.9	313.8	573.2	1088.0	1283.8
125°	281.7	332.5	567.3	1027.8	1205.7
127.5°	295.5	350.4	564.3	978.4	1138.5
130°	308.3	366.2	561.3	932.9	1083.1
132.5°	318.2	380.5	560.3	890.4	1028.8
135°	330.1	393.8	559.4	846.4	977.4
137.5°	341.0	404.6	557.4	804.9	923.0
140°	351.8	414.6	556.4	764.4	865.7
142.5°	363.7	423.4	554.4	727.4	812.4
145°	376.5	431.4	552.4	694.2	763.9
147.5°	389.4	439.8	549.5	668.6	722.4
150°	402.2	446.7	545.5	645.8	686.8
152.5°	415.1	454.1	540.6	626.1	657.2
155°	427.9	461.5	534.6	607.8	633.5
157.5°	437.8	468.0	529.7	590.0	610.7
160°	449.7	473.4	523.8	573.7	589.0
162.5°	458.6	477.4	517.8	558.3	569.2
165°	467.4	480.8	511.9	543.0	552.4
167.5°	474.4	483.8	506.0	529.7	535.6
170°	480.3	485.2	500.1	517.8	520.8
172.5°	484.2	486.7	495.1	507.5	507.0
175°	487.2	487.7	491.2	498.1	497.1
177.5°	489.2	488.2	488.2	492.2	490.2
180°	488.2	488.2	488.2	488.2	488.2

(END OF REPORT)