

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011966

Luminaire Tested: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011966
REPORT IS A COMBINATION OF REPORTS P990320 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7546.1 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011966

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011966

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1011966

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.5
10°-20°	327.3	4.3
20°-30°	483.4	6.4
30°-40°	564.6	7.5
40°-50°	567.5	7.5
50°-60°	498.6	6.6
60°-70°	371.3	4.9
70°-80°	211.3	2.8
80°-90°	63.3	0.8
90°-100°	327.3	4.3
100°-110°	914.9	12.1
110°-120°	892.1	11.8
120°-130°	710.4	9.4
130°-140°	560.8	7.4
140°-150°	418.4	5.5
150°-160°	291.8	3.9
160°-170°	171.5	2.3
170°-180°	55.8	0.7
0°-30°	926.6	12.3
0°-40°	1491.2	19.8
0°-60°	2557.3	33.9
0°-90°	3203.2	42.4
90°-120°	2134.3	28.3
90°-150°	3823.8	50.7
90°-180°	4343.0	57.6
0°-180°	7546.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	2	14	29	33	34	7
95°	40	129	691	202	135	42
105°	135	200	938	1639	1483	144
115°	239	298	717	1572	1804	237
125°	332	392	669	1213	1422	295
135°	389	465	660	999	1153	301
145°	444	509	652	819	901	278
155°	505	545	631	717	747	232
165°	552	567	604	641	652	155
175°	575	575	580	588	586	55
180°	576	576	576	576	576	

TEST NUMBER: P1011966

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	2.3	14.0	29.2	32.6	33.8
92.5°	17.5	70.0	216.9	74.0	61.8
95°	39.6	128.8	691.4	201.7	135.3
97.5°	63.0	147.5	1063.4	507.2	277.5
100°	86.3	162.6	1104.2	1061.1	731.1
102.5°	110.8	180.1	1028.4	1420.8	1157.9
105°	135.3	200.0	937.5	1639.4	1483.2
107.5°	160.9	223.3	857.0	1735.6	1695.4
110°	188.9	247.2	790.6	1738.5	1816.6

TEST NUMBER: P1011966

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.5	272.2	746.2	1672.6	1841.1
115°	239.0	298.0	717.1	1572.4	1803.8
117.5°	263.5	322.4	697.3	1465.1	1722.2
120°	289.2	346.9	684.4	1363.6	1614.9
122.5°	311.3	370.2	676.3	1283.8	1514.7
125°	332.3	392.4	669.3	1212.6	1422.5
127.5°	348.6	413.4	665.8	1154.4	1343.2
130°	363.8	432.0	662.3	1100.8	1278.0
132.5°	375.5	449.0	661.1	1050.6	1213.8
135°	389.4	464.6	660.0	998.7	1153.2
137.5°	402.3	477.5	657.6	949.8	1089.1
140°	415.1	489.2	656.5	901.9	1021.4
142.5°	429.1	499.6	654.1	858.2	958.5
145°	444.3	509.0	651.8	819.1	901.3
147.5°	459.4	518.8	648.3	788.8	852.4
150°	474.6	527.0	643.6	762.0	810.4
152.5°	489.7	535.8	637.8	738.6	775.4
155°	504.9	544.6	630.8	717.1	747.4
157.5°	516.5	552.1	625.0	696.1	720.6
160°	530.5	558.6	618.0	676.9	694.9
162.5°	541.0	563.2	611.0	658.8	671.6
165°	551.5	567.2	604.0	640.7	651.8
167.5°	559.7	570.8	597.0	625.0	632.0
170°	566.7	572.5	590.0	611.0	614.5
172.5°	571.3	574.2	584.2	598.8	598.2
175°	574.8	575.4	579.5	587.7	586.5
177.5°	577.2	576.0	576.0	580.7	578.3
180°	576.0	576.0	576.0	576.0	576.0

(END OF REPORT)