

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011975

Luminaire Tested: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011975
REPORT IS A COMBINATION OF REPORTS P990329 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB40-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7471.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011975

CATALOG NUMBER: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011975

CATALOG NUMBER: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13135	12651	12631
10°	13018	12222	12097
15°	12837	11777	11514
20°	12630	11282	10937
25°	12361	10762	10320
30°	12067	10221	9670
35°	11760	9669	9025
40°	11437	9091	8391
45°	11083	8527	7728
50°	10723	7898	7063
55°	10259	7243	6387
60°	9783	6520	5671
65°	9336	5738	4922
70°	8693	4872	4048
75°	7764	3858	3143
80°	6705	2712	2223
85°	5225	1456	1113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11083 cd/sqm

TEST NUMBER: P1011975

CATALOG NUMBER: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	1.5
10°-20°	324.0	4.3
20°-30°	478.6	6.4
30°-40°	558.9	7.5
40°-50°	561.9	7.5
50°-60°	493.6	6.6
60°-70°	367.6	4.9
70°-80°	209.2	2.8
80°-90°	62.7	0.8
90°-100°	324.1	4.3
100°-110°	905.8	12.1
110°-120°	883.3	11.8
120°-130°	703.3	9.4
130°-140°	555.2	7.4
140°-150°	414.2	5.5
150°-160°	289.0	3.9
160°-170°	169.8	2.3
170°-180°	55.2	0.7
0°-30°	917.4	12.3
0°-40°	1476.3	19.8
0°-60°	2531.7	33.9
0°-90°	3171.2	42.4
90°-120°	2113.2	28.3
90°-150°	3785.9	50.7
90°-180°	4300.0	57.6
0°-180°	7471.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	58
90°	2	14	29	32	34	7
95°	39	128	685	200	134	42
105°	134	198	928	1623	1468	142
115°	237	295	710	1557	1786	234
125°	329	388	663	1201	1408	292
135°	386	460	653	989	1142	298
145°	440	504	645	811	892	276
155°	500	539	625	710	740	230
165°	546	562	598	634	645	154
175°	569	570	574	582	581	54
180°	570	570	570	570	570	

TEST NUMBER: P1011975

CATALOG NUMBER: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	2.3	13.8	28.9	32.4	33.5
92.5°	17.3	69.3	214.7	73.3	61.2
95°	39.3	127.6	684.6	199.7	133.9
97.5°	62.3	146.0	1052.9	502.2	274.8
100°	85.4	161.0	1093.3	1050.6	723.8
102.5°	109.7	178.4	1018.2	1406.7	1146.4
105°	133.9	198.0	928.2	1623.2	1468.5
107.5°	159.3	221.0	848.5	1718.4	1678.6
110°	187.0	244.8	782.7	1721.3	1798.6

TEST NUMBER: P1011975

CATALOG NUMBER: S123DIP-B775D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.4	269.6	738.8	1656.0	1822.9
115°	236.7	295.0	710.0	1556.8	1785.9
117.5°	260.9	319.2	690.4	1450.6	1705.1
120°	286.3	343.4	677.7	1350.1	1598.9
122.5°	308.2	366.6	669.6	1271.1	1499.6
125°	329.0	388.5	662.7	1200.6	1408.4
127.5°	345.2	409.2	659.2	1142.9	1329.9
130°	360.2	427.7	655.7	1089.8	1265.3
132.5°	371.7	444.5	654.6	1040.2	1201.8
135°	385.6	460.0	653.4	988.8	1141.8
137.5°	398.3	472.8	651.1	940.3	1078.3
140°	411.0	484.3	650.0	893.0	1011.3
142.5°	424.8	494.7	647.6	849.7	949.0
145°	439.8	503.9	645.3	811.0	892.4
147.5°	454.9	513.8	641.9	781.0	843.9
150°	469.9	521.8	637.3	754.4	802.3
152.5°	484.9	530.5	631.5	731.4	767.7
155°	499.9	539.1	624.6	710.0	740.0
157.5°	511.4	546.6	618.8	689.2	713.5
160°	525.3	553.0	611.9	670.2	688.1
162.5°	535.7	557.6	604.9	652.2	665.0
165°	546.1	561.7	598.0	634.4	645.3
167.5°	554.1	565.1	591.1	618.8	625.7
170°	561.1	566.8	584.2	605.0	608.4
172.5°	565.7	568.6	578.4	592.8	592.2
175°	569.1	569.7	573.8	581.8	580.7
177.5°	571.5	570.3	570.3	574.9	572.6
180°	570.3	570.3	570.3	570.3	570.3

(END OF REPORT)