

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011721

Luminaire Tested: S123DIP-B560D1195UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011721
REPORT IS A COMBINATION OF REPORTS P989979 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB27-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7082.0 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot





TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33						
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28						
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24						
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21						
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18						
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16						
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17	14						
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12						
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11						
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10						
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9						

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8402	8402	8402	8402
5°	8408	9682	8432	7225
10°	8354	11716	8363	6310
15°	8239	13894	8307	5680
20°	8140	15996	8157	5226
25°	7992	16400	8010	4990
30°	7887	13549	7887	4835
35°	7756	9061	7707	4697
40°	7600	6542	7506	4488
45°	7403	5181	7189	4227
50°	6926	4400	6678	3971
55°	6400	3866	6141	3686
60°	5868	3366	5557	3387
65°	5284	2883	5028	2986
70°	4676	2393	4367	2517
75°	3998	1805	3739	1944
80°	3160	1204	2915	1276
85°	2180	554	1748	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13551 cd/sqm

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.1
10°-20°	246.6	3.5
20°-30°	414.9	5.9
30°-40°	468.9	6.6
40°-50°	419.9	5.9
50°-60°	339.0	4.8
60°-70°	236.2	3.3
70°-80°	124.0	1.8
80°-90°	32.8	0.5
90°-100°	54.6	0.8
100°-110°	264.1	3.7
110°-120°	647.3	9.1
120°-130°	821.7	11.6
130°-140°	877.8	12.4
140°-150°	820.8	11.6
150°-160°	662.1	9.3
160°-170°	427.3	6.0
170°-180°	147.2	2.1
0°-30°	738.2	10.4
0°-40°	1207.1	17.0
0°-60°	1966.1	27.8
0°-90°	2359.1	33.3
90°-120°	966.0	13.6
90°-150°	3486.3	49.2
90°-180°	4723.0	66.7
0°-180°	7082.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	781	781	781	781	781	
5°	780	927	782	692	780	74
15°	744	1380	750	564	744	210
25°	681	1638	682	498	681	314
35°	601	883	597	458	601	376
45°	498	476	484	389	498	381
55°	353	324	339	309	353	316
65°	219	210	208	218	219	218
75°	105	108	98	116	105	113
85°	23	25	18	23	23	26
90°	1	34	1	34	1	6
95°	70	44	70	44	70	84
105°	343	51	343	51	343	364
115°	643	677	643	677	643	635
125°	907	925	907	925	907	810
135°	1129	1141	1129	1141	1129	869
145°	1303	1316	1303	1316	1303	816
155°	1435	1433	1435	1433	1435	661
165°	1514	1510	1514	1510	1514	428
175°	1549	1544	1549	1544	1549	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	782.9	788.9	792.0	796.5	801.0	807.8	810.1	813.9	812.4	815.4	816.9
5°	779.9	790.4	799.5	810.9	821.5	829.0	836.6	848.7	857.8	859.3	866.1
7.5°	774.6	789.7	805.6	821.5	841.9	854.0	867.6	884.2	897.9	919.8	928.1
10°	767.7	788.9	811.6	833.6	861.5	880.5	897.1	925.1	953.1	975.8	996.9
12.5°	757.2	783.6	813.1	845.7	882.0	903.9	926.6	963.7	1006.0	1040.8	1063.5
15°	744.3	777.6	815.4	850.2	890.3	931.1	955.3	996.9	1057.5	1090.0	1148.2
17.5°	733.7	767.7	805.6	860.0	914.5	955.3	972.7	1049.1	1090.7	1145.2	1211.0
20°	717.1	760.2	808.6	863.1	933.4	958.4	993.9	1071.1	1122.5	1193.6	1274.5
22.5°	699.7	745.8	804.1	860.8	939.5	965.9	1014.3	1075.6	1157.3	1227.6	1316.9
25°	680.8	730.7	789.7	857.0	934.2	972.7	1018.1	1093.8	1182.3	1270.8	1353.2
27.5°	661.9	716.3	777.6	844.9	919.8	965.2	1010.6	1089.2	1202.7	1298.7	1403.9
30°	643.7	698.2	759.4	828.3	906.9	950.8	993.9	1092.2	1218.6	1326.7	1432.6
32.5°	624.0	680.0	744.3	801.8	881.2	928.1	976.5	1092.2	1228.4	1343.4	1440.2
35°	600.6	658.1	713.3	770.8	849.4	901.6	956.1	1084.7	1237.5	1348.7	1408.4
37.5°	577.9	628.6	676.2	732.2	814.6	870.6	933.4	1075.6	1232.9	1326.0	1342.6
40°	552.2	602.9	641.4	693.6	780.6	845.7	909.2	1063.5	1213.3	1272.3	1223.9
42.5°	527.2	567.3	600.6	651.3	745.8	809.4	878.2	1041.6	1174.7	1186.8	1077.9
45°	498.5	527.2	556.7	614.2	708.0	773.0	849.4	1009.8	1112.7	1077.9	940.2
47.5°	461.4	487.1	519.6	572.6	667.9	735.2	807.8	969.0	1022.7	950.0	799.5
50°	425.9	447.8	478.0	529.5	625.5	691.4	768.5	904.7	931.1	816.9	689.1
52.5°	390.3	406.9	436.4	487.9	583.9	647.5	717.8	838.9	823.7	701.2	587.7
55°	353.2	367.6	395.6	446.3	535.5	596.0	663.4	757.9	718.6	602.1	511.3
57.5°	316.9	332.1	360.8	403.2	487.1	546.1	599.8	674.0	615.0	521.9	441.7
60°	284.4	297.3	319.2	360.8	437.2	484.9	534.0	584.7	535.5	445.5	384.3
62.5°	250.4	262.5	282.9	320.7	386.5	428.9	468.2	509.8	455.4	389.5	335.1
65°	218.6	228.4	247.3	282.1	335.8	370.6	402.4	431.1	387.3	326.8	285.9
67.5°	189.9	198.2	214.1	245.1	290.5	315.4	341.1	365.3	328.3	279.9	245.1
70°	158.8	165.7	180.0	202.7	239.0	264.7	283.7	301.8	268.5	229.9	206.5
72.5°	131.6	138.4	147.5	170.9	195.9	211.8	232.2	242.0	223.1	191.4	167.9
75°	105.1	110.4	118.8	133.9	157.3	167.9	180.8	188.3	170.9	149.8	135.4
77.5°	82.4	84.7	90.8	101.4	117.2	129.3	139.2	143.7	131.6	118.0	105.9
80°	58.2	61.3	65.8	74.9	87.0	90.8	96.8	102.1	94.6	82.4	74.9
82.5°	38.6	42.4	44.6	48.4	56.0	60.5	62.0	66.6	59.8	55.2	52.2
85°	22.7	24.2	25.0	27.2	31.0	33.3	35.6	36.3	34.8	34.0	31.0
87.5°	11.3	11.3	11.3	12.9	13.6	15.1	15.9	15.9	15.9	15.1	14.4
90°	1.2	3.8	6.3	8.9	11.4	12.7	14.4	17.7	21.0	24.3	27.6
92.5°	26.5	25.0	23.4	21.9	20.4	19.6	20.7	23.0	25.3	27.6	29.9
95°	70.2	59.7	49.2	38.7	28.2	23.0	24.4	27.2	30.1	32.9	35.7
97.5°	127.8	120.6	113.4	106.3	99.1	95.5	89.0	75.9	62.9	49.8	36.8
100°	194.5	199.6	204.7	209.8	214.9	217.5	197.6	157.7	117.8	77.9	38.0
102.5°	270.5	273.8	277.1	280.4	283.7	285.4	263.2	218.7	174.2	129.7	85.2
105°	343.0	345.8	348.6	351.5	354.3	355.7	344.2	321.2	298.1	275.1	252.1
107.5°	420.1	422.4	424.7	427.0	429.3	430.5	432.4	436.2	440.1	443.9	447.7
110°	497.2	499.2	501.3	503.3	505.4	506.4	507.8	510.6	513.5	516.3	519.1

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	570.9	572.7	574.5	576.2	578.0	578.9	580.3	583.1	586.0	588.8	591.6
115°	643.4	644.9	646.5	648.0	649.5	650.3	651.5	653.8	656.1	658.4	660.7
117.5°	714.8	716.6	718.4	720.1	721.9	722.8	723.4	724.7	726.0	727.3	728.6
120°	780.4	782.7	785.0	787.3	789.6	790.7	791.1	791.9	792.6	793.4	794.2
122.5°	847.1	848.9	850.7	852.5	854.3	855.2	855.7	856.7	857.8	858.8	859.8
125°	907.0	909.0	911.1	913.1	915.2	916.2	916.7	917.7	918.8	919.8	920.8
127.5°	966.8	968.8	970.9	972.9	975.0	976.0	976.6	977.9	979.2	980.5	981.8
130°	1022.1	1024.1	1026.2	1028.2	1030.3	1031.3	1031.8	1032.8	1033.9	1034.9	1035.9
132.5°	1075.0	1077.0	1079.1	1081.1	1083.2	1084.2	1084.6	1085.4	1086.1	1086.9	1087.7
135°	1129.1	1130.6	1132.2	1133.7	1135.2	1136.0	1136.5	1137.5	1138.6	1139.6	1140.6
137.5°	1175.1	1177.2	1179.2	1181.3	1183.4	1184.4	1184.7	1185.2	1185.7	1186.2	1186.7
140°	1221.2	1222.7	1224.3	1225.8	1227.3	1228.1	1228.5	1229.2	1230.0	1230.7	1231.5
142.5°	1263.8	1265.3	1266.9	1268.4	1269.9	1270.7	1271.1	1271.8	1272.6	1273.3	1274.1
145°	1302.9	1304.7	1306.5	1308.3	1310.1	1311.0	1311.3	1311.8	1312.3	1312.8	1313.3
147.5°	1340.9	1342.2	1343.4	1344.7	1346.0	1346.6	1346.9	1347.4	1347.9	1348.4	1348.9
150°	1375.4	1376.2	1377.0	1377.7	1378.5	1378.9	1379.2	1379.7	1380.2	1380.7	1381.2
152.5°	1406.5	1406.7	1407.0	1407.2	1407.5	1407.6	1407.7	1408.0	1408.3	1408.5	1408.8
155°	1435.3	1434.8	1434.3	1433.8	1433.3	1433.0	1433.1	1433.4	1433.6	1433.9	1434.1
157.5°	1458.3	1458.3	1458.3	1458.3	1458.3	1458.3	1458.2	1457.9	1457.6	1457.4	1457.1
160°	1479.0	1478.8	1478.5	1478.3	1478.0	1477.9	1477.8	1477.5	1477.2	1477.0	1476.7
162.5°	1498.6	1497.8	1497.0	1496.3	1495.5	1495.1	1495.0	1494.7	1494.5	1494.2	1494.0
165°	1513.5	1512.7	1512.0	1511.2	1510.5	1510.1	1510.0	1509.7	1509.4	1509.2	1508.9
167.5°	1526.2	1525.2	1524.2	1523.1	1522.1	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6
170°	1536.6	1535.6	1534.5	1533.5	1532.4	1531.9	1531.9	1531.9	1531.9	1531.9	1531.9
172.5°	1543.5	1542.2	1540.9	1539.6	1538.3	1537.7	1537.8	1538.1	1538.4	1538.6	1538.9
175°	1549.2	1547.9	1546.7	1545.4	1544.1	1543.5	1543.6	1543.9	1544.1	1544.4	1544.6
177.5°	1551.5	1550.2	1549.0	1547.7	1546.4	1545.8	1545.9	1546.2	1546.4	1546.7	1546.9
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	822.2	823.7	829.0	832.8	840.4	839.6	839.6	838.9	836.6	840.4	842.6
5°	879.7	892.6	894.1	910.7	911.5	918.3	922.8	919.0	928.1	927.4	920.5
7.5°	950.8	968.2	976.5	992.4	1010.6	1006.0	1023.4	1026.4	1024.9	1032.5	1037.8
10°	1028.7	1059.0	1080.1	1109.6	1117.2	1121.7	1133.1	1142.9	1162.6	1147.5	1157.3
12.5°	1118.0	1139.9	1167.9	1214.8	1238.2	1253.4	1258.7	1265.5	1279.1	1270.8	1271.5
15°	1192.8	1222.3	1270.0	1328.2	1335.1	1354.0	1349.4	1390.3	1409.9	1380.4	1397.1
17.5°	1270.8	1310.1	1366.8	1417.5	1446.2	1459.1	1471.2	1510.5	1509.0	1504.5	1508.3
20°	1320.7	1385.0	1455.3	1522.6	1531.0	1540.8	1573.3	1590.0	1586.9	1599.8	1608.1
22.5°	1391.0	1459.1	1534.0	1578.6	1597.5	1608.9	1634.6	1645.2	1649.7	1652.7	1647.4
25°	1450.0	1522.6	1577.9	1617.2	1628.5	1634.6	1642.9	1645.9	1643.7	1638.4	1642.9
27.5°	1490.1	1548.4	1586.2	1604.3	1598.3	1588.4	1572.6	1562.0	1538.5	1527.2	1540.8
30°	1506.8	1532.5	1543.8	1513.6	1483.3	1459.1	1428.8	1372.9	1329.0	1341.9	1324.5
32.5°	1480.3	1463.6	1409.2	1331.3	1307.8	1268.5	1183.0	1117.2	1119.5	1084.7	1099.1
35°	1402.4	1326.7	1223.9	1105.9	1074.8	1053.7	959.9	945.5	915.2	882.7	891.8
37.5°	1264.7	1154.3	1029.5	942.5	896.3	850.2	797.2	765.5	747.3	733.7	744.3
40°	1096.8	962.1	859.3	781.4	742.0	712.5	676.2	644.5	624.0	621.8	625.5
42.5°	931.9	818.4	723.9	649.8	636.9	602.1	578.6	553.7	547.6	537.8	543.1
45°	788.9	696.6	618.7	558.2	543.1	534.0	505.3	489.4	482.6	476.5	485.6
47.5°	685.3	588.5	531.8	495.4	480.3	465.2	449.3	438.7	433.4	434.2	433.4
50°	585.5	514.4	464.4	436.4	427.4	416.8	403.9	397.1	394.8	388.0	393.3
52.5°	503.8	452.3	417.5	391.1	384.3	376.7	366.1	362.3	357.0	355.5	355.5
55°	438.0	397.9	369.9	352.5	344.2	338.1	332.1	327.5	323.7	323.7	323.7
57.5°	386.5	351.7	331.3	316.2	313.2	307.1	300.3	300.3	295.0	294.2	296.5
60°	342.7	311.6	295.8	282.9	278.4	276.8	270.0	270.0	268.5	264.7	267.8
62.5°	298.0	275.3	261.7	251.9	247.3	247.3	242.0	238.3	238.3	239.0	237.5
65°	257.2	240.5	228.4	220.9	218.6	215.6	214.8	211.8	209.5	210.3	209.5
67.5°	220.9	208.0	199.7	193.6	189.9	188.3	186.1	186.1	184.6	185.3	181.5
70°	188.3	175.5	168.7	162.6	161.1	161.1	158.1	158.8	157.3	159.6	158.1
72.5°	155.1	145.2	139.9	137.7	136.2	135.4	133.9	132.4	131.6	133.1	132.4
75°	125.6	117.2	113.5	111.9	110.4	110.4	109.7	108.9	108.2	108.2	108.2
77.5°	97.6	92.3	87.7	89.3	87.0	87.7	85.5	85.5	86.2	85.5	85.5
80°	71.9	68.1	68.1	66.6	63.5	65.1	65.1	62.8	62.0	63.5	61.3
82.5°	47.7	46.9	45.4	44.6	43.1	43.9	43.1	42.4	41.6	43.1	41.6
85°	28.0	28.0	27.2	25.7	27.2	26.5	25.7	25.7	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.3	12.1	11.3	10.6	11.3	10.6
90°	28.6	29.6	30.7	31.7	32.2	32.5	33.0	33.5	34.0	34.5	34.0
92.5°	31.7	33.5	35.3	37.1	38.0	38.1	38.4	38.6	38.9	39.1	38.9
95°	37.5	39.3	41.0	42.8	43.7	43.7	43.7	43.7	43.7	43.7	43.7
97.5°	38.8	40.9	42.9	45.0	46.0	46.1	46.4	46.7	46.9	47.2	46.9
100°	40.0	42.1	44.1	46.2	47.2	47.3	47.6	47.8	48.1	48.3	48.1
102.5°	76.8	68.3	59.9	51.4	47.2	47.5	48.0	48.5	49.0	49.5	49.0
105°	206.8	161.5	116.2	70.9	48.3	48.6	49.1	49.6	50.1	50.6	50.1
107.5°	408.3	368.9	329.6	290.2	270.5	253.7	220.2	186.7	153.2	119.7	153.2
110°	510.7	502.2	493.8	485.3	481.1	462.8	426.2	389.7	353.1	316.5	353.1

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	593.9	596.2	598.5	600.8	602.0	601.7	601.2	600.7	600.2	599.7	600.2
115°	663.3	665.8	668.4	670.9	672.2	672.7	673.7	674.8	675.8	676.8	675.8
117.5°	730.6	732.7	734.7	736.8	737.8	737.9	738.2	738.4	738.7	738.9	738.7
120°	796.2	798.3	800.3	802.4	803.4	803.4	803.4	803.4	803.4	803.4	803.4
122.5°	861.1	862.3	863.6	864.9	865.5	865.6	865.9	866.2	866.4	866.7	866.4
125°	921.3	921.8	922.3	922.8	923.1	923.4	923.9	924.4	924.9	925.4	924.9
127.5°	982.6	983.3	984.1	984.8	985.2	984.9	984.4	983.9	983.4	982.9	983.4
130°	1036.9	1037.9	1039.0	1040.0	1040.5	1040.2	1039.7	1039.2	1038.7	1038.2	1038.7
132.5°	1088.7	1089.7	1090.8	1091.8	1092.3	1091.9	1091.1	1090.4	1089.6	1088.8	1089.6
135°	1141.4	1142.2	1142.9	1143.7	1144.1	1143.7	1142.9	1142.2	1141.4	1140.6	1141.4
137.5°	1188.0	1189.2	1190.5	1191.8	1192.4	1192.1	1191.6	1191.1	1190.6	1190.1	1190.6
140°	1232.5	1233.5	1234.6	1235.6	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3
142.5°	1274.9	1275.7	1276.4	1277.2	1277.6	1277.2	1276.4	1275.7	1274.9	1274.1	1274.9
145°	1313.8	1314.3	1314.8	1315.3	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6
147.5°	1349.4	1349.9	1350.4	1350.9	1351.2	1350.6	1349.3	1348.0	1346.8	1345.5	1346.8
150°	1381.7	1382.2	1382.7	1383.2	1383.5	1383.1	1382.3	1381.6	1380.8	1380.0	1380.8
152.5°	1409.8	1410.8	1411.9	1412.9	1413.4	1412.8	1411.5	1410.2	1408.9	1407.6	1408.9
155°	1435.4	1436.7	1438.0	1439.3	1439.9	1439.1	1437.6	1436.1	1434.5	1433.0	1434.5
157.5°	1458.6	1460.2	1461.7	1463.2	1464.0	1463.0	1460.9	1458.9	1456.8	1454.8	1456.8
160°	1478.2	1479.8	1481.3	1482.8	1483.6	1482.7	1480.9	1479.2	1477.4	1475.6	1477.4
162.5°	1495.8	1497.6	1499.3	1501.1	1502.0	1501.2	1499.7	1498.2	1496.6	1495.1	1496.6
165°	1510.9	1513.0	1515.0	1517.1	1518.1	1517.2	1515.4	1513.7	1511.9	1510.1	1511.9
167.5°	1523.6	1525.7	1527.7	1529.8	1530.8	1529.8	1527.7	1525.7	1523.6	1521.6	1523.6
170°	1534.0	1536.0	1538.1	1540.2	1541.2	1540.2	1538.1	1536.0	1534.0	1531.9	1534.0
172.5°	1540.9	1543.0	1545.0	1547.1	1548.1	1546.9	1544.6	1542.3	1540.0	1537.7	1540.0
175°	1546.4	1548.2	1550.0	1551.8	1552.7	1551.7	1549.6	1547.6	1545.5	1543.5	1545.5
177.5°	1548.9	1551.0	1553.0	1555.1	1556.1	1554.8	1552.3	1549.7	1547.2	1544.6	1547.2
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	836.6	838.9	832.8	831.3	831.3	834.3	832.0	811.6	815.4	810.9	809.4
5°	928.9	924.3	918.3	915.2	911.5	900.9	900.1	876.7	872.1	857.0	850.2
7.5°	1030.2	1026.4	1008.3	1006.0	1004.5	994.7	969.7	944.7	926.6	909.2	892.6
10°	1146.0	1134.6	1126.3	1109.6	1101.3	1087.7	1055.2	1031.7	1000.7	974.2	939.5
12.5°	1285.1	1272.3	1244.3	1232.2	1221.6	1183.8	1151.2	1124.8	1064.3	1046.1	1003.0
15°	1387.2	1360.0	1357.0	1330.5	1329.0	1287.4	1225.4	1196.6	1149.7	1083.2	1038.5
17.5°	1497.7	1473.5	1454.6	1422.8	1418.3	1378.9	1333.5	1263.2	1211.8	1148.2	1091.5
20°	1578.6	1565.8	1533.2	1520.4	1493.9	1460.6	1413.7	1326.7	1263.9	1200.4	1130.8
22.5°	1642.9	1630.0	1604.3	1586.9	1571.8	1528.7	1472.7	1398.6	1312.4	1229.2	1157.3
25°	1642.2	1638.4	1627.8	1619.5	1608.1	1576.3	1529.4	1458.3	1362.3	1270.8	1170.9
27.5°	1549.1	1559.7	1577.9	1586.9	1584.7	1580.1	1553.7	1493.9	1407.7	1298.7	1186.8
30°	1355.5	1394.1	1428.1	1473.5	1487.1	1520.4	1535.5	1501.5	1432.6	1331.3	1207.2
32.5°	1124.0	1180.0	1254.1	1279.1	1322.2	1386.5	1458.3	1471.2	1428.1	1350.2	1220.1
35°	922.1	968.2	1025.7	1065.0	1103.6	1208.0	1298.7	1377.4	1391.8	1340.3	1217.1
37.5°	763.2	795.7	846.4	879.7	915.2	1004.5	1131.6	1233.7	1305.6	1307.1	1208.7
40°	648.2	662.6	706.5	730.7	764.7	841.9	955.3	1088.5	1193.6	1242.0	1186.8
42.5°	549.1	568.1	604.4	622.5	644.5	711.8	786.7	913.0	1043.1	1146.7	1146.0
45°	490.1	503.8	520.4	535.5	560.5	600.6	686.1	780.6	905.4	1022.7	1068.8
47.5°	438.0	450.8	467.5	472.0	488.6	526.5	578.6	661.1	777.6	894.1	981.1
50°	394.1	404.7	416.0	424.3	431.9	462.9	502.3	571.8	664.9	777.6	885.7
52.5°	360.0	367.6	377.4	382.0	388.8	411.5	441.7	493.2	569.6	672.4	777.6
55°	328.3	333.6	339.6	347.2	350.2	366.9	390.3	434.2	490.9	583.2	683.0
57.5°	298.8	301.0	304.8	309.4	313.2	327.5	347.9	377.4	427.4	498.5	593.0
60°	265.5	271.5	273.8	278.4	280.6	292.0	307.9	332.8	371.4	432.7	503.8
62.5°	237.5	241.3	245.1	247.3	252.6	256.4	269.3	292.0	323.7	369.1	433.4
65°	212.5	214.1	216.3	218.6	220.1	224.7	236.8	251.9	276.1	316.2	366.1
67.5°	183.8	185.3	188.3	189.1	190.6	196.7	203.5	216.3	236.8	267.0	307.9
70°	155.8	158.1	159.6	161.1	163.4	165.7	173.2	183.8	199.7	220.9	252.6
72.5°	131.6	133.9	133.9	135.4	134.6	137.7	145.2	152.8	163.4	180.8	208.8
75°	107.4	107.4	108.9	109.7	110.4	113.5	116.5	122.5	130.9	144.5	161.9
77.5°	84.7	84.0	85.5	85.5	85.5	87.7	90.8	93.8	99.1	108.9	122.5
80°	62.0	62.0	63.5	64.3	62.8	63.5	65.1	68.1	71.9	78.7	86.2
82.5°	40.8	43.9	43.1	43.9	43.1	44.6	45.4	46.1	47.7	50.7	56.0
85°	25.0	25.0	25.0	25.7	25.0	25.7	25.7	25.7	26.5	28.0	30.3
87.5°	10.6	10.6	10.6	11.3	10.6	10.6	11.3	10.6	11.3	11.3	12.1
90°	33.5	33.0	32.5	32.2	31.7	30.7	29.6	28.6	27.6	24.3	21.0
92.5°	38.6	38.4	38.1	38.0	37.1	35.3	33.5	31.7	29.9	27.6	25.3
95°	43.7	43.7	43.7	43.7	42.8	41.0	39.3	37.5	35.7	32.9	30.1
97.5°	46.7	46.4	46.1	46.0	45.0	42.9	40.9	38.8	36.8	49.8	62.9
100°	47.8	47.6	47.3	47.2	46.2	44.1	42.1	40.0	38.0	77.9	117.8
102.5°	48.5	48.0	47.5	47.2	51.4	59.9	68.3	76.8	85.2	129.7	174.2
105°	49.6	49.1	48.6	48.3	70.9	116.2	161.5	206.8	252.1	275.1	298.1
107.5°	186.7	220.2	253.7	270.5	290.2	329.6	368.9	408.3	447.7	443.9	440.1
110°	389.7	426.2	462.8	481.1	485.3	493.8	502.2	510.7	519.1	516.3	513.5

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	600.7	601.2	601.7	602.0	600.8	598.5	596.2	593.9	591.6	588.8	586.0
115°	674.8	673.7	672.7	672.2	670.9	668.4	665.8	663.3	660.7	658.4	656.1
117.5°	738.4	738.2	737.9	737.8	736.8	734.7	732.7	730.6	728.6	727.3	726.0
120°	803.4	803.4	803.4	803.4	802.4	800.3	798.3	796.2	794.2	793.4	792.6
122.5°	866.2	865.9	865.6	865.5	864.9	863.6	862.3	861.1	859.8	858.8	857.8
125°	924.4	923.9	923.4	923.1	922.8	922.3	921.8	921.3	920.8	919.8	918.8
127.5°	983.9	984.4	984.9	985.2	984.8	984.1	983.3	982.6	981.8	980.5	979.2
130°	1039.2	1039.7	1040.2	1040.5	1040.0	1039.0	1037.9	1036.9	1035.9	1034.9	1033.9
132.5°	1090.4	1091.1	1091.9	1092.3	1091.8	1090.8	1089.7	1088.7	1087.7	1086.9	1086.1
135°	1142.2	1142.9	1143.7	1144.1	1143.7	1142.9	1142.2	1141.4	1140.6	1139.6	1138.6
137.5°	1191.1	1191.6	1192.1	1192.4	1191.8	1190.5	1189.2	1188.0	1186.7	1186.2	1185.7
140°	1234.8	1235.3	1235.8	1236.1	1235.6	1234.6	1233.5	1232.5	1231.5	1230.7	1230.0
142.5°	1275.7	1276.4	1277.2	1277.6	1277.2	1276.4	1275.7	1274.9	1274.1	1273.3	1272.6
145°	1315.6	1315.6	1315.6	1315.6	1315.3	1314.8	1314.3	1313.8	1313.3	1312.8	1312.3
147.5°	1348.0	1349.3	1350.6	1351.2	1350.9	1350.4	1349.9	1349.4	1348.9	1348.4	1347.9
150°	1381.6	1382.3	1383.1	1383.5	1383.2	1382.7	1382.2	1381.7	1381.2	1380.7	1380.2
152.5°	1410.2	1411.5	1412.8	1413.4	1412.9	1411.9	1410.8	1409.8	1408.8	1408.5	1408.3
155°	1436.1	1437.6	1439.1	1439.9	1439.3	1438.0	1436.7	1435.4	1434.1	1433.9	1433.6
157.5°	1458.9	1460.9	1463.0	1464.0	1463.2	1461.7	1460.2	1458.6	1457.1	1457.4	1457.6
160°	1479.2	1480.9	1482.7	1483.6	1482.8	1481.3	1479.8	1478.2	1476.7	1477.0	1477.2
162.5°	1498.2	1499.7	1501.2	1502.0	1501.1	1499.3	1497.6	1495.8	1494.0	1494.2	1494.5
165°	1513.7	1515.4	1517.2	1518.1	1517.1	1515.0	1513.0	1510.9	1508.9	1509.2	1509.4
167.5°	1525.7	1527.7	1529.8	1530.8	1529.8	1527.7	1525.7	1523.6	1521.6	1521.6	1521.6
170°	1536.0	1538.1	1540.2	1541.2	1540.2	1538.1	1536.0	1534.0	1531.9	1531.9	1531.9
172.5°	1542.3	1544.6	1546.9	1548.1	1547.1	1545.0	1543.0	1540.9	1538.9	1538.6	1538.4
175°	1547.6	1549.6	1551.7	1552.7	1551.8	1550.0	1548.2	1546.4	1544.6	1544.4	1544.1
177.5°	1549.7	1552.3	1554.8	1556.1	1555.1	1553.0	1551.0	1548.9	1546.9	1546.7	1546.4
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	801.8	799.5	799.5	798.0	793.5	785.1	784.4	785.9	781.4	776.8	770.0
5°	841.1	826.7	822.2	817.7	808.6	793.5	787.4	782.1	773.8	764.0	753.4
7.5°	874.4	854.0	847.9	839.6	821.5	800.3	786.7	775.3	764.0	750.4	737.5
10°	916.0	886.5	872.1	860.0	835.1	805.6	785.1	768.5	750.4	733.7	717.1
12.5°	962.9	915.2	910.7	881.2	852.5	808.6	783.6	759.4	735.2	714.8	697.4
15°	1002.2	950.0	931.1	911.5	856.2	801.8	777.6	750.4	722.4	700.4	674.7
17.5°	1027.2	984.1	944.0	917.5	860.0	811.6	764.7	733.7	704.2	674.0	652.8
20°	1057.5	994.7	959.9	924.3	867.6	804.1	757.2	718.6	682.3	655.0	629.3
22.5°	1087.7	1003.0	974.2	935.7	869.1	796.5	743.5	705.0	663.4	636.1	608.1
25°	1084.7	1015.1	967.4	934.9	854.0	789.7	727.7	682.3	643.7	608.9	580.9
27.5°	1087.0	1001.5	953.1	915.2	843.4	779.9	711.0	663.4	623.3	587.0	557.5
30°	1087.7	981.1	938.7	893.3	823.7	756.4	692.1	643.7	601.3	562.0	535.5
32.5°	1085.4	964.4	911.5	870.6	792.7	733.7	670.2	618.7	575.6	539.3	514.4
35°	1080.1	944.7	883.5	832.0	760.9	701.2	649.8	596.8	550.7	517.4	488.6
37.5°	1065.8	923.6	854.0	803.3	723.9	663.4	618.0	574.1	529.5	490.1	465.9
40°	1055.2	894.8	824.5	769.3	683.8	624.8	587.0	545.4	501.5	465.9	442.5
42.5°	1031.0	867.6	794.2	728.4	644.5	583.9	548.4	515.1	477.3	442.5	421.3
45°	991.6	838.1	757.2	690.6	601.3	543.9	511.3	484.1	450.8	417.5	396.4
47.5°	936.4	795.7	717.8	651.3	559.0	500.7	468.2	447.8	421.3	393.3	375.2
50°	876.7	749.6	677.7	611.9	518.1	461.4	429.6	410.7	393.3	367.6	350.2
52.5°	798.8	700.4	631.6	568.8	474.3	419.8	391.8	378.2	360.0	341.9	326.8
55°	723.1	636.9	580.2	520.4	431.1	380.5	353.2	338.9	328.3	313.2	301.0
57.5°	635.4	577.9	525.7	471.2	391.1	344.9	319.2	301.8	295.0	288.2	276.8
60°	554.4	510.6	468.2	422.8	349.5	307.9	282.9	269.3	262.5	257.9	250.4
62.5°	480.3	446.3	410.0	373.7	307.1	269.3	250.4	236.8	230.7	229.9	223.1
65°	409.2	385.0	355.5	320.0	267.8	234.5	216.3	208.0	201.2	201.2	195.9
67.5°	338.1	321.5	298.0	273.1	232.2	201.2	184.6	177.0	173.2	173.2	169.4
70°	281.4	270.0	248.9	226.9	191.4	167.9	155.1	148.3	146.0	146.7	143.7
72.5°	228.4	216.3	198.9	183.0	156.6	139.2	130.1	122.5	118.8	119.5	118.8
75°	177.0	170.9	155.8	143.7	122.5	110.4	102.1	98.3	95.3	96.1	94.6
77.5°	133.1	124.1	115.7	107.4	94.6	84.7	77.9	74.1	71.9	71.9	71.9
80°	90.8	89.3	82.4	77.9	67.3	59.8	54.5	53.7	51.4	51.4	51.4
82.5°	59.0	55.2	51.4	48.4	42.4	37.8	35.6	34.0	33.3	32.5	34.0
85°	32.5	30.3	28.7	25.7	23.4	21.2	18.9	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.8	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	17.7	14.4	12.7	11.4	8.9	6.3	3.8	1.2	3.8	6.3	8.9
92.5°	23.0	20.7	19.6	20.4	21.9	23.4	25.0	26.5	25.0	23.4	21.9
95°	27.2	24.4	23.0	28.2	38.7	49.2	59.7	70.2	59.7	49.2	38.7
97.5°	75.9	89.0	95.5	99.1	106.3	113.4	120.6	127.8	120.6	113.4	106.3
100°	157.7	197.6	217.5	214.9	209.8	204.7	199.6	194.5	199.6	204.7	209.8
102.5°	218.7	263.2	285.4	283.7	280.4	277.1	273.8	270.5	273.8	277.1	280.4
105°	321.2	344.2	355.7	354.3	351.5	348.6	345.8	343.0	345.8	348.6	351.5
107.5°	436.2	432.4	430.5	429.3	427.0	424.7	422.4	420.1	422.4	424.7	427.0
110°	510.6	507.8	506.4	505.4	503.3	501.3	499.2	497.2	499.2	501.3	503.3

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	583.1	580.3	578.9	578.0	576.2	574.5	572.7	570.9	572.7	574.5	576.2
115°	653.8	651.5	650.3	649.5	648.0	646.5	644.9	643.4	644.9	646.5	648.0
117.5°	724.7	723.4	722.8	721.9	720.1	718.4	716.6	714.8	716.6	718.4	720.1
120°	791.9	791.1	790.7	789.6	787.3	785.0	782.7	780.4	782.7	785.0	787.3
122.5°	856.7	855.7	855.2	854.3	852.5	850.7	848.9	847.1	848.9	850.7	852.5
125°	917.7	916.7	916.2	915.2	913.1	911.1	909.0	907.0	909.0	911.1	913.1
127.5°	977.9	976.6	976.0	975.0	972.9	970.9	968.8	966.8	968.8	970.9	972.9
130°	1032.8	1031.8	1031.3	1030.3	1028.2	1026.2	1024.1	1022.1	1024.1	1026.2	1028.2
132.5°	1085.4	1084.6	1084.2	1083.2	1081.1	1079.1	1077.0	1075.0	1077.0	1079.1	1081.1
135°	1137.5	1136.5	1136.0	1135.2	1133.7	1132.2	1130.6	1129.1	1130.6	1132.2	1133.7
137.5°	1185.2	1184.7	1184.4	1183.4	1181.3	1179.2	1177.2	1175.1	1177.2	1179.2	1181.3
140°	1229.2	1228.5	1228.1	1227.3	1225.8	1224.3	1222.7	1221.2	1222.7	1224.3	1225.8
142.5°	1271.8	1271.1	1270.7	1269.9	1268.4	1266.9	1265.3	1263.8	1265.3	1266.9	1268.4
145°	1311.8	1311.3	1311.0	1310.1	1308.3	1306.5	1304.7	1302.9	1304.7	1306.5	1308.3
147.5°	1347.4	1346.9	1346.6	1346.0	1344.7	1343.4	1342.2	1340.9	1342.2	1343.4	1344.7
150°	1379.7	1379.2	1378.9	1378.5	1377.7	1377.0	1376.2	1375.4	1376.2	1377.0	1377.7
152.5°	1408.0	1407.7	1407.6	1407.5	1407.2	1407.0	1406.7	1406.5	1406.7	1407.0	1407.2
155°	1433.4	1433.1	1433.0	1433.3	1433.8	1434.3	1434.8	1435.3	1434.8	1434.3	1433.8
157.5°	1457.9	1458.2	1458.3	1458.3	1458.3	1458.3	1458.3	1458.3	1458.3	1458.3	1458.3
160°	1477.5	1477.8	1477.9	1478.0	1478.3	1478.5	1478.8	1479.0	1478.8	1478.5	1478.3
162.5°	1494.7	1495.0	1495.1	1495.5	1496.3	1497.0	1497.8	1498.6	1497.8	1497.0	1496.3
165°	1509.7	1510.0	1510.1	1510.5	1511.2	1512.0	1512.7	1513.5	1512.7	1512.0	1511.2
167.5°	1521.6	1521.6	1521.6	1522.1	1523.1	1524.2	1525.2	1526.2	1525.2	1524.2	1523.1
170°	1531.9	1531.9	1531.9	1532.4	1533.5	1534.5	1535.6	1536.6	1535.6	1534.5	1533.5
172.5°	1538.1	1537.8	1537.7	1538.3	1539.6	1540.9	1542.2	1543.5	1542.2	1540.9	1539.6
175°	1543.9	1543.6	1543.5	1544.1	1545.4	1546.7	1547.9	1549.2	1547.9	1546.7	1545.4
177.5°	1546.2	1545.9	1545.8	1546.4	1547.7	1549.0	1550.2	1551.5	1550.2	1549.0	1547.7
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	768.5	767.7	769.3	764.7	757.2	753.4	742.8	740.5	739.8	740.5	741.3
5°	747.3	746.6	744.3	736.7	727.7	720.9	708.0	707.2	702.7	698.2	700.4
7.5°	726.9	723.9	719.3	709.5	697.4	689.8	679.2	671.7	665.6	661.9	658.8
10°	706.5	701.9	697.4	684.5	669.4	658.1	645.2	639.2	632.4	629.3	626.3
12.5°	680.0	675.5	667.1	652.0	642.9	628.6	615.7	609.7	605.9	599.8	596.0
15°	658.8	649.8	645.2	629.3	610.4	608.9	585.5	583.9	576.4	576.4	570.3
17.5°	634.6	627.8	619.5	603.6	590.0	576.4	564.3	559.7	552.9	551.4	548.4
20°	611.2	602.1	599.1	583.2	568.8	552.2	539.3	534.8	531.8	528.7	531.0
22.5°	587.0	579.4	571.8	557.5	546.9	530.2	522.7	518.1	513.6	512.1	512.8
25°	563.5	556.7	549.1	534.8	523.4	509.8	503.0	500.7	498.5	498.5	497.7
27.5°	540.8	534.0	527.2	514.4	503.0	493.2	487.9	485.6	483.3	484.9	486.4
30°	517.4	511.3	505.3	493.9	484.9	475.8	472.8	471.2	470.5	474.3	474.3
32.5°	496.2	490.9	486.4	475.8	466.7	459.1	456.9	457.6	458.4	460.6	462.2
35°	474.3	470.5	465.9	456.9	449.3	442.5	443.3	443.3	444.8	448.5	451.6
37.5°	454.6	449.3	445.5	438.0	431.9	425.9	428.1	430.4	431.9	436.4	438.0
40°	431.1	428.9	425.9	418.3	413.0	412.2	413.0	414.5	417.5	419.8	422.1
42.5°	412.2	409.2	405.4	399.4	394.8	395.6	396.4	397.9	399.4	403.2	405.4
45°	391.1	388.8	385.8	380.5	376.7	377.4	378.2	378.2	379.7	384.3	385.8
47.5°	367.6	368.4	364.6	359.3	357.0	357.0	357.0	358.5	362.3	363.8	364.6
50°	344.9	343.4	342.7	337.4	335.8	335.1	335.8	336.6	341.9	341.1	343.4
52.5°	320.7	320.7	320.0	316.9	314.7	314.7	313.2	316.9	318.4	320.0	322.2
55°	297.3	295.0	294.2	292.7	289.7	288.9	290.5	295.0	296.5	298.0	300.3
57.5°	271.5	271.5	270.0	267.8	267.8	267.8	267.8	270.8	273.1	274.6	279.1
60°	248.1	245.1	242.8	242.8	242.8	242.0	246.6	246.6	251.1	251.9	253.4
62.5°	220.1	218.6	217.1	217.8	217.1	218.6	220.1	223.1	223.9	226.2	228.4
65°	193.6	193.6	192.1	196.7	193.6	193.6	197.4	197.4	198.9	201.2	204.2
67.5°	167.9	168.7	167.2	167.2	168.7	169.4	170.2	173.2	174.0	177.0	180.8
70°	141.4	143.0	143.7	142.2	143.7	145.2	146.7	147.5	150.5	152.0	154.3
72.5°	118.0	119.5	117.2	118.0	118.8	120.3	121.0	122.5	124.1	128.6	130.1
75°	94.6	93.8	93.0	96.1	94.6	97.6	98.3	98.3	99.8	103.6	105.1
77.5°	72.6	72.6	73.4	71.9	74.1	73.4	74.1	76.4	78.7	78.7	84.7
80°	50.7	52.2	52.2	52.2	52.9	53.7	52.2	56.0	56.7	56.7	59.0
82.5°	32.5	33.3	32.5	34.0	34.0	35.6	34.8	35.6	37.1	38.6	39.3
85°	17.4	17.4	18.9	18.9	18.2	18.9	18.2	18.9	20.4	20.4	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	11.4	12.7	14.4	17.7	21.0	24.3	27.6	28.6	29.6	30.7	31.7
92.5°	20.4	19.6	20.7	23.0	25.3	27.6	29.9	31.7	33.5	35.3	37.1
95°	28.2	23.0	24.4	27.2	30.1	32.9	35.7	37.5	39.3	41.0	42.8
97.5°	99.1	95.5	89.0	75.9	62.9	49.8	36.8	38.8	40.9	42.9	45.0
100°	214.9	217.5	197.6	157.7	117.8	77.9	38.0	40.0	42.1	44.1	46.2
102.5°	283.7	285.4	263.2	218.7	174.2	129.7	85.2	76.8	68.3	59.9	51.4
105°	354.3	355.7	344.2	321.2	298.1	275.1	252.1	206.8	161.5	116.2	70.9
107.5°	429.3	430.5	432.4	436.2	440.1	443.9	447.7	408.3	368.9	329.6	290.2
110°	505.4	506.4	507.8	510.6	513.5	516.3	519.1	510.7	502.2	493.8	485.3

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	578.0	578.9	580.3	583.1	586.0	588.8	591.6	593.9	596.2	598.5	600.8
115°	649.5	650.3	651.5	653.8	656.1	658.4	660.7	663.3	665.8	668.4	670.9
117.5°	721.9	722.8	723.4	724.7	726.0	727.3	728.6	730.6	732.7	734.7	736.8
120°	789.6	790.7	791.1	791.9	792.6	793.4	794.2	796.2	798.3	800.3	802.4
122.5°	854.3	855.2	855.7	856.7	857.8	858.8	859.8	861.1	862.3	863.6	864.9
125°	915.2	916.2	916.7	917.7	918.8	919.8	920.8	921.3	921.8	922.3	922.8
127.5°	975.0	976.0	976.6	977.9	979.2	980.5	981.8	982.6	983.3	984.1	984.8
130°	1030.3	1031.3	1031.8	1032.8	1033.9	1034.9	1035.9	1036.9	1037.9	1039.0	1040.0
132.5°	1083.2	1084.2	1084.6	1085.4	1086.1	1086.9	1087.7	1088.7	1089.7	1090.8	1091.8
135°	1135.2	1136.0	1136.5	1137.5	1138.6	1139.6	1140.6	1141.4	1142.2	1142.9	1143.7
137.5°	1183.4	1184.4	1184.7	1185.2	1185.7	1186.2	1186.7	1188.0	1189.2	1190.5	1191.8
140°	1227.3	1228.1	1228.5	1229.2	1230.0	1230.7	1231.5	1232.5	1233.5	1234.6	1235.6
142.5°	1269.9	1270.7	1271.1	1271.8	1272.6	1273.3	1274.1	1274.9	1275.7	1276.4	1277.2
145°	1310.1	1311.0	1311.3	1311.8	1312.3	1312.8	1313.3	1313.8	1314.3	1314.8	1315.3
147.5°	1346.0	1346.6	1346.9	1347.4	1347.9	1348.4	1348.9	1349.4	1349.9	1350.4	1350.9
150°	1378.5	1378.9	1379.2	1379.7	1380.2	1380.7	1381.2	1381.7	1382.2	1382.7	1383.2
152.5°	1407.5	1407.6	1407.7	1408.0	1408.3	1408.5	1408.8	1409.8	1410.8	1411.9	1412.9
155°	1433.3	1433.0	1433.1	1433.4	1433.6	1433.9	1434.1	1435.4	1436.7	1438.0	1439.3
157.5°	1458.3	1458.3	1458.2	1457.9	1457.6	1457.4	1457.1	1458.6	1460.2	1461.7	1463.2
160°	1478.0	1477.9	1477.8	1477.5	1477.2	1477.0	1476.7	1478.2	1479.8	1481.3	1482.8
162.5°	1495.5	1495.1	1495.0	1494.7	1494.5	1494.2	1494.0	1495.8	1497.6	1499.3	1501.1
165°	1510.5	1510.1	1510.0	1509.7	1509.4	1509.2	1508.9	1510.9	1513.0	1515.0	1517.1
167.5°	1522.1	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1523.6	1525.7	1527.7	1529.8
170°	1532.4	1531.9	1531.9	1531.9	1531.9	1531.9	1531.9	1534.0	1536.0	1538.1	1540.2
172.5°	1538.3	1537.7	1537.8	1538.1	1538.4	1538.6	1538.9	1540.9	1543.0	1545.0	1547.1
175°	1544.1	1543.5	1543.6	1543.9	1544.1	1544.4	1544.6	1546.4	1548.2	1550.0	1551.8
177.5°	1546.4	1545.8	1545.9	1546.2	1546.4	1546.7	1546.9	1548.9	1551.0	1553.0	1555.1
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	740.5	741.3	738.2	736.0	742.0	738.2	738.2	739.0	737.5	739.8	739.0
5°	698.9	699.7	694.4	695.9	692.9	692.1	691.4	695.9	695.1	694.4	695.9
7.5°	658.1	658.1	655.8	654.3	654.3	652.0	655.0	654.3	655.8	655.8	658.1
10°	624.0	625.5	621.8	618.0	617.2	618.0	618.0	618.7	619.5	624.8	624.0
12.5°	596.0	593.8	593.0	590.8	587.0	585.5	583.9	592.3	590.0	590.0	590.0
15°	565.0	570.3	569.6	562.8	561.3	564.3	562.8	562.8	570.3	569.6	568.8
17.5°	548.4	546.9	545.4	541.6	542.3	541.6	542.3	542.3	546.9	546.9	546.9
20°	529.5	526.5	526.5	524.9	524.9	522.7	525.7	526.5	529.5	529.5	530.2
22.5°	512.8	510.6	510.6	509.8	511.3	508.3	511.3	512.1	512.1	514.4	514.4
25°	498.5	497.0	497.0	498.5	498.5	498.5	498.5	501.5	499.2	500.0	499.2
27.5°	485.6	486.4	487.1	487.9	487.1	487.9	488.6	490.1	490.9	490.1	488.6
30°	473.5	475.8	476.5	476.5	478.0	478.8	479.6	479.6	480.3	478.0	479.6
32.5°	464.4	464.4	465.9	466.7	468.2	469.0	469.0	470.5	469.7	467.5	468.2
35°	451.6	451.6	454.6	456.1	458.4	457.6	458.4	458.4	459.1	457.6	455.4
37.5°	438.7	440.2	440.2	443.3	444.0	444.8	444.0	445.5	444.8	443.3	442.5
40°	423.6	422.8	423.6	425.9	426.6	426.6	426.6	428.1	428.1	428.1	427.4
42.5°	404.7	406.9	406.2	408.5	407.7	407.7	409.2	410.7	411.5	409.2	410.0
45°	386.5	386.5	388.0	388.0	388.8	388.8	391.8	390.3	391.8	390.3	391.1
47.5°	366.9	367.6	367.6	368.4	369.9	371.4	369.9	370.6	370.6	371.4	369.9
50°	344.9	344.9	346.4	348.7	351.7	350.2	349.5	352.5	350.2	350.2	348.7
52.5°	322.2	324.5	325.3	327.5	329.8	330.5	331.3	329.8	330.5	328.3	329.0
55°	300.3	301.0	304.1	306.3	308.6	308.6	307.9	308.6	309.4	306.3	306.3
57.5°	278.4	280.6	283.7	283.7	286.7	286.7	285.9	285.9	286.7	284.4	283.7
60°	254.9	257.2	261.0	261.0	265.5	266.3	264.7	263.2	263.2	261.0	261.7
62.5°	229.9	232.2	234.5	238.3	241.3	239.8	242.8	239.8	240.5	236.0	236.0
65°	208.0	208.8	212.5	216.3	216.3	217.8	216.3	217.1	214.8	214.8	211.8
67.5°	182.3	182.3	186.1	189.9	193.6	193.6	193.6	191.4	191.4	189.1	189.1
70°	159.6	158.8	162.6	164.9	167.2	167.9	166.4	165.7	164.1	161.9	161.1
72.5°	131.6	133.1	136.9	138.4	142.2	141.4	145.2	140.7	140.7	136.9	136.2
75°	106.7	108.2	111.9	114.2	116.5	116.5	118.8	116.5	113.5	111.9	111.2
77.5°	84.7	84.0	87.0	90.8	91.5	90.8	92.3	91.5	88.5	88.5	87.0
80°	60.5	62.8	65.8	65.1	68.1	67.3	67.3	65.8	65.8	63.5	65.1
82.5°	40.1	42.4	43.1	42.4	43.1	44.6	45.4	44.6	44.6	43.1	43.9
85°	21.2	21.2	22.7	23.4	22.7	22.7	23.4	25.7	24.2	22.7	24.2
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	32.2	32.5	33.0	33.5	34.0	34.5	34.0	33.5	33.0	32.5	32.2
92.5°	38.0	38.1	38.4	38.6	38.9	39.1	38.9	38.6	38.4	38.1	38.0
95°	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7	43.7
97.5°	46.0	46.1	46.4	46.7	46.9	47.2	46.9	46.7	46.4	46.1	46.0
100°	47.2	47.3	47.6	47.8	48.1	48.3	48.1	47.8	47.6	47.3	47.2
102.5°	47.2	47.5	48.0	48.5	49.0	49.5	49.0	48.5	48.0	47.5	47.2
105°	48.3	48.6	49.1	49.6	50.1	50.6	50.1	49.6	49.1	48.6	48.3
107.5°	270.5	253.7	220.2	186.7	153.2	119.7	153.2	186.7	220.2	253.7	270.5
110°	481.1	462.8	426.2	389.7	353.1	316.5	353.1	389.7	426.2	462.8	481.1

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	602.0	601.7	601.2	600.7	600.2	599.7	600.2	600.7	601.2	601.7	602.0
115°	672.2	672.7	673.7	674.8	675.8	676.8	675.8	674.8	673.7	672.7	672.2
117.5°	737.8	737.9	738.2	738.4	738.7	738.9	738.7	738.4	738.2	737.9	737.8
120°	803.4	803.4	803.4	803.4	803.4	803.4	803.4	803.4	803.4	803.4	803.4
122.5°	865.5	865.6	865.9	866.2	866.4	866.7	866.4	866.2	865.9	865.6	865.5
125°	923.1	923.4	923.9	924.4	924.9	925.4	924.9	924.4	923.9	923.4	923.1
127.5°	985.2	984.9	984.4	983.9	983.4	982.9	983.4	983.9	984.4	984.9	985.2
130°	1040.5	1040.2	1039.7	1039.2	1038.7	1038.2	1038.7	1039.2	1039.7	1040.2	1040.5
132.5°	1092.3	1091.9	1091.1	1090.4	1089.6	1088.8	1089.6	1090.4	1091.1	1091.9	1092.3
135°	1144.1	1143.7	1142.9	1142.2	1141.4	1140.6	1141.4	1142.2	1142.9	1143.7	1144.1
137.5°	1192.4	1192.1	1191.6	1191.1	1190.6	1190.1	1190.6	1191.1	1191.6	1192.1	1192.4
140°	1236.1	1235.8	1235.3	1234.8	1234.3	1233.8	1234.3	1234.8	1235.3	1235.8	1236.1
142.5°	1277.6	1277.2	1276.4	1275.7	1274.9	1274.1	1274.9	1275.7	1276.4	1277.2	1277.6
145°	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6	1315.6
147.5°	1351.2	1350.6	1349.3	1348.0	1346.8	1345.5	1346.8	1348.0	1349.3	1350.6	1351.2
150°	1383.5	1383.1	1382.3	1381.6	1380.8	1380.0	1380.8	1381.6	1382.3	1383.1	1383.5
152.5°	1413.4	1412.8	1411.5	1410.2	1408.9	1407.6	1408.9	1410.2	1411.5	1412.8	1413.4
155°	1439.9	1439.1	1437.6	1436.1	1434.5	1433.0	1434.5	1436.1	1437.6	1439.1	1439.9
157.5°	1464.0	1463.0	1460.9	1458.9	1456.8	1454.8	1456.8	1458.9	1460.9	1463.0	1464.0
160°	1483.6	1482.7	1480.9	1479.2	1477.4	1475.6	1477.4	1479.2	1480.9	1482.7	1483.6
162.5°	1502.0	1501.2	1499.7	1498.2	1496.6	1495.1	1496.6	1498.2	1499.7	1501.2	1502.0
165°	1518.1	1517.2	1515.4	1513.7	1511.9	1510.1	1511.9	1513.7	1515.4	1517.2	1518.1
167.5°	1530.8	1529.8	1527.7	1525.7	1523.6	1521.6	1523.6	1525.7	1527.7	1529.8	1530.8
170°	1541.2	1540.2	1538.1	1536.0	1534.0	1531.9	1534.0	1536.0	1538.1	1540.2	1541.2
172.5°	1548.1	1546.9	1544.6	1542.3	1540.0	1537.7	1540.0	1542.3	1544.6	1546.9	1548.1
175°	1552.7	1551.7	1549.6	1547.6	1545.5	1543.5	1545.5	1547.6	1549.6	1551.7	1552.7
177.5°	1556.1	1554.8	1552.3	1549.7	1547.2	1544.6	1547.2	1549.7	1552.3	1554.8	1556.1
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	741.3	742.8	743.5	740.5	738.2	742.0	747.3	751.1	754.1	757.9	760.2
5°	697.4	702.7	702.7	704.2	706.5	710.3	720.1	726.9	733.0	737.5	741.3
7.5°	660.3	664.1	666.4	670.2	674.0	679.2	690.6	700.4	709.5	714.8	720.9
10°	627.1	630.1	633.9	636.1	642.9	650.5	664.9	673.2	683.8	692.1	699.7
12.5°	595.3	605.9	608.1	607.4	613.4	621.8	636.1	649.0	660.3	668.7	677.0
15°	572.6	576.4	580.9	580.2	593.0	595.3	607.4	622.5	637.6	642.9	650.5
17.5°	547.6	553.7	558.2	560.5	564.3	572.6	583.9	595.3	615.0	615.7	635.4
20°	528.0	534.0	537.0	540.1	542.3	552.2	562.0	574.9	590.8	599.1	609.7
22.5°	515.1	518.1	520.4	522.7	525.7	531.0	543.1	557.5	568.1	577.1	583.9
25°	500.0	503.0	506.0	507.5	509.8	512.8	521.9	533.3	548.4	554.4	561.3
27.5°	489.4	489.4	490.9	490.9	493.9	497.0	503.8	514.4	526.5	534.0	543.1
30°	478.0	477.3	478.0	477.3	476.5	481.1	487.1	496.2	504.5	513.6	519.6
32.5°	466.7	465.9	465.9	466.7	463.7	465.9	469.0	477.3	486.4	490.9	497.7
35°	454.6	453.1	453.1	453.1	451.6	450.1	453.1	460.6	466.7	472.8	478.0
37.5°	442.5	440.2	440.2	438.7	437.2	434.9	434.9	441.0	449.3	451.6	458.4
40°	425.9	425.9	424.3	423.6	422.1	420.6	418.3	423.6	431.1	433.4	438.7
42.5°	409.2	406.9	406.2	406.2	406.2	403.9	402.4	406.2	410.7	414.5	417.5
45°	390.3	388.8	389.5	388.8	387.3	386.5	385.8	387.3	392.6	394.1	397.9
47.5°	369.9	369.1	369.1	368.4	367.6	368.4	365.3	369.1	370.6	372.2	375.2
50°	348.7	347.9	347.2	346.4	346.4	347.2	346.4	346.4	349.5	351.0	354.0
52.5°	327.5	325.3	325.3	324.5	324.5	323.0	324.5	325.3	326.8	328.3	329.8
55°	304.8	304.8	302.6	302.6	301.0	301.0	301.8	301.0	304.1	305.6	305.6
57.5°	282.9	279.9	280.6	279.1	277.6	276.8	276.8	278.4	279.9	279.9	281.4
60°	259.4	256.4	255.7	252.6	254.2	251.9	252.6	252.6	255.7	254.2	255.7
62.5°	236.0	232.2	229.9	228.4	228.4	229.2	227.7	226.9	228.4	229.9	233.0
65°	211.0	208.8	206.5	204.2	204.2	203.5	205.0	202.7	202.0	202.7	204.2
67.5°	185.3	183.0	180.8	178.5	179.3	177.0	175.5	177.8	176.2	177.0	178.5
70°	160.4	158.8	154.3	152.8	152.0	152.8	152.0	150.5	152.8	152.0	152.8
72.5°	135.4	133.9	131.6	127.8	127.8	127.1	126.3	126.3	125.6	125.6	125.6
75°	111.2	108.2	105.9	105.1	103.6	102.9	102.1	100.6	101.4	102.1	100.6
77.5°	86.2	82.4	81.7	81.7	79.4	79.4	80.2	79.4	78.7	78.7	78.7
80°	63.5	60.5	60.5	59.0	57.5	57.5	57.5	57.5	56.7	56.0	56.7
82.5°	40.8	40.1	39.3	39.3	40.8	37.8	39.3	38.6	37.8	37.8	37.1
85°	22.7	23.4	22.7	23.4	21.9	22.7	22.7	22.7	21.9	22.7	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.1
90°	31.7	30.7	29.6	28.6	27.6	24.3	21.0	17.7	14.4	12.7	11.4
92.5°	37.1	35.3	33.5	31.7	29.9	27.6	25.3	23.0	20.7	19.6	20.4
95°	42.8	41.0	39.3	37.5	35.7	32.9	30.1	27.2	24.4	23.0	28.2
97.5°	45.0	42.9	40.9	38.8	36.8	49.8	62.9	75.9	89.0	95.5	99.1
100°	46.2	44.1	42.1	40.0	38.0	77.9	117.8	157.7	197.6	217.5	214.9
102.5°	51.4	59.9	68.3	76.8	85.2	129.7	174.2	218.7	263.2	285.4	283.7
105°	70.9	116.2	161.5	206.8	252.1	275.1	298.1	321.2	344.2	355.7	354.3
107.5°	290.2	329.6	368.9	408.3	447.7	443.9	440.1	436.2	432.4	430.5	429.3
110°	485.3	493.8	502.2	510.7	519.1	516.3	513.5	510.6	507.8	506.4	505.4

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	600.8	598.5	596.2	593.9	591.6	588.8	586.0	583.1	580.3	578.9	578.0
115°	670.9	668.4	665.8	663.3	660.7	658.4	656.1	653.8	651.5	650.3	649.5
117.5°	736.8	734.7	732.7	730.6	728.6	727.3	726.0	724.7	723.4	722.8	721.9
120°	802.4	800.3	798.3	796.2	794.2	793.4	792.6	791.9	791.1	790.7	789.6
122.5°	864.9	863.6	862.3	861.1	859.8	858.8	857.8	856.7	855.7	855.2	854.3
125°	922.8	922.3	921.8	921.3	920.8	919.8	918.8	917.7	916.7	916.2	915.2
127.5°	984.8	984.1	983.3	982.6	981.8	980.5	979.2	977.9	976.6	976.0	975.0
130°	1040.0	1039.0	1037.9	1036.9	1035.9	1034.9	1033.9	1032.8	1031.8	1031.3	1030.3
132.5°	1091.8	1090.8	1089.7	1088.7	1087.7	1086.9	1086.1	1085.4	1084.6	1084.2	1083.2
135°	1143.7	1142.9	1142.2	1141.4	1140.6	1139.6	1138.6	1137.5	1136.5	1136.0	1135.2
137.5°	1191.8	1190.5	1189.2	1188.0	1186.7	1186.2	1185.7	1185.2	1184.7	1184.4	1183.4
140°	1235.6	1234.6	1233.5	1232.5	1231.5	1230.7	1230.0	1229.2	1228.5	1228.1	1227.3
142.5°	1277.2	1276.4	1275.7	1274.9	1274.1	1273.3	1272.6	1271.8	1271.1	1270.7	1269.9
145°	1315.3	1314.8	1314.3	1313.8	1313.3	1312.8	1312.3	1311.8	1311.3	1311.0	1310.1
147.5°	1350.9	1350.4	1349.9	1349.4	1348.9	1348.4	1347.9	1347.4	1346.9	1346.6	1346.0
150°	1383.2	1382.7	1382.2	1381.7	1381.2	1380.7	1380.2	1379.7	1379.2	1378.9	1378.5
152.5°	1412.9	1411.9	1410.8	1409.8	1408.8	1408.5	1408.3	1408.0	1407.7	1407.6	1407.5
155°	1439.3	1438.0	1436.7	1435.4	1434.1	1433.9	1433.6	1433.4	1433.1	1433.0	1433.3
157.5°	1463.2	1461.7	1460.2	1458.6	1457.1	1457.4	1457.6	1457.9	1458.2	1458.3	1458.3
160°	1482.8	1481.3	1479.8	1478.2	1476.7	1477.0	1477.2	1477.5	1477.8	1477.9	1478.0
162.5°	1501.1	1499.3	1497.6	1495.8	1494.0	1494.2	1494.5	1494.7	1495.0	1495.1	1495.5
165°	1517.1	1515.0	1513.0	1510.9	1508.9	1509.2	1509.4	1509.7	1510.0	1510.1	1510.5
167.5°	1529.8	1527.7	1525.7	1523.6	1521.6	1521.6	1521.6	1521.6	1521.6	1521.6	1522.1
170°	1540.2	1538.1	1536.0	1534.0	1531.9	1531.9	1531.9	1531.9	1531.9	1531.9	1532.4
172.5°	1547.1	1545.0	1543.0	1540.9	1538.9	1538.6	1538.4	1538.1	1537.8	1537.7	1538.3
175°	1551.8	1550.0	1548.2	1546.4	1544.6	1544.4	1544.1	1543.9	1543.6	1543.5	1544.1
177.5°	1555.1	1553.0	1551.0	1548.9	1546.9	1546.7	1546.4	1546.2	1545.9	1545.8	1546.4
180°	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2	1549.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	780.6	780.6	780.6	780.6
2.5°	764.0	766.2	773.8	782.9
5°	748.8	754.9	765.5	779.9
7.5°	732.2	741.3	756.4	774.6
10°	713.3	726.1	745.1	767.7
12.5°	692.9	709.5	733.7	757.2
15°	680.0	696.6	718.6	744.3
17.5°	655.0	674.7	697.4	733.7
20°	629.3	651.3	680.8	717.1
22.5°	609.7	633.1	661.1	699.7
25°	586.2	610.4	640.7	680.8
27.5°	561.3	585.5	619.5	661.9
30°	542.3	565.8	598.3	643.7
32.5°	519.6	542.3	576.4	624.0
35°	493.9	519.6	552.2	600.6
37.5°	474.3	497.7	531.8	577.9
40°	453.1	473.5	506.8	552.2
42.5°	430.4	453.1	481.8	527.2
45°	409.2	425.9	455.4	498.5
47.5°	386.5	405.4	428.1	461.4
50°	362.3	378.2	403.2	425.9
52.5°	338.9	351.7	372.9	390.3
55°	313.9	326.8	342.7	353.2
57.5°	290.5	299.5	310.1	316.9
60°	261.7	270.8	277.6	284.4
62.5°	236.0	242.8	246.6	250.4
65°	209.5	213.3	215.6	218.6
67.5°	180.8	184.6	185.3	189.9
70°	154.3	155.1	156.6	158.8
72.5°	129.3	130.9	130.1	131.6
75°	103.6	105.1	103.6	105.1
77.5°	78.7	80.2	80.2	82.4
80°	56.7	57.5	58.2	58.2
82.5°	37.1	39.3	37.8	38.6
85°	21.2	21.9	21.9	22.7
87.5°	9.8	10.6	9.8	11.3
90°	8.9	6.3	3.8	1.2
92.5°	21.9	23.4	25.0	26.5
95°	38.7	49.2	59.7	70.2
97.5°	106.3	113.4	120.6	127.8
100°	209.8	204.7	199.6	194.5
102.5°	280.4	277.1	273.8	270.5
105°	351.5	348.6	345.8	343.0
107.5°	427.0	424.7	422.4	420.1
110°	503.3	501.3	499.2	497.2

TEST NUMBER: P1011721

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	576.2	574.5	572.7	570.9
115°	648.0	646.5	644.9	643.4
117.5°	720.1	718.4	716.6	714.8
120°	787.3	785.0	782.7	780.4
122.5°	852.5	850.7	848.9	847.1
125°	913.1	911.1	909.0	907.0
127.5°	972.9	970.9	968.8	966.8
130°	1028.2	1026.2	1024.1	1022.1
132.5°	1081.1	1079.1	1077.0	1075.0
135°	1133.7	1132.2	1130.6	1129.1
137.5°	1181.3	1179.2	1177.2	1175.1
140°	1225.8	1224.3	1222.7	1221.2
142.5°	1268.4	1266.9	1265.3	1263.8
145°	1308.3	1306.5	1304.7	1302.9
147.5°	1344.7	1343.4	1342.2	1340.9
150°	1377.7	1377.0	1376.2	1375.4
152.5°	1407.2	1407.0	1406.7	1406.5
155°	1433.8	1434.3	1434.8	1435.3
157.5°	1458.3	1458.3	1458.3	1458.3
160°	1478.3	1478.5	1478.8	1479.0
162.5°	1496.3	1497.0	1497.8	1498.6
165°	1511.2	1512.0	1512.7	1513.5
167.5°	1523.1	1524.2	1525.2	1526.2
170°	1533.5	1534.5	1535.6	1536.6
172.5°	1539.6	1540.9	1542.2	1543.5
175°	1545.4	1546.7	1547.9	1549.2
177.5°	1547.7	1549.0	1550.2	1551.5
180°	1549.2	1549.2	1549.2	1549.2

(END OF REPORT)