

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011728

Luminaire Tested: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011728
REPORT IS A COMBINATION OF REPORTS P989986 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6353.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011728

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011728

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1011728

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.3
10°-20°	234.1	3.7
20°-30°	345.8	5.4
30°-40°	403.8	6.4
40°-50°	406.0	6.4
50°-60°	356.6	5.6
60°-70°	265.6	4.2
70°-80°	151.1	2.4
80°-90°	46.1	0.7
90°-100°	94.3	1.5
100°-110°	285.6	4.5
110°-120°	486.1	7.7
120°-130°	639.5	10.1
130°-140°	718.9	11.3
140°-150°	706.7	11.1
150°-160°	595.0	9.4
160°-170°	396.1	6.2
170°-180°	138.7	2.2
0°-30°	662.8	10.4
0°-40°	1066.7	16.8
0°-60°	1829.3	28.8
0°-90°	2292.1	36.1
90°-120°	866.0	13.6
90°-150°	2931.1	46.1
90°-180°	4061.0	63.9
0°-180°	6353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	1	13	28	32	34	8
95°	68	76	85	90	90	75
105°	259	261	272	272	274	277
115°	489	493	490	492	490	484
125°	716	720	717	713	708	639
135°	929	936	935	930	928	716
145°	1127	1129	1133	1132	1127	704
155°	1291	1291	1292	1296	1288	594
165°	1406	1402	1402	1409	1401	396
175°	1462	1458	1458	1464	1456	139
180°	1466	1466	1466	1466	1466	

TEST NUMBER: P1011728

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	1.2	12.7	27.6	32.2	34.5
92.5°	34.5	41.4	48.4	51.8	49.5
95°	67.9	76.0	85.2	89.8	89.8
97.5°	111.7	117.4	124.3	130.1	128.9
100°	156.6	163.5	169.2	172.7	175.0
102.5°	208.4	211.8	219.9	223.4	222.2
105°	259.0	261.3	271.7	271.7	274.0
107.5°	318.9	320.1	324.7	328.1	327.0
110°	374.2	376.5	378.8	383.4	381.1

TEST NUMBER: P1011728

CATALOG NUMBER: S123DIP-B560D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	431.7	432.9	432.9	438.6	438.6
115°	489.3	492.8	490.5	491.6	490.5
117.5°	548.0	549.2	546.9	546.9	543.4
120°	602.1	609.0	603.3	602.1	599.8
122.5°	658.5	663.1	660.8	657.4	653.9
125°	716.1	719.6	717.3	712.7	708.0
127.5°	769.1	776.0	773.7	766.8	762.2
130°	822.0	831.2	827.8	823.2	815.1
132.5°	875.0	884.2	881.9	876.1	870.4
135°	929.1	936.0	934.9	930.2	927.9
137.5°	978.6	984.4	987.8	982.1	978.6
140°	1030.4	1036.2	1037.3	1036.2	1028.1
142.5°	1077.6	1083.4	1085.7	1084.5	1078.8
145°	1127.1	1129.4	1132.9	1131.7	1127.1
147.5°	1169.7	1174.3	1177.8	1177.8	1170.9
150°	1214.6	1216.9	1219.2	1219.2	1212.3
152.5°	1251.5	1254.9	1256.1	1258.4	1252.6
155°	1290.6	1290.6	1291.8	1296.4	1288.3
157.5°	1324.0	1322.8	1324.0	1328.6	1321.7
160°	1355.1	1352.8	1352.8	1358.5	1353.9
162.5°	1382.7	1379.2	1380.4	1386.2	1378.1
165°	1405.7	1402.3	1402.3	1409.2	1401.1
167.5°	1425.3	1420.7	1421.8	1428.8	1421.8
170°	1441.4	1436.8	1436.8	1444.9	1436.8
172.5°	1454.1	1449.5	1449.5	1456.4	1448.3
175°	1462.1	1457.5	1457.5	1464.4	1456.4
177.5°	1466.7	1462.1	1462.1	1469.1	1461.0
180°	1465.6	1465.6	1465.6	1465.6	1465.6

(END OF REPORT)