

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012034

Luminaire Tested: S123DIP-B775D585UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012034
REPORT IS A COMBINATION OF REPORTS P990406 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5159.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012034

CATALOG NUMBER: S123DIP-B775D585UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012034

CATALOG NUMBER: S123DIP-B775D585UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	26
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13065	13065	13065
5°	13097	12615	12595
10°	12981	12187	12063
15°	12801	11744	11481
20°	12593	11250	10906
25°	12326	10730	10290
30°	12033	10192	9643
35°	11726	9642	9000
40°	11405	9065	8367
45°	11051	8502	7706
50°	10692	7875	7042
55°	10230	7222	6369
60°	9756	6501	5654
65°	9309	5723	4908
70°	8667	4858	4038
75°	7741	3846	3135
80°	6688	2702	2217
85°	5216	1454	1110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11051 cd/sqm

TEST NUMBER: P1012034

CATALOG NUMBER: S123DIP-B775D585UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	2.2
10°-20°	323.1	6.3
20°-30°	477.2	9.2
30°-40°	557.3	10.8
40°-50°	560.3	10.9
50°-60°	492.2	9.5
60°-70°	366.6	7.1
70°-80°	208.6	4.0
80°-90°	60.8	1.2
90°-100°	46.4	0.9
100°-110°	140.5	2.7
110°-120°	239.2	4.6
120°-130°	314.7	6.1
130°-140°	353.8	6.9
140°-150°	347.8	6.7
150°-160°	292.8	5.7
160°-170°	194.9	3.8
170°-180°	68.3	1.3
0°-30°	914.7	17.7
0°-40°	1472.1	28.5
0°-60°	2524.5	48.9
0°-90°	3160.5	61.3
90°-120°	426.2	8.3
90°-150°	1442.5	28.0
90°-180°	1998.0	38.7
0°-180°	5159.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1214	1214	1214	1214	1214	
5°	1215	1210	1198	1209	1206	115
15°	1156	1152	1139	1147	1141	326
25°	1050	1044	1030	1031	1028	484
35°	908	902	888	882	877	568
45°	744	740	726	714	709	574
55°	565	564	550	538	533	506
65°	385	380	370	361	358	380
75°	204	199	196	191	188	217
85°	54	52	52	50	50	58
90°	1	6	14	16	17	6
95°	33	37	42	44	44	37
105°	128	129	134	134	135	136
115°	241	242	241	242	241	238
125°	352	354	353	351	348	314
135°	457	461	460	458	457	352
145°	555	556	558	557	555	346
155°	635	635	636	638	634	292
165°	692	690	690	694	690	195
175°	720	717	717	721	717	68
180°	721	721	721	721	721	

TEST NUMBER: P1012034

CATALOG NUMBER: S123DIP-B775D585UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1213.8	1213.8	1213.8	1213.8	1213.8
2.5°	1219.0	1214.8	1203.4	1213.8	1212.8
5°	1214.8	1209.6	1198.2	1208.6	1206.5
7.5°	1205.5	1200.2	1188.8	1198.2	1197.1
10°	1192.9	1187.7	1174.1	1183.5	1181.5
12.5°	1176.2	1172.1	1159.5	1165.8	1164.8
15°	1156.4	1152.2	1138.7	1147.0	1140.7
17.5°	1134.5	1129.3	1115.7	1122.0	1119.9
20°	1109.4	1103.2	1089.6	1093.8	1090.7
22.5°	1081.3	1075.0	1061.4	1064.6	1060.4
25°	1049.9	1043.7	1030.1	1031.2	1028.0
27.5°	1017.6	1011.3	996.7	997.8	994.6
30°	982.1	976.9	962.3	962.3	955.0
32.5°	946.6	939.3	928.9	921.6	918.4
35°	908.0	901.7	888.2	881.9	876.7
37.5°	869.4	861.0	847.5	840.2	837.0
40°	828.7	822.4	807.8	799.5	795.3
42.5°	788.0	780.7	766.1	757.7	753.5
45°	744.1	740.0	726.4	713.9	708.7
47.5°	701.4	695.1	682.6	670.0	665.9
50°	657.5	652.3	638.7	627.3	621.0
52.5°	611.6	608.5	593.9	584.5	578.2
55°	564.6	563.6	550.0	538.5	533.3
57.5°	520.8	516.6	506.2	495.8	489.5
60°	472.8	471.7	459.2	449.8	444.6
62.5°	430.0	426.9	414.3	404.9	401.8
65°	385.1	379.9	369.5	361.1	358.0
67.5°	337.1	332.9	324.6	317.3	313.1
70°	294.3	288.1	281.8	274.5	269.3
72.5°	249.4	245.3	238.0	231.7	229.6
75°	203.5	199.3	196.2	191.0	187.9
77.5°	162.8	160.7	156.6	152.4	152.4
80°	123.2	120.0	117.9	116.9	116.9
82.5°	84.5	84.5	84.5	82.5	81.4
85°	54.3	52.2	52.2	50.1	50.1
87.5°	27.1	24.0	23.0	21.9	21.9
90°	0.6	6.2	13.6	15.9	17.0
92.5°	17.0	20.4	23.8	25.5	24.4
95°	33.4	37.4	41.9	44.2	44.2
97.5°	55.0	57.8	61.2	64.0	63.5
100°	77.1	80.5	83.3	85.0	86.1
102.5°	102.6	104.3	108.2	109.9	109.4
105°	127.5	128.6	133.7	133.7	134.8
107.5°	156.9	157.5	159.8	161.5	160.9
110°	184.1	185.3	186.4	188.7	187.5



TEST NUMBER: P1012034

CATALOG NUMBER: S123DIP-B775D585UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	213.0	213.0	215.9	215.9
115°	240.8	242.5	241.4	241.9	241.4
117.5°	269.7	270.3	269.1	269.1	267.4
120°	296.3	299.7	296.9	296.3	295.2
122.5°	324.1	326.4	325.2	323.5	321.8
125°	352.4	354.1	353.0	350.7	348.4
127.5°	378.5	381.9	380.7	377.3	375.1
130°	404.5	409.1	407.4	405.1	401.1
132.5°	430.6	435.1	434.0	431.2	428.3
135°	457.2	460.6	460.1	457.8	456.7
137.5°	481.6	484.4	486.1	483.3	481.6
140°	507.1	509.9	510.5	509.9	506.0
142.5°	530.3	533.2	534.3	533.7	530.9
145°	554.7	555.8	557.5	556.9	554.7
147.5°	575.6	577.9	579.6	579.6	576.2
150°	597.7	598.9	600.0	600.0	596.6
152.5°	615.9	617.6	618.1	619.3	616.4
155°	635.1	635.1	635.7	638.0	634.0
157.5°	651.6	651.0	651.6	653.8	650.4
160°	666.9	665.7	665.7	668.6	666.3
162.5°	680.5	678.8	679.3	682.2	678.2
165°	691.8	690.1	690.1	693.5	689.5
167.5°	701.4	699.2	699.7	703.1	699.7
170°	709.4	707.1	707.1	711.1	707.1
172.5°	715.6	713.3	713.3	716.7	712.8
175°	719.6	717.3	717.3	720.7	716.7
177.5°	721.8	719.6	719.6	723.0	719.0
180°	721.3	721.3	721.3	721.3	721.3

(END OF REPORT)