

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011746

Luminaire Tested: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011746
REPORT IS A COMBINATION OF REPORTS P990019 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6435.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011746

CATALOG NUMBER: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011746

CATALOG NUMBER: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	20
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1011746

CATALOG NUMBER: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.3
10°-20°	237.2	3.7
20°-30°	350.3	5.4
30°-40°	409.1	6.4
40°-50°	411.3	6.4
50°-60°	361.3	5.6
60°-70°	269.1	4.2
70°-80°	153.1	2.4
80°-90°	46.7	0.7
90°-100°	95.6	1.5
100°-110°	289.2	4.5
110°-120°	492.4	7.7
120°-130°	647.7	10.1
130°-140°	728.0	11.3
140°-150°	715.8	11.1
150°-160°	602.6	9.4
160°-170°	401.2	6.2
170°-180°	140.5	2.2
0°-30°	671.5	10.4
0°-40°	1080.6	16.8
0°-60°	1853.3	28.8
0°-90°	2322.2	36.1
90°-120°	877.1	13.6
90°-150°	2968.6	46.1
90°-180°	4113.0	63.9
0°-180°	6435.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	1	13	28	33	35	8
95°	69	77	86	91	91	76
105°	262	265	275	275	278	281
115°	496	499	497	498	497	490
125°	725	729	726	722	717	647
135°	941	948	947	942	940	725
145°	1142	1144	1147	1146	1142	713
155°	1307	1307	1308	1313	1305	602
165°	1424	1420	1420	1427	1419	402
175°	1481	1476	1476	1483	1475	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1011746

CATALOG NUMBER: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	1.2	12.8	28.0	32.6	35.0
92.5°	35.0	42.0	49.0	52.5	50.1
95°	68.8	77.0	86.3	90.9	90.9
97.5°	113.1	118.9	125.9	131.8	130.6
100°	158.6	165.6	171.4	174.9	177.2
102.5°	211.1	214.5	222.7	226.2	225.0
105°	262.4	264.7	275.2	275.2	277.5
107.5°	323.0	324.2	328.8	332.3	331.2
110°	379.0	381.3	383.6	388.3	386.0

TEST NUMBER: P1011746

CATALOG NUMBER: S123DIP-B560D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.3	438.4	438.4	444.3	444.3
115°	495.6	499.1	496.7	497.9	496.7
117.5°	555.0	556.2	553.9	553.9	550.4
120°	609.8	616.8	611.0	609.8	607.5
122.5°	667.0	671.6	669.3	665.8	662.3
125°	725.3	728.8	726.4	721.8	717.1
127.5°	778.9	785.9	783.6	776.6	771.9
130°	832.5	841.9	838.4	833.7	825.5
132.5°	886.2	895.5	893.2	887.3	881.5
135°	941.0	948.0	946.8	942.1	939.8
137.5°	991.1	997.0	1000.4	994.6	991.1
140°	1043.6	1049.4	1050.6	1049.4	1041.3
142.5°	1091.4	1097.2	1099.6	1098.4	1092.6
145°	1141.5	1143.9	1147.4	1146.2	1141.5
147.5°	1184.7	1189.3	1192.8	1192.8	1185.8
150°	1230.2	1232.5	1234.8	1234.8	1227.8
152.5°	1267.5	1271.0	1272.1	1274.5	1268.6
155°	1307.1	1307.1	1308.3	1312.9	1304.8
157.5°	1340.9	1339.8	1340.9	1345.6	1338.6
160°	1372.4	1370.1	1370.1	1375.9	1371.2
162.5°	1400.4	1396.9	1398.1	1403.9	1395.7
165°	1423.7	1420.2	1420.2	1427.2	1419.1
167.5°	1443.5	1438.9	1440.0	1447.0	1440.0
170°	1459.9	1455.2	1455.2	1463.4	1455.2
172.5°	1472.7	1468.0	1468.0	1475.0	1466.9
175°	1480.9	1476.2	1476.2	1483.2	1475.0
177.5°	1485.5	1480.9	1480.9	1487.8	1479.7
180°	1484.3	1484.3	1484.3	1484.3	1484.3

(END OF REPORT)