

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011750

Luminaire Tested: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011750
REPORT IS A COMBINATION OF REPORTS P990023 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB40-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6656.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36			
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30			
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26			
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27	22			
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19			
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17			
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15			
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13			
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12			
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10			
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8427	8427	8427	8427
5°	8433	9710	8457	7247
10°	8379	11751	8388	6328
15°	8263	13935	8331	5697
20°	8164	16043	8181	5241
25°	8016	16448	8034	5005
30°	7910	13589	7910	4849
35°	7780	9088	7730	4712
40°	7622	6560	7528	4502
45°	7426	5196	7210	4239
50°	6945	4413	6698	3984
55°	6420	3878	6159	3697
60°	5887	3376	5573	3395
65°	5299	2891	5043	2996
70°	4691	2400	4379	2525
75°	4013	1810	3751	1949
80°	3171	1208	2926	1280
85°	2190	554	1748	505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13592 cd/sqm

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	1.2
10°-20°	247.3	3.7
20°-30°	416.1	6.3
30°-40°	470.3	7.1
40°-50°	421.2	6.3
50°-60°	340.0	5.1
60°-70°	236.9	3.6
70°-80°	124.3	1.9
80°-90°	33.0	0.5
90°-100°	309.5	4.6
100°-110°	906.0	13.6
110°-120°	884.8	13.3
120°-130°	704.6	10.6
130°-140°	555.9	8.4
140°-150°	414.7	6.2
150°-160°	289.2	4.3
160°-170°	169.9	2.6
170°-180°	55.3	0.8
0°-30°	740.4	11.1
0°-40°	1210.7	18.2
0°-60°	1971.9	29.6
0°-90°	2366.1	35.5
90°-120°	2100.3	31.6
90°-150°	3775.6	56.7
90°-180°	4290.0	64.5
0°-180°	6656.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	783	783	783	783	783	
5°	782	930	784	694	782	74
15°	746	1384	753	566	746	211
25°	683	1643	684	500	683	315
35°	602	885	599	459	602	377
45°	500	478	486	390	500	382
55°	354	325	340	310	354	317
65°	219	211	209	218	219	218
75°	106	108	99	117	106	113
85°	23	25	18	23	23	26
90°	2	34	2	34	2	5
95°	39	134	39	134	39	42
105°	134	1468	134	1468	134	142
115°	237	1786	237	1786	237	234
125°	329	1408	329	1408	329	292
135°	386	1142	386	1142	386	298
145°	440	892	440	892	440	276
155°	500	740	500	740	500	230
165°	546	645	546	645	546	154
175°	569	581	569	581	569	54
180°	570	570	570	570	570	

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	785.2	791.3	794.3	798.9	803.4	810.2	812.5	816.3	814.8	817.8	819.3
5°	782.2	792.8	801.9	813.3	823.9	831.5	839.1	851.2	860.3	861.8	868.7
7.5°	776.9	792.0	808.0	823.9	844.4	856.5	870.2	886.9	900.5	922.5	930.9
10°	770.0	791.3	814.0	836.0	864.1	883.1	899.8	927.8	955.9	978.7	999.9
12.5°	759.4	786.0	815.5	848.2	884.6	906.6	929.3	966.5	1009.0	1043.9	1066.7
15°	746.5	779.9	817.8	852.7	892.9	933.9	958.2	999.9	1060.6	1093.2	1151.6
17.5°	735.9	770.0	808.0	862.6	917.2	958.2	975.6	1052.2	1094.0	1148.6	1214.6
20°	719.2	762.4	811.0	865.6	936.2	961.2	996.9	1074.2	1125.8	1197.2	1278.3
22.5°	701.8	748.0	806.4	863.3	942.2	968.8	1017.4	1078.8	1160.7	1231.3	1320.8
25°	682.8	732.9	792.0	859.6	936.9	975.6	1021.1	1097.0	1185.8	1274.5	1357.2
27.5°	663.8	718.4	779.9	847.4	922.5	968.0	1013.6	1092.5	1206.3	1302.6	1408.1
30°	645.6	700.2	761.7	830.7	909.6	953.6	996.9	1095.5	1222.2	1330.7	1436.9
32.5°	625.9	682.0	746.5	804.2	883.8	930.9	979.4	1095.5	1232.0	1347.4	1444.5
35°	602.4	660.0	715.4	773.1	852.0	904.3	958.9	1087.9	1241.2	1352.7	1412.6
37.5°	579.6	630.4	678.2	734.4	817.1	873.2	936.2	1078.8	1236.6	1329.9	1346.6
40°	553.8	604.6	643.3	695.7	782.9	848.2	911.9	1066.7	1216.9	1276.0	1227.5
42.5°	528.8	569.0	602.4	653.2	748.0	811.8	880.8	1044.7	1178.2	1190.3	1081.1
45°	500.0	528.8	558.4	616.0	710.1	775.3	852.0	1012.8	1116.0	1081.1	943.0
47.5°	462.8	488.6	521.2	574.3	669.9	737.4	810.2	971.8	1025.7	952.9	801.9
50°	427.1	449.1	479.5	531.1	627.4	693.4	770.8	907.3	933.9	819.3	691.1
52.5°	391.5	408.2	437.7	489.3	585.7	649.4	720.0	841.3	826.2	703.3	589.5
55°	354.3	368.7	396.8	447.6	537.1	597.8	665.3	760.2	720.7	603.9	512.8
57.5°	317.9	333.0	361.9	404.4	488.6	547.7	601.6	676.0	616.8	523.5	443.1
60°	285.3	298.1	320.2	361.9	438.5	486.3	535.6	586.4	537.1	446.8	385.4
62.5°	251.1	263.3	283.7	321.7	387.7	430.2	469.6	511.3	456.7	390.7	336.1
65°	219.2	229.1	248.1	283.0	336.8	371.7	403.6	432.4	388.4	327.7	286.8
67.5°	190.4	198.8	214.7	245.8	291.3	316.4	342.2	366.4	329.3	280.7	245.8
70°	159.3	166.1	180.6	203.3	239.7	265.5	284.5	302.7	269.3	230.6	207.1
72.5°	132.0	138.8	147.9	171.5	196.5	212.4	232.9	242.8	223.8	191.9	168.4
75°	105.5	110.8	119.1	134.3	157.8	168.4	181.3	188.9	171.5	150.2	135.8
77.5°	82.7	85.0	91.0	101.7	117.6	129.7	139.6	144.1	132.0	118.3	106.2
80°	58.4	61.5	66.0	75.1	87.2	91.0	97.1	102.4	94.8	82.7	75.1
82.5°	38.7	42.5	44.8	48.6	56.1	60.7	62.2	66.8	59.9	55.4	52.3
85°	22.8	24.3	25.0	27.3	31.1	33.4	35.7	36.4	34.9	34.1	31.1
87.5°	11.4	11.4	11.4	12.9	13.7	15.2	15.9	15.9	15.9	15.2	14.4
90°	2.3	4.6	6.9	10.4	12.7	13.8	15.0	18.5	21.9	25.4	28.9
92.5°	17.3	25.4	36.9	47.3	58.9	69.3	79.7	116.6	177.8	237.8	214.7
95°	39.3	42.7	55.4	75.0	105.1	127.6	150.1	248.2	420.2	609.5	684.6
97.5°	62.3	63.5	73.9	91.2	121.2	146.0	170.9	267.8	467.6	786.2	1052.9
100°	85.4	86.6	94.7	110.8	138.5	161.0	183.6	264.4	435.2	738.8	1093.3
102.5°	109.7	112.0	118.9	133.9	158.2	178.4	198.6	269.0	407.5	669.6	1018.2
105°	133.9	137.4	144.3	158.2	180.1	198.0	215.9	278.2	397.1	615.3	928.2
107.5°	159.3	162.8	169.7	183.6	204.3	221.0	237.8	293.2	394.8	576.1	848.5
110°	187.0	190.5	196.3	209.0	228.6	244.8	260.9	312.9	400.6	555.3	782.7

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	212.4	215.9	221.7	234.4	254.0	269.6	285.1	332.5	412.1	543.7	738.8
115°	236.7	241.3	248.2	259.8	279.4	295.0	310.5	354.4	424.8	542.6	710.0
117.5°	260.9	266.7	272.5	282.8	304.8	319.2	333.6	377.5	441.0	543.7	690.4
120°	286.3	289.8	295.5	307.1	329.0	343.4	357.9	399.4	459.5	548.4	677.7
122.5°	308.2	311.7	317.5	330.2	351.0	366.6	382.1	422.5	476.8	556.4	669.6
125°	329.0	331.3	338.3	351.0	372.9	388.5	404.1	444.5	495.3	564.5	662.7
127.5°	345.2	348.6	356.7	369.4	393.7	409.2	424.8	464.1	510.3	573.8	659.2
130°	360.2	363.7	374.0	387.9	412.1	427.7	443.3	481.4	525.3	583.0	655.7
132.5°	371.7	376.4	387.9	405.2	429.5	444.5	459.5	496.4	539.1	589.9	654.6
135°	385.6	390.2	402.9	420.2	444.5	460.0	475.6	511.4	550.7	596.9	653.4
137.5°	398.3	402.9	415.6	434.1	458.3	472.8	487.2	521.8	559.9	601.5	651.1
140°	411.0	416.8	428.3	446.8	469.9	484.3	498.7	532.2	566.8	606.1	650.0
142.5°	424.8	429.5	442.2	458.3	481.4	494.7	508.0	540.3	573.8	609.5	647.6
145°	439.8	443.3	453.7	471.0	490.6	503.9	517.2	547.2	578.4	610.7	645.3
147.5°	454.9	457.2	467.6	482.6	502.2	513.8	525.3	553.0	581.8	610.7	641.9
150°	469.9	471.0	480.3	495.3	511.4	521.8	532.2	558.8	583.0	610.7	637.3
152.5°	484.9	484.9	494.1	506.8	520.7	530.5	540.3	562.2	585.3	607.2	631.5
155°	499.9	499.9	506.8	518.3	531.0	539.1	547.2	566.8	585.3	604.9	624.6
157.5°	511.4	512.6	518.3	528.7	540.3	546.6	553.0	569.1	586.5	601.5	618.8
160°	525.3	525.3	529.9	539.1	547.2	553.0	558.8	572.6	586.5	599.2	611.9
162.5°	535.7	535.7	539.1	546.1	553.0	557.6	562.2	573.8	585.3	594.5	604.9
165°	546.1	544.9	547.2	553.0	557.6	561.7	565.7	574.9	583.0	589.9	598.0
167.5°	554.1	553.0	554.1	558.8	562.2	565.1	568.0	574.9	581.8	585.3	591.1
170°	561.1	558.8	559.9	563.4	565.7	566.8	568.0	573.8	578.4	580.7	584.2
172.5°	565.7	564.5	564.5	566.8	568.0	568.6	569.1	573.8	577.2	577.2	578.4
175°	569.1	568.0	566.8	569.1	569.1	569.7	570.3	572.6	574.9	573.8	573.8
177.5°	571.5	570.3	569.1	570.3	570.3	570.3	570.3	571.5	573.8	571.5	570.3
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	824.7	826.2	831.5	835.3	842.9	842.1	842.1	841.3	839.1	842.9	845.1
5°	882.3	895.2	896.7	913.4	914.2	921.0	925.6	921.8	930.9	930.1	923.3
7.5°	953.6	971.1	979.4	995.3	1013.6	1009.0	1026.5	1029.5	1028.0	1035.6	1040.9
10°	1031.8	1062.1	1083.4	1112.9	1120.5	1125.1	1136.5	1146.3	1166.0	1150.9	1160.7
12.5°	1121.3	1143.3	1171.4	1218.4	1241.9	1257.1	1262.4	1269.2	1282.9	1274.5	1275.3
15°	1196.4	1226.0	1273.8	1332.2	1339.0	1358.0	1353.4	1394.4	1414.1	1384.5	1401.2
17.5°	1274.5	1314.0	1370.9	1421.7	1450.5	1463.4	1475.6	1515.0	1513.5	1509.0	1512.7
20°	1324.6	1389.1	1459.6	1527.2	1535.5	1545.4	1578.0	1594.7	1591.6	1604.5	1612.9
22.5°	1395.2	1463.4	1538.5	1583.3	1602.3	1613.6	1639.4	1650.1	1654.6	1657.7	1652.3
25°	1454.3	1527.2	1582.5	1622.0	1633.4	1639.4	1647.8	1650.8	1648.5	1643.2	1647.8
27.5°	1494.5	1553.0	1590.9	1609.1	1603.0	1593.2	1577.2	1566.6	1543.1	1531.7	1545.4
30°	1511.2	1537.0	1548.4	1518.1	1487.7	1463.4	1433.1	1377.0	1332.9	1345.8	1328.4
32.5°	1484.7	1468.0	1413.4	1335.2	1311.7	1272.3	1186.5	1120.5	1122.8	1087.9	1102.3
35°	1406.5	1330.7	1227.5	1109.1	1078.0	1056.8	962.7	948.3	918.0	885.3	894.4
37.5°	1268.5	1157.7	1032.5	945.3	899.0	852.7	799.6	767.8	749.5	735.9	746.5
40°	1100.0	965.0	861.8	783.7	744.2	714.6	678.2	646.4	625.9	623.6	627.4
42.5°	934.7	820.9	726.0	651.7	638.8	603.9	580.4	555.3	549.3	539.4	544.7
45°	791.3	698.7	620.6	559.9	544.7	535.6	506.8	490.8	484.0	477.9	487.1
47.5°	687.3	590.2	533.3	496.9	481.7	466.6	450.6	440.0	434.7	435.5	434.7
50°	587.2	515.9	465.8	437.7	428.6	418.0	405.1	398.3	396.0	389.2	394.5
52.5°	505.3	453.7	418.8	392.2	385.4	377.8	367.2	363.4	358.1	356.6	356.6
55°	439.3	399.1	371.0	353.5	345.2	339.1	333.0	328.5	324.7	324.7	324.7
57.5°	387.7	352.8	332.3	317.1	314.1	308.0	301.2	301.2	295.9	295.1	297.4
60°	343.7	312.6	296.6	283.7	279.2	277.7	270.8	270.8	269.3	265.5	268.6
62.5°	298.9	276.1	262.5	252.6	248.1	248.1	242.8	239.0	239.0	239.7	238.2
65°	257.9	241.3	229.1	221.5	219.2	216.2	215.5	212.4	210.1	210.9	210.1
67.5°	221.5	208.6	200.3	194.2	190.4	188.9	186.6	186.6	185.1	185.9	182.1
70°	188.9	176.0	169.2	163.1	161.6	161.6	158.6	159.3	157.8	160.1	158.6
72.5°	155.5	145.7	140.4	138.1	136.6	135.8	134.3	132.8	132.0	133.5	132.8
75°	125.9	117.6	113.8	112.3	110.8	110.8	110.0	109.2	108.5	108.5	108.5
77.5°	97.9	92.6	88.0	89.5	87.2	88.0	85.7	85.7	86.5	85.7	85.7
80°	72.1	68.3	68.3	66.8	63.7	65.2	65.2	63.0	62.2	63.7	61.5
82.5°	47.8	47.0	45.5	44.8	43.2	44.0	43.2	42.5	41.7	43.2	41.7
85°	28.1	28.1	27.3	25.8	27.3	26.6	25.8	25.8	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.4	12.1	11.4	10.6	11.4	10.6
90°	27.7	28.9	30.0	31.2	32.4	33.5	32.3	33.5	34.6	33.5	34.6
92.5°	160.5	114.3	88.9	77.3	73.3	69.3	67.0	62.3	63.5	61.2	63.5
95°	555.3	415.6	281.7	220.5	199.7	178.9	157.0	146.6	138.5	133.9	138.5
97.5°	1088.6	954.7	720.4	568.0	502.2	436.4	359.0	315.2	287.5	274.8	287.5
100°	1320.7	1361.1	1267.6	1132.5	1050.6	968.6	852.0	767.7	722.7	723.8	722.7
102.5°	1332.2	1496.2	1515.8	1451.1	1406.7	1362.3	1278.0	1215.6	1179.8	1146.4	1179.8
105°	1259.5	1500.8	1616.2	1638.2	1623.2	1608.1	1555.0	1511.2	1474.2	1468.5	1474.2
107.5°	1155.6	1431.5	1612.8	1702.8	1718.4	1734.0	1727.1	1706.3	1691.3	1678.6	1691.3
110°	1058.6	1323.0	1535.4	1680.9	1721.3	1761.7	1794.0	1803.3	1800.9	1798.6	1800.9

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	974.4	1215.6	1433.8	1601.2	1656.0	1710.9	1776.7	1810.2	1821.7	1822.9	1821.7
115°	909.7	1123.3	1324.2	1493.9	1556.8	1619.7	1706.3	1757.1	1780.2	1785.9	1780.2
117.5°	867.0	1051.7	1229.5	1385.3	1450.6	1515.8	1605.8	1662.4	1697.0	1705.1	1697.0
120°	834.7	997.4	1153.3	1291.8	1350.1	1408.4	1499.6	1564.3	1592.0	1598.9	1592.0
122.5°	808.1	954.7	1092.1	1217.9	1271.1	1324.2	1402.7	1459.2	1490.4	1499.6	1490.4
125°	786.2	917.8	1043.6	1154.5	1200.6	1246.8	1320.7	1371.5	1400.3	1408.4	1400.3
127.5°	765.4	884.3	998.6	1100.2	1142.9	1185.6	1252.6	1296.4	1323.0	1329.9	1323.0
130°	749.2	853.1	957.0	1050.5	1089.8	1129.1	1190.2	1231.8	1256.0	1265.3	1256.0
132.5°	734.2	824.3	917.8	1003.2	1040.2	1077.1	1133.7	1175.2	1196.0	1201.8	1196.0
135°	721.5	798.9	880.8	955.9	988.8	1021.7	1078.3	1112.9	1133.7	1141.8	1133.7
137.5°	710.0	774.6	843.9	910.9	940.3	969.7	1018.2	1054.0	1071.3	1078.3	1071.3
140°	699.6	753.9	812.7	868.1	893.0	917.8	961.7	994.0	1012.5	1011.3	1012.5
142.5°	690.4	734.2	782.7	828.9	849.7	870.5	906.2	934.0	950.1	949.0	950.1
145°	682.3	719.2	757.3	794.3	811.0	827.7	856.6	880.8	890.1	892.4	890.1
147.5°	674.2	706.5	737.7	768.9	781.0	793.1	816.2	833.5	842.7	843.9	842.7
150°	666.1	692.7	719.2	743.5	754.4	765.4	782.7	795.4	802.3	802.3	802.3
152.5°	656.9	680.0	701.9	722.7	731.4	740.0	752.7	764.2	767.7	767.7	767.7
155°	647.6	667.3	685.7	703.1	710.0	716.9	727.3	736.5	738.8	740.0	738.8
157.5°	637.3	653.4	669.6	683.4	689.2	695.0	704.2	711.1	713.5	713.5	713.5
160°	626.9	641.9	654.6	666.1	670.2	674.2	682.3	689.2	689.2	688.1	689.2
162.5°	616.5	628.0	638.4	648.8	652.2	655.7	660.3	666.1	666.1	665.0	666.1
165°	607.2	616.5	623.4	631.5	634.4	637.3	641.9	646.5	645.3	645.3	645.3
167.5°	598.0	606.1	611.9	616.5	618.8	621.1	623.4	626.9	625.7	625.7	625.7
170°	589.9	595.7	599.2	603.8	605.0	606.1	607.2	609.5	608.4	608.4	608.4
172.5°	581.8	586.5	588.8	592.2	592.8	593.4	593.4	595.7	593.4	592.2	593.4
175°	576.1	578.4	579.5	581.8	581.8	581.8	581.8	583.0	581.8	580.7	581.8
177.5°	571.5	572.6	573.8	574.9	574.9	574.9	573.8	574.9	572.6	572.6	572.6
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	839.1	841.3	835.3	833.8	833.8	836.8	834.5	814.0	817.8	813.3	811.8
5°	931.6	927.1	921.0	918.0	914.2	903.6	902.8	879.3	874.7	859.6	852.7
7.5°	1033.3	1029.5	1011.3	1009.0	1007.5	997.6	972.6	947.6	929.3	911.9	895.2
10°	1149.4	1138.0	1129.6	1112.9	1104.6	1090.9	1058.3	1034.8	1003.7	977.1	942.2
12.5°	1288.9	1276.0	1248.0	1235.8	1225.2	1187.3	1154.7	1128.1	1067.4	1049.2	1006.0
15°	1391.4	1364.1	1361.0	1334.5	1332.9	1291.2	1229.0	1200.2	1153.1	1086.4	1041.6
17.5°	1502.1	1477.9	1458.9	1427.0	1422.5	1383.0	1337.5	1266.9	1215.4	1151.6	1094.7
20°	1583.3	1570.4	1537.8	1524.9	1498.3	1465.0	1417.9	1330.7	1267.7	1204.0	1134.2
22.5°	1647.8	1634.9	1609.1	1591.6	1576.5	1533.2	1477.1	1402.7	1316.3	1232.8	1160.7
25°	1647.0	1643.2	1632.6	1624.3	1612.9	1581.0	1534.0	1462.7	1366.3	1274.5	1174.4
27.5°	1553.7	1564.3	1582.5	1591.6	1589.4	1584.8	1558.3	1498.3	1411.8	1302.6	1190.3
30°	1359.5	1398.2	1432.3	1477.9	1491.5	1524.9	1540.1	1505.9	1436.9	1335.2	1210.8
32.5°	1127.4	1183.5	1257.8	1282.9	1326.1	1390.6	1462.7	1475.6	1432.3	1354.2	1223.7
35°	924.8	971.1	1028.7	1068.2	1106.9	1211.6	1302.6	1381.5	1395.9	1344.3	1220.7
37.5°	765.5	798.1	848.9	882.3	918.0	1007.5	1134.9	1237.4	1309.4	1310.9	1212.3
40°	650.2	664.6	708.6	732.9	767.0	844.4	958.2	1091.7	1197.2	1245.7	1190.3
42.5°	550.8	569.7	606.2	624.4	646.4	713.9	789.0	915.7	1046.2	1150.1	1149.4
45°	491.6	505.3	522.0	537.1	562.2	602.4	688.1	782.9	908.1	1025.7	1072.0
47.5°	439.3	452.2	468.8	473.4	490.1	528.0	580.4	663.1	779.9	896.7	984.0
50°	395.3	405.9	417.3	425.6	433.2	464.3	503.7	573.5	666.9	779.9	888.4
52.5°	361.1	368.7	378.6	383.1	389.9	412.7	443.1	494.6	571.3	674.4	779.9
55°	329.3	334.6	340.6	348.2	351.3	367.9	391.5	435.5	492.4	584.9	685.1
57.5°	299.7	301.9	305.7	310.3	314.1	328.5	349.0	378.6	428.6	500.0	594.8
60°	266.3	272.4	274.6	279.2	281.5	292.8	308.8	333.8	372.5	433.9	505.3
62.5°	238.2	242.0	245.8	248.1	253.4	257.2	270.1	292.8	324.7	370.2	434.7
65°	213.2	214.7	217.0	219.2	220.8	225.3	237.5	252.6	276.9	317.1	367.2
67.5°	184.4	185.9	188.9	189.7	191.2	197.2	204.1	217.0	237.5	267.8	308.8
70°	156.3	158.6	160.1	161.6	163.9	166.1	173.7	184.4	200.3	221.5	253.4
72.5°	132.0	134.3	134.3	135.8	135.0	138.1	145.7	153.2	163.9	181.3	209.4
75°	107.7	107.7	109.2	110.0	110.8	113.8	116.8	122.9	131.2	144.9	162.4
77.5°	85.0	84.2	85.7	85.7	85.7	88.0	91.0	94.1	99.4	109.2	122.9
80°	62.2	62.2	63.7	64.5	63.0	63.7	65.2	68.3	72.1	78.9	86.5
82.5°	41.0	44.0	43.2	44.0	43.2	44.8	45.5	46.3	47.8	50.8	56.1
85°	25.0	25.0	25.0	25.8	25.0	25.8	25.8	25.8	26.6	28.1	30.3
87.5°	10.6	10.6	10.6	11.4	10.6	10.6	11.4	10.6	11.4	11.4	12.1
90°	33.5	32.3	33.5	32.4	31.2	30.0	28.9	27.7	28.9	25.4	21.9
92.5°	62.3	67.0	69.3	73.3	77.3	88.9	114.3	160.5	214.7	237.8	177.8
95°	146.6	157.0	178.9	199.7	220.5	281.7	415.6	555.3	684.6	609.5	420.2
97.5°	315.2	359.0	436.4	502.2	568.0	720.4	954.7	1088.6	1052.9	786.2	467.6
100°	767.7	852.0	968.6	1050.6	1132.5	1267.6	1361.1	1320.7	1093.3	738.8	435.2
102.5°	1215.6	1278.0	1362.3	1406.7	1451.1	1515.8	1496.2	1332.2	1018.2	669.6	407.5
105°	1511.2	1555.0	1608.1	1623.2	1638.2	1616.2	1500.8	1259.5	928.2	615.3	397.1
107.5°	1706.3	1727.1	1734.0	1718.4	1702.8	1612.8	1431.5	1155.6	848.5	576.1	394.8
110°	1803.3	1794.0	1761.7	1721.3	1680.9	1535.4	1323.0	1058.6	782.7	555.3	400.6

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1810.2	1776.7	1710.9	1656.0	1601.2	1433.8	1215.6	974.4	738.8	543.7	412.1
115°	1757.1	1706.3	1619.7	1556.8	1493.9	1324.2	1123.3	909.7	710.0	542.6	424.8
117.5°	1662.4	1605.8	1515.8	1450.6	1385.3	1229.5	1051.7	867.0	690.4	543.7	441.0
120°	1564.3	1499.6	1408.4	1350.1	1291.8	1153.3	997.4	834.7	677.7	548.4	459.5
122.5°	1459.2	1402.7	1324.2	1271.1	1217.9	1092.1	954.7	808.1	669.6	556.4	476.8
125°	1371.5	1320.7	1246.8	1200.6	1154.5	1043.6	917.8	786.2	662.7	564.5	495.3
127.5°	1296.4	1252.6	1185.6	1142.9	1100.2	998.6	884.3	765.4	659.2	573.8	510.3
130°	1231.8	1190.2	1129.1	1089.8	1050.5	957.0	853.1	749.2	655.7	583.0	525.3
132.5°	1175.2	1133.7	1077.1	1040.2	1003.2	917.8	824.3	734.2	654.6	589.9	539.1
135°	1112.9	1078.3	1021.7	988.8	955.9	880.8	798.9	721.5	653.4	596.9	550.7
137.5°	1054.0	1018.2	969.7	940.3	910.9	843.9	774.6	710.0	651.1	601.5	559.9
140°	994.0	961.7	917.8	893.0	868.1	812.7	753.9	699.6	650.0	606.1	566.8
142.5°	934.0	906.2	870.5	849.7	828.9	782.7	734.2	690.4	647.6	609.5	573.8
145°	880.8	856.6	827.7	811.0	794.3	757.3	719.2	682.3	645.3	610.7	578.4
147.5°	833.5	816.2	793.1	781.0	768.9	737.7	706.5	674.2	641.9	610.7	581.8
150°	795.4	782.7	765.4	754.4	743.5	719.2	692.7	666.1	637.3	610.7	583.0
152.5°	764.2	752.7	740.0	731.4	722.7	701.9	680.0	656.9	631.5	607.2	585.3
155°	736.5	727.3	716.9	710.0	703.1	685.7	667.3	647.6	624.6	604.9	585.3
157.5°	711.1	704.2	695.0	689.2	683.4	669.6	653.4	637.3	618.8	601.5	586.5
160°	689.2	682.3	674.2	670.2	666.1	654.6	641.9	626.9	611.9	599.2	586.5
162.5°	666.1	660.3	655.7	652.2	648.8	638.4	628.0	616.5	604.9	594.5	585.3
165°	646.5	641.9	637.3	634.4	631.5	623.4	616.5	607.2	598.0	589.9	583.0
167.5°	626.9	623.4	621.1	618.8	616.5	611.9	606.1	598.0	591.1	585.3	581.8
170°	609.5	607.2	606.1	605.0	603.8	599.2	595.7	589.9	584.2	580.7	578.4
172.5°	595.7	593.4	593.4	592.8	592.2	588.8	586.5	581.8	578.4	577.2	577.2
175°	583.0	581.8	581.8	581.8	581.8	579.5	578.4	576.1	573.8	573.8	574.9
177.5°	574.9	573.8	574.9	574.9	574.9	573.8	572.6	571.5	570.3	571.5	573.8
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	804.2	801.9	801.9	800.4	795.8	787.5	786.7	788.2	783.7	779.1	772.3
5°	843.6	829.2	824.7	820.1	811.0	795.8	789.8	784.4	776.1	766.2	755.6
7.5°	877.0	856.5	850.4	842.1	823.9	802.7	789.0	777.6	766.2	752.6	739.7
10°	918.7	889.1	874.7	862.6	837.6	808.0	787.5	770.8	752.6	735.9	719.2
12.5°	965.8	918.0	913.4	883.8	855.0	811.0	786.0	761.7	737.4	716.9	699.5
15°	1005.2	952.9	933.9	914.2	858.8	804.2	779.9	752.6	724.5	702.5	676.7
17.5°	1030.2	987.0	946.8	920.2	862.6	814.0	767.0	735.9	706.3	676.0	654.7
20°	1060.6	997.6	962.7	927.1	870.2	806.4	759.4	720.7	684.3	657.0	631.2
22.5°	1090.9	1006.0	977.1	938.5	871.7	798.9	745.8	707.1	665.3	638.0	610.0
25°	1087.9	1018.1	970.3	937.7	856.5	792.0	729.8	684.3	645.6	610.7	582.6
27.5°	1090.2	1004.5	955.9	918.0	845.9	782.2	713.1	665.3	625.1	588.7	559.1
30°	1090.9	984.0	941.5	896.0	826.2	758.7	694.2	645.6	603.1	563.7	537.1
32.5°	1088.7	967.3	914.2	873.2	795.1	735.9	672.2	620.6	577.3	540.9	515.9
35°	1083.4	947.6	886.1	834.5	763.2	703.3	651.7	598.6	552.3	518.9	490.1
37.5°	1068.9	926.3	856.5	805.7	726.0	665.3	619.8	575.8	531.1	491.6	467.3
40°	1058.3	897.5	826.9	771.5	685.8	626.6	588.7	547.0	503.0	467.3	443.8
42.5°	1034.0	870.2	796.6	730.6	646.4	585.7	550.0	516.6	478.7	443.8	422.6
45°	994.6	840.6	759.4	692.6	603.1	545.5	512.8	485.5	452.2	418.8	397.5
47.5°	939.2	798.1	720.0	653.2	560.6	502.2	469.6	449.1	422.6	394.5	376.3
50°	879.3	751.8	679.8	613.7	519.7	462.8	430.9	411.9	394.5	368.7	351.3
52.5°	801.1	702.5	633.5	570.5	475.7	421.1	393.0	379.3	361.1	342.9	327.7
55°	725.3	638.8	581.9	522.0	432.4	381.6	354.3	339.9	329.3	314.1	301.9
57.5°	637.3	579.6	527.3	472.6	392.2	345.9	320.2	302.7	295.9	289.0	277.7
60°	556.1	512.1	469.6	424.1	350.5	308.8	283.7	270.1	263.3	258.7	251.1
62.5°	481.7	447.6	411.2	374.8	308.0	270.1	251.1	237.5	231.4	230.6	223.8
65°	410.4	386.2	356.6	320.9	268.6	235.2	217.0	208.6	201.8	201.8	196.5
67.5°	339.1	322.4	298.9	273.9	232.9	201.8	185.1	177.5	173.7	173.7	169.9
70°	282.2	270.8	249.6	227.6	191.9	168.4	155.5	148.7	146.4	147.2	144.1
72.5°	229.1	217.0	199.5	183.6	157.0	139.6	130.5	122.9	119.1	119.9	119.1
75°	177.5	171.5	156.3	144.1	122.9	110.8	102.4	98.6	95.6	96.3	94.8
77.5°	133.5	124.4	116.1	107.7	94.8	85.0	78.1	74.3	72.1	72.1	72.1
80°	91.0	89.5	82.7	78.1	67.5	59.9	54.6	53.9	51.6	51.6	51.6
82.5°	59.2	55.4	51.6	48.6	42.5	37.9	35.7	34.1	33.4	32.6	34.1
85°	32.6	30.3	28.8	25.8	23.5	21.2	19.0	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.9	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	18.5	15.0	13.8	12.7	10.4	6.9	4.6	2.3	4.6	6.9	10.4
92.5°	116.6	79.7	69.3	58.9	47.3	36.9	25.4	17.3	25.4	36.9	47.3
95°	248.2	150.1	127.6	105.1	75.0	55.4	42.7	39.3	42.7	55.4	75.0
97.5°	267.8	170.9	146.0	121.2	91.2	73.9	63.5	62.3	63.5	73.9	91.2
100°	264.4	183.6	161.0	138.5	110.8	94.7	86.6	85.4	86.6	94.7	110.8
102.5°	269.0	198.6	178.4	158.2	133.9	118.9	112.0	109.7	112.0	118.9	133.9
105°	278.2	215.9	198.0	180.1	158.2	144.3	137.4	133.9	137.4	144.3	158.2
107.5°	293.2	237.8	221.0	204.3	183.6	169.7	162.8	159.3	162.8	169.7	183.6
110°	312.9	260.9	244.8	228.6	209.0	196.3	190.5	187.0	190.5	196.3	209.0

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	332.5	285.1	269.6	254.0	234.4	221.7	215.9	212.4	215.9	221.7	234.4
115°	354.4	310.5	295.0	279.4	259.8	248.2	241.3	236.7	241.3	248.2	259.8
117.5°	377.5	333.6	319.2	304.8	282.8	272.5	266.7	260.9	266.7	272.5	282.8
120°	399.4	357.9	343.4	329.0	307.1	295.5	289.8	286.3	289.8	295.5	307.1
122.5°	422.5	382.1	366.6	351.0	330.2	317.5	311.7	308.2	311.7	317.5	330.2
125°	444.5	404.1	388.5	372.9	351.0	338.3	331.3	329.0	331.3	338.3	351.0
127.5°	464.1	424.8	409.2	393.7	369.4	356.7	348.6	345.2	348.6	356.7	369.4
130°	481.4	443.3	427.7	412.1	387.9	374.0	363.7	360.2	363.7	374.0	387.9
132.5°	496.4	459.5	444.5	429.5	405.2	387.9	376.4	371.7	376.4	387.9	405.2
135°	511.4	475.6	460.0	444.5	420.2	402.9	390.2	385.6	390.2	402.9	420.2
137.5°	521.8	487.2	472.8	458.3	434.1	415.6	402.9	398.3	402.9	415.6	434.1
140°	532.2	498.7	484.3	469.9	446.8	428.3	416.8	411.0	416.8	428.3	446.8
142.5°	540.3	508.0	494.7	481.4	458.3	442.2	429.5	424.8	429.5	442.2	458.3
145°	547.2	517.2	503.9	490.6	471.0	453.7	443.3	439.8	443.3	453.7	471.0
147.5°	553.0	525.3	513.8	502.2	482.6	467.6	457.2	454.9	457.2	467.6	482.6
150°	558.8	532.2	521.8	511.4	495.3	480.3	471.0	469.9	471.0	480.3	495.3
152.5°	562.2	540.3	530.5	520.7	506.8	494.1	484.9	484.9	484.9	494.1	506.8
155°	566.8	547.2	539.1	531.0	518.3	506.8	499.9	499.9	499.9	506.8	518.3
157.5°	569.1	553.0	546.6	540.3	528.7	518.3	512.6	511.4	512.6	518.3	528.7
160°	572.6	558.8	553.0	547.2	539.1	529.9	525.3	525.3	525.3	529.9	539.1
162.5°	573.8	562.2	557.6	553.0	546.1	539.1	535.7	535.7	535.7	539.1	546.1
165°	574.9	565.7	561.7	557.6	553.0	547.2	544.9	546.1	544.9	547.2	553.0
167.5°	574.9	568.0	565.1	562.2	558.8	554.1	553.0	554.1	553.0	554.1	558.8
170°	573.8	568.0	566.8	565.7	563.4	559.9	558.8	561.1	558.8	559.9	563.4
172.5°	573.8	569.1	568.6	568.0	566.8	564.5	564.5	565.7	564.5	564.5	566.8
175°	572.6	570.3	569.7	569.1	569.1	566.8	568.0	569.1	568.0	566.8	569.1
177.5°	571.5	570.3	570.3	570.3	570.3	569.1	570.3	571.5	570.3	569.1	570.3
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	770.8	770.0	771.5	767.0	759.4	755.6	745.0	742.7	742.0	742.7	743.5
5°	749.5	748.8	746.5	738.9	729.8	723.0	710.1	709.3	704.8	700.2	702.5
7.5°	729.1	726.0	721.5	711.6	699.5	691.9	681.3	673.7	667.6	663.8	660.8
10°	708.6	704.0	699.5	686.6	671.4	660.0	647.1	641.1	634.2	631.2	628.2
12.5°	682.0	677.5	669.1	654.0	644.9	630.4	617.5	611.5	607.7	601.6	597.8
15°	660.8	651.7	647.1	631.2	612.2	610.7	587.2	585.7	578.1	578.1	572.0
17.5°	636.5	629.7	621.3	605.4	591.7	578.1	566.0	561.4	554.6	553.1	550.0
20°	613.0	603.9	600.9	584.9	570.5	553.8	540.9	536.4	533.3	530.3	532.6
22.5°	588.7	581.1	573.5	559.1	548.5	531.8	524.2	519.7	515.1	513.6	514.4
25°	565.2	558.4	550.8	536.4	525.0	511.3	504.5	502.2	500.0	500.0	499.2
27.5°	542.4	535.6	528.8	515.9	504.5	494.6	489.3	487.1	484.8	486.3	487.8
30°	518.9	512.8	506.8	495.4	486.3	477.2	474.2	472.6	471.9	475.7	475.7
32.5°	497.7	492.4	487.8	477.2	468.1	460.5	458.2	459.0	459.7	462.0	463.5
35°	475.7	471.9	467.3	458.2	450.6	443.8	444.6	444.6	446.1	449.9	452.9
37.5°	455.9	450.6	446.8	439.3	433.2	427.1	429.4	431.7	433.2	437.7	439.3
40°	432.4	430.2	427.1	419.5	414.2	413.5	414.2	415.7	418.8	421.1	423.3
42.5°	413.5	410.4	406.6	400.6	396.0	396.8	397.5	399.1	400.6	404.4	406.6
45°	392.2	389.9	386.9	381.6	377.8	378.6	379.3	379.3	380.8	385.4	386.9
47.5°	368.7	369.5	365.7	360.4	358.1	358.1	358.1	359.6	363.4	364.9	365.7
50°	345.9	344.4	343.7	338.4	336.8	336.1	336.8	337.6	342.9	342.2	344.4
52.5°	321.7	321.7	320.9	317.9	315.6	315.6	314.1	317.9	319.4	320.9	323.2
55°	298.1	295.9	295.1	293.6	290.6	289.8	291.3	295.9	297.4	298.9	301.2
57.5°	272.4	272.4	270.8	268.6	268.6	268.6	268.6	271.6	273.9	275.4	279.9
60°	248.8	245.8	243.5	243.5	243.5	242.8	247.3	247.3	251.9	252.6	254.1
62.5°	220.8	219.2	217.7	218.5	217.7	219.2	220.8	223.8	224.6	226.8	229.1
65°	194.2	194.2	192.7	197.2	194.2	194.2	198.0	198.0	199.5	201.8	204.8
67.5°	168.4	169.2	167.7	167.7	169.2	169.9	170.7	173.7	174.5	177.5	181.3
70°	141.9	143.4	144.1	142.6	144.1	145.7	147.2	147.9	151.0	152.5	154.8
72.5°	118.3	119.9	117.6	118.3	119.1	120.6	121.4	122.9	124.4	129.0	130.5
75°	94.8	94.1	93.3	96.3	94.8	97.9	98.6	98.6	100.1	103.9	105.5
77.5°	72.8	72.8	73.6	72.1	74.3	73.6	74.3	76.6	78.9	78.9	85.0
80°	50.8	52.3	52.3	52.3	53.1	53.9	52.3	56.1	56.9	56.9	59.2
82.5°	32.6	33.4	32.6	34.1	34.1	35.7	34.9	35.7	37.2	38.7	39.4
85°	17.4	17.4	19.0	19.0	18.2	19.0	18.2	19.0	20.5	20.5	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	12.7	13.8	15.0	18.5	21.9	25.4	28.9	27.7	28.9	30.0	31.2
92.5°	58.9	69.3	79.7	116.6	177.8	237.8	214.7	160.5	114.3	88.9	77.3
95°	105.1	127.6	150.1	248.2	420.2	609.5	684.6	555.3	415.6	281.7	220.5
97.5°	121.2	146.0	170.9	267.8	467.6	786.2	1052.9	1088.6	954.7	720.4	568.0
100°	138.5	161.0	183.6	264.4	435.2	738.8	1093.3	1320.7	1361.1	1267.6	1132.5
102.5°	158.2	178.4	198.6	269.0	407.5	669.6	1018.2	1332.2	1496.2	1515.8	1451.1
105°	180.1	198.0	215.9	278.2	397.1	615.3	928.2	1259.5	1500.8	1616.2	1638.2
107.5°	204.3	221.0	237.8	293.2	394.8	576.1	848.5	1155.6	1431.5	1612.8	1702.8
110°	228.6	244.8	260.9	312.9	400.6	555.3	782.7	1058.6	1323.0	1535.4	1680.9

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	254.0	269.6	285.1	332.5	412.1	543.7	738.8	974.4	1215.6	1433.8	1601.2
115°	279.4	295.0	310.5	354.4	424.8	542.6	710.0	909.7	1123.3	1324.2	1493.9
117.5°	304.8	319.2	333.6	377.5	441.0	543.7	690.4	867.0	1051.7	1229.5	1385.3
120°	329.0	343.4	357.9	399.4	459.5	548.4	677.7	834.7	997.4	1153.3	1291.8
122.5°	351.0	366.6	382.1	422.5	476.8	556.4	669.6	808.1	954.7	1092.1	1217.9
125°	372.9	388.5	404.1	444.5	495.3	564.5	662.7	786.2	917.8	1043.6	1154.5
127.5°	393.7	409.2	424.8	464.1	510.3	573.8	659.2	765.4	884.3	998.6	1100.2
130°	412.1	427.7	443.3	481.4	525.3	583.0	655.7	749.2	853.1	957.0	1050.5
132.5°	429.5	444.5	459.5	496.4	539.1	589.9	654.6	734.2	824.3	917.8	1003.2
135°	444.5	460.0	475.6	511.4	550.7	596.9	653.4	721.5	798.9	880.8	955.9
137.5°	458.3	472.8	487.2	521.8	559.9	601.5	651.1	710.0	774.6	843.9	910.9
140°	469.9	484.3	498.7	532.2	566.8	606.1	650.0	699.6	753.9	812.7	868.1
142.5°	481.4	494.7	508.0	540.3	573.8	609.5	647.6	690.4	734.2	782.7	828.9
145°	490.6	503.9	517.2	547.2	578.4	610.7	645.3	682.3	719.2	757.3	794.3
147.5°	502.2	513.8	525.3	553.0	581.8	610.7	641.9	674.2	706.5	737.7	768.9
150°	511.4	521.8	532.2	558.8	583.0	610.7	637.3	666.1	692.7	719.2	743.5
152.5°	520.7	530.5	540.3	562.2	585.3	607.2	631.5	656.9	680.0	701.9	722.7
155°	531.0	539.1	547.2	566.8	585.3	604.9	624.6	647.6	667.3	685.7	703.1
157.5°	540.3	546.6	553.0	569.1	586.5	601.5	618.8	637.3	653.4	669.6	683.4
160°	547.2	553.0	558.8	572.6	586.5	599.2	611.9	626.9	641.9	654.6	666.1
162.5°	553.0	557.6	562.2	573.8	585.3	594.5	604.9	616.5	628.0	638.4	648.8
165°	557.6	561.7	565.7	574.9	583.0	589.9	598.0	607.2	616.5	623.4	631.5
167.5°	562.2	565.1	568.0	574.9	581.8	585.3	591.1	598.0	606.1	611.9	616.5
170°	565.7	566.8	568.0	573.8	578.4	580.7	584.2	589.9	595.7	599.2	603.8
172.5°	568.0	568.6	569.1	573.8	577.2	577.2	578.4	581.8	586.5	588.8	592.2
175°	569.1	569.7	570.3	572.6	574.9	573.8	573.8	576.1	578.4	579.5	581.8
177.5°	570.3	570.3	570.3	571.5	573.8	571.5	570.3	571.5	572.6	573.8	574.9
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	742.7	743.5	740.4	738.2	744.2	740.4	740.4	741.2	739.7	742.0	741.2
5°	701.0	701.8	696.4	698.0	694.9	694.2	693.4	698.0	697.2	696.4	698.0
7.5°	660.0	660.0	657.7	656.2	656.2	654.0	657.0	656.2	657.7	657.7	660.0
10°	625.9	627.4	623.6	619.8	619.1	619.8	619.8	620.6	621.3	626.6	625.9
12.5°	597.8	595.5	594.8	592.5	588.7	587.2	585.7	594.0	591.7	591.7	591.7
15°	566.7	572.0	571.3	564.4	562.9	566.0	564.4	564.4	572.0	571.3	570.5
17.5°	550.0	548.5	547.0	543.2	544.0	543.2	544.0	544.0	548.5	548.5	548.5
20°	531.1	528.0	528.0	526.5	526.5	524.2	527.3	528.0	531.1	531.1	531.8
22.5°	514.4	512.1	512.1	511.3	512.8	509.8	512.8	513.6	513.6	515.9	515.9
25°	500.0	498.4	498.4	500.0	500.0	500.0	500.0	503.0	500.7	501.5	500.7
27.5°	487.1	487.8	488.6	489.3	488.6	489.3	490.1	491.6	492.4	491.6	490.1
30°	474.9	477.2	477.9	477.9	479.5	480.2	481.0	481.0	481.7	479.5	481.0
32.5°	465.8	465.8	467.3	468.1	469.6	470.4	470.4	471.9	471.1	468.8	469.6
35°	452.9	452.9	455.9	457.5	459.7	459.0	459.7	459.7	460.5	459.0	456.7
37.5°	440.0	441.5	441.5	444.6	445.3	446.1	445.3	446.8	446.1	444.6	443.8
40°	424.8	424.1	424.8	427.1	427.9	427.9	427.9	429.4	429.4	429.4	428.6
42.5°	405.9	408.2	407.4	409.7	408.9	408.9	410.4	411.9	412.7	410.4	411.2
45°	387.7	387.7	389.2	389.2	389.9	389.9	393.0	391.5	393.0	391.5	392.2
47.5°	367.9	368.7	368.7	369.5	371.0	372.5	371.0	371.7	371.7	372.5	371.0
50°	345.9	345.9	347.5	349.7	352.8	351.3	350.5	353.5	351.3	351.3	349.7
52.5°	323.2	325.5	326.2	328.5	330.8	331.5	332.3	330.8	331.5	329.3	330.0
55°	301.2	301.9	305.0	307.3	309.5	309.5	308.8	309.5	310.3	307.3	307.3
57.5°	279.2	281.5	284.5	284.5	287.5	287.5	286.8	286.8	287.5	285.3	284.5
60°	255.7	257.9	261.7	261.7	266.3	267.0	265.5	264.0	264.0	261.7	262.5
62.5°	230.6	232.9	235.2	239.0	242.0	240.5	243.5	240.5	241.3	236.7	236.7
65°	208.6	209.4	213.2	217.0	217.0	218.5	217.0	217.7	215.5	215.5	212.4
67.5°	182.8	182.8	186.6	190.4	194.2	194.2	194.2	191.9	191.9	189.7	189.7
70°	160.1	159.3	163.1	165.4	167.7	168.4	166.9	166.1	164.6	162.4	161.6
72.5°	132.0	133.5	137.3	138.8	142.6	141.9	145.7	141.1	141.1	137.3	136.6
75°	107.0	108.5	112.3	114.6	116.8	116.8	119.1	116.8	113.8	112.3	111.5
77.5°	85.0	84.2	87.2	91.0	91.8	91.0	92.6	91.8	88.8	88.8	87.2
80°	60.7	63.0	66.0	65.2	68.3	67.5	67.5	66.0	66.0	63.7	65.2
82.5°	40.2	42.5	43.2	42.5	43.2	44.8	45.5	44.8	44.8	43.2	44.0
85°	21.2	21.2	22.8	23.5	22.8	22.8	23.5	25.8	24.3	22.8	24.3
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	32.4	33.5	32.3	33.5	34.6	33.5	34.6	33.5	32.3	33.5	32.4
92.5°	73.3	69.3	67.0	62.3	63.5	61.2	63.5	62.3	67.0	69.3	73.3
95°	199.7	178.9	157.0	146.6	138.5	133.9	138.5	146.6	157.0	178.9	199.7
97.5°	502.2	436.4	359.0	315.2	287.5	274.8	287.5	315.2	359.0	436.4	502.2
100°	1050.6	968.6	852.0	767.7	722.7	723.8	722.7	767.7	852.0	968.6	1050.6
102.5°	1406.7	1362.3	1278.0	1215.6	1179.8	1146.4	1179.8	1215.6	1278.0	1362.3	1406.7
105°	1623.2	1608.1	1555.0	1511.2	1474.2	1468.5	1474.2	1511.2	1555.0	1608.1	1623.2
107.5°	1718.4	1734.0	1727.1	1706.3	1691.3	1678.6	1691.3	1706.3	1727.1	1734.0	1718.4
110°	1721.3	1761.7	1794.0	1803.3	1800.9	1798.6	1800.9	1803.3	1794.0	1761.7	1721.3



TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1656.0	1710.9	1776.7	1810.2	1821.7	1822.9	1821.7	1810.2	1776.7	1710.9	1656.0
115°	1556.8	1619.7	1706.3	1757.1	1780.2	1785.9	1780.2	1757.1	1706.3	1619.7	1556.8
117.5°	1450.6	1515.8	1605.8	1662.4	1697.0	1705.1	1697.0	1662.4	1605.8	1515.8	1450.6
120°	1350.1	1408.4	1499.6	1564.3	1592.0	1598.9	1592.0	1564.3	1499.6	1408.4	1350.1
122.5°	1271.1	1324.2	1402.7	1459.2	1490.4	1499.6	1490.4	1459.2	1402.7	1324.2	1271.1
125°	1200.6	1246.8	1320.7	1371.5	1400.3	1408.4	1400.3	1371.5	1320.7	1246.8	1200.6
127.5°	1142.9	1185.6	1252.6	1296.4	1323.0	1329.9	1323.0	1296.4	1252.6	1185.6	1142.9
130°	1089.8	1129.1	1190.2	1231.8	1256.0	1265.3	1256.0	1231.8	1190.2	1129.1	1089.8
132.5°	1040.2	1077.1	1133.7	1175.2	1196.0	1201.8	1196.0	1175.2	1133.7	1077.1	1040.2
135°	988.8	1021.7	1078.3	1112.9	1133.7	1141.8	1133.7	1112.9	1078.3	1021.7	988.8
137.5°	940.3	969.7	1018.2	1054.0	1071.3	1078.3	1071.3	1054.0	1018.2	969.7	940.3
140°	893.0	917.8	961.7	994.0	1012.5	1011.3	1012.5	994.0	961.7	917.8	893.0
142.5°	849.7	870.5	906.2	934.0	950.1	949.0	950.1	934.0	906.2	870.5	849.7
145°	811.0	827.7	856.6	880.8	890.1	892.4	890.1	880.8	856.6	827.7	811.0
147.5°	781.0	793.1	816.2	833.5	842.7	843.9	842.7	833.5	816.2	793.1	781.0
150°	754.4	765.4	782.7	795.4	802.3	802.3	802.3	795.4	782.7	765.4	754.4
152.5°	731.4	740.0	752.7	764.2	767.7	767.7	767.7	764.2	752.7	740.0	731.4
155°	710.0	716.9	727.3	736.5	738.8	740.0	738.8	736.5	727.3	716.9	710.0
157.5°	689.2	695.0	704.2	711.1	713.5	713.5	713.5	711.1	704.2	695.0	689.2
160°	670.2	674.2	682.3	689.2	689.2	688.1	689.2	689.2	682.3	674.2	670.2
162.5°	652.2	655.7	660.3	666.1	666.1	665.0	666.1	666.1	660.3	655.7	652.2
165°	634.4	637.3	641.9	646.5	645.3	645.3	645.3	646.5	641.9	637.3	634.4
167.5°	618.8	621.1	623.4	626.9	625.7	625.7	625.7	626.9	623.4	621.1	618.8
170°	605.0	606.1	607.2	609.5	608.4	608.4	608.4	609.5	607.2	606.1	605.0
172.5°	592.8	593.4	593.4	595.7	593.4	592.2	593.4	595.7	593.4	593.4	592.8
175°	581.8	581.8	581.8	583.0	581.8	580.7	581.8	583.0	581.8	581.8	581.8
177.5°	574.9	574.9	573.8	574.9	572.6	572.6	572.6	574.9	573.8	574.9	574.9
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9	782.9
2.5°	743.5	745.0	745.8	742.7	740.4	744.2	749.5	753.3	756.4	760.2	762.4
5°	699.5	704.8	704.8	706.3	708.6	712.4	722.2	729.1	735.1	739.7	743.5
7.5°	662.3	666.1	668.4	672.2	676.0	681.3	692.6	702.5	711.6	716.9	723.0
10°	628.9	632.0	635.7	638.0	644.9	652.4	666.9	675.2	685.8	694.2	701.8
12.5°	597.1	607.7	610.0	609.2	615.3	623.6	638.0	650.9	662.3	670.6	679.0
15°	574.3	578.1	582.6	581.9	594.8	597.1	609.2	624.4	639.5	644.9	652.4
17.5°	549.3	555.3	559.9	562.2	566.0	574.3	585.7	597.1	616.8	617.5	637.3
20°	529.5	535.6	538.6	541.7	544.0	553.8	563.7	576.6	592.5	600.9	611.5
22.5°	516.6	519.7	522.0	524.2	527.3	532.6	544.7	559.1	569.7	578.9	585.7
25°	501.5	504.5	507.5	509.1	511.3	514.4	523.5	534.8	550.0	556.1	562.9
27.5°	490.8	490.8	492.4	492.4	495.4	498.4	505.3	515.9	528.0	535.6	544.7
30°	479.5	478.7	479.5	478.7	477.9	482.5	488.6	497.7	506.0	515.1	521.2
32.5°	468.1	467.3	467.3	468.1	465.1	467.3	470.4	478.7	487.8	492.4	499.2
35°	455.9	454.4	454.4	454.4	452.9	451.4	454.4	462.0	468.1	474.2	479.5
37.5°	443.8	441.5	441.5	440.0	438.5	436.2	436.2	442.3	450.6	452.9	459.7
40°	427.1	427.1	425.6	424.8	423.3	421.8	419.5	424.8	432.4	434.7	440.0
42.5°	410.4	408.2	407.4	407.4	407.4	405.1	403.6	407.4	411.9	415.7	418.8
45°	391.5	389.9	390.7	389.9	388.4	387.7	386.9	388.4	393.7	395.3	399.1
47.5°	371.0	370.2	370.2	369.5	368.7	369.5	366.4	370.2	371.7	373.3	376.3
50°	349.7	349.0	348.2	347.5	347.5	348.2	347.5	347.5	350.5	352.0	355.0
52.5°	328.5	326.2	326.2	325.5	325.5	323.9	325.5	326.2	327.7	329.3	330.8
55°	305.7	305.7	303.5	303.5	301.9	301.9	302.7	301.9	305.0	306.5	306.5
57.5°	283.7	280.7	281.5	279.9	278.4	277.7	277.7	279.2	280.7	280.7	282.2
60°	260.2	257.2	256.4	253.4	254.9	252.6	253.4	253.4	256.4	254.9	256.4
62.5°	236.7	232.9	230.6	229.1	229.1	229.9	228.4	227.6	229.1	230.6	233.7
65°	211.7	209.4	207.1	204.8	204.8	204.1	205.6	203.3	202.6	203.3	204.8
67.5°	185.9	183.6	181.3	179.0	179.8	177.5	176.0	178.3	176.8	177.5	179.0
70°	160.8	159.3	154.8	153.2	152.5	153.2	152.5	151.0	153.2	152.5	153.2
72.5°	135.8	134.3	132.0	128.2	128.2	127.5	126.7	126.7	125.9	125.9	125.9
75°	111.5	108.5	106.2	105.5	103.9	103.2	102.4	100.9	101.7	102.4	100.9
77.5°	86.5	82.7	81.9	81.9	79.7	79.7	80.4	79.7	78.9	78.9	78.9
80°	63.7	60.7	60.7	59.2	57.7	57.7	57.7	57.7	56.9	56.1	56.9
82.5°	41.0	40.2	39.4	39.4	41.0	37.9	39.4	38.7	37.9	37.9	37.2
85°	22.8	23.5	22.8	23.5	22.0	22.8	22.8	22.8	22.0	22.8	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.9	9.1	9.1
90°	31.2	30.0	28.9	27.7	28.9	25.4	21.9	18.5	15.0	13.8	12.7
92.5°	77.3	88.9	114.3	160.5	214.7	237.8	177.8	116.6	79.7	69.3	58.9
95°	220.5	281.7	415.6	555.3	684.6	609.5	420.2	248.2	150.1	127.6	105.1
97.5°	568.0	720.4	954.7	1088.6	1052.9	786.2	467.6	267.8	170.9	146.0	121.2
100°	1132.5	1267.6	1361.1	1320.7	1093.3	738.8	435.2	264.4	183.6	161.0	138.5
102.5°	1451.1	1515.8	1496.2	1332.2	1018.2	669.6	407.5	269.0	198.6	178.4	158.2
105°	1638.2	1616.2	1500.8	1259.5	928.2	615.3	397.1	278.2	215.9	198.0	180.1
107.5°	1702.8	1612.8	1431.5	1155.6	848.5	576.1	394.8	293.2	237.8	221.0	204.3
110°	1680.9	1535.4	1323.0	1058.6	782.7	555.3	400.6	312.9	260.9	244.8	228.6

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1601.2	1433.8	1215.6	974.4	738.8	543.7	412.1	332.5	285.1	269.6	254.0
115°	1493.9	1324.2	1123.3	909.7	710.0	542.6	424.8	354.4	310.5	295.0	279.4
117.5°	1385.3	1229.5	1051.7	867.0	690.4	543.7	441.0	377.5	333.6	319.2	304.8
120°	1291.8	1153.3	997.4	834.7	677.7	548.4	459.5	399.4	357.9	343.4	329.0
122.5°	1217.9	1092.1	954.7	808.1	669.6	556.4	476.8	422.5	382.1	366.6	351.0
125°	1154.5	1043.6	917.8	786.2	662.7	564.5	495.3	444.5	404.1	388.5	372.9
127.5°	1100.2	998.6	884.3	765.4	659.2	573.8	510.3	464.1	424.8	409.2	393.7
130°	1050.5	957.0	853.1	749.2	655.7	583.0	525.3	481.4	443.3	427.7	412.1
132.5°	1003.2	917.8	824.3	734.2	654.6	589.9	539.1	496.4	459.5	444.5	429.5
135°	955.9	880.8	798.9	721.5	653.4	596.9	550.7	511.4	475.6	460.0	444.5
137.5°	910.9	843.9	774.6	710.0	651.1	601.5	559.9	521.8	487.2	472.8	458.3
140°	868.1	812.7	753.9	699.6	650.0	606.1	566.8	532.2	498.7	484.3	469.9
142.5°	828.9	782.7	734.2	690.4	647.6	609.5	573.8	540.3	508.0	494.7	481.4
145°	794.3	757.3	719.2	682.3	645.3	610.7	578.4	547.2	517.2	503.9	490.6
147.5°	768.9	737.7	706.5	674.2	641.9	610.7	581.8	553.0	525.3	513.8	502.2
150°	743.5	719.2	692.7	666.1	637.3	610.7	583.0	558.8	532.2	521.8	511.4
152.5°	722.7	701.9	680.0	656.9	631.5	607.2	585.3	562.2	540.3	530.5	520.7
155°	703.1	685.7	667.3	647.6	624.6	604.9	585.3	566.8	547.2	539.1	531.0
157.5°	683.4	669.6	653.4	637.3	618.8	601.5	586.5	569.1	553.0	546.6	540.3
160°	666.1	654.6	641.9	626.9	611.9	599.2	586.5	572.6	558.8	553.0	547.2
162.5°	648.8	638.4	628.0	616.5	604.9	594.5	585.3	573.8	562.2	557.6	553.0
165°	631.5	623.4	616.5	607.2	598.0	589.9	583.0	574.9	565.7	561.7	557.6
167.5°	616.5	611.9	606.1	598.0	591.1	585.3	581.8	574.9	568.0	565.1	562.2
170°	603.8	599.2	595.7	589.9	584.2	580.7	578.4	573.8	568.0	566.8	565.7
172.5°	592.2	588.8	586.5	581.8	578.4	577.2	577.2	573.8	569.1	568.6	568.0
175°	581.8	579.5	578.4	576.1	573.8	573.8	574.9	572.6	570.3	569.7	569.1
177.5°	574.9	573.8	572.6	571.5	570.3	571.5	573.8	571.5	570.3	570.3	570.3
180°	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3	570.3

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	782.9	782.9	782.9	782.9
2.5°	766.2	768.5	776.1	785.2
5°	751.1	757.1	767.8	782.2
7.5°	734.4	743.5	758.7	776.9
10°	715.4	728.3	747.3	770.0
12.5°	694.9	711.6	735.9	759.4
15°	682.0	698.7	720.7	746.5
17.5°	657.0	676.7	699.5	735.9
20°	631.2	653.2	682.8	719.2
22.5°	611.5	635.0	663.1	701.8
25°	588.0	612.2	642.6	682.8
27.5°	562.9	587.2	621.3	663.8
30°	544.0	567.5	600.1	645.6
32.5°	521.2	544.0	578.1	625.9
35°	495.4	521.2	553.8	602.4
37.5°	475.7	499.2	533.3	579.6
40°	454.4	474.9	508.3	553.8
42.5°	431.7	454.4	483.3	528.8
45°	410.4	427.1	456.7	500.0
47.5°	387.7	406.6	429.4	462.8
50°	363.4	379.3	404.4	427.1
52.5°	339.9	352.8	374.0	391.5
55°	314.8	327.7	343.7	354.3
57.5°	291.3	300.4	311.0	317.9
60°	262.5	271.6	278.4	285.3
62.5°	236.7	243.5	247.3	251.1
65°	210.1	213.9	216.2	219.2
67.5°	181.3	185.1	185.9	190.4
70°	154.8	155.5	157.0	159.3
72.5°	129.7	131.2	130.5	132.0
75°	103.9	105.5	103.9	105.5
77.5°	78.9	80.4	80.4	82.7
80°	56.9	57.7	58.4	58.4
82.5°	37.2	39.4	37.9	38.7
85°	21.2	22.0	22.0	22.8
87.5°	9.9	10.6	9.9	11.4
90°	10.4	6.9	4.6	2.3
92.5°	47.3	36.9	25.4	17.3
95°	75.0	55.4	42.7	39.3
97.5°	91.2	73.9	63.5	62.3
100°	110.8	94.7	86.6	85.4
102.5°	133.9	118.9	112.0	109.7
105°	158.2	144.3	137.4	133.9
107.5°	183.6	169.7	162.8	159.3
110°	209.0	196.3	190.5	187.0

TEST NUMBER: P1011750

CATALOG NUMBER: S123DIP-B560D1195UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	234.4	221.7	215.9	212.4
115°	259.8	248.2	241.3	236.7
117.5°	282.8	272.5	266.7	260.9
120°	307.1	295.5	289.8	286.3
122.5°	330.2	317.5	311.7	308.2
125°	351.0	338.3	331.3	329.0
127.5°	369.4	356.7	348.6	345.2
130°	387.9	374.0	363.7	360.2
132.5°	405.2	387.9	376.4	371.7
135°	420.2	402.9	390.2	385.6
137.5°	434.1	415.6	402.9	398.3
140°	446.8	428.3	416.8	411.0
142.5°	458.3	442.2	429.5	424.8
145°	471.0	453.7	443.3	439.8
147.5°	482.6	467.6	457.2	454.9
150°	495.3	480.3	471.0	469.9
152.5°	506.8	494.1	484.9	484.9
155°	518.3	506.8	499.9	499.9
157.5°	528.7	518.3	512.6	511.4
160°	539.1	529.9	525.3	525.3
162.5°	546.1	539.1	535.7	535.7
165°	553.0	547.2	544.9	546.1
167.5°	558.8	554.1	553.0	554.1
170°	563.4	559.9	558.8	561.1
172.5°	566.8	564.5	564.5	565.7
175°	569.1	566.8	568.0	569.1
177.5°	570.3	569.1	570.3	571.5
180°	570.3	570.3	570.3	570.3

(END OF REPORT)