

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011764

Luminaire Tested: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011764
REPORT IS A COMBINATION OF REPORTS P990037 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6161.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011764

CATALOG NUMBER: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011764

CATALOG NUMBER: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36	36	36
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36	30	30	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25	25	25
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21	21	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18	18	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16	16	16
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14	14	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12	12	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11	11	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10	10	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9182	9182	9182
5°	9204	8865	8852
10°	9122	8564	8477
15°	8996	8253	8069
20°	8851	7906	7664
25°	8663	7541	7232
30°	8457	7162	6776
35°	8241	6776	6324
40°	8015	6370	5880
45°	7767	5975	5415
50°	7514	5535	4949
55°	7190	5075	4476
60°	6857	4569	3974
65°	6541	4021	3449
70°	6090	3413	2837
75°	5440	2703	2202
80°	4696	1900	1557
85°	3660	1022	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7767 cd/sqm

TEST NUMBER: P1011764

CATALOG NUMBER: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	1.3
10°-20°	227.1	3.7
20°-30°	335.4	5.4
30°-40°	391.7	6.4
40°-50°	393.8	6.4
50°-60°	345.9	5.6
60°-70°	257.6	4.2
70°-80°	146.6	2.4
80°-90°	44.7	0.7
90°-100°	91.5	1.5
100°-110°	276.9	4.5
110°-120°	471.4	7.7
120°-130°	620.2	10.1
130°-140°	697.1	11.3
140°-150°	685.3	11.1
150°-160°	577.0	9.4
160°-170°	384.1	6.2
170°-180°	134.5	2.2
0°-30°	642.8	10.4
0°-40°	1034.5	16.8
0°-60°	1774.1	28.8
0°-90°	2223.0	36.1
90°-120°	839.8	13.6
90°-150°	2842.4	46.1
90°-180°	3938.0	63.9
0°-180°	6161.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	853	853	853	853	853	
5°	854	850	842	849	848	81
15°	813	810	800	806	802	229
25°	738	734	724	725	722	340
35°	638	634	624	620	616	399
45°	523	520	510	502	498	404
55°	397	396	386	378	375	355
65°	271	267	260	254	252	267
75°	143	140	138	134	132	153
85°	38	37	37	35	35	41
90°	1	12	27	31	34	8
95°	66	74	83	87	87	73
105°	251	253	264	264	266	269
115°	474	478	476	477	476	470
125°	694	698	696	691	687	619
135°	901	908	907	902	900	694
145°	1093	1095	1099	1098	1093	683
155°	1252	1252	1253	1257	1249	576
165°	1363	1360	1360	1366	1359	384
175°	1418	1413	1413	1420	1412	135
180°	1421	1421	1421	1421	1421	

TEST NUMBER: P1011764

CATALOG NUMBER: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.0	853.0	853.0	853.0	853.0
2.5°	856.7	853.7	845.7	853.0	852.3
5°	853.7	850.1	842.0	849.3	847.9
7.5°	847.1	843.5	835.4	842.0	841.3
10°	838.3	834.7	825.1	831.7	830.3
12.5°	826.6	823.7	814.9	819.3	818.5
15°	812.7	809.7	800.2	806.1	801.7
17.5°	797.3	793.6	784.1	788.5	787.0
20°	779.7	775.3	765.7	768.7	766.5
22.5°	759.9	755.5	745.9	748.1	745.2
25°	737.9	733.5	723.9	724.7	722.5
27.5°	715.1	710.7	700.4	701.2	699.0
30°	690.2	686.5	676.2	676.2	671.1
32.5°	665.2	660.1	652.8	647.6	645.4
35°	638.1	633.7	624.2	619.8	616.1
37.5°	611.0	605.1	595.6	590.4	588.2
40°	582.4	578.0	567.7	561.8	558.9
42.5°	553.8	548.6	538.4	532.5	529.6
45°	523.0	520.0	510.5	501.7	498.0
47.5°	492.9	488.5	479.7	470.9	467.9
50°	462.1	458.4	448.9	440.8	436.4
52.5°	429.8	427.6	417.3	410.7	406.3
55°	396.8	396.1	386.5	378.5	374.8
57.5°	366.0	363.1	355.7	348.4	344.0
60°	332.3	331.5	322.7	316.1	312.5
62.5°	302.2	300.0	291.2	284.6	282.4
65°	270.6	267.0	259.6	253.8	251.6
67.5°	236.9	234.0	228.1	223.0	220.0
70°	206.8	202.4	198.0	192.9	189.2
72.5°	175.3	172.4	167.2	162.8	161.4
75°	143.0	140.1	137.9	134.2	132.0
77.5°	114.4	113.0	110.0	107.1	107.1
80°	86.5	84.3	82.9	82.1	82.1
82.5°	59.4	59.4	59.4	57.9	57.2
85°	38.1	36.7	36.7	35.2	35.2
87.5°	19.1	16.9	16.1	15.4	15.4
90°	1.1	12.3	26.8	31.3	33.5
92.5°	33.5	40.2	46.9	50.2	48.0
95°	65.9	73.7	82.6	87.1	87.1
97.5°	108.3	113.9	120.6	126.2	125.0
100°	151.8	158.5	164.1	167.5	169.7
102.5°	202.1	205.4	213.2	216.6	215.5
105°	251.2	253.4	263.5	263.5	265.7
107.5°	309.3	310.4	314.8	318.2	317.1
110°	362.8	365.1	367.3	371.8	369.5

TEST NUMBER: P1011764

CATALOG NUMBER: S123DIP-B560D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	418.7	419.8	419.8	425.4	425.4
115°	474.5	477.8	475.6	476.7	475.6
117.5°	531.4	532.5	530.3	530.3	527.0
120°	583.9	590.6	585.0	583.9	581.7
122.5°	638.6	643.1	640.8	637.5	634.1
125°	694.4	697.8	695.5	691.1	686.6
127.5°	745.8	752.5	750.3	743.6	739.1
130°	797.1	806.1	802.7	798.3	790.4
132.5°	848.5	857.4	855.2	849.6	844.0
135°	901.0	907.7	906.6	902.1	899.9
137.5°	949.0	954.6	957.9	952.3	949.0
140°	999.2	1004.8	1005.9	1004.8	997.0
142.5°	1045.0	1050.6	1052.8	1051.7	1046.1
145°	1093.0	1095.2	1098.6	1097.5	1093.0
147.5°	1134.3	1138.8	1142.1	1142.1	1135.4
150°	1177.9	1180.1	1182.3	1182.3	1175.6
152.5°	1213.6	1216.9	1218.0	1220.3	1214.7
155°	1251.5	1251.5	1252.7	1257.1	1249.3
157.5°	1283.9	1282.8	1283.9	1288.4	1281.7
160°	1314.1	1311.8	1311.8	1317.4	1312.9
162.5°	1340.9	1337.5	1338.6	1344.2	1336.4
165°	1363.2	1359.8	1359.8	1366.5	1358.7
167.5°	1382.2	1377.7	1378.8	1385.5	1378.8
170°	1397.8	1393.3	1393.3	1401.1	1393.3
172.5°	1410.1	1405.6	1405.6	1412.3	1404.5
175°	1417.9	1413.4	1413.4	1420.1	1412.3
177.5°	1422.4	1417.9	1417.9	1424.6	1416.8
180°	1421.2	1421.2	1421.2	1421.2	1421.2

(END OF REPORT)