

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011791

Luminaire Tested: S123DIP-B560D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011791
REPORT IS A COMBINATION OF REPORTS P990079 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3579.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011791

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011791

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	79	74	69	70	66	62	62	59	56	54	52	49
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1011791

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	2.3
10°-20°	237.2	6.6
20°-30°	350.3	9.8
30°-40°	409.1	11.4
40°-50°	411.3	11.5
50°-60°	361.3	10.1
60°-70°	269.1	7.5
70°-80°	153.1	4.3
80°-90°	44.5	1.2
90°-100°	29.3	0.8
100°-110°	88.5	2.5
110°-120°	150.7	4.2
120°-130°	198.3	5.5
130°-140°	222.9	6.2
140°-150°	219.1	6.1
150°-160°	184.5	5.2
160°-170°	122.8	3.4
170°-180°	43.0	1.2
0°-30°	671.5	18.8
0°-40°	1080.6	30.2
0°-60°	1853.3	51.8
0°-90°	2320.0	64.8
90°-120°	268.5	7.5
90°-150°	908.8	25.4
90°-180°	1259.0	35.2
0°-180°	3579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	0	4	9	10	11	4
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	220	198
135°	288	290	290	288	288	222
145°	350	350	351	351	350	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	452	43
180°	454	454	454	454	454	

TEST NUMBER: P1011791

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	0.4	3.9	8.6	10.0	10.7
92.5°	10.7	12.9	15.0	16.1	15.3
95°	21.1	23.6	26.4	27.8	27.8
97.5°	34.6	36.4	38.6	40.3	40.0
100°	48.5	50.7	52.5	53.5	54.3
102.5°	64.6	65.7	68.2	69.2	68.9
105°	80.3	81.0	84.2	84.2	85.0
107.5°	98.9	99.2	100.7	101.7	101.4
110°	116.0	116.7	117.4	118.9	118.1



TEST NUMBER: P1011791

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.9	134.2	134.2	136.0	136.0
115°	151.7	152.8	152.1	152.4	152.1
117.5°	169.9	170.3	169.5	169.5	168.5
120°	186.7	188.8	187.0	186.7	186.0
122.5°	204.2	205.6	204.9	203.8	202.7
125°	222.0	223.1	222.4	220.9	219.5
127.5°	238.4	240.6	239.9	237.7	236.3
130°	254.9	257.7	256.6	255.2	252.7
132.5°	271.3	274.1	273.4	271.6	269.9
135°	288.1	290.2	289.8	288.4	287.7
137.5°	303.4	305.2	306.3	304.5	303.4
140°	319.5	321.3	321.6	321.3	318.8
142.5°	334.1	335.9	336.6	336.2	334.5
145°	349.5	350.2	351.2	350.9	349.5
147.5°	362.7	364.1	365.2	365.2	363.0
150°	376.6	377.3	378.0	378.0	375.9
152.5°	388.0	389.1	389.4	390.1	388.4
155°	400.1	400.1	400.5	401.9	399.4
157.5°	410.5	410.1	410.5	411.9	409.8
160°	420.1	419.4	419.4	421.2	419.8
162.5°	428.7	427.6	428.0	429.8	427.3
165°	435.8	434.8	434.8	436.9	434.4
167.5°	441.9	440.5	440.8	443.0	440.8
170°	446.9	445.5	445.5	448.0	445.5
172.5°	450.8	449.4	449.4	451.5	449.0
175°	453.3	451.9	451.9	454.0	451.5
177.5°	454.7	453.3	453.3	455.5	453.0
180°	454.4	454.4	454.4	454.4	454.4

(END OF REPORT)