

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011792

Luminaire Tested: S123DIP-B560D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011792
REPORT IS A COMBINATION OF REPORTS P990080 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3650.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011792

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011792

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58
2	92	84	78	72	86	79	74	69	70	65	62	61	58	55	53	51	49
3	84	74	66	60	78	70	63	57	62	56	52	54	50	47	47	44	41
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1011792

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	2.3
10°-20°	237.2	6.5
20°-30°	350.3	9.6
30°-40°	409.1	11.2
40°-50°	411.3	11.3
50°-60°	361.3	9.9
60°-70°	269.1	7.4
70°-80°	153.1	4.2
80°-90°	44.5	1.2
90°-100°	100.2	2.7
100°-110°	280.2	7.7
110°-120°	273.2	7.5
120°-130°	217.6	6.0
130°-140°	171.7	4.7
140°-150°	128.1	3.5
150°-160°	89.4	2.4
160°-170°	52.5	1.4
170°-180°	17.1	0.5
0°-30°	671.5	18.4
0°-40°	1080.6	29.6
0°-60°	1853.3	50.8
0°-90°	2320.0	63.6
90°-120°	653.7	17.9
90°-150°	1171.1	32.1
90°-180°	1330.0	36.4
0°-180°	3650.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	1	4	9	10	10	4
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	220	482	552	72
125°	102	120	205	371	436	90
135°	119	142	202	306	353	92
145°	136	156	200	251	276	85
155°	155	167	193	220	229	71
165°	169	174	185	196	200	48
175°	176	176	178	180	180	17
180°	176	176	176	176	176	

TEST NUMBER: P1011792

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	0.7	4.2	8.9	10.0	10.4
92.5°	5.4	21.4	66.4	22.6	18.9
95°	12.1	39.4	211.8	61.8	41.4
97.5°	19.3	45.2	325.7	155.4	85.0
100°	26.4	49.8	338.2	325.0	223.9
102.5°	33.9	55.2	315.0	435.2	354.6
105°	41.4	61.2	287.1	502.2	454.3
107.5°	49.3	68.4	262.5	531.6	519.3
110°	57.9	75.7	242.1	532.5	556.4



TEST NUMBER: P1011792

CATALOG NUMBER: S123DIP-B560D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.7	83.4	228.6	512.2	563.9
115°	73.2	91.2	219.6	481.6	552.5
117.5°	80.7	98.8	213.6	448.7	527.5
120°	88.6	106.2	209.6	417.6	494.6
122.5°	95.4	113.4	207.1	393.2	463.9
125°	101.8	120.2	205.0	371.4	435.7
127.5°	106.8	126.6	203.9	353.6	411.4
130°	111.4	132.3	202.8	337.2	391.4
132.5°	115.0	137.4	202.5	321.8	371.8
135°	119.3	142.3	202.1	305.8	353.2
137.5°	123.2	146.2	201.4	290.9	333.5
140°	127.1	149.8	201.1	276.2	312.8
142.5°	131.4	153.0	200.3	262.8	293.6
145°	136.1	155.9	199.6	250.9	276.1
147.5°	140.7	158.9	198.6	241.6	261.1
150°	145.3	161.4	197.1	233.4	248.2
152.5°	150.0	164.1	195.3	226.2	237.5
155°	154.6	166.8	193.2	219.6	228.9
157.5°	158.2	169.1	191.4	213.2	220.7
160°	162.5	171.0	189.3	207.4	212.8
162.5°	165.7	172.5	187.1	201.8	205.7
165°	168.9	173.8	185.0	196.2	199.6
167.5°	171.4	174.8	182.8	191.4	193.6
170°	173.6	175.4	180.7	187.2	188.2
172.5°	175.0	175.9	178.9	183.4	183.2
175°	176.1	176.2	177.5	180.0	179.6
177.5°	176.8	176.4	176.4	177.8	177.1
180°	176.4	176.4	176.4	176.4	176.4

(END OF REPORT)