

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012125

Luminaire Tested: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012125
REPORT IS A COMBINATION OF REPORTS P992740 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7452.6 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012125

CATALOG NUMBER: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012125

CATALOG NUMBER: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	83	77	72	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1012125

CATALOG NUMBER: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.1
10°-20°	436.3	5.9
20°-30°	628.2	8.4
30°-40°	707.4	9.5
40°-50°	676.7	9.1
50°-60°	553.9	7.4
60°-70°	373.5	5.0
70°-80°	187.3	2.5
80°-90°	51.7	0.7
90°-100°	277.4	3.7
100°-110°	775.4	10.4
110°-120°	756.1	10.1
120°-130°	602.1	8.1
130°-140°	475.2	6.4
140°-150°	354.6	4.8
150°-160°	247.4	3.3
160°-170°	145.3	1.9
170°-180°	47.3	0.6
0°-30°	1221.3	16.4
0°-40°	1928.7	25.9
0°-60°	3159.3	42.4
0°-90°	3771.7	50.6
90°-120°	1809.0	24.3
90°-150°	3240.9	43.5
90°-180°	3681.0	49.4
0°-180°	7452.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	2	12	25	28	29	7
95°	34	109	586	171	115	36
105°	115	170	795	1389	1257	122
115°	203	252	608	1333	1529	201
125°	282	332	567	1028	1206	250
135°	330	394	559	846	977	255
145°	376	431	552	694	764	236
155°	428	462	535	608	634	197
165°	467	481	512	543	552	132
175°	487	488	491	498	497	46
180°	488	488	488	488	488	

TEST NUMBER: P1012125

CATALOG NUMBER: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	2.0	11.9	24.7	27.7	28.7
92.5°	14.8	59.3	183.8	62.8	52.4
95°	33.6	109.2	586.0	171.0	114.6
97.5°	53.4	125.0	901.3	429.9	235.2
100°	73.1	137.8	935.9	899.4	619.6
102.5°	93.9	152.7	871.6	1204.2	981.3
105°	114.6	169.5	794.6	1389.4	1257.1
107.5°	136.4	189.2	726.4	1471.1	1436.9
110°	160.1	209.5	670.0	1473.5	1539.7

TEST NUMBER: P1012125

CATALOG NUMBER: S123RDIP-B1000D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	230.8	632.5	1417.6	1560.5
115°	202.6	252.5	607.8	1332.6	1528.8
117.5°	223.3	273.2	591.0	1241.8	1459.7
120°	245.1	294.0	580.1	1155.8	1368.7
122.5°	263.9	313.8	573.2	1088.0	1283.8
125°	281.7	332.5	567.3	1027.8	1205.7
127.5°	295.5	350.4	564.3	978.4	1138.5
130°	308.3	366.2	561.3	932.9	1083.1
132.5°	318.2	380.5	560.3	890.4	1028.8
135°	330.1	393.8	559.4	846.4	977.4
137.5°	341.0	404.6	557.4	804.9	923.0
140°	351.8	414.6	556.4	764.4	865.7
142.5°	363.7	423.4	554.4	727.4	812.4
145°	376.5	431.4	552.4	694.2	763.9
147.5°	389.4	439.8	549.5	668.6	722.4
150°	402.2	446.7	545.5	645.8	686.8
152.5°	415.1	454.1	540.6	626.1	657.2
155°	427.9	461.5	534.6	607.8	633.5
157.5°	437.8	468.0	529.7	590.0	610.7
160°	449.7	473.4	523.8	573.7	589.0
162.5°	458.6	477.4	517.8	558.3	569.2
165°	467.4	480.8	511.9	543.0	552.4
167.5°	474.4	483.8	506.0	529.7	535.6
170°	480.3	485.2	500.1	517.8	520.8
172.5°	484.2	486.7	495.1	507.5	507.0
175°	487.2	487.7	491.2	498.1	497.1
177.5°	489.2	488.2	488.2	492.2	490.2
180°	488.2	488.2	488.2	488.2	488.2

(END OF REPORT)