

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012142

Luminaire Tested: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012142
REPORT IS A COMBINATION OF REPORTS P992757 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6978.0 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012142

CATALOG NUMBER: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012142

CATALOG NUMBER: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36
4	75	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	26	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17295	16656	16611
10°	17159	16030	15714
15°	16936	15255	14731
20°	16643	14414	13633
25°	16343	13539	12593
30°	15956	12608	11363
35°	15558	11694	10244
40°	15183	10701	9006
45°	14704	9730	7894
50°	14175	8694	6743
55°	13626	7584	5687
60°	13101	6446	4616
65°	12423	5280	3603
70°	11570	3992	2574
75°	10343	2703	2040
80°	8827	1880	1432
85°	6628	1014	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14704 cd/sqm

TEST NUMBER: P1012142

CATALOG NUMBER: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	2.2
10°-20°	419.5	6.0
20°-30°	604.0	8.7
30°-40°	680.2	9.7
40°-50°	650.6	9.3
50°-60°	532.6	7.6
60°-70°	359.1	5.1
70°-80°	180.1	2.6
80°-90°	49.6	0.7
90°-100°	77.9	1.1
100°-110°	235.7	3.4
110°-120°	401.2	5.7
120°-130°	527.8	7.6
130°-140°	593.3	8.5
140°-150°	583.2	8.4
150°-160°	491.0	7.0
160°-170°	326.9	4.7
170°-180°	114.5	1.6
0°-30°	1174.3	16.8
0°-40°	1854.5	26.6
0°-60°	3037.7	43.5
0°-90°	3626.6	52.0
90°-120°	714.7	10.2
90°-150°	2419.0	34.7
90°-180°	3351.0	48.0
0°-180°	6978.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1582	1594	1591	152
15°	1530	1516	1479	1473	1464	431
25°	1392	1360	1300	1272	1258	640
35°	1205	1158	1077	1021	998	754
45°	990	932	831	757	726	764
55°	752	688	578	502	476	674
65°	514	442	341	277	263	509
75°	272	210	138	125	122	290
85°	69	40	36	34	34	76
90°	1	10	23	27	28	8
95°	56	63	70	74	74	62
105°	214	216	224	224	226	229
115°	404	407	405	406	405	400
125°	591	594	592	588	584	527
135°	767	772	772	768	766	591
145°	930	932	935	934	930	581
155°	1065	1065	1066	1070	1063	490
165°	1160	1157	1157	1163	1156	327
175°	1207	1203	1203	1209	1202	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1012142

CATALOG NUMBER: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1610.6	1605.4	1589.8	1604.1	1601.5
5°	1604.1	1597.6	1582.0	1593.7	1591.1
7.5°	1592.4	1585.9	1566.4	1574.2	1570.3
10°	1576.8	1567.7	1544.3	1545.6	1539.1
12.5°	1554.7	1544.3	1514.4	1513.1	1505.2
15°	1530.0	1515.7	1479.2	1472.7	1463.6
17.5°	1500.0	1484.4	1438.9	1425.9	1412.9
20°	1466.2	1445.4	1396.0	1379.1	1363.4
22.5°	1428.5	1403.8	1350.4	1328.3	1314.0
25°	1392.1	1359.5	1299.7	1272.4	1258.1
27.5°	1347.8	1312.7	1247.7	1211.2	1189.1
30°	1302.3	1263.3	1190.4	1146.2	1125.4
32.5°	1256.8	1211.2	1133.2	1083.7	1061.6
35°	1204.7	1157.9	1077.2	1021.3	997.9
37.5°	1152.7	1101.9	1017.4	954.9	926.3
40°	1103.2	1046.0	953.6	886.0	856.1
42.5°	1047.3	990.1	893.8	818.3	792.3
45°	990.1	931.5	831.3	757.2	726.0
47.5°	934.1	869.1	770.2	689.5	662.2
50°	871.7	810.5	705.1	624.5	594.6
52.5°	815.7	748.1	644.0	559.4	533.4
55°	752.0	688.2	577.6	502.2	476.2
57.5°	694.7	625.8	513.9	442.3	420.2
60°	634.9	563.3	455.3	385.1	363.0
62.5°	575.0	503.5	395.5	330.5	307.0
65°	513.9	442.3	340.9	277.1	262.8
67.5°	452.7	379.9	281.0	232.9	217.3
70°	392.9	322.6	231.6	186.0	171.7
72.5°	333.1	264.1	183.4	148.3	144.4
75°	271.9	209.5	137.9	124.9	122.3
77.5°	216.0	158.7	108.0	100.2	97.6
80°	162.6	109.3	82.0	78.1	75.5
82.5°	111.9	67.7	58.5	54.6	54.6
85°	69.0	40.3	36.4	33.8	33.8
87.5°	31.2	16.9	16.9	15.6	14.3
90°	1.0	10.5	22.8	26.6	28.5
92.5°	28.5	34.2	39.9	42.8	40.9
95°	56.1	62.7	70.3	74.1	74.1
97.5°	92.2	96.9	102.6	107.4	106.4
100°	129.2	134.9	139.7	142.5	144.4
102.5°	172.0	174.8	181.5	184.3	183.4
105°	213.8	215.7	224.2	224.2	226.1
107.5°	263.2	264.1	267.9	270.8	269.8
110°	308.8	310.7	312.6	316.4	314.5

TEST NUMBER: P1012142

CATALOG NUMBER: S123RDIP-B1000D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.3	357.3	357.3	362.0	362.0
115°	403.8	406.7	404.8	405.7	404.8
117.5°	452.3	453.2	451.3	451.3	448.5
120°	496.9	502.6	497.9	496.9	495.0
122.5°	543.5	547.3	545.4	542.5	539.7
125°	591.0	593.8	591.9	588.1	584.3
127.5°	634.7	640.4	638.5	632.8	629.0
130°	678.4	686.0	683.2	679.4	672.7
132.5°	722.1	729.7	727.8	723.1	718.3
135°	766.8	772.5	771.5	767.7	765.8
137.5°	807.6	812.4	815.2	810.5	807.6
140°	850.4	855.1	856.1	855.1	848.5
142.5°	889.3	894.1	896.0	895.0	890.3
145°	930.2	932.1	935.0	934.0	930.2
147.5°	965.4	969.2	972.0	972.0	966.3
150°	1002.4	1004.3	1006.2	1006.2	1000.5
152.5°	1032.8	1035.7	1036.6	1038.5	1033.8
155°	1065.1	1065.1	1066.1	1069.9	1063.2
157.5°	1092.7	1091.7	1092.7	1096.5	1090.8
160°	1118.3	1116.4	1116.4	1121.2	1117.4
162.5°	1141.1	1138.3	1139.2	1144.0	1137.3
165°	1160.1	1157.3	1157.3	1163.0	1156.3
167.5°	1176.3	1172.5	1173.4	1179.1	1173.4
170°	1189.6	1185.8	1185.8	1192.4	1185.8
172.5°	1200.0	1196.2	1196.2	1201.9	1195.3
175°	1206.7	1202.9	1202.9	1208.6	1201.9
177.5°	1210.5	1206.7	1206.7	1212.4	1205.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)