

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012149

Luminaire Tested: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012149
REPORT IS A COMBINATION OF REPORTS P992764 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8027.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012149

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012149

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	89	86	89	86	83	80	72	70	67	59	58	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	41	45	39	35	37	33	30	30	28	25
6	63	51	43	38	58	48	40	35	40	35	31	34	30	27	28	25	22
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1012149

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	1.9
10°-20°	432.5	5.4
20°-30°	622.7	7.8
30°-40°	701.2	8.7
40°-50°	670.7	8.4
50°-60°	549.1	6.8
60°-70°	370.2	4.6
70°-80°	185.7	2.3
80°-90°	51.7	0.6
90°-100°	323.2	4.0
100°-110°	903.3	11.3
110°-120°	880.8	11.0
120°-130°	701.4	8.7
130°-140°	553.6	6.9
140°-150°	413.0	5.1
150°-160°	288.1	3.6
160°-170°	169.3	2.1
170°-180°	55.1	0.7
0°-30°	1210.6	15.1
0°-40°	1911.8	23.8
0°-60°	3131.6	39.0
0°-90°	3739.2	46.6
90°-120°	2107.3	26.3
90°-150°	3775.3	47.0
90°-180°	4288.0	53.4
0°-180°	8027.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	2	14	29	32	33	7
95°	39	127	683	199	134	41
105°	134	197	926	1619	1464	142
115°	236	294	708	1552	1781	234
125°	328	387	661	1197	1404	291
135°	384	459	652	986	1139	297
145°	439	502	644	809	890	275
155°	498	538	623	708	738	229
165°	544	560	596	633	644	153
175°	568	568	572	580	579	54
180°	569	569	569	569	569	

TEST NUMBER: P1012149

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	2.3	13.8	28.8	32.2	33.4
92.5°	17.3	69.1	214.1	73.1	61.0
95°	39.1	127.2	682.7	199.2	133.5
97.5°	62.2	145.6	1049.9	500.8	274.0
100°	85.2	160.6	1090.2	1047.6	721.8
102.5°	109.4	177.8	1015.4	1402.8	1143.2
105°	133.5	197.4	925.6	1618.6	1464.4
107.5°	158.9	220.5	846.1	1713.6	1673.9
110°	186.5	244.0	780.5	1716.5	1793.6

TEST NUMBER: P1012149

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.8	268.8	736.8	1651.4	1817.8
115°	236.0	294.2	708.0	1552.4	1780.9
117.5°	260.2	318.3	688.4	1446.6	1700.4
120°	285.5	342.5	675.8	1346.4	1594.4
122.5°	307.4	365.6	667.7	1267.5	1495.4
125°	328.1	387.4	660.8	1197.2	1404.5
127.5°	344.2	408.2	657.3	1139.7	1326.2
130°	359.2	426.6	653.9	1086.8	1261.7
132.5°	370.7	443.2	652.7	1037.2	1198.4
135°	384.5	458.8	651.6	986.0	1138.6
137.5°	397.2	471.4	649.3	937.6	1075.2
140°	409.8	482.9	648.1	890.4	1008.5
142.5°	423.7	493.3	645.8	847.3	946.3
145°	438.6	502.5	643.5	808.7	889.9
147.5°	453.6	512.3	640.1	778.8	841.5
150°	468.5	520.4	635.5	752.3	800.1
152.5°	483.5	529.0	629.7	729.3	765.6
155°	498.5	537.7	622.8	708.0	737.9
157.5°	510.0	545.1	617.1	687.2	711.5
160°	523.8	551.4	610.1	668.3	686.1
162.5°	534.2	556.0	603.2	650.4	663.1
165°	544.5	560.0	596.3	632.6	643.5
167.5°	552.6	563.5	589.4	617.1	624.0
170°	559.5	565.2	582.5	603.2	606.7
172.5°	564.1	567.0	576.8	591.2	590.6
175°	567.6	568.2	572.2	580.2	579.1
177.5°	569.9	568.7	568.7	573.3	571.0
180°	568.7	568.7	568.7	568.7	568.7

(END OF REPORT)