

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012161

Luminaire Tested: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012161
REPORT IS A COMBINATION OF REPORTS P992786 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8131.1 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012161

CATALOG NUMBER: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012161

CATALOG NUMBER: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	89	86	89	86	83	80	72	70	67	59	58	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	41	45	39	35	37	33	30	30	28	25
6	63	51	43	38	58	48	40	35	40	35	31	34	30	27	28	25	22
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1012161

CATALOG NUMBER: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	1.9
10°-20°	438.1	5.4
20°-30°	630.8	7.8
30°-40°	710.4	8.7
40°-50°	679.5	8.4
50°-60°	556.3	6.8
60°-70°	375.0	4.6
70°-80°	188.1	2.3
80°-90°	52.4	0.6
90°-100°	327.3	4.0
100°-110°	914.9	11.3
110°-120°	892.1	11.0
120°-130°	710.4	8.7
130°-140°	560.8	6.9
140°-150°	418.4	5.1
150°-160°	291.8	3.6
160°-170°	171.5	2.1
170°-180°	55.8	0.7
0°-30°	1226.5	15.1
0°-40°	1936.9	23.8
0°-60°	3172.7	39.0
0°-90°	3788.2	46.6
90°-120°	2134.3	26.2
90°-150°	3823.8	47.0
90°-180°	4343.0	53.4
0°-180°	8131.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	2	14	29	33	34	7
95°	40	129	691	202	135	42
105°	135	200	938	1639	1483	144
115°	239	298	717	1572	1804	237
125°	332	392	669	1213	1422	295
135°	389	465	660	999	1153	301
145°	444	509	652	819	901	278
155°	505	545	631	717	747	232
165°	552	567	604	641	652	155
175°	575	575	580	588	586	55
180°	576	576	576	576	576	

TEST NUMBER: P1012161

CATALOG NUMBER: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	2.3	14.0	29.2	32.6	33.8
92.5°	17.5	70.0	216.9	74.0	61.8
95°	39.6	128.8	691.4	201.7	135.3
97.5°	63.0	147.5	1063.4	507.2	277.5
100°	86.3	162.6	1104.2	1061.1	731.1
102.5°	110.8	180.1	1028.4	1420.8	1157.9
105°	135.3	200.0	937.5	1639.4	1483.2
107.5°	160.9	223.3	857.0	1735.6	1695.4
110°	188.9	247.2	790.6	1738.5	1816.6

TEST NUMBER: P1012161

CATALOG NUMBER: S123RDIP-B1000D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.5	272.2	746.2	1672.6	1841.1
115°	239.0	298.0	717.1	1572.4	1803.8
117.5°	263.5	322.4	697.3	1465.1	1722.2
120°	289.2	346.9	684.4	1363.6	1614.9
122.5°	311.3	370.2	676.3	1283.8	1514.7
125°	332.3	392.4	669.3	1212.6	1422.5
127.5°	348.6	413.4	665.8	1154.4	1343.2
130°	363.8	432.0	662.3	1100.8	1278.0
132.5°	375.5	449.0	661.1	1050.6	1213.8
135°	389.4	464.6	660.0	998.7	1153.2
137.5°	402.3	477.5	657.6	949.8	1089.1
140°	415.1	489.2	656.5	901.9	1021.4
142.5°	429.1	499.6	654.1	858.2	958.5
145°	444.3	509.0	651.8	819.1	901.3
147.5°	459.4	518.8	648.3	788.8	852.4
150°	474.6	527.0	643.6	762.0	810.4
152.5°	489.7	535.8	637.8	738.6	775.4
155°	504.9	544.6	630.8	717.1	747.4
157.5°	516.5	552.1	625.0	696.1	720.6
160°	530.5	558.6	618.0	676.9	694.9
162.5°	541.0	563.2	611.0	658.8	671.6
165°	551.5	567.2	604.0	640.7	651.8
167.5°	559.7	570.8	597.0	625.0	632.0
170°	566.7	572.5	590.0	611.0	614.5
172.5°	571.3	574.2	584.2	598.8	598.2
175°	574.8	575.4	579.5	587.7	586.5
177.5°	577.2	576.0	576.0	580.7	578.3
180°	576.0	576.0	576.0	576.0	576.0

(END OF REPORT)