

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012178

Luminaire Tested: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012178
REPORT IS A COMBINATION OF REPORTS P992803 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4980.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012178

CATALOG NUMBER: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012178

CATALOG NUMBER: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	104	100	96	92	99	95	92	88	86	84	81	78	76	74	71	69	68
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50
4	80	69	61	55	76	66	59	53	60	54	50	55	50	47	50	47	43
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	41	38
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1012178

CATALOG NUMBER: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	3.1
10°-20°	432.5	8.7
20°-30°	622.7	12.5
30°-40°	701.2	14.1
40°-50°	670.7	13.5
50°-60°	549.1	11.0
60°-70°	370.2	7.4
70°-80°	185.7	3.7
80°-90°	49.5	1.0
90°-100°	28.9	0.6
100°-110°	87.4	1.8
110°-120°	148.8	3.0
120°-130°	195.8	3.9
130°-140°	220.0	4.4
140°-150°	216.3	4.3
150°-160°	182.1	3.7
160°-170°	121.2	2.4
170°-180°	42.5	0.9
0°-30°	1210.6	24.3
0°-40°	1911.8	38.4
0°-60°	3131.6	62.9
0°-90°	3737.0	75.0
90°-120°	265.1	5.3
90°-150°	897.2	18.0
90°-180°	1243.0	25.0
0°-180°	4980.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	0	4	8	10	11	6
95°	21	23	26	28	28	23
105°	79	80	83	83	84	85
115°	150	151	150	150	150	148
125°	219	220	220	218	217	195
135°	284	286	286	285	284	219
145°	345	346	347	346	345	216
155°	395	395	395	397	394	182
165°	430	429	429	431	429	121
175°	448	446	446	448	446	43
180°	449	449	449	449	449	

TEST NUMBER: P1012178

CATALOG NUMBER: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.4	3.9	8.5	9.9	10.6
92.5°	10.6	12.7	14.8	15.9	15.2
95°	20.8	23.3	26.1	27.5	27.5
97.5°	34.2	35.9	38.1	39.8	39.5
100°	47.9	50.0	51.8	52.9	53.6
102.5°	63.8	64.8	67.3	68.4	68.0
105°	79.3	80.0	83.2	83.2	83.9
107.5°	97.6	98.0	99.4	100.4	100.1
110°	114.5	115.2	115.9	117.4	116.6

TEST NUMBER: P1012178

CATALOG NUMBER: S123RDIP-B1000D365UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.2	132.5	132.5	134.3	134.3
115°	149.8	150.8	150.1	150.5	150.1
117.5°	167.7	168.1	167.4	167.4	166.3
120°	184.3	186.4	184.7	184.3	183.6
122.5°	201.6	203.0	202.3	201.2	200.2
125°	219.2	220.3	219.6	218.1	216.7
127.5°	235.4	237.5	236.8	234.7	233.3
130°	251.6	254.4	253.4	252.0	249.5
132.5°	267.8	270.7	269.9	268.2	266.4
135°	284.4	286.5	286.2	284.8	284.0
137.5°	299.6	301.3	302.4	300.6	299.6
140°	315.4	317.2	317.5	317.2	314.7
142.5°	329.9	331.6	332.3	332.0	330.2
145°	345.0	345.7	346.8	346.4	345.0
147.5°	358.1	359.5	360.5	360.5	358.4
150°	371.8	372.5	373.2	373.2	371.1
152.5°	383.1	384.1	384.5	385.2	383.4
155°	395.1	395.1	395.4	396.8	394.4
157.5°	405.3	404.9	405.3	406.7	404.6
160°	414.8	414.1	414.1	415.8	414.4
162.5°	423.2	422.2	422.5	424.3	421.8
165°	430.3	429.2	429.2	431.4	428.9
167.5°	436.3	434.9	435.2	437.3	435.2
170°	441.2	439.8	439.8	442.3	439.8
172.5°	445.1	443.7	443.7	445.8	443.3
175°	447.6	446.2	446.2	448.3	445.8
177.5°	449.0	447.6	447.6	449.7	447.2
180°	448.6	448.6	448.6	448.6	448.6

(END OF REPORT)