

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012185

Luminaire Tested: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012185
REPORT IS A COMBINATION OF REPORTS P992820 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5094.1 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012185

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012185

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	99	96	92	98	95	91	88	86	83	81	77	75	74	70	68	67
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	57
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	49	55	50	46	50	46	43
5	73	62	53	47	70	59	52	46	54	48	43	49	44	40	45	41	38
6	68	56	47	41	64	53	46	40	49	43	38	45	40	36	41	37	33
7	63	51	42	37	60	48	41	36	45	38	34	41	36	32	38	33	30
8	59	46	38	33	56	44	37	32	41	35	30	38	32	29	35	30	27
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	32	28	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1012185

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	3.1
10°-20°	436.3	8.6
20°-30°	628.2	12.3
30°-40°	707.4	13.9
40°-50°	676.7	13.3
50°-60°	553.9	10.9
60°-70°	373.5	7.3
70°-80°	187.3	3.7
80°-90°	50.0	1.0
90°-100°	99.8	2.0
100°-110°	278.9	5.5
110°-120°	272.0	5.3
120°-130°	216.6	4.3
130°-140°	171.0	3.4
140°-150°	127.6	2.5
150°-160°	89.0	1.7
160°-170°	52.3	1.0
170°-180°	17.0	0.3
0°-30°	1221.3	24.0
0°-40°	1928.7	37.9
0°-60°	3159.3	62.0
0°-90°	3770.0	74.0
90°-120°	650.7	12.8
90°-150°	1165.8	22.9
90°-180°	1324.0	26.0
0°-180°	5094.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	1	4	9	10	10	5
95°	12	39	211	62	41	13
105°	41	61	286	500	452	44
115°	73	91	219	479	550	72
125°	101	120	204	370	434	90
135°	119	142	201	304	352	92
145°	135	155	199	250	275	85
155°	154	166	192	219	228	71
165°	168	173	184	195	199	47
175°	175	175	177	179	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1012185

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	0.7	4.2	8.9	10.0	10.3
92.5°	5.3	21.3	66.1	22.6	18.8
95°	12.1	39.3	210.8	61.5	41.2
97.5°	19.2	45.0	324.2	154.6	84.6
100°	26.3	49.6	336.7	323.6	222.9
102.5°	33.8	54.9	313.6	433.2	353.0
105°	41.2	61.0	285.8	499.8	452.2
107.5°	49.1	68.0	261.3	529.2	516.9
110°	57.6	75.4	241.0	530.0	553.9



TEST NUMBER: P1012185

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.0	227.5	510.0	561.3
115°	72.9	90.8	218.6	479.4	550.0
117.5°	80.3	98.3	212.6	446.7	525.1
120°	88.2	105.8	208.7	415.8	492.4
122.5°	94.9	112.9	206.2	391.5	461.8
125°	101.3	119.6	204.1	369.7	433.7
127.5°	106.3	126.0	203.0	352.0	409.5
130°	110.9	131.7	201.9	335.6	389.6
132.5°	114.5	136.8	201.6	320.3	370.1
135°	118.7	141.7	201.2	304.5	351.6
137.5°	122.6	145.6	200.5	289.6	332.0
140°	126.6	149.1	200.1	275.0	311.4
142.5°	130.8	152.3	199.4	261.7	292.2
145°	135.4	155.2	198.7	249.8	274.8
147.5°	140.1	158.2	197.7	240.5	259.9
150°	144.7	160.7	196.2	232.3	247.1
152.5°	149.3	163.4	194.5	225.2	236.4
155°	153.9	166.0	192.3	218.6	227.9
157.5°	157.5	168.4	190.6	212.2	219.7
160°	161.8	170.3	188.4	206.4	211.9
162.5°	165.0	171.7	186.3	200.9	204.8
165°	168.2	173.0	184.2	195.4	198.7
167.5°	170.6	174.0	182.0	190.6	192.7
170°	172.8	174.6	179.9	186.2	187.4
172.5°	174.2	175.1	178.1	182.6	182.4
175°	175.3	175.4	176.7	179.2	178.8
177.5°	176.0	175.6	175.6	177.0	176.3
180°	175.6	175.6	175.6	175.6	175.6

(END OF REPORT)