

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011876

Luminaire Tested: S123DIP-B560D805UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011876
REPORT IS A COMBINATION OF REPORTS P990200 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5177.7 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011876

CATALOG NUMBER: S123DIP-B560D805UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011876

CATALOG NUMBER: S123DIP-B560D805UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1011876

CATALOG NUMBER: S123DIP-B560D805UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.6
10°-20°	237.2	4.6
20°-30°	350.3	6.8
30°-40°	409.1	7.9
40°-50°	411.3	7.9
50°-60°	361.3	7.0
60°-70°	269.1	5.2
70°-80°	153.1	3.0
80°-90°	45.7	0.9
90°-100°	215.3	4.2
100°-110°	601.8	11.6
110°-120°	586.8	11.3
120°-130°	467.2	9.0
130°-140°	368.8	7.1
140°-150°	275.2	5.3
150°-160°	192.0	3.7
160°-170°	112.8	2.2
170°-180°	36.7	0.7
0°-30°	671.5	13.0
0°-40°	1080.6	20.9
0°-60°	1853.3	35.8
0°-90°	2321.1	44.8
90°-120°	1403.9	27.1
90°-150°	2515.1	48.6
90°-180°	2857.0	55.2
0°-180°	5177.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	2	9	19	21	22	5
95°	26	85	455	133	89	28
105°	89	132	617	1078	976	94
115°	157	196	472	1034	1186	156
125°	219	258	440	798	936	194
135°	256	306	434	657	758	198
145°	292	335	429	539	593	183
155°	332	358	415	472	492	153
165°	363	373	397	421	429	102
175°	378	378	381	386	386	36
180°	379	379	379	379	379	

TEST NUMBER: P1011876

CATALOG NUMBER: S123DIP-B560D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	1.5	9.2	19.2	21.4	22.2
92.5°	11.5	46.0	142.7	48.7	40.6
95°	26.1	84.8	454.8	132.7	89.0
97.5°	41.4	97.0	699.5	333.6	182.5
100°	56.8	107.0	726.3	698.0	480.9
102.5°	72.9	118.5	676.4	934.5	761.6
105°	89.0	131.5	616.6	1078.4	975.6
107.5°	105.8	146.8	563.7	1141.6	1115.1
110°	124.2	162.6	520.0	1143.6	1194.9

TEST NUMBER: P1011876

CATALOG NUMBER: S123DIP-B560D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.1	179.0	490.8	1100.2	1211.0
115°	157.2	196.0	471.7	1034.2	1186.5
117.5°	173.3	212.0	458.6	963.6	1132.8
120°	190.2	228.2	450.2	897.0	1062.2
122.5°	204.8	243.6	444.8	844.4	996.3
125°	218.6	258.0	440.2	797.6	935.7
127.5°	229.3	271.8	437.9	759.3	883.5
130°	239.3	284.2	435.6	724.0	840.6
132.5°	247.0	295.2	434.9	691.0	798.4
135°	256.2	305.6	434.1	656.8	758.5
137.5°	264.6	314.1	432.6	624.7	716.3
140°	273.0	321.7	431.8	593.2	671.8
142.5°	282.2	328.6	430.3	564.5	630.4
145°	292.2	334.8	428.7	538.8	592.8
147.5°	302.2	341.3	426.4	518.8	560.6
150°	312.1	346.7	423.4	501.2	533.0
152.5°	322.1	352.4	419.5	485.8	510.0
155°	332.1	358.2	414.9	471.7	491.6
157.5°	339.8	363.2	411.1	457.8	474.0
160°	349.0	367.4	406.5	445.2	457.1
162.5°	355.9	370.4	401.9	433.3	441.8
165°	362.8	373.1	397.3	421.4	428.7
167.5°	368.1	375.4	392.7	411.0	415.7
170°	372.7	376.6	388.1	401.8	404.2
172.5°	375.8	377.7	384.2	393.8	393.4
175°	378.1	378.5	381.2	386.5	385.8
177.5°	379.6	378.9	378.9	381.9	380.4
180°	378.9	378.9	378.9	378.9	378.9

(END OF REPORT)