

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011885

Luminaire Tested: S123DIP-B560D805UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011885
REPORT IS A COMBINATION OF REPORTS P990209 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D805UB40-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5125.6 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011885

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011885

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1011885

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.6
10°-20°	234.8	4.6
20°-30°	346.8	6.8
30°-40°	405.1	7.9
40°-50°	407.2	7.9
50°-60°	357.7	7.0
60°-70°	266.4	5.2
70°-80°	151.6	3.0
80°-90°	45.2	0.9
90°-100°	213.1	4.2
100°-110°	595.7	11.6
110°-120°	580.8	11.3
120°-130°	462.5	9.0
130°-140°	365.1	7.1
140°-150°	272.4	5.3
150°-160°	190.0	3.7
160°-170°	111.6	2.2
170°-180°	36.3	0.7
0°-30°	664.8	13.0
0°-40°	1069.9	20.9
0°-60°	1834.9	35.8
0°-90°	2298.1	44.8
90°-120°	1389.6	27.1
90°-150°	2489.6	48.6
90°-180°	2828.0	55.2
0°-180°	5125.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	2	9	19	21	22	5
95°	26	84	450	131	88	27
105°	88	130	610	1067	966	94
115°	156	194	467	1024	1174	154
125°	216	255	436	790	926	192
135°	254	303	430	650	751	196
145°	289	331	424	533	587	181
155°	329	354	411	467	487	151
165°	359	369	393	417	424	101
175°	374	375	377	383	382	36
180°	375	375	375	375	375	

TEST NUMBER: P1011885

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	1.5	9.2	19.0	21.2	22.0
92.5°	11.4	45.6	141.2	48.2	40.2
95°	25.8	83.9	450.2	131.4	88.1
97.5°	41.0	96.1	692.3	330.2	180.7
100°	56.2	105.9	718.9	690.8	476.0
102.5°	72.1	117.3	669.6	925.0	753.8
105°	88.1	130.2	610.4	1067.4	965.6
107.5°	104.8	145.4	558.0	1130.0	1103.8
110°	123.0	161.0	514.7	1131.9	1182.7

TEST NUMBER: P1011885

CATALOG NUMBER: S123DIP-B560D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.7	177.2	485.9	1089.0	1198.7
115°	155.6	194.0	466.9	1023.7	1174.4
117.5°	171.6	209.9	454.0	953.9	1121.3
120°	188.3	225.8	445.6	887.8	1051.4
122.5°	202.7	241.0	440.3	835.8	986.1
125°	216.4	255.4	435.7	789.5	926.2
127.5°	227.0	269.2	433.5	751.6	874.5
130°	236.9	281.2	431.2	716.6	832.0
132.5°	244.4	292.2	430.4	684.0	790.3
135°	253.6	302.6	429.7	650.2	750.8
137.5°	261.9	310.9	428.2	618.4	709.0
140°	270.3	318.5	427.4	587.2	665.0
142.5°	279.4	325.3	425.9	558.8	624.0
145°	289.2	331.4	424.4	533.3	586.8
147.5°	299.1	337.8	422.1	513.6	554.9
150°	309.0	343.2	419.0	496.1	527.6
152.5°	318.8	348.8	415.3	480.9	504.8
155°	328.7	354.5	410.7	466.8	486.6
157.5°	336.3	359.5	406.9	453.2	469.2
160°	345.4	363.6	402.3	440.6	452.5
162.5°	352.2	366.6	397.8	428.9	437.3
165°	359.1	369.4	393.2	417.2	424.4
167.5°	364.4	371.6	388.7	406.9	411.5
170°	368.9	372.8	384.1	397.8	400.1
172.5°	372.0	373.9	380.3	389.8	389.4
175°	374.3	374.6	377.3	382.6	381.9
177.5°	375.8	375.0	375.0	378.1	376.5
180°	375.0	375.0	375.0	375.0	375.0

(END OF REPORT)