

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012207

Luminaire Tested: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012207
REPORT IS A COMBINATION OF REPORTS P992844 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5847.9 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012207

CATALOG NUMBER: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012207

CATALOG NUMBER: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59
2	93	85	79	74	87	80	75	70	71	67	63	63	59	57	55	52	50
3	85	75	68	62	79	71	65	59	63	58	54	56	52	48	49	46	43
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21
10	50	38	30	26	47	36	29	25	32	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1012207

CATALOG NUMBER: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.7
10°-20°	432.5	7.4
20°-30°	622.7	10.6
30°-40°	701.2	12.0
40°-50°	670.7	11.5
50°-60°	549.1	9.4
60°-70°	370.2	6.3
70°-80°	185.7	3.2
80°-90°	50.1	0.9
90°-100°	159.1	2.7
100°-110°	444.6	7.6
110°-120°	433.5	7.4
120°-130°	345.2	5.9
130°-140°	272.5	4.7
140°-150°	203.3	3.5
150°-160°	141.8	2.4
160°-170°	83.3	1.4
170°-180°	27.1	0.5
0°-30°	1210.6	20.7
0°-40°	1911.8	32.7
0°-60°	3131.6	53.6
0°-90°	3737.6	63.9
90°-120°	1037.2	17.7
90°-150°	1858.1	31.8
90°-180°	2110.0	36.1
0°-180°	5847.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	1	7	14	16	16	6
95°	19	63	336	98	66	20
105°	66	97	456	797	721	70
115°	116	145	348	764	876	115
125°	162	191	325	589	691	143
135°	189	226	321	485	560	146
145°	216	247	317	398	438	135
155°	245	265	306	348	363	113
165°	268	276	294	311	317	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1012207

CATALOG NUMBER: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	1.1	6.8	14.2	15.8	16.4
92.5°	8.5	34.0	105.4	36.0	30.0
95°	19.3	62.6	336.0	98.0	65.7
97.5°	30.6	71.7	516.7	246.5	134.9
100°	41.9	79.0	536.6	515.6	355.3
102.5°	53.8	87.6	499.7	690.4	562.6
105°	65.7	97.2	455.5	796.6	720.7
107.5°	78.2	108.5	416.5	843.4	823.8
110°	91.8	120.2	384.2	844.8	882.8



TEST NUMBER: P1012207

CATALOG NUMBER: S123RDIP-B1000D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.3	132.4	362.6	812.8	894.7
115°	116.2	144.8	348.5	764.0	876.5
117.5°	128.1	156.6	338.8	711.9	836.9
120°	140.5	168.6	332.6	662.6	784.7
122.5°	151.3	179.8	328.6	623.8	736.0
125°	161.5	190.6	325.2	589.2	691.3
127.5°	169.4	200.8	323.5	561.0	652.7
130°	176.8	210.0	321.8	534.8	621.0
132.5°	182.4	218.2	321.3	510.5	589.8
135°	189.2	225.8	320.7	485.2	560.4
137.5°	195.5	232.0	319.6	461.4	529.2
140°	201.7	237.7	319.0	438.2	496.3
142.5°	208.5	242.8	317.9	417.0	465.7
145°	215.9	247.3	316.7	398.0	438.0
147.5°	223.2	252.2	315.0	383.4	414.2
150°	230.6	256.1	312.8	370.3	393.8
152.5°	238.0	260.4	309.9	359.0	376.8
155°	245.3	264.6	306.5	348.5	363.2
157.5°	251.0	268.3	303.7	338.2	350.2
160°	257.8	271.4	300.3	328.9	337.7
162.5°	262.9	273.6	296.9	320.1	326.4
165°	268.0	275.6	293.5	311.4	316.7
167.5°	272.0	277.4	290.1	303.7	307.1
170°	275.4	278.2	286.7	296.9	298.6
172.5°	277.6	279.0	283.9	291.0	290.7
175°	279.3	279.6	281.6	285.6	285.0
177.5°	280.5	279.9	279.9	282.2	281.0
180°	279.9	279.9	279.9	279.9	279.9

(END OF REPORT)