

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011902

Luminaire Tested: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011902
REPORT IS A COMBINATION OF REPORTS P990226 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6617.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011902

CATALOG NUMBER: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011902

CATALOG NUMBER: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13065	13065	13065
5°	13097	12615	12595
10°	12981	12187	12063
15°	12801	11744	11481
20°	12593	11250	10906
25°	12326	10730	10290
30°	12033	10192	9643
35°	11726	9642	9000
40°	11405	9065	8367
45°	11051	8502	7706
50°	10692	7875	7042
55°	10230	7222	6369
60°	9756	6501	5654
65°	9309	5723	4908
70°	8667	4858	4038
75°	7741	3846	3135
80°	6688	2702	2217
85°	5216	1454	1110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11051 cd/sqm

TEST NUMBER: P1011902

CATALOG NUMBER: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	1.7
10°-20°	323.1	4.9
20°-30°	477.2	7.2
30°-40°	557.3	8.4
40°-50°	560.3	8.5
50°-60°	492.2	7.4
60°-70°	366.6	5.5
70°-80°	208.6	3.2
80°-90°	61.9	0.9
90°-100°	80.3	1.2
100°-110°	243.0	3.7
110°-120°	413.6	6.3
120°-130°	544.2	8.2
130°-140°	611.7	9.2
140°-150°	601.3	9.1
150°-160°	506.3	7.7
160°-170°	337.0	5.1
170°-180°	118.0	1.8
0°-30°	914.7	13.8
0°-40°	1472.1	22.2
0°-60°	2524.5	38.2
0°-90°	3161.6	47.8
90°-120°	736.9	11.1
90°-150°	2494.0	37.7
90°-180°	3455.0	52.2
0°-180°	6617.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1214	1214	1214	1214	1214	
5°	1215	1210	1198	1209	1206	115
15°	1156	1152	1139	1147	1141	326
25°	1050	1044	1030	1031	1028	484
35°	908	902	888	882	877	568
45°	744	740	726	714	709	574
55°	565	564	550	538	533	506
65°	385	380	370	361	358	380
75°	204	199	196	191	188	217
85°	54	52	52	50	50	58
90°	1	11	24	27	29	8
95°	58	65	72	76	76	64
105°	220	222	231	231	233	236
115°	416	419	417	418	417	412
125°	609	612	610	606	602	543
135°	791	796	796	792	790	609
145°	959	961	964	963	959	599
155°	1098	1098	1099	1103	1096	506
165°	1196	1193	1193	1199	1192	337
175°	1244	1240	1240	1246	1239	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1011902

CATALOG NUMBER: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1213.8	1213.8	1213.8	1213.8	1213.8
2.5°	1219.0	1214.8	1203.4	1213.8	1212.8
5°	1214.8	1209.6	1198.2	1208.6	1206.5
7.5°	1205.5	1200.2	1188.8	1198.2	1197.1
10°	1192.9	1187.7	1174.1	1183.5	1181.5
12.5°	1176.2	1172.1	1159.5	1165.8	1164.8
15°	1156.4	1152.2	1138.7	1147.0	1140.7
17.5°	1134.5	1129.3	1115.7	1122.0	1119.9
20°	1109.4	1103.2	1089.6	1093.8	1090.7
22.5°	1081.3	1075.0	1061.4	1064.6	1060.4
25°	1049.9	1043.7	1030.1	1031.2	1028.0
27.5°	1017.6	1011.3	996.7	997.8	994.6
30°	982.1	976.9	962.3	962.3	955.0
32.5°	946.6	939.3	928.9	921.6	918.4
35°	908.0	901.7	888.2	881.9	876.7
37.5°	869.4	861.0	847.5	840.2	837.0
40°	828.7	822.4	807.8	799.5	795.3
42.5°	788.0	780.7	766.1	757.7	753.5
45°	744.1	740.0	726.4	713.9	708.7
47.5°	701.4	695.1	682.6	670.0	665.9
50°	657.5	652.3	638.7	627.3	621.0
52.5°	611.6	608.5	593.9	584.5	578.2
55°	564.6	563.6	550.0	538.5	533.3
57.5°	520.8	516.6	506.2	495.8	489.5
60°	472.8	471.7	459.2	449.8	444.6
62.5°	430.0	426.9	414.3	404.9	401.8
65°	385.1	379.9	369.5	361.1	358.0
67.5°	337.1	332.9	324.6	317.3	313.1
70°	294.3	288.1	281.8	274.5	269.3
72.5°	249.4	245.3	238.0	231.7	229.6
75°	203.5	199.3	196.2	191.0	187.9
77.5°	162.8	160.7	156.6	152.4	152.4
80°	123.2	120.0	117.9	116.9	116.9
82.5°	84.5	84.5	84.5	82.5	81.4
85°	54.3	52.2	52.2	50.1	50.1
87.5°	27.1	24.0	23.0	21.9	21.9
90°	1.0	10.8	23.5	27.4	29.4
92.5°	29.4	35.3	41.1	44.1	42.1
95°	57.8	64.7	72.5	76.4	76.4
97.5°	95.0	99.9	105.8	110.7	109.7
100°	133.2	139.1	144.0	146.9	148.9
102.5°	177.3	180.2	187.1	190.0	189.1
105°	220.4	222.4	231.2	231.2	233.1
107.5°	271.4	272.3	276.3	279.2	278.2
110°	318.4	320.3	322.3	326.2	324.3

TEST NUMBER: P1011902

CATALOG NUMBER: S123DIP-B775D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	367.4	368.3	368.3	373.2	373.2
115°	416.3	419.3	417.3	418.3	417.3
117.5°	466.3	467.3	465.3	465.3	462.4
120°	512.3	518.2	513.3	512.3	510.4
122.5°	560.3	564.3	562.3	559.4	556.4
125°	609.3	612.3	610.3	606.4	602.5
127.5°	654.4	660.3	658.3	652.4	648.5
130°	699.4	707.3	704.3	700.4	693.6
132.5°	744.5	752.3	750.4	745.5	740.6
135°	790.6	796.4	795.5	791.5	789.6
137.5°	832.7	837.6	840.5	835.6	832.7
140°	876.8	881.7	882.6	881.7	874.8
142.5°	916.9	921.8	923.8	922.8	917.9
145°	959.0	961.0	963.9	963.0	959.0
147.5°	995.3	999.2	1002.2	1002.2	996.3
150°	1033.5	1035.5	1037.4	1037.4	1031.5
152.5°	1064.8	1067.8	1068.8	1070.7	1065.8
155°	1098.2	1098.2	1099.1	1103.1	1096.2
157.5°	1126.6	1125.6	1126.6	1130.5	1124.6
160°	1153.0	1151.1	1151.1	1156.0	1152.0
162.5°	1176.5	1173.6	1174.6	1179.5	1172.6
165°	1196.1	1193.2	1193.2	1199.1	1192.2
167.5°	1212.8	1208.9	1209.8	1215.7	1209.8
170°	1226.5	1222.6	1222.6	1229.4	1222.6
172.5°	1237.3	1233.3	1233.3	1239.2	1232.4
175°	1244.1	1240.2	1240.2	1246.1	1239.2
177.5°	1248.0	1244.1	1244.1	1250.0	1243.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)