

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011911

Luminaire Tested: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011911
REPORT IS A COMBINATION OF REPORTS P990250 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6674.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011911

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011911

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	86	82	79	72	69	67	59	58	56	48	47	46
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1011911

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.7
10°-20°	325.9	4.9
20°-30°	481.3	7.2
30°-40°	562.1	8.4
40°-50°	565.1	8.5
50°-60°	496.4	7.4
60°-70°	369.7	5.5
70°-80°	210.4	3.2
80°-90°	62.5	0.9
90°-100°	81.0	1.2
100°-110°	245.1	3.7
110°-120°	417.2	6.3
120°-130°	548.9	8.2
130°-140°	617.0	9.2
140°-150°	606.5	9.1
150°-160°	510.6	7.7
160°-170°	340.0	5.1
170°-180°	119.0	1.8
0°-30°	922.6	13.8
0°-40°	1484.6	22.2
0°-60°	2546.1	38.1
0°-90°	3188.7	47.8
90°-120°	743.3	11.1
90°-150°	2515.7	37.7
90°-180°	3485.0	52.2
0°-180°	6674.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	1	11	24	28	30	8
95°	58	65	73	77	77	64
105°	222	224	233	233	235	238
115°	420	423	421	422	421	416
125°	615	618	616	612	608	548
135°	797	803	802	798	796	614
145°	967	969	972	971	967	604
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1011911

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	1.0	10.9	23.7	27.7	29.6
92.5°	29.6	35.6	41.5	44.5	42.5
95°	58.3	65.2	73.1	77.1	77.1
97.5°	95.8	100.8	106.7	111.7	110.7
100°	134.4	140.3	145.3	148.2	150.2
102.5°	178.8	181.8	188.7	191.7	190.7
105°	222.3	224.3	233.2	233.2	235.2
107.5°	273.7	274.7	278.6	281.6	280.6
110°	321.1	323.1	325.1	329.0	327.1

TEST NUMBER: P1011911

CATALOG NUMBER: S123DIP-B775D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.5	371.5	371.5	376.5	376.5
115°	420.0	422.9	420.9	421.9	420.9
117.5°	470.3	471.3	469.4	469.4	466.4
120°	516.8	522.7	517.8	516.8	514.8
122.5°	565.2	569.2	567.2	564.2	561.3
125°	614.6	617.6	615.6	611.6	607.7
127.5°	660.1	666.0	664.0	658.1	654.1
130°	705.5	713.4	710.5	706.5	699.6
132.5°	751.0	758.9	756.9	752.0	747.0
135°	797.4	803.3	802.4	798.4	796.4
137.5°	839.9	844.8	847.8	842.9	839.9
140°	884.4	889.3	890.3	889.3	882.4
142.5°	924.9	929.8	931.8	930.8	925.9
145°	967.4	969.3	972.3	971.3	967.4
147.5°	1003.9	1007.9	1010.8	1010.8	1004.9
150°	1042.5	1044.4	1046.4	1046.4	1040.5
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)