

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011920

Luminaire Tested: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011920
REPORT IS A COMBINATION OF REPORTS P990259 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6703.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011920

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011920

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	86	82	79	72	69	67	59	58	56	48	47	46
2	89	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1011920

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.7
10°-20°	327.3	4.9
20°-30°	483.4	7.2
30°-40°	564.6	8.4
40°-50°	567.5	8.5
50°-60°	498.6	7.4
60°-70°	371.3	5.5
70°-80°	211.3	3.2
80°-90°	62.7	0.9
90°-100°	81.3	1.2
100°-110°	246.1	3.7
110°-120°	419.0	6.3
120°-130°	551.2	8.2
130°-140°	619.6	9.2
140°-150°	609.2	9.1
150°-160°	512.8	7.7
160°-170°	341.4	5.1
170°-180°	119.6	1.8
0°-30°	926.6	13.8
0°-40°	1491.2	22.2
0°-60°	2557.3	38.2
0°-90°	3202.7	47.8
90°-120°	746.5	11.1
90°-150°	2526.5	37.7
90°-180°	3500.0	52.2
0°-180°	6703.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	1	11	24	28	30	8
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1011920

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5

TEST NUMBER: P1011920

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)