

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011921

Luminaire Tested: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011921
REPORT IS A COMBINATION OF REPORTS P990260 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1025UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6899.6 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011921

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011921

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	46	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1011921

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.7
10°-20°	327.3	4.7
20°-30°	483.4	7.0
30°-40°	564.6	8.2
40°-50°	567.5	8.2
50°-60°	498.6	7.2
60°-70°	371.3	5.4
70°-80°	211.3	3.1
80°-90°	62.8	0.9
90°-100°	278.6	4.0
100°-110°	778.8	11.3
110°-120°	759.4	11.0
120°-130°	604.7	8.8
130°-140°	477.3	6.9
140°-150°	356.1	5.2
150°-160°	248.4	3.6
160°-170°	145.9	2.1
170°-180°	47.5	0.7
0°-30°	926.6	13.4
0°-40°	1491.2	21.6
0°-60°	2557.3	37.1
0°-90°	3202.7	46.4
90°-120°	1816.8	26.3
90°-150°	3255.0	47.2
90°-180°	3697.0	53.6
0°-180°	6899.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	2	12	25	28	29	6
95°	34	110	589	172	115	36
105°	115	170	798	1396	1262	122
115°	204	254	610	1338	1536	201
125°	283	334	570	1032	1211	251
135°	332	396	562	850	982	256
145°	378	433	555	697	767	237
155°	430	464	537	610	636	198
165°	470	483	514	545	555	132
175°	489	490	493	500	499	46
180°	490	490	490	490	490	

TEST NUMBER: P1011921

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	2.0	11.9	24.8	27.8	28.8
92.5°	14.9	59.6	184.6	63.0	52.6
95°	33.7	109.6	588.6	171.7	115.1
97.5°	53.6	125.6	905.2	431.8	236.2
100°	73.4	138.4	940.0	903.2	622.3
102.5°	94.3	153.4	875.4	1209.4	985.6
105°	115.1	170.2	798.0	1395.5	1262.5
107.5°	137.0	190.1	729.5	1477.4	1443.2
110°	160.8	210.4	673.0	1480.0	1546.4

TEST NUMBER: P1011921

CATALOG NUMBER: S123DIP-B775D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.6	231.8	635.2	1423.8	1567.3
115°	203.5	253.6	610.4	1338.5	1535.5
117.5°	224.3	274.4	593.6	1247.2	1466.0
120°	246.2	295.3	582.6	1160.8	1374.7
122.5°	265.0	315.1	575.7	1092.8	1289.3
125°	282.9	334.0	569.7	1032.3	1210.9
127.5°	296.8	351.9	566.8	982.6	1143.4
130°	309.7	367.7	563.8	937.0	1087.8
132.5°	319.6	382.1	562.8	894.3	1033.3
135°	331.5	395.5	561.8	850.1	981.6
137.5°	342.4	406.4	559.8	808.4	927.1
140°	353.4	416.4	558.8	767.8	869.5
142.5°	365.3	425.3	556.8	730.6	815.9
145°	378.2	433.2	554.8	697.3	767.3
147.5°	391.1	441.7	551.9	671.4	725.6
150°	404.0	448.6	547.9	648.7	689.8
152.5°	416.9	456.0	542.9	628.8	660.1
155°	429.8	463.6	537.0	610.4	636.2
157.5°	439.7	470.0	532.0	592.6	613.4
160°	451.6	475.4	526.1	576.2	591.6
162.5°	460.5	479.4	520.1	560.8	571.7
165°	469.5	482.9	514.1	545.4	554.8
167.5°	476.4	485.8	508.2	532.0	538.0
170°	482.4	487.4	502.2	520.1	523.1
172.5°	486.4	488.8	497.3	509.7	509.2
175°	489.3	489.8	493.3	500.3	499.3
177.5°	491.3	490.3	490.3	494.3	492.3
180°	490.3	490.3	490.3	490.3	490.3

(END OF REPORT)