

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012264

Luminaire Tested: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012264
REPORT IS A COMBINATION OF REPORTS P992923 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7809.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012264

CATALOG NUMBER: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012264

CATALOG NUMBER: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		73	73	73		61	61	61
1	99	95	91	88		92	89	85	82		76	74	72		65	64	62		55	54	53
2	91	84	78	73		84	78	73	68		67	63	60		58	55	52		49	47	45
3	83	74	67	61		77	69	63	57		60	55	51		51	48	45		43	41	39
4	76	66	58	52		71	61	54	49		53	48	44		46	42	39		39	36	34
5	70	59	51	45		65	55	48	42		48	42	38		41	37	34		35	32	29
6	65	53	45	39		60	49	42	37		43	38	33		38	33	30		32	29	26
7	60	48	40	34		56	45	38	33		39	34	29		34	30	26		29	26	23
8	56	43	36	30		52	41	34	29		36	30	26		31	27	24		27	24	21
9	52	40	32	27		48	37	31	26		33	28	24		29	25	21		25	22	19
10	49	37	29	25		45	34	28	24		31	25	21		27	22	19		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1012264

CATALOG NUMBER: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.3
10°-20°	503.7	6.4
20°-30°	725.2	9.3
30°-40°	816.6	10.5
40°-50°	781.2	10.0
50°-60°	639.4	8.2
60°-70°	431.1	5.5
70°-80°	216.2	2.8
80°-90°	59.2	0.8
90°-100°	80.3	1.0
100°-110°	243.0	3.1
110°-120°	413.6	5.3
120°-130°	544.2	7.0
130°-140°	611.7	7.8
140°-150°	601.3	7.7
150°-160°	506.3	6.5
160°-170°	337.0	4.3
170°-180°	118.0	1.5
0°-30°	1409.9	18.1
0°-40°	2226.5	28.5
0°-60°	3647.1	46.7
0°-90°	4353.6	55.8
90°-120°	736.9	9.4
90°-150°	2494.0	31.9
90°-180°	3455.0	44.2
0°-180°	7809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	1	11	24	27	29	9
95°	58	65	72	76	76	64
105°	220	222	231	231	233	236
115°	416	419	417	418	417	412
125°	609	612	610	606	602	543
135°	791	796	796	792	790	609
145°	959	961	964	963	959	599
155°	1098	1098	1099	1103	1096	506
165°	1196	1193	1193	1199	1192	337
175°	1244	1240	1240	1246	1239	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1012264

CATALOG NUMBER: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	1.0	10.8	23.5	27.4	29.4
92.5°	29.4	35.3	41.1	44.1	42.1
95°	57.8	64.7	72.5	76.4	76.4
97.5°	95.0	99.9	105.8	110.7	109.7
100°	133.2	139.1	144.0	146.9	148.9
102.5°	177.3	180.2	187.1	190.0	189.1
105°	220.4	222.4	231.2	231.2	233.1
107.5°	271.4	272.3	276.3	279.2	278.2
110°	318.4	320.3	322.3	326.2	324.3



TEST NUMBER: P1012264

CATALOG NUMBER: S123RDIP-B1165D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	367.4	368.3	368.3	373.2	373.2
115°	416.3	419.3	417.3	418.3	417.3
117.5°	466.3	467.3	465.3	465.3	462.4
120°	512.3	518.2	513.3	512.3	510.4
122.5°	560.3	564.3	562.3	559.4	556.4
125°	609.3	612.3	610.3	606.4	602.5
127.5°	654.4	660.3	658.3	652.4	648.5
130°	699.4	707.3	704.3	700.4	693.6
132.5°	744.5	752.3	750.4	745.5	740.6
135°	790.6	796.4	795.5	791.5	789.6
137.5°	832.7	837.6	840.5	835.6	832.7
140°	876.8	881.7	882.6	881.7	874.8
142.5°	916.9	921.8	923.8	922.8	917.9
145°	959.0	961.0	963.9	963.0	959.0
147.5°	995.3	999.2	1002.2	1002.2	996.3
150°	1033.5	1035.5	1037.4	1037.4	1031.5
152.5°	1064.8	1067.8	1068.8	1070.7	1065.8
155°	1098.2	1098.2	1099.1	1103.1	1096.2
157.5°	1126.6	1125.6	1126.6	1130.5	1124.6
160°	1153.0	1151.1	1151.1	1156.0	1152.0
162.5°	1176.5	1173.6	1174.6	1179.5	1172.6
165°	1196.1	1193.2	1193.2	1199.1	1192.2
167.5°	1212.8	1208.9	1209.8	1215.7	1209.8
170°	1226.5	1222.6	1222.6	1229.4	1222.6
172.5°	1237.3	1233.3	1233.3	1239.2	1232.4
175°	1244.1	1240.2	1240.2	1246.1	1239.2
177.5°	1248.0	1244.1	1244.1	1250.0	1243.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)