

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011956

Luminaire Tested: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011956
REPORT IS A COMBINATION OF REPORTS P990310 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7285.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011956

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011956

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1011956

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.6
10°-20°	325.9	4.5
20°-30°	481.3	6.6
30°-40°	562.1	7.7
40°-50°	565.1	7.8
50°-60°	496.4	6.8
60°-70°	369.7	5.1
70°-80°	210.4	2.9
80°-90°	62.9	0.9
90°-100°	95.2	1.3
100°-110°	288.0	4.0
110°-120°	490.3	6.7
120°-130°	645.0	8.9
130°-140°	725.0	10.0
140°-150°	712.8	9.8
150°-160°	600.1	8.2
160°-170°	399.5	5.5
170°-180°	139.9	1.9
0°-30°	922.6	12.7
0°-40°	1484.6	20.4
0°-60°	2546.1	35.0
0°-90°	3189.1	43.8
90°-120°	873.5	12.0
90°-150°	2956.4	40.6
90°-180°	4096.0	56.2
0°-180°	7285.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	1	13	28	32	35	9
95°	68	77	86	91	91	75
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	722	726	723	719	714	644
135°	937	944	943	938	936	722
145°	1137	1139	1143	1142	1137	710
155°	1302	1302	1303	1308	1299	599
165°	1418	1414	1414	1421	1413	400
175°	1475	1470	1470	1477	1469	140
180°	1478	1478	1478	1478	1478	

TEST NUMBER: P1011956

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	1.2	12.8	27.9	32.5	34.8
92.5°	34.8	41.8	48.8	52.3	49.9
95°	68.5	76.6	85.9	90.6	90.6
97.5°	112.6	118.4	125.4	131.2	130.1
100°	157.9	164.9	170.7	174.2	176.5
102.5°	210.2	213.7	221.8	225.3	224.1
105°	261.3	263.6	274.0	274.0	276.4
107.5°	321.7	322.8	327.5	330.9	329.8
110°	377.4	379.7	382.0	386.7	384.4

TEST NUMBER: P1011956

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.5	436.6	436.6	442.4	442.4
115°	493.5	497.0	494.7	495.8	494.7
117.5°	552.7	553.9	551.6	551.6	548.1
120°	607.3	614.3	608.5	607.3	605.0
122.5°	664.2	668.9	666.5	663.1	659.6
125°	722.3	725.8	723.4	718.8	714.1
127.5°	775.7	782.7	780.3	773.4	768.7
130°	829.1	838.4	834.9	830.3	822.1
132.5°	882.5	891.8	889.5	883.7	877.9
135°	937.1	944.1	942.9	938.3	935.9
137.5°	987.0	992.8	996.3	990.5	987.0
140°	1039.3	1045.1	1046.2	1045.1	1037.0
142.5°	1086.9	1092.7	1095.0	1093.9	1088.1
145°	1136.8	1139.1	1142.6	1141.5	1136.8
147.5°	1179.8	1184.4	1187.9	1187.9	1180.9
150°	1225.1	1227.4	1229.7	1229.7	1222.8
152.5°	1262.2	1265.7	1266.9	1269.2	1263.4
155°	1301.7	1301.7	1302.9	1307.5	1299.4
157.5°	1335.4	1334.2	1335.4	1340.0	1333.1
160°	1366.7	1364.4	1364.4	1370.2	1365.6
162.5°	1394.6	1391.1	1392.3	1398.1	1390.0
165°	1417.8	1414.4	1414.4	1421.3	1413.2
167.5°	1437.6	1432.9	1434.1	1441.1	1434.1
170°	1453.8	1449.2	1449.2	1457.3	1449.2
172.5°	1466.6	1462.0	1462.0	1468.9	1460.8
175°	1474.7	1470.1	1470.1	1477.1	1468.9
177.5°	1479.4	1474.7	1474.7	1481.7	1473.6
180°	1478.2	1478.2	1478.2	1478.2	1478.2

(END OF REPORT)